


LOC	DIST	REVISIONS				
G	05	P	LTR	DESCRIPTION	DATE	APVD
			D	CREATED DWG AT THIS REVISION	24SEPT09	JR TM



AMP
WIRE RANGE

1/0 AWG
STRANDED

- 1 STAMP AMP 1/0W* APPROX AS SHOWN
- 2 NICKEL PLATE .000300 MIN THK PER SAE-AMS-QQ-N-290.
- 3 MATERIAL, COPPER PER ASTM B-152, ANNEALED.

CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 343° C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 24SEPT09		Tyco Electronics Corporation Harrisburg, PA 17105-3608		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK TOM MICHIELUTTI 24SEPT09	NAME			
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 42.4-60.6mm² [83,700-119,500] STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± -	APVD TOM MICHIELUTTI 24SEPT09	TERMINAL, RING TONGUE, STRATO-THERM, BENT 45			
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	MATERIAL - 3	FINISH - 2	PRODUCT SPEC -	APPLICATION SPEC -	SIZE A3	CAGE CODE 00779	
					WEIGHT -	DRAWING NO C-696735	RESTRICTED TO -		
					CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	REV D