

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19075-0011

Status:

Active

Overview:

Solderless Terminals

Description:

InsulKrimp™ Steel Star Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5)

Documents:

Drawing (PDF)

Product Specification PS-19902-013 (PDF)

Product Specification PS-19902-011 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19075

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

Solderless Terminals

Product Name

InsulKrimp™

Type

Ring

UPC

800753079564

Physical

Barrel Type

Closed

Flammability

94V-0

Insulation

PVC

Material - Plating Mating

Tin

Net Weight

0.557/g

Packaging Type

Bag

Stud Size

10 (M5)

Wire Insulation Diameter

3.68mm

Wire Size AWG

18, 20, 22

Wire Size mm²

0.25 - 1.30

Material Info

Old Part Number

SRA-S-229-10X

Reference - Drawing Numbers

Product Specification

PS-19902-011, PS-19902-013

Sales Drawing

CD2115



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19075Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050500
Hand Crimp Tool	0640010500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19075-0011](#)