




Copyright FCI.



DM 53742-1 NC	Ct coax femelle sortie droite	1.70	2.46	3.13	3.84	RG 179 BU
Ref contact	Designation	$\phi A^{+0.10}_0$	$\phi B^{+0.05}_0$	$\phi C^{+0.10}_0$	$\phi D^{+0.10}_0$	Ref cable

Part number	DM537421NC
-------------	------------

European Views

www.fciconnect.com				surface ISO 1302 ☒	tolerance std ISO 406 ISO 1101	projection 	mm
				TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	BOUITIER	1992/03/24		ANGULAR	0.X	± 0.1	size A3
Eng	PESSON	1992/03/24		LINEAR	0.XX	± 0.1	Scale 5
Chr	LEGARE	1992/03/24		0.XX' $\pm 2^\circ$	0.XXX	± 0.1	ECN LS06-0095
Appr	LEGARE	1992/03/24		Product family		D-SUB	Spec ref -
				FEMALE COAX CONTACT STRAIGHT			
				CRIMP TO CABLE			
				catalog no	-	CUSTOMER	sheet 1 of 1

REV F - 2006-04-17

PDM: Rev:F

STATUS: Released

Printed: Oct 01, 2010