




AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		'A'	'B'	MATERIAL			PART NO	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: NOT APPLICABLE	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± - ANGLES ± -		DR 6/23/93 DK SCHRUM		AMP AMP Incorporated Harrisburg, PA 17105-3608		
			WIRE CROSS SECTIONAL AREA RANGE: 0.139-0.190mm² [275-375] MCM SOLID OR STRANDED			CHK 7/1/93 AJ KAUFMAN				
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111			MATERIAL COPPER PER ASTM B-152 ANNEALED		APPD 7/1/93 RE ROSER		NAME TERMINAL, RING TONGUE, COPALUM™, STRANDED/SOLID, WIRE SIZE: 300-350 MCM		
						APPD 7/1/93 JL MECKLEY				
				FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727		PRODUCT SPEC -		SIZE B CAGE CODE 00779 DRAWING NO C-52558		
						APPLICATION SPEC -				
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				WEIGHT -		SCALE 1:1		SHEET 1 OF 1