

RESETABLE CIRCUIT
BREAKER

LIGHTED ON/OFF
POWER SWITCH

482.60 mm
[19.000 in]

43.64 mm
[1.718 in]

165.10 mm
[6.500 in]

38.10 mm TYP
[1.500 in]

76.20 mm TYP
[3.000 in]

SURGE INDICATOR
LIGHT

ASSEMBLY - VIEW FROM FRONT

19.05 mm
[0.750 in]

444.50 mm
[17.500 in]

5.08 mm
[0.200 in]

67.58 mm
[2.661 in]

6' FOOT TWIST
POWER CORD
(NEMA L5-15P)

ASSEMBLY - VIEW FROM BOTTOM

10.31 mm
[0.406 in]

461.98 mm
[18.188 in]


5.97 mm
[0.235 in]

31.70 mm
[1.248 in]


127.00 mm
[5.000 in]

R3.18 mm
[0.125 in]

SECTION A-A



ISOMETRIC VIEW



ASSEMBLY - VIEW FROM SIDE

1582H6**S**

Finish - Front - Black Painted Steel

Back - Black Painted Steel

Rated - 125 VAC, 60 Hz, 15 Amps

Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)

- CSA No. 8-M1986

Surge Specs - 780 Joules, 54000 Amps Transient Current

- Protection in 3 AC Modes (L-N, N-G, L-G)

Colours & Cord Length

1582H6C1SBK - Black w/ 6' Foot Twist Power Cord (NEMA L5-15P)

1582H6C1S - ASA 61 Grey w/ 6' Foot Twist Power Cord (NEMA L5-15P)

1582H6D1SBK - Black w/ 15' Foot Twist Power Cord (NEMA L5-15P)

1582H6D1S - ASA 61 Grey w/ 15' Foot Twist Power Cord (NEMA L5-15P)

1582H6D1S - ASA 61 Grey w/ 15' Foot Twist Power Cord (NEMA L5-15P)

HAMMOND
MANUFACTURING™
1582H6S****
www.hammondmfg.com