



- Small overall size allows use where space is limited
- Install with a screw or rivet for a strong, secure installation
- Low profile design keeps bundle close to mounting surface where overhead space is limited

‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Ties.

Part Number: LPMM-S5-C
Product Family: Low Profile Mounts – Screw Applied
Product Line: Screw/Rivet Applied

RoHS Compliancy Status: Compliant

Part Description: Low Profile Cable Tie Mount

Product Type: Cable Tie Mounts - Screw / Rivet Mounted

Material: Nylon 6.6

Color: Natural

UL Recognized: E136577

Height (In.): .10

Height (mm): 2.5

Length (In.): .40

Length (mm): 10.2

Width (In.): .32

Width (mm): 8.1

CE Compliant: CT-ACC4 / 10.96

Environment: Indoors

Flammability Rating: UL94 V-2

Hole Diameter (In.): .137

Hole Diameter (mm): 3.5

Metric Screw Size: M3

