

# 米国軍用規格長蝶番(MS規格)

## MILITARY STANDARD CONTINUOUS HINGES

MS-20257・MS-35822・MS-35823・MS-35825

アルミニウム製



B

長蝶番

CONTINUOUS HINGES

平蝶番

裏蝶番

抜差し蝶番

段付蝶番

クリーンヒンジ

特装車蝶番


フリーザーヒンジ

特殊蝶番

トルクヒンジ

ステー

周辺機器(B)



## 特徴 Feature

- アルミニウム製で耐食性・耐薬品性に優れています。
- 切断して使用できます。
- Corrosion-resistant/chemical-resistant aluminum is used.
- Cut and use.

仕様 材質: アルミニウム合金板(軸はステンレス製)

用途 表面仕上: アルマイト処理

納期 品種: 航空機・通信機器・測定機器・船舶・車両・小型

備考 コンテナなどの筐体

標準品...納期お問合せください。

表中の [ ] は中止予定品です。納期お問合せください。

輸入品のため色が異なることがあります。

航空機にはMS規格品をご使用ください。

必要な寸法に切断後軸にカシメ等の抜け止め加工をしてご使用ください。

両端に抜け止め加工を行う場合は、必ず同じ羽根で行ってください。異なる羽根で行うと作動不良の原因となります。

長尺商品のため、送料が掛かります。詳細はお問合せください。

Specifications 材質: Aluminum alloy plate. (Shaft: Stainless steel)

Finish: Alumite treatment

Specific use Cases for aircraft, communication equipment, measuring equipment, ships, vehicles and small containers



Remarks Items scheduled to be discontinued. Please inquire regarding delivery dates.

A color is sometimes different for the imports.

The MS (Military Standard) articles must be used for the air crafts.

The hinge is not processed to prevent extraction of the shaft. After cutting the hinge to size and before use, fix stops, etc., on the shaft to prevent its extraction.

When fixing stops on both ends, always fix on the same wing. Fixing on different wings may cause faulty operation.



| 商品番号<br>Product No. | RoHS<br>CAD | L <sub>1</sub> | L <sub>2</sub> | W  | t   | ϕD  | 製品質量(g)<br>Mass | コード<br>Code | 単価<br>Price    | 量販価格<br>Bulk Price |
|---------------------|-------------|----------------|----------------|----|-----|-----|-----------------|-------------|----------------|--------------------|
|                     |             |                |                |    |     |     |                 |             | 数量<br>Quantity | 単価<br>Price        |
| MS-35822-9A         |             | 1829           | 12.4           | 27 | 1.0 | 2.3 | 180             | 12463       |                |                    |
| MS-35822-10A        |             | 1829           | 12.4           | 32 | 1.0 | 2.3 | 210             | 12464       |                |                    |
| MS-35822-12A        |             | 1829           | 12.4           | 51 | 1.0 | 2.3 | 320             | 12466       |                |                    |
| MS-35823-6A         |             | 1829           | 16             | 38 | 1.2 | 3.2 | 320             | 12467       |                |                    |
| MS-35825-14A        |             | 2133           | 25             | 38 | 1.5 | 3.2 | 480             | 12469       |                |                    |
| MS-35825-16A        |             | 2133           | 25             | 64 | 1.5 | 3.2 | 690             | 12471       |                |                    |

価格はお問合せください

軸はステンレス製です。 Shaft is made of stainless steel

※大量のご注文は更にお安くなります。

● : RoHS指令対応品 ▲ : RoHS指令に対応可能です。

| 商品番号<br>Product No. | RoHS<br>CAD | L <sub>1</sub> | L <sub>2</sub> | W            | t          | ϕD         | 製品質量(g)<br>Mass | コード<br>Code | 単価<br>Price    | 量販価格<br>Bulk Price |
|---------------------|-------------|----------------|----------------|--------------|------------|------------|-----------------|-------------|----------------|--------------------|
|                     |             |                |                |              |            |            |                 |             | 数量<br>Quantity | 単価<br>Price        |
| MS-20257-P1         |             | 72(1829)       | 1/2(12.7)      | 3/4(19.1)    | 0.032(0.8) | 0.062(1.6) | 120             | 12457       |                |                    |
| MS-20257-P2         |             | 72(1829)       | 1/2(12.7)      | 1 1/16(27.0) | 0.040(1.0) | 0.089(2.3) | 245             | 12458       |                |                    |
| MS-20257-P3         |             | 72(1829)       | 1/2(12.7)      | 1 1/4(31.8)  | 0.040(1.0) | 0.089(2.3) | 220             | 12459       |                |                    |
| MS-20257-P4         |             | 72(1829)       | 1/2(12.7)      | 1 1/4(38.1)  | 0.040(1.0) | 0.089(2.3) | 270             | 12460       |                |                    |
| MS-20257-P6         |             | 72(1829)       | 2(50.8)        | 2(50.8)      | 0.064(1.6) | 0.179(4.5) | 700             | 12462       |                |                    |

価格はお問合せください

単位はインチ( )内寸法はmmを示します。 Unit: inches/dimensions in parentheses: mm ※大量のご注文は更にお安くなります。  
※表中の [ ] は中止予定品です。 The gray shading on the chart indicates items scheduled to be discontinued.

● : RoHS指令対応品 ▲ : RoHS指令に対応可能です。