

UL MNX **UL PC 125/75 HG**



Sample photo

Order symbol:	UL PC 125/75 HG
Product nbr:	6411308
Description:	UL Enclosure, PC
Remarks:	Grey cover

EAN: 6418074014337
El. number:
 Finland:
 Denmark: 8212030284
 Italy: 7351057U
 Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		130	130	75	Ingress Protection (EN 60529): IP 66/67
inch:		5.1	5.1	3.0	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			UL Type: UL TYPE 1, 4, 4X, 6
Gasket material:		TPE			Certificates:
Temperatures:					Germanischer Lloyd (GL)
Short term:		-40 ... 120 °C			Underwriters Laboratories
Continuous:		-40 ... 80 °C			Det Norske Veritas
Short term:		-40 ... 250 °F			Fimko
Continuous:		-40 ... 175 °F			Europe EN 62208: 2003
Accessories:					UL Canada
					Gost R

