





REV. 1
DCO 16052

COIL: @ 25° C
RESISTANCE 675 OHMS ± 10%
NOMINAL VOLTAGE 26.5 VDC
MUST OPERATE 13.5 VDC
MUST RELEASE 1.47 VDC

ENVIRONMENT:
VIBRATION 10 CPS TO 2000 CPS @ 20 g's
SHOCK 100 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 5 MS MAX.
CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
3 AMPS 28 VDC RESISTIVE
100,000 OPERATIONS

DR. R.B. 3/30/99 CK.G4H 2-7-00

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. C. I. I. STD.
CUST. NO.

TYPE "FW" RELAY

FW1105G00