



har-port USB coupler

Advantages

- Compact and well-shaped service interface in a timeless attractive design
- Easy mounting
- Compact and robust design
- Practical accessories

Technical characteristics

Number of ports	2x USB Typ A
Mounting	Screwable in cover plates
Degree of protection	IP 20
Mating cycles	min. 1500
Temperature range	-25 °C ... +70 °C
Housing material	Polyamide

Identification

Part No.

Drawing

Dimensions in mm

har-port USB 2.0 A-A coupler

09 45 452 1901

har-port USB 3.0 A-A coupler

09 45 452 1902

har-port USB 2.0 A-A coupler with cable


Length: 0.5 m
1.0 m
1.5 m
2.0 m
3.0 m
5.0 m

09 45 452 1920
09 45 452 1921
09 45 452 1922
09 45 452 1923
09 45 452 1924
09 45 452 1925

har-port USB 2.0 B-B coupler with cable

Length: 0.5 m
1.5 m
3.0 m

09 45 452 1910
09 45 452 1912
09 45 452 1914





har-port RJ45 coupler

Advantages

- Compact and well-shaped service interface in a timeless attractive design
- Easy mounting
- Transmission category 6, performance class E_A, suitable for 1/10 Gigabit Ethernet
- Compact and robust design
- Practical accessories

Technical characteristics

Number of ports	2x RJ45
Transmission performance	Category 6 / class E _A acc. to ISO/IEC 11 801:2002, EN 50 173-1
Transmission rate	10/100 Mbit/s and 1/10 Gbit/s
Shielding	Fully shielded, 360° shielding contact
Mounting	Screwable in cover plates
Degree of protection	IP 20
Mating cycles	min. 750
Temperature range	-25 °C ... +70 °C
Housing material	Polyamide

Identification


Part No.

Drawing

Dimensions in mm

har-port RJ45 Cat. 6 coupler


09 45 452 1560



har-port RJ45 Cat. 6 coupler with cable

Length: 0.2 m
0.5 m
1.0 m
1.5 m
2.0 m
3.0 m
5.0 m
10.0 m

09 45 452 1501
09 45 452 1504
09 45 452 1509
09 45 452 1510
09 45 452 1511
09 45 452 1513
09 45 452 1516
09 45 452 1518



har-port HIFF coupler housing (for all HIFF compatible modules)

09 45 452 0000



har-port accessories

Advantages

- Compact and well-shaped service interface in a timeless attractive design
- Easy mounting
- Compact and robust design
- Practical accessories

Technical characteristics

Temperature range	-25 °C ... +70 °C
Housing material	Polyamide

Identification	Part No.	Drawing	Dimensions in mm
Accessories			
har-port protection cover IP 65 / IP 67 black	09 45 502 0000		
har-port sealing cover	09 45 502 0001		
har-port label holder	09 45 502 0002	 har-port label holder 09 45 502 0002	
har-port label for label holder 09 45 502 0002	09 45 502 0003	 position for har-port label 09 45 502 0003	
har-port blind cover IP 65 / 67	09 45 502 0004		