




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	DIMENSIONS				WEIGHT lbs/100pcs (kg)/100pcs
	A (REF)	B (REF)	C	D	
BR-.50	0.5 [13]	1.8 [45]	0.15 [4] MINIMUM	.161 [4.08] .157 [4.00]	1.9 (0.87)
BR-.75	.75 [19]	2.0 [52]	0.15 [4] MINIMUM	.161 [4.08] .157 [4.00]	2.4 (1.1)
BR-1.25	1.25 [32]	2.5 [64]	0.33 [8] MINIMUM	.161 [4.08] .157 [4.00]	3.3 (1.5)
BR-2.0	2.0 [51]	3.3 [83]	0.33 [8] MINIMUM	.161 [4.08] .157 [4.00]	5.1 (2.3)



ISOMETRIC VIEW

NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. FOR USE WITH PANDUIT PART #BR-MPCL.

DIMENSIONS IN BRACKETS ARE METRIC [mm]	
CAD FILENAME/LAYERS G03668CM_DC_GB3668CM/01B	
PANDUIT CORP. TINLEY PARK, ILLINOIS	
BR- BRIDLE RING	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25] (.XX) ±0.02 [0.5] ANGLES ±5°	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
DRAWN BY ARHA	MAT'L: LOW CARBON STEEL WITH BRIGHT ZINC ELECTROPLATE
DATE 09-15-09	SCALE NONE
CHK'D KCN	DRAWING NO. GB3668CM
DWG A	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
01B	09/25/09	ARHA	OK	CORRECTED PART NUMBER FOR BR-.50	GB3668CM	01B		KCN
01A	09/15/09	ARHA		INITIAL RELEASE	GB3668CM	01A		