

Series image - Reference only

Mates With Part(s):
51111, 51111 With Retainer

Product Environmental Compliance

EU ELV:Product not active

EU RoHS:Product not active

EU RoHS Phthalates:Product not active

China RoHS:

REACH SVHC:Product not active

Low-Halogen Status:Product not active

 EU RoHS Certificate of Compliance (PDF)

 Multiple Part Product Compliance Statements
EU RoHS, REACH SVHC, & Low-Halogen

 Multiple Part Industry Compliance Documents

*IPC 1752A Class C
*IPC 1752A Class D
*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? Email ProductCompliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

Part Detail

Status	Obsolete
Category	Crimp Housings
Series	51112
Application	Signal
Product Name	N/A
UPC	800754309479

▼ Physical

Circuits (maximum)	11
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Compliant	No
Material - Resin	Polyester
Net Weight	2218.400/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number.
[Click here to visit the UL Database](#)

CSA	LR19980
UL	E29179

- Antennas
- Application Tooling
- Cable Assemblies
- Connected Lighting
- Connectors
- Copper Flex
- Electrical Products
- Industrial Automation
- Membrane Switches
- Optical Solutions
- Printed Electronic Solutions

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Industries](#)
- [Investor Relations](#)
- [Literature](#)
- [Molex Racing](#)
- [Press Room / Press Releases](#)
- [Product Index](#)
- [Sitemap](#)
- [Terms & Conditions](#)

- Supply Chain Transparency
- Business Continuity
- Compliance
- ecocare
- Feedback | Help
- Jobs
- Legal | Trademarks
- Mobile Site
- Supplier Portal
- Privacy Policy
- Tradeshows

