

Protect It! Surge Suppressor

MODEL NUMBER: **SUPER5DEU**



Description

Tripp Lite's Protect It! SUPER5DEU offers economical AC surge suppression for full protection of 220-250V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. The SUPER5DEU offers 5 Schuko outlets and a 3 meter AC line cord with German/French plug. AC suppression rated at 1050 joules shields equipment from surges and line noise. An on/off switch with integrated circuit breaker provides power control over connected equipment. Internal safety covers protect against accidental contact with unused outlets. Attractive light gray high-impact housing. Lifetime warranty.

INPUT: 3 m AC line cord with German/French plug

OUTPUT: 5 Schuko receptacles

ELECTRICAL: 220-250V AC, 50/60Hz, 10A

FORMAT: Corded multi-outlet strip

SUPPRESSION: - AC: 1050 joules

Features

- Protect It! SUPER5DEU offers economical AC surge suppression
- 1050 joules AC surge suppression shields equipment from surges and line noise
- 5 Schuko outlets protect computers and peripherals
- 3 m AC line cord with German/French plug
- Built-in power switch and 10 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Attractive light gray high-impact housing with keyhole mounting tabs allow versatile placement options
- Internal safety covers protect against accidental contact with unused outlets
- Lifetime warranty

Highlights

- 5 Schuko outlets
- 3 m power cord with German/French plug
- 1050 joule rating
- On/off switch with integrated circuit breaker
- Internal safety covers
- Lifetime warranty

Applications

- Ideal for any desktop, network or home computing application requiring AC surge suppression

Package Includes

- SUPER5DEU AC surge suppressor
- Instruction manual and warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	10
Overload protection	10A resettable illuminated combo switch/circuit breaker
Outlet quantity / type	5 Schuko outlets
INPUT	
Recommended Electrical Service	230V (220-250V)
Input connection type	German/French plug
Input cord length (ft.)	10
Input cord length (m)	3
Voltage compatibility (VAC)	220-250
LEDS ALARMS & SWITCHES	
Switches	Two position power switch
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	1050
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (HWD/in)	16.50 x 4.50 x 2.50
Shipping Dimensions (HWD/cm)	41.91 x 11.43 x 6.35
Shipping weight (lbs)	1.28
Shipping weight (kg)	0.58
Unit Dimensions (HWD/in)	13.25 x 2.00 x 1.75



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Dimensions (HWD/cm)	33.67 x 5.08 x 4.45
Unit weight (lbs)	0.60
Unit weight (kg)	0.27
Material of construction	Plastic
Integrated keyhole mounting tabs	Yes - slotted
AC line cord color	light gray
Style	Strip
CERTIFICATIONS	
Approvals	CE
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)
[SUPER5DEU](#)