

32.768kHz CERAMIC SMD CRYSTAL OSCILLATOR

ASFLK SERIES



RoHS
Compliant



5.0 x 3.2 x 1.3mm

FEATURES:

- Pb-Free/RoHS Compliant
- Tri state function
- Suitable for high density SMT
- IR reflow capable
- Seam sealed ceramic package

APPLICATIONS:

- CCD clock for VTR camera
- Computers and peripherals
- Portable MP3 players and games

STANDARD SPECIFICATIONS:

PARAMETERS	
ABRACON P/N:	ASFLK Series
Frequency range:	32.768kHz
Operating temperature:	0°C to +70°C (see options)
Storage temperature:	-55°C to +125°C
Overall Frequency Stability:	± 100ppm max. (see options)
Supply Voltage (Vdd):	3.3 Vdc ± 10% (see options)
Supply current:	Vdd = 2.5 ~ 3.3V, 0.5mA typ. 1.0mA max. Vdd = 5.0V, 1.5mA typ. 5.0mA max.
Symmetry:	40/60 % max.@ 1/2Vdd (see options)
Rise and fall time (Tr/Tf):	250 ns max.
Output Load:	15pF or 10TTL max.
Output Voltage:	VOH = 2.97V min. VOL = 0.33V max.
Start-up-time	30ms max.
Tristate function:	Logic "1" or open: Oscillation Logic "0" (VIL < 0.8 Vdc) : Hi Z
Aging at 25°C/year :	± 3ppm/year max.
Phase jitter:	1ps RMS max.

OPTIONS AND PART IDENTIFICATION:

(Left blank if standard)

ASFLK-□ - 32.768kHz - □ - □ - □ - □

Supply Voltage	
Blank	3.3V±10%
1	3.0V±10%
2	2.5V±10%
4	5.0V±10%

Operating Temp.	
E	-20°C to +70°C
F	-30°C to +70°C
N	-30°C to +85°C
L	-40°C to +85°C

*Contact ABRACON for extended temperature range.

Freq. Stability	
J	±20ppm
R	±25ppm
K	±30ppm
H	±35ppm
B	±40ppm
C	±50ppm

Packaging	
T	Tape and Reel

Symmetry	
S	45/55% max at 1/2Vdd



32.768kHz CERAMIC SMD CRYSTAL OSCILLATOR

ASFLK SERIES




RoHS
Compliant




5.0 x 3.2 x 1.3mm

OUTLINE DRAWING:




Recommended Land Pattern




Note: Recommend using an approximately 0.01uF bypass capacitor between PIN 2 and 4.

PIN	FUNCTION
1	Tri-state
2	GND
3	Output
4	Vdd

TAPE & REEL: Tape and reel (1,000pcs/reel)



REFLOW PROFILE



Need a test socket for the ASFLK series? To view compatible **PRECISION TEST & BURN-IN SOCKETS** for these parts, [click here](#).

*** NOTE:** Abracon manufactured products are intended for general commercial and industrial use. For applications requiring high reliability and/or presenting extreme operating environment, written consent & authorization from Abracon is required.

ABRACON IS
ISO 9001 / QS 9000
CERTIFIED



Visit www.abracon.com for Terms & Conditions of Sale **Revised: 09.14.09**
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com