

2014



Professional HEX Tools





Inch & Metric



Complete Hex Program




Wiha Hex Tools Index

	DESCRIPTION	Page
	T-handles	13
	PocketStar Fold Outs	17
	L-keys - Long/Short Nickel & Black Finish	18-20
	Insulated T-handle	21
	Insulated Hex Drivers	21
	Insulated L-keys	22
	Insulated Sockets	22
	Drive-Loc VI Blades	23
	ESD Safe Precision	26
	Precision	28
	PicoFinish	27
	SYSTEM 4 Blades	29
	SYSTEM 4 Micro Bits	31
	Insert/Power Bit Sets	32
	XSelectors	34
	Bit Insert & Power Bits	35-37
	Sockets	38-40



Wiha Security Hex Index

	DESCRIPTION	Page
	SYSTEM 4 Micro Bits	31
	Insert Bits	35
	Sockets	39-40

Wiha Ball End Hex Tools Index

	DESCRIPTION	Page
	Ball End L-keys & Sets Chrome Finish	6
	Colored Coded L-keys Chrome Finish	5
	Ball End L-keys & Sets Long, Mid-Length & Short Black Finish	7-9
	Stainless Steel L-keys & Set	7
	Soft Grip T-handles Chrome & Black Finish	11-12
	3K Series Screwdrivers	16
	Drive-Loc VI Blades	23
	Precision	29
	PicoFinish Soft Grip	27
	SYSTEM 4 Blades	29
	Stubby Bit Holder Sets	32
	Ball End Hex Insert Bit	36
	Ball End Hex Socket	39

MagicRing Screw Holding Hex Tools Index

	DESCRIPTION	Page
	L-keys Screw Holding	4
	T-handles Screw Holding	10
	SoftFinish Screw Holding Cushion Grip	14-15
	PocketStars Screw Holding	17
	Insert Bits Screw Holding	33
	Power Bits Screw Holding	33
	Bit-Selectors Screw Holding Insert & Power Bits	33,34

Wiha Drive-Loc VI Index

DESCRIPTION	Page
 Drive-Loc VI Handle SoftFinish® Cushion Grip	23
 Drive-Loc VI Handle ESD Safe Cushion Grip	23
 Drive-Loc VI Handle MicroFinish Non-Slip Grip	23
 Drive-Loc VI Blades Ball End Hex & Hex Inch/Metric	23
 Drive-Loc VI Blade Set	23


Wiha Power & Insert Bits Index

DESCRIPTION	Page
 MagicRing Hex Inch & Metric Insert/Power Bits	33
 Hex Inch & Metric Insert/Power Bits	35-37
 Security Bits Inch & Metric Insert/Power Bits	35
 Ball End Hex Inch & Metric	36
 Stainless Steel Metric	36


Wiha TorqueControl Tools Index

DESCRIPTION	Page
 TorqueFix Handle	24
 TorqueVario Handle	24
 Hex Inch/Metric Blades	24
 T-handle Torque Tools	25
 Hex Inch/Metric Blades	25

Wiha Sockets & Sets Index

DESCRIPTION	Page
 Insulated Sockets	22
 Hex Bit Sockets 1/4" Drive	38-39
 Hex Bit Sockets 3/8" Drive	39
 Ball End Sockets	39
 6" Bit Sockets 1/4" & 3/8" Drive	38
 Socket Sets	40

Wiha Bit Sets Index

DESCRIPTION	Page
 MicroBit Sets	31
 Stubby Bit Holder Sets	32
 Topra Bit Sets	32
 Bit Selector Sets	33
 Power Bit Belt Packs	34
 XSelectors	34
 PokitPaks	34

MagicRing Ball End Hex Keys



669 MagicRing Ball End Metric Hex L-key Long blade Chrome-V-Moly, hardened, hard chrome finish.

Item No.	mm	mm	mm	lbs.	pkg.	
66904*	1.5	90	14	.01	10	No Ring
66908*	2.0	99	16	.01	10	No Ring
66912*	2.5	111	18	.01	10	No Ring
MagicRing						
66916	3.0	125	20	.02	10	
66920	4.0	138	25	.04	10	
66924	5.0	158	28	.07	10	
66928	6.0	178	32	.12	10	
66936	8.0	198	36	.23	10	
66944	10.0	221	40	.40	10	

* Standard Ball - No Ring




66990 9 Pc. MagicRing Long Metric Ball End Hex L-key Set, In ErgoStar Holder Blade Chrome-V-Moly, hardened, hard chrome finish.

Item							
No.		mm	mm		mm	mm	lbs.
66990	66904*	1.5	90	66924	5.0	158	.94
	66908*	2.0	99	66928	6.0	178	
	66912*	2.5	111	66936	8.0	197	
	66916	3.0	125	66944	10.0	221	
	66920	4.0	138				

* Standard Ball - No Ring

Screw Holding Hex Tools!



669 MagicRing Ball End Inch Hex L-key, Long blade Chrome-V-Moly, hardened, hard chrome finish.

Item No.	Inch	Inch	Inch	lbs.	pkg.	
66945*	.050	2.8	.5	.01	10	No Ring
66946*	1/16	3.1	.6	.01	10	No Ring
66947*	5/64	3.5	.7	.01	10	No Ring
66950*	3/32	3.9	.7	.01	10	No Ring
66952*	7/64	4.3	.7	.02	10	No Ring
MagicRing						
66953	1/8	4.6	.8	.02	10	
66955	9/64	5.2	.9	.03	10	
66956	5/32	5.7	1.0	.04	10	
66959	3/16	6.2	1.1	.06	10	
66962	7/32	6.7	1.2	.09	10	
66965	1/4	7.3	1.2	.13	10	
66968	5/16	8.0	1.4	.22	10	
66971	3/8	8.8	1.6	.36	10	

* Standard Ball - No Ring



66991 13 Piece MagicRing Long Inch Ball End Hex L-key Set, In ErgoStar Holder Chrome-V-Moly, hardened, hard chrome finish.

Item							
No.		Inch	Inch		Inch	Inch	lbs.
66991	66945*	.050	2.8	66956	5/32	5.7	1.08
	66946*	1/16	3.1	66959	3/16	6.2	
	66947*	5/64	3.5	66962	7/32	6.7	
	66950*	3/32	3.9	66965	1/4	7.3	
	66952*	7/64	4.3	66968	5/16	8.0	
	66953	1/8	4.6	66971	3/8	8.8	
	66955	9/64	5.2				

* Standard Ball - No Ring



66992 22 Piece Combination MagicRing L-key Set, In ErgoStar Holder Blade Chrome-V-Moly, hardened, hard chrome finish.

Item No.	lbs.
66992	Set includes Inch & Metric: 2.02
	66990 Set - 1.5*, 2.0*, 2.5*, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm
	66991 Set - .050*, 1/16*, 5/64*, 3/32*, 7/64*, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"


* Standard Ball - No Ring

Inch & Metric Ball End Hex Keys Color Coded



Wiha exclusive Chrome-V-Moly super tool steel, through hardened


Wiha standard extra long for extended reach



Color coding for immediate identification of L-keys

Corrosion resistant nickel chrome base finish

25° Working Angles



25° Angle
For angle entry



569 Ball End Inch Hex Long Arm L-key, Set With Color Coded Keys Blade Chrome-V-Moly, hardened.

Item No.	Color Key	Inch
56901	Brown	.050
56902	Green	1/16
56903	Chrome	5/64
56904	Blue	3/32
56905	Purple	7/64
56906	Red	1/8
56907	Copper	9/64
56908	Gold	5/32
56909	Grey	3/16
56910	Black	7/32
56911	Chrome	1/4
56912	Green	5/16
56913	Brown	3/8




569 Ball End Metric Hex Long Arm L-key, Set With Color Coded Keys Blade Chrome-V-Moly, hardened.

Item No.	Color Key	mm	mm	mm	lbs.
56914	brown	1.5	91	15	.005
56915	green	2.0	101	18	.009
56916	chrome	2.5	113	20	.017
56917	blue	3.0	128	23	.019
56918	purple	4.0	142	29	.04
56919	red	5.0	163	33	.06
56920	Copper	6.0	184	38	.10
56921	gold	8.0	206	44	.20
56922	grey	10.0	231	50	.38



36986 13 Piece Inch Ball End Hex Long L-key Set With Color Coded Keys Chrome-V-Moly, hardened

Item No.	Inch:	lbs.
36986	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	.90



36987 9 Piece Metric Ball End Hex Long L-key Set With Color Coded Keys Chrome-V-Moly, hardened

Item No.	Metric:	lbs.
36987	1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm	.90

Metric Ball End Hex Keys Chrome Finish



669 Ball End Metric Hex L-key, Long Arm

Blade Chrome-V-Moly, hardened, hard chrome finish.




Item No.	mm	mm	mm	lbs.	pkg.
66904	1.5	90	14	.004	10
66908	2.0	99	16	.007	10
66912	2.5	111	18	.012	10
66918	3.0	125	20	.019	10
66922	4.0	138	25	.042	10
66926	5.0	158	28	.072	10
66930	6.0	178	32	.12	10
66937	8.0	198	36	.23	10
66938	10.0	221	40	.40	10



66994 9 Piece Metric Ball End Hex Long L-key Set

Item No.	Metric: 1.5, 2.0, 2.5, 3.0, 4.0,	
66994	5.0, 6.0, 8.0, 10.0mm	lbs. .98



66995 6 Piece Metric Ball End Hex Long L-key Set

Item No.		
66995	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0mm	lbs. .21



66998 11 Piece Metric Ball End Hex Long L-key Set

Item No.	Metric: 1.5, 2.0, 2.5, 3.0, 4.0,	
66998	5.0, 6.0, 7.0, 8.0, 9.0, 10.0mm	lbs. 1.36

Inch Ball End Hex Keys Chrome Finish



369 Ball End Inch Hex L-key, Long Arm

Blade Chrome-V-Moly, hardened, hard chrome finish.



Item No.	Inch	Inch	Inch	lbs.	pkg.
36940	.050	2.8	.5	.002	10
36941	1/16	3.1	.6	.004	10
36942	5/64	3.5	.7	.007	10
36943	3/32	3.9	.7	.010	10
36948	7/64	4.3	.7	.016	10
36949	1/8	4.6	.8	.021	10
36951	9/64	5.2	.9	.029	10
36954	5/32	5.7	1.0	.035	10
36957	3/16	6.2	1.1	.059	10
36958	7/32	6.7	1.2	.092	10
36960	1/4	7.3	1.2	.13	10
36961	5/16	8.0	1.4	.22	10
36963	3/8	8.8	1.6	.36	10



36998 13 Piece Inch Ball End Hex Long L-key Set, In Plastic

Holder Blade Chrome-V-Moly, hardened, hard chrome finish.

Item No.	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8,	
36998	9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	lbs. 1.0



66993 2 Pack Inch & Metric Ball End Hex L-key Sets High alloy Chrome-V-Moly, hardened, hard chrome finish. In molded Holders

Item No		
66993	2 Sets with 22 L-keys include:	lbs.
	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm	2.0
	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	

ErgoStar Ball End Hex Keys Chrome Finish

Fast Auto Open Key Holder   [SHOP](#)


66996 9 Piece ErgoStar Metric Ball End Hex Long L-key Set

Item No.	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm		lbs. 1.02
----------	--	---	-----------

Fast Auto Open Key Holder    [SHOP](#)

66988 13 Piece ErgoStar Inch Ball End Hex Long L-key Set

Item No.	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"		lbs. 1.08
----------	--	---	-----------

 Fast Auto Open Key Holder   [SHOP](#)

66982 22 Piece ErgoStar Inch/Metric Ball End Hex Long L-key Set


Item No.	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"		lbs. 2.10
	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm		



ErgoStar Inch Ball End L-key Set

- Patented ErgoStar auto open key holder
- Keys of chrome-vanadium-molybdenum steel
- 60HRC through hardened durability
- Hard chrome finish for best wear resistance

Stainless Steel Metric Ball End Hex Key



369 Stainless Steel Ball End Metric Hex L-key, Long Arm
Blade hardened, hard chrome finish.

Item No.	mm	mm	mm	lbs.	pkg.
36911	1.5	91	14	.004	10
36913	2.0	101	18	.007	10
36914	2.5	113	20	.012	10
36915	3.0	128	23	.020	10
36917	4.0	142	29	.050	10
36918	5.0	163	33	.074	10
36919	6.0	184	38	.13	10
36921	8.0	206	44	.25	10
36922	10.0	231	50	.44	10



36988 9 Pc. Stainless Steel Ball End L-key Set
In molded ergo holder

Item No.	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0mm	lbs.
36988	6.0, 8.0, 10.0mm	.88

L-keys Black Finish Sets



36995 2 Pack Inch & Metric Ball End Hex L-key Sets High alloy Chrome-V-Moly, hardened, black finish.


Item No	lbs. 2.21
36995	2 Sets with 22 L-keys include:
	Sizes: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm
	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"



36696 3 Pack Inch & Metric Mid-Length Ball End Hex & TORX L-key Sets Blade Chrome-V-Moly, hardened, black finish.

Item No	lbs. 2.58
36696	3 Sets with Hex & TORX L-keys include:
	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm
	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"
	TORX: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30

Metric Ball End Inch & Metric Hex Keys Black Finish



369 Ball End Hex Metric L-key, Long Arm

Blade Chrome-V-Moly, hardened, black finish.


Item No.	mm	mm	mm	lbs.	pkg.
36904	1.5	90	14	.004	10
36908	2.0	99	16	.007	10
36912	2.5	111	18	.012	10
36916	3.0	125	20	.019	10
36920	4.0	138	25	.042	10
36924	5.0	158	28	.072	10
36928	6.0	178	32	.12	10
36936	8.0	198	36	.23	10
36944	10.0	221	40	.40	10



36990 9 Piece Metric Ball End Hex Long L-key Set

Blade Chrome-V-Moly, hardened, black finish.


Blade Chrome-V-Moly, hardened, black finish.							
Item							
No.		mm	mm		mm	mm	lbs.
36990	36904	1.5	90	36924	5.0	158	.98
	36908	2.0	99	36928	6.0	178	
	36912	2.5	111	36936	8.0	198	
	36916	3.0	125	36944	10.0	221	
	36920	4.0	138				



36992 6 Piece Metric Ball End Long Hex L-key Set

Blade Chrome-V-Moly, hardened, black finish.

Blade Chrome-V-Moly, hardened, black finish.						
Item						
No.		mm	mm	mm	mm	lbs.
36992	36904	1.5	90	36916	3.0	125
	36908	2.0	99	36920	4.0	138
	36912	2.5	111	36924	5.0	158



369 Ball End Hex Inch L-key, Long Arm

Blade Chrome-V-Moly, hardened, black finish.

Item No.	Inch	Inch	Inch	lbs.	pkg.
36945	.050	2.8	.5	.002	10
36946	1/16	3.1	.6	.004	10
36947	5/64	3.5	.7	.007	10
36950	3/32	3.9	.7	.010	10
36952	7/64	4.3	.7	.016	10
36953	1/8	4.6	.8	.021	10
36955	9/64	5.2	.9	.029	10
36956	5/32	5.7	1.0	.035	10
36959	3/16	6.2	1.1	.059	10
36962	7/32	6.7	1.2	.092	10
36965	1/4	7.3	1.2	.13	10
36968	5/16	8.0	1.4	.22	10
36971	3/8	8.8	1.6	.36	10



36991 13 Piece Inch Ball End Hex Long L-key Set

Blade Chrome-V-Moly, hardened, black finish.

Blade Chrome-V-Moly, hardened, black finish.	
Item No.	
36991 13 pc. set includes: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	lbs. 1.0



36993 8 Piece Inch Ball End Hex Long L-key Set

Blade Chrome-V-Moly, hardened, black finish.

Blade Chrome-V-Moly, hardened, black finish.	
Item No.	
36993 8 pc. set includes: 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16"	lbs. .62

Mid-Length Ball End Hex Keys Black Finish



Ball End Hex Keys
Chamfered ends for
easy insertion

**Ball End Hex
L-keys**
Working angle
up to 25°



369 Ball End Hex Inch Mid-Length L-keys

Blade Chrome-V-Moly, hardened, black finish.

Item No.	Inch	Inch	Inch	lbs.	pkg.	10 Pack Item No.	pkg.
36901	.050	2.82	.45	.002	1	46701	10
36902	1/16	3.05	.53	.004	1	46703	10
36903	5/64	3.27	.63	.007	1	46705	10
36905	3/32	3.43	.68	.010	1	46707	10
36906	7/64	3.62	.76	.016	1	46709	10
36907	1/8	3.84	.76	.021	1	46711	10
36909	9/64	4.08	.87	.029	1	46713	10
36910	5/32	4.36	.96	.035	1	46717	10
36923	3/16	4.67	1.08	.059	1	46719	10
36925	7/32	5.05	1.18	.092	1	46721	10
36926	1/4	5.73	1.25	.13	1	46723	10
36927	5/16	6.75	1.36	.22	1	46727	10
36929	3/8	7.0	1.50	.36	1	46731	10



36937 13 Piece Inch Mid-Length Ball End Hex L-key Set

Blade Chrome-V-Moly, hardened, black finish.

Item No.		lbs.
36937	13 pc. set includes: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	.82



369 Ball End Hex Metric Mid-Length L-keys

Blade Chrome-V-Moly, hardened, black finish.

Item No.	mm	mm	mm	lbs.	pkg.	10 Pack Item No.	pkg.
36930	1.5	79	13	.010	1	46732	10
36931	2.0	84	15	.016	1	46733	10
36932	2.5	90	17	.029	1	46734	10
36933	3.0	100	19	.035	1	46735	10
36934	4.0	113	24	.059	1	46736	10
36935	5.0	123	26	.092	1	46737	10
36938	6.0	144	31	.13	1	46738	10
36939	8.0	159	35	.22	1	46739	10
36966	10.0	181	37	.36	1	46741	10



36999 9 Piece Metric Mid-Length Ball End Hex L-key Set

Blade Chrome-V-Moly, hardened, black finish.

Item No.		lbs.
36999	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm	.72



Inch & Metric



36900 2 Pack Inch & Metric Mid-Length Ball End Hex L-key Sets

Chrome-V-Moly, hardened, black finish.

Item No.		lbs.
36900	2 Sets with 22 L-keys include: Sizes: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	1.54

Ball End Hex Keys Black Finish Short Arm



36989 9 Pc. Short Arm Metric Ball End Hex L-key Set, In Plastic Holder Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

lbs. .59 pkg. 1



Wiha MagicRing Screw Holding T-handle

Hole for hanging

Proportioned ergonomic handle designed for high torque

Blade Wiha exclusive Chrome-V-Moly super tool steel, hardened, hard chrome finish

Screw Holding Hex Tools

Handle is molded directly onto blade

Smooth edges prevent injuries & eliminate pressure marks




540 MagicRing Hex **Metric** Ball End, With Wiha T-handle [SHOP](#)

Blade Chrome-V-Moly, hardened, hard chromed. Ball end for easy insertion. Wiha T-handle high quality plastic, impact resistant.

Item No.	mm	mm	mm	mm	Inch	lbs.	pkg.
54040	4.0	150	80	176	6.9	.08	10
54050	5.0	150	100	182	7.1	.14	10
54060	6.0	150	100	182	7.1	.17	10
54080	8.0	200	100	232	9.1	.29	10
54086	10.0	200	120	238	9.3	.49	10

540 MagicRing Hex **Inch** Ball End, With Wiha T-handle [SHOP](#)

Blade Chrome-V-Moly, hardened, hard chromed. Ball end for easy insertion. Wiha T-handle high quality plastic, impact resistant.

Item No.	Inch	Inch	Inch	Inch	lbs.	pkg.
54012	5/32	5.8	2.8	6.9	.08	10
54014	3/16	5.8	4.0	7.2	.14	10
54016	7/32	5.8	4.0	7.2	.16	10
54018	1/4	5.8	4.0	7.2	.19	10
54022	5/16	7.8	4.0	7.2	.29	10
54024	3/8	7.8	4.7	7.5	.45	10



54090 5 Piece MagicRing Ball End T-handle Set, **Metric** Sizes [SHOP](#)

Blade Chrome-V-Moly, hardened, hard chromed. Wiha T-handle high quality plastic, impact resistant.

Item		 		 			
No.		mm	mm		mm	mm	lbs.
54090	54040	4.0	150	54080	8.0	200	1.49
	54050	5.0	150	54086	10.0	200	
	54060	6.0	150				

54091 6 Piece MagicRing Ball End T-handle Set, **Inch** Sizes [SHOP](#)

Blade Chrome-V-Moly, hardened, hard chromed. Wiha T-handle high quality plastic, impact resistant.

Item No.		 Inch	 Inch	 Inch	 Inch	 lbs.
54091	54012	5/32	5.8	54018	1/4	5.8
	54014	3/16	5.8	54022	5/16	7.8
	54016	7/32	5.8	54024	3/8	7.8

Wiha Soft Grip Dual Drive T-handle



Two Tools In One!

Through the handle side torque drive

Ball & Standard Hex In One Powerful Tool

Two component soft grip handle

Wiha exclusive Chrome-V-Moly super tool steel, through hardened durability, hard chrome finish

Maximum Comfort & Maximum Power



Hard Chrome Finish

For angle entry

- Chrome-V-Moly, hardened, hard chrome finish
- Ball tip for speed & easy insertion
- Wiha soft grip are molded on and include through the handle side torque drive.

SHOP

540 Soft Grip Ball End Hex Metric Dual Drive T-handle

Item No.	mm	mm	Tip	lbs.	pkg.
54020	2.0	150	Ball	.06	10
54025	2.5	150	Ball	.06	10
54030	3.0	150	Ball	.07	10
54042	4.0	150	Ball	.09	10
54052	5.0	150	Ball	.18	10
54062	6.0	150	Ball	.21	10
54082	8.0	200	Ball	.35	10
54088	10.0	200	Ball	.55	10

54095 8 Pc. Ball End Hex Metric Soft Grip T-handle Set- No stand

Item								
No.		mm	mm			mm	mm	lbs.
54095	54020	2.0	150	54052	5.0	150		1.90
	54025	2.5	150	54062	6.0	150		
	54030	3.0	150	54082	8.0	200		
	54042	4.0	150	54088	10.0	200		



54092 8 Piece Ball End Hex Metric Soft Grip T-handle Set


Blade Chrome-V-Moly, hardened, chrome finish. Wiha soft grips are molded on with through the handle side torque drive.



In metal stand

Item No.	mm	mm	lbs.	
54092	54020	2.0	150	3.34
	54025	2.5	150	
	54030	3.0	150	
	54042	4.0	150	
	54052	5.0	150	
	54062	6.0	150	
	54082	8.0	200	
	54088	10.0	200	

SHOP



540 Soft Grip Ball End Hex Inch Dual Drive T-handle Chrome-V-Moly, hardened, hard chrome finish. Ball tip for speed & easy insertion. Wiha soft grips are molded on with through the handle side torque drive.

Item No.	Inch	Inch	Tip	lbs.	pkg.
54007	3/32	5.9	Ball	.06	10
54008	7/64	5.9	Ball	.07	10
54009	1/8	5.9	Ball	.08	10
54010	9/64	5.9	Ball	.08	10
54001	5/32	5.9	Ball	.09	10
54002	3/16	5.9	Ball	.17	10
54003	7/32	5.9	Ball	.20	10
54004	1/4	5.9	Ball	.23	10
54005	5/16	7.9	Ball	.35	10
54006	3/8	7.9	Ball	.51	10

54097 10 Pc. Ball End Hex Inch Soft Grip T-handle Set- No stand

Item											
No.		Inch	Inch		Inch	Inch		Inch	Inch		lbs.
54097	54007	3/32	5.9		54002	3/16	5.9				2.15
	54008	7/64	5.9		54003	7/32	5.9				
	54009	1/8	5.9		54004	1/4	5.9				
	54010	9/64	5.9		54005	5/16	7.9				
	54001	5/32	5.9		54006	3/8	7.9				




54094 8 Piece Ball End Hex Inch Soft Grip T-handle Set

Blade Chrome-V-Moly, hardened, chrome finish. Wiha soft grips are molded on with through the handle side torque drive.

Item							
No.		Inch	Inch	Inch	Inch		lbs.
54094	54009	1/8	5.9	54003	7/32	5.9	3.37
	54010	9/64	5.9	54004	1/4	5.9	
	54001	5/32	5.9	54005	5/16	5.9	
	54002	3/16	5.9	54006	3/8	7.9	

Soft Grip Dual Drive T-handle - Black Finish



334 Soft Grip Ball End Hex **Metric** Dual Drive T-handle Chrome-V-Moly, hardened, black finish. Ball tip for speed & easy insertion. Wiha soft grip are molded on with through the handle side torque drive.

Item No.				
	mm	mm	lbs.	pkg.
33442*	2.0	150	.06	10
33444*	2.5	150	.06	10
33446*	3.0	150	.07	10
33448	4.0	150	.09	10
33450	5.0	150	.18	10
33452	6.0	150	.21	10
33454	8.0	200	.35	10
33458	10.0	200	.55	10

*No Ball - Standard Hex



33496 8 Pc. Ball End Hex **Metric** Soft Grip T-handle Set

Blade Chrome-V-Moly, hardened, black finish. Wiha soft grip are molded on with through the handle side torque drive.

Item							
No.		mm	mm		mm	mm	lbs.
33496	33442*	2.0	150	33450	5.0	150	2.04
	33444*	2.5	150	33452	6.0	150	
	33446*	3.0	150	33454	8.0	200	
	33448	4.0	150	33458	10.0	200	

*No Ball - Standard Hex

33489 8 Piece Hex & Ball End Hex **Metric** Soft Grip T-handle Set

Blade Chrome-V-Moly, hardened, black finish. Wiha soft grips are molded on with through the handle side torque drive.





Item No.			
	mm	mm	lbs.
33489	33442*	2.0	150
	33444*	2.5	150
	33446*	3.0	150
	33448	4.0	150
	33450	5.0	150
	33452	6.0	150
	33454	8.0	200
	33458	10.0	200



*No Ball - Standard Hex

In metal stand



334 Soft Grip Ball End Hex Inch Dual Drive T-handle Chrome-V-Moly, hardened, black finish. Ball tip for speed & easy insertion. Wiha soft grips are molded on with through the handle side torque drive.

Item No.				
	Inch	Inch	lbs.	pkg.
33418*	5/64	5.9	.06	10
33420*	3/32	5.9	.06	10
33422*	7/64	5.9	.07	10
33424*	1/8	5.9	.08	10
33426*	9/64	5.9	.08	10
33428	5/32	5.9	.09	10
33430	3/16	5.9	.17	10
33432	7/32	5.9	.20	10
33433	1/4	5.9	.23	10
33439	5/16	7.9	.35	10
33440	3/8	7.9	.51	10

*No Ball - Standard Hex

33494 11 Pc. Ball End Hex Inch Soft Grip Dual Drive T-handle Set

Item		 		 			
No.		Inch	Inch	Inch	Inch	lbs.	
33494	33418*	5/64	5.9	33430	3/16	5.9	
	33420*	3/32	5.9	33432	7/32	5.9	
	33422*	7/64	5.9	33433	1/4	5.9	
	33424*	1/8	5.9	33439	5/16	7.9	
	33426*	9/64	5.9	33440	3/8	7.9	
	33428	5/32	5.9				

*No Ball - Standard Hex

33498 8 Piece Ball End Hex Inch Soft Grip T-handle Set

Item No.							
		Inch	Inch		Inch	Inch	lbs.
33498	33424*	1/8	5.9	33432	7/32	5.9	2.15
	33426*	9/64	5.9	33433	1/4	5.9	
	33428	5/32	5.9	33439	5/16	7.9	
	33430	3/16	5.9	33440	3/8	7.9	

*No Ball - Standard Hex

33499 8 Piece Hex & Ball End Hex Inch Soft Grip T-handle Set

Blade Chrome-V-Moly, hardened, black finish. Wiha soft grips are molded on with through the handle side torque drive.



Item No.			
	Inch	Inch	lbs.
33499	33424*	1/8	5.9
	33426*	9/64	5.9
	33428	5/32	5.9
	33430	3/16	5.9
	33432	7/32	5.9
	33433	1/4	5.9
	33439	5/16	7.9
	33440	3/8	7.9



In metal

*No Ball - Standard Hex

In metal stand

Wiha T-handle Hex Tools

Ergonomic handle design for high torque

Hole for hanging

Handle is molded directly onto blade

Smooth edges prevent injuries & eliminate pressure marks

Blade Wiha exclusive Chrome-V-Moly super tool steel hardened, nickel-plated



Yellow = Inch
Red = Metric

334 Hex Inch & Metric Drivers, With Wiha T-handle Chamfered tip for easy insertion. Wiha-T-handle high quality plastic, impact resistant.

Item No.	Inch	Inch	Inch	Inch	lbs.	pkg.	
33453	3/32	6.0	2.8	7.0	.05	10	
33456	7/64	6.0	2.8	7.0	.05	10	
33459	1/8	6.0	2.8	7.0	.06	10	
33462	9/64	6.0	2.8	7.0	.07	10	
33465	5/32	6.0	2.8	7.0	.08	10	
33468	3/16	6.0	3.5	7.0	.13	10	
33471	7/32	6.0	3.5	7.0	.16	10	
33474	1/4	6.0	3.5	7.0	.18	10	
33477	5/16	6.0	3.5	7.0	.25	10	
33480	3/8	6.0	4.1	7.0	.39	10	
Item No.	mm	mm	mm	mm	Inch	lbs.	pkg.
33401	2.0	100	80	126	4.9	.05	10
33436	2.0	200	80	226	8.9	.05	10
33402	2.5	100	80	126	4.9	.05	10
33437	2.5	200	80	226	8.9	.08	10
33403	3.0	100	80	126	4.9	.05	10
33404	3.0	150	80	176	6.9	.08	10
33405	3.0	200	80	226	8.9	.09	10
33435	3.0	350	100	382	15.0	.22	10
33406	4.0	100	80	126	4.9	.07	10
33407	4.0	150	80	176	6.9	.10	10
33408	4.0	200	80	226	8.9	.09	10
33438	4.0	350	100	382	15.0	.26	10
33409	5.0	100	100	132	5.2	.13	10
33410	5.0	150	100	182	7.1	.17	10
33411	5.0	200	100	232	9.1	.16	10
33412	5.0	350	100	382	15.0	.26	10
33413	5.0	450	120	488	19.1	.53	10
33414	6.0	100	100	132	5.2	.14	10
33415	6.0	150	100	182	7.1	.18	10
33416	6.0	200	100	232	9.1	.20	10
33417	6.0	350	100	382	15.0	.32	10
33419	7.0	200	100	232	9.1	.22	10
33421	8.0	100	100	132	5.2	.20	10
33423	8.0	200	100	232	9.1	.29	10
33434	8.0	350	100	372	14.6	.48	10
33425	10.0	100	120	138	5.4	.34	10
33427	10.0	200	120	238	9.3	.49	10
33429	12.0	200	120	238	9.3	.58	10



SHOP

33492 10 Piece Hex Driver T-handle Set, Inch Sizes

 				  			
Item No.		Inch	Inch		Inch	Inch	lbs.
33492	33453	3/32	6.0	33468	3/16	6.0	1.74
	33456	7/64	6.0	33471	7/32	6.0	
	33459	1/8	6.0	33474	1/4	6.0	
	33462	9/64	6.0	33477	5/16	6.0	
	33465	5/32	6.0	33480	3/8	6.0	



SHOP

33493 8 Piece Hex Driver T-handle Set, Metric Sizes

Item							
No.		mm	mm		mm	mm	lbs.
33493	33401	2.0	100	33409	5.0	100	1.64
	33402	2.5	100	33416	6.0	200	
	33403	3.0	100	33423	8.0	200	
	33406	4.0	100	33427	10.0	200	



SHOP

33484 8 Pc. Hex Driver T-handle Set, Inch Sizes - In metal stand

Item											
No.		Inch		Inch		Inch		Inch		lbs.	
33484	33459	1/8	6.0			33471	7/32	6.0		3.07	
	33462	9/64	6.0			33474	1/4	6.0			
	33465	5/32	6.0			33477	5/16	6.0			
	33468	3/16	6.0			33480	3/8	6.0			

33488 8 Pc. Hex Driver T-handle Set, Metric Sizes - In metal stand

Item											
No.		mm	mm		mm	mm		mm	mm		lbs.
33488	33401	2.0	100		33410	5.0	150				3.07
	33402	2.5	100		33415	6.0	150				
	33403	3.0	100		33423	8.0	200				
	33406	4.0	100		33427	10.0	200				

SHOP

Wiha MagicRing SoftFinish® Hex Drivers

Screw Holding Hex Tools



SHOP


367 MagicRing Ball End Hex-Driver Inch, With Wiha-SoftFinish®

Handle Hex blade, Chrome-V-Moly, hardened, hard chromed.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Inch	Inch	mm	mm	lbs.	pkg.
36710*	.050	3.1	80	179	.06	10
36713*	1/16	3.1	80	204	.06	10
36716*	5/64	3.9	100	204	.07	10
36719*	3/32	3.9	100	204	.07	10
36723*	7/64	3.9	100	211	.07	10
With MagicRing						
36726	1/8	3.9	100	243	.12	10
36728	9/64	3.9	100	243	.12	10
36732	5/32	5.0	125	271	.12	10
36734	3/16	6.0	150	271	.16	10
36736	7/32	6.0	150	271	.23	10
36738	1/4	6.0	150	271	.25	10
36742	5/16	8.0	200	271	.37	10
36744	3/8	8.0	200	271	.54	10

* Standard Ball - No Ring



SHOP

36793 8 Piece MagicRing Inch Ball End Screwdriver Set

Hex blade Chrome-V-Moly, hardened, hard chromed.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item											
No.		Inch		Inch		Inch		Inch		lbs.	
36793	36726	1/8	4.0			36736	7/32	6.0		2.25	
	36728	9/64	4.0			36738	1/4	6.0			
	36732	5/32	5.0			36742	5/16	8.0			
	36734	3/16	6.0			36744	3/8	8.0			

Don't Drop That Screw!
Save Valuable Time!
Improve Productivity!
Make The Job Easy!



SHOP


36791 13 Piece MagicRing Inch Ball End Screwdriver Set

Hex blade Chrome-V-Moly, hardened, hard chromed.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item					
No.	Inch	Inch	Inch	Inch	lbs.
36791	36710*	.050 3.0	36732	5/32 5.0	2.58
	36713*	1/16 3.0	36734	3/16 6.0	
	36716*	5/64 4.0	36736	7/32 6.0	
	36719*	3/32 4.0	36738	1/4 6.0	
	36723*	7/64 4.0	36742	5/16 8.0	
	36726	1/8 4.0	36744	3/8 8.0	
	36728	9/64 4.0			

* Standard Ball - No Ring



SHOP

36794 6 Piece MagicRing Inch Ball End Screwdriver Set

Hex blade Chrome-V-Moly, hardened, hard chromed.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item								
No.		Inch	Inch		Inch	Inch		lbs.
36794	36726	1/8	4.0	36734	3/16	6.0		1.34
	36728	9/64	4.0	36736	7/32	6.0		
	36732	5/32	5.0	36738	1/4	6.0		

Wiha MagicRing SoftFinish® Hex Drivers

Screw Holding Hex Tools



Don't Drop That Screw!
Save Valuable Time!
Improve Productivity!
Make The Job Easy!



367 MagicRing Ball End Hex Driver Metric, With Wiha-SoftFinish®
Handle Hex blade, Chrome-V-Moly, hardened, hard chromed.
Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	mm	mm	mm	lbs.	pkg.
36715*	1.5	75	179	.06	10
36720*	2.0	100	204	.07	10
36725*	2.5	100	204	.07	10
With MagicRing					
36730	3.0	100	204	.07	10
36740	4.0	125	211	.12	10
36750	5.0	150	243	.16	10
36760	6.0	150	243	.23	10
36780	8.0	200	268	.37	10
36786	10.0	200	271	.54	10

* Standard Ball - No Ring

Hardened spring steel retaining
ring holds screws on

Hard chrome super durable
corrosion resistant finish

Precision machined for exact fit

Made from Wiha exclusive
Chrome-V-Moly hardened tool steel

36790 9 Piece MagicRing Metric Ball End Hex Screwdriver Set
Hex blade Chrome-V-Moly, hardened, hard chromed.
Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	mm	mm	mm	mm	lbs.
36790	36715*	1.5	75	36750	5.0 150
	36720*	2.0	100	36760	6.0 150
	36725*	2.5	100	36780	8.0 200
	36730	3.0	100	36786	10.0 200
	36740	4.0	125		

* Standard Ball - No Ring



36792 6 Piece MagicRing Metric Ball End Hex Screwdriver Set
Hex blade Chrome-V-Moly, hardened, hard chromed.
Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	mm	mm	mm	mm	lbs.
36792	36730	3.0	100	36760	6.0 150
	36740	4.0	125	36780	8.0 200
	36750	5.0	150	36786	10.0 200

Wiha Ball End 3K Series Drivers & Sets



467 Ball End Hex Inch Drivers, With 3K Ergo Soft Grip Handles
Blades Chrome-V-Moly, hardened, black finish. Ergo soft grip handles.

Item No.	Inch	Inch	Inch	lbs.	pkg.
46702	.050	2.9	6.3	.07	10
46704	1/16	2.9	6.3	.07	10
46706	5/64	3.9	7.3	.07	10
46708	3/32	3.9	7.3	.07	10
46710	7/64	3.9	7.3	.07	10
46712	1/8	3.9	7.7	.09	10
46714	9/64	3.9	7.7	.10	10
46716	5/32	3.9	7.7	.11	10
46718	3/16	3.9	7.7	.12	10
46722	7/32	5.9	10.0	.19	10
46724	1/4	5.9	10.0	.22	10
46726	5/16	7.9	12.0	.34	10
46728	3/8	7.9	12.5	.48	10




46794 6 Piece 3K Ergo Inch Ball End Hex Screwdriver set

Item No.		
46794	Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	lbs. .97



46793 8 Piece 3K Ergo Inch Ball End Hex Screwdriver Set

Item No.		
46793	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"	lbs. 1.19



46797 13 Piece 3K Ergo Inch Ball End Hex Screwdriver Set

Item No.		
46797	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	lbs. 2.40

Yellow = Inch
Red = Metric



- Soft panel grip
- Fast angle entry
- Convenient hang hole
- Exact fit precision machined tips
- Wiha exclusive Chrome-V-Moly super tool steel



467 Ball End Hex Metric Screwdriver, With Wiha-3K Ergo Handle

Blades Chrome-V-Moly, hardened, black finish. Molded on Wiha-3K Ergo soft grip handles.


Item No.	mm	mm	mm	lbs.	pkg.
46715	1.5	75	161	.07	10
46720	2.0	100	186	.07	10
46725	2.5	100	186	.07	10
46730	3.0	100	186	.07	10
46740	4.0	100	197	.11	10
46750	5.0	100	197	.13	10
46760	6.0	150	257	.21	10
46780	8.0	200	307	.34	10
46786	10.0	200	319	.52	10



46796 7 Piece Metric Ball End Hex Screwdriver Set

Blades Chrome-V-Moly, hardened, black finish. Molded on Wiha-3k Ergo soft grip handles.

Item No.		
46796	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm	lbs. 1.15



46799 9 Piece Metric Ball End Hex Screwdriver Set

Item No.		
46799	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm	lbs. 1.93

Wiha PocketStar Fold-Ups



Push button key release

36997 9 Piece MagicRing Inch PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 36997	
Inch PocketStar: 5/64*, 3/32*, 7/64*	lbs. .46
1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	

* Standard Ball - No Ring



Push button key release

36996 7 Piece MagicRing Metric PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 36996	
PocketStar	lbs. .50
Metric: 2.0*, 2.5*, 3.0, 4.0, 5.0, 6.0, 8.0mm	

* Standard Ball - No Ring



Push button key release

66997 2 Pack MagicRing PocketStar Fold Outs Inch & Metric

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 66997	
Fold Outs Inch/Metric Includes:	lbs. .98
36996 - 2.0*, 2.5*, 3.0, 4.0, 5.0, 6.0, 8.0mm	
36997 - 5/64*, 3/32*, 7/64*, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	

* Standard Ball - No Ring



#35195

#35196

35195 7 Piece Metric Hex PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 35195	
PocketStar	lbs. .51
Metric: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	

35196 7 Piece Metric Hex PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 35196	
PocketStar	lbs. .31
Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm	



Push button key release

35197 9 Piece Inch Hex PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 35197	
Inch PocketStar:	lbs. .47
5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	



Push button key release

35198 6 Pc. Slotted, Phillips & Hex Metric PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 35198	
PocketStar	lbs. .35
Slotted: 5.5mm Phillips: #2	
Metric: 3.0, 4.0, 5.0, 6.0mm	

Nickel-Plated Long Arm Hex L-keys



Nickel-Plated

• Ideal for use in clean rooms & other environments where non-oxidizing surfaces are specified or required.

352 Inch							
Inch & Metric Hex L-keys, Long Arm							
Item No.	Inch	mm	Inch	mm	lbs.	pkg.	
35231	.050	75	3.0	.01	.01	10	
35233	1/16	78	3.1	.01	.01	10	
35235	5/64	82	3.2	.01	.01	10	
35237	3/32	85	3.3	.01	.01	10	
35239	7/64	92	3.6	.01	.01	10	
35241	1/8	95	3.7	.02	.02	10	
35243	9/64	100	3.9	.03	.03	10	
35251	5/32	105	4.1	.03	.03	10	
35252	3/16	113	4.4	.05	.05	10	
35253	7/32	122	4.8	.07	.07	10	
35254	1/4	135	5.3	.10	.10	10	
35255	5/16	152	6.0	.18	.18	10	
35256	3/8	173	6.8	.30	.30	10	
35257	1/2	209	8.2	.77	.77	1	
35258	9/16	230	9.1	1.04	1.04	1	
35259	5/8	245	9.6	1.27	1.27	1	
35261	3/4	286	11.3	2.01	2.01	1	
352 Metric							
Item No.	mm	mm	Inch	mm	mm	lbs.	pkg.
35201	1.5	89	3.5	14	.6	.01	10
35202	2.0	99	3.9	16	.6	.01	10
35204	2.5	110	4.3	18	.7	.02	10
35206	3.0	124	4.9	20	.8	.02	10
35208	4.0	138	5.4	25	1.0	.04	10
35210	5.0	158	6.2	28	1.1	.07	10
35211	6.0	178	7.0	32	1.3	.12	10
35212	7.0	187	7.4	34	1.3	.17	10
35214	8.0	196	7.7	36	1.4	.23	10
35217	10.0	219	8.6	40	1.6	.40	10
35219	12.0	245	9.6	45	1.8	.77	1
35221	14.0	277	10.9	56	2.2	1.12	1
35223	17.0	316	12.4	63	2.5	1.80	1
35227	19.0	355	14.0	70	2.8	2.46	1



SHOP

35295 13 Piece Inch Hex L-key Set, In Plastic Holder

Equipped with .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Item No.	lbs.	pkg.
35295	.90	1



SHOP

35297 9 Piece Metric Hex L-key Set, In Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

Item No.	lbs.	pkg.
35297	1.00	1

Black Finish Long Arm Hex L-keys



Black Finish

High alloy CVM steel, hardened, black finish. Precision machined, burr free chamfered ends.

352 Inch							
L-key Hex, Long Arm							
Item No.	Inch	mm	Inch	mm	lbs.	pkg.	
35200	.028	67	2.6	.01	.01	10	
35203	.035	69	2.7	.01	.01	10	
35213	.050	75	3.0	.01	.01	10	
35216	1/16	78	3.1	.01	.01	10	
35218	5/64	82	3.2	.01	.01	10	
35222	3/32	85	3.3	.01	.01	10	
35224	7/64	92	3.6	.02	.02	10	
35226	1/8	95	3.7	.02	.02	10	
35228	9/64	100	3.9	.03	.03	10	
35232	5/32	105	4.1	.04	.04	10	
35234	3/16	113	4.4	.05	.05	10	
35236	7/32	122	4.8	.07	.07	10	
35238	1/4	135	5.3	.10	.10	10	
35242	5/16	152	6.0	.18	.18	10	
35244	3/8	173	6.8	.30	.30	10	
35245	1/2	209	8.2	.75	.75	1	
35246	9/16	230	9.1	.99	.99	1	
35247	5/8	245	9.6	1.26	1.26	1	
35248	3/4	286	11.3	2.02	2.02	1	
35249	1"	359	14.1	4.38	4.38	1	
352 Metric							
Item No.	mm	mm	Inch	mm	mm	lbs.	pkg.
35200	0.7	66	2.6	5	.2	.01	10
35203	0.9	68	2.7	8	.3	.01	10
35205	1.3	72	2.8	12	.5	.01	10
35215	1.5	76	3.5	14	.6	.01	10
35220	2.0	99	3.9	16	.6	.01	10
35225	2.5	110	4.3	18	.7	.02	10
35230	3.0	124	4.9	20	.8	.02	10
35240	4.0	138	5.4	25	1.0	.04	10
35250	5.0	158	6.2	28	1.1	.07	10
35260	6.0	178	7.0	32	1.3	.12	10
35270	7.0	187	7.4	34	1.3	.18	10
35280	8.0	196	7.7	36	1.4	.24	10
35282	10.0	219	8.6	40	1.6	.40	10
35284	12.0	245	9.6	45	1.8	.77	1
35285	14.0	277	10.9	56	2.2	1.13	1
35286	17.0	316	12.4	63	2.5	1.80	1
35288	19.0	355	14.0	70	2.8	2.45	1



#35291

Black Finish

#35290

35291 13 Piece Inch Hex L-key Set, In Plastic Holder

.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Item No.	lbs.	pkg.
35291	.98	1

35290 9 Piece Metric Hex L-key Set, In Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

Item No.	lbs.	pkg.
35290	.97	1

SHOP

Short Arm Hex L-keys Nickel Finish

- Ideal for use in clean rooms & other environments where non-oxidizing surfaces are specified or required.

Nickel-Plated

[SHOP](#)

351 Metric L-key Hex Metric, Short Arm high alloy CVM steel, hardened, nickel plated. Precision machined, burr free chamfered ends.

Item No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
35104	1.5	45	1.8	14	.6	.01	10
35108	2.0	49	1.9	16	.6	.01	10
35112	2.5	55	2.2	18	.7	.01	10
35116	3.0	61	2.4	20	.8	.02	10
35120	4.0	68	2.7	25	1.0	.03	10
35124	5.0	78	3.1	28	1.1	.04	10
35128	6.0	88	3.5	32	1.3	.07	10
35132	7.0	92	3.6	34	1.3	.10	10
35136	8.0	97	3.8	36	1.4	.13	10
35140	9.0	103	4.1	38	1.5	.18	10
35144	10.0	109	4.3	40	1.6	.23	10
35145	12.0	122	4.8	45	1.8	.40	1
35175	14.0	137	5.4	56	2.2	.61	1
35177	17.0	156	6.1	63	2.5	1.02	1
35179	19.0	176	6.9	70	2.8	1.40	1

- Ideal for use in clean rooms & other environments where non-oxidizing surfaces are specified or required.

Nickel-Plated

[SHOP](#)

351 Inch L-key Hex, Short Arm Nickel-plated

Item No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
35143	.050	40	1.6	10	.39	.01	10
35146	1/16	46	1.8	14	.55	.01	10
35147	5/64	50	2.0	16	.63	.01	10
35150	3/32	52	2.1	19	.75	.01	10
35152	7/64	54	2.1	19	.75	.01	10
35153	1/8	58	2.3	21	.83	.02	10
35155	9/64	62	2.4	23	.91	.02	10
35156	5/32	68	2.7	25	.99	.02	10
35159	3/16	70	2.8	26	1.0	.04	10
35162	7/32	77	3.1	29	1.2	.05	10
35165	1/4	88	3.5	31	1.2	.08	10
35168	5/16	98	3.9	36	1.4	.13	10
35171	3/8	107	4.2	38	1.5	.20	10
35174	1/2	133	5.2	44	1.7	.46	1
35176	9/16	158	6.2	64	2.5	.64	1
35178	5/8	175	6.9	71	2.8	.85	1
35180	3/4	198	7.8	89	3.5	1.40	1



[SHOP](#)

35191 9 Piece Metric Hex L-key Set, In Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

lbs. .59 pkg. 1



[SHOP](#)

35193 6 Piece Metric Hex L-key Set, In Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0mm

lbs. .20 pkg. 1



[SHOP](#)

35192 8 Piece Inch Hex L-key Set, In Plastic Holder

Equipped with 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16"

lbs. .41 pkg. 1



[SHOP](#)

35194 13 Piece Inch Hex L-key Set, In Plastic Holder

Equipped with .050 - 3/8"

lbs. .72 pkg. 1

Short Arm Hex L-keys Black Finish


 Black Finish



353 Metric L-key Hex Metric, Short Arm high alloy CVM steel, hardened, black finish. Precision machined, burr free chamfered ends.

Item No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
35301	0.7	31	1.2	-	-	.01	10
35302	0.9	31	1.2	-	-	.01	10
35303	1.3	40	1.6	12	.5	.01	10
35304	1.5	45	1.8	14	.6	.01	10
35305	2.0	49	1.9	16	.6	.01	10
35306	2.5	55	2.2	18	.7	.01	10
35307	3.0	61	2.4	20	.8	.02	10
35308	4.0	68	2.7	25	1.0	.03	10
35309	5.0	78	3.1	28	1.1	.04	10
35310	6.0	88	3.5	32	1.3	.07	10
35311	7.0	92	3.6	34	1.3	.10	10
35312	8.0	97	3.8	36	1.4	.13	10
35313	9.0	103	4.1	38	1.5	.17	10
35314	10.0	109	4.3	40	1.6	.23	10
35316	11.0	115	4.5	42	1.7	.29	10
35317	12.0	122	4.8	45	1.8	.40	1
35318	14.0	137	5.4	56	2.2	.61	1
35319	17.0	156	6.1	63	2.5	1.03	1
35320	19.0	176	6.9	70	2.8	1.40	1
35321	22.0	195	7.7	80	3.1	2.17	1


 Black Finish




353 Inch L-key Hex Inch, Short Arm black finish

Item No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
35301	.028	31	1.2	-	-	.01	10
35302	.035	31	1.2	-	-	.01	10
35330	.050	40	1.6	10	.4	.01	10
35331	1/16	46	1.8	14	.6	.01	10
35332	5/64	50	2.0	16	.6	.01	10
35333	3/32	52	2.1	19	.8	.01	10
35334	7/64	54	2.1	19	.8	.01	10
35335	1/8	58	2.3	21	.8	.02	10
35336	9/64	62	2.4	23	.9	.02	10
35337	5/32	68	2.7	25	1.0	.02	10
35338	3/16	70	2.8	26	1.0	.05	10
35339	7/32	77	3.1	29	1.2	.07	10
35340	1/4	88	3.5	31	1.2	.07	10
35341	5/16	98	3.9	36	1.4	.13	10
35342	3/8	107	4.2	38	1.5	.20	10
35343	1/2	133	5.2	44	1.7	.49	1
35345	9/16	158	6.2	64	2.5	.66	1
35346	5/8	175	6.9	71	2.8	.86	1
35347	3/4	198	7.8	89	3.5	1.45	1
35348	1"	220	8.7	91	3.6	3.14	1





35390 9 Piece Metric Hex L-key Set, In Plastic Holder
 Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm
 lbs. .59  pkg. 1




35392 5 Piece Mini Metric Hex L-key Set, In Plastic Holder
 Equipped with 0.7, 0.9, 1.3, 1.5, 2.0mm
 lbs. .03  pkg. 1




35391 13 Piece Inch Hex L-key Set, In Plastic Holder
 Equipped with .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"
 lbs. .64  pkg. 1




35393 5 Piece Mini Inch Hex L-key Set, In Plastic Holder
 Equipped with .028, .035, .050, 1/16, 5/64"
 lbs. .03  pkg. 1

Wiha Insulated T-handles

Insulation Test Standards:

Insulation according to EN/IEC 60900, ASTM F-1505-01, VDE 0682/part 201, DIN 7437, NFPA70E, CSA

Responds to OSHA's use specification 29 CFR1910


Insulation

Molded directly onto blade for permanent bonding

Each tool individually tested to 10,000 volts and certified to 1000 Volt ac or 1500 Volt dc

Blade CVM tool steel, hardened to average 58/60RC

1000V



1000Volt

SHOP

334 **Metric** T-handle, With Wiha-Molded Handle. Insulation According to ASTM, VDE, EN/IEC, NFPA70E and CSA, **1000 Volt. Individually Tested.**

Item	Hex	mm	Inch	mm	Inch	lbs.	pkg.
33441	4.0	150	5.9	176	6.9	.09	10
33443	5.0	150	5.9	176	6.9	.15	10
33445	6.0	150	5.9	176	6.9	.18	10
33447	8.0	150	5.9	176	6.9	.26	10
33449	10.0	150	5.9	176	6.9	.46	10



1000Volt

SHOP

33478 5 Piece Hex **Metric** T-handle Set

Item	Hex	lbs.
No.	Hex Metric :	lbs.
33478	4.0, 5.0, 6.0, 8.0, 10.0mm	1.20

Wiha Insulated Hex Metric Screwdrivers




1000Volt

SHOP

323 Hex **Metric** Screwdriver, With Wiha-SoftFinish® Handle Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA, **1000 Volt. Individually Tested.** Blade high alloy CVM steel, hardened, black finish. Insulation molded directly onto blade. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item	Hex	mm	Inch	mm	Inch	lbs.	pkg.
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
32302	2.5	75	3.0	179	7.0	.06	10
32303	3.0	75	3.0	179	7.0	.08	10
32304	4.0	75	3.0	186	7.3	.12	10
32305	5.0	75	3.0	186	7.3	.15	10
32306	6.0	100	3.9	218	8.6	.21	10
32308	8.0	100	3.9	218	8.6	.34	10




1000Volt

SHOP

32366 6 Piece Insulated Hex **Metric** Screwdriver Set

Item No.	Hex	lbs.
No.	Hex Metric :	lbs.
32366	2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	1.06



1000Volt

SHOP

334 Inch T-handle, With Wiha-Molded Handle Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201, EN/IEC 60900, NFPA70E and CSA, **1000 Volt. Individually Tested.**

Blade CVM steel, hardened. Insulation molded directly onto blade. Wiha-SoftFinish® handle, multi-component.

Item	Hex	Inch	Inch	mm	lbs.	pkg.
No.	Inch	Inch	Inch	mm	lbs.	pkg.
33481	5/32	5.9	6.9	176	.09	10
33482	3/16	5.9	6.9	176	.15	10
33483	7/32	5.9	6.9	176	.19	10
33485	1/4	6.9	6.9	176	.20	10
33486	5/16	6.9	6.9	176	.26	10
33487	3/8	6.9	6.9	176	.44	10



1000Volt

SHOP

33490 6 Piece Hex Inch T-handle Set

Item	Hex	lbs.
No.	Hex Inch:	lbs.
33490	5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	1.66

Wiha Insulated Hex L-keys

Insulation Test Standards:

Insulation according to ASTM,
F-1505-01, EN/IEC 60900
and CSA



Insulation
Applied directly
onto blade for
permanent
bonding

**Each tool individually
tested to 10,000 volts
and certified to 1000
Volt ac or 1500 Volt dc**

1000V



1000V

SHOP

136 Inch Insulated Hex L-keys, With Insulated Handle

Insulation According to IEC 60900 specification, up to 1000 Volt.
Individually Tested. Blade chrome-vanadium steel, hardened.

Item No.	ØMM	OAL	OAL	lbs.	pkg.
No.	Inch	mm	Inch	lbs.	pkg.
13670	1/16	79	3.1	.05	1
13671	5/64	84	3.3	.05	1
13672	3/32	89	3.5	.05	1
13673	7/64	94	3.7	.06	1
13663	1/8	104	4.1	.06	1
13665	5/32	104	4.1	.06	1
13666	3/16	134	5.3	.10	1
13667	7/32	134	5.3	.12	1
13668	1/4	134	5.3	.16	1
13669	5/16	144	5.7	.24	1
13662	3/8	234	9.2	.51	1
13664	1/2	234	9.2	.77	1




1000V

SHOP

136 Metric Insulated Hex L-keys, With Insulated Handle

Insulation According to IEC 60900 specification, up to 1000 Volt.
Individually Tested. Blade chrome-vanadium steel, hardened.

Item No.	ØMM	OAL	OAL	lbs.	pkg.
No.	mm	mm	Inch	lbs.	pkg.
13650	1.5	100	3.9	.09	1
13651	2.0	105	4.1	.09	1
13652	2.5	115	4.5	.09	1
13653	3.0	130	5.1	.10	1
13654	4.0	120	4.7	.10	1
13655	5.0	140	5.5	.10	1
13656	6.0	140	5.5	.13	1
13658	8.0	150	5.9	.24	1
13659	10.0	220	8.7	.51	1
13657	12.0	260	10.2	.77	1



#13691

#13690

1000V

SHOP

13690 8 Piece Insulated Hex L-key Set - Inch

Item No.		lbs.
13690	1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 1/2"	2.17

13691 7 Piece Insulated Hex L-key Set - Metric

Item No.		lbs.
13691	3.0, 4.0, 5.0, 6.0, 8.0, 10.0, 12.0mm	2.07



1000V

SHOP

13693 10 Piece Insulated Hex L-key Set - Metric

Item No.		lbs.
13693	1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0, 12.0mm	2.26

13694 12 Piece Insulated Hex L-key Set - Inch

Item No.		lbs.
13694	1/16, 5/64, 3/32, 7/64, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 1/2"	2.40

Wiha Insulated 3/8" Bit Sockets & Set



1000V

SHOP

318 Insulated 3/8" Drive Sockets - Insulation according to

EN/IEC 60900, DIN 7448 specification, up to 1000 Volt.

Individually Tested. Chrome-vanadium steel, forged, oil-hardened.

Item No.	Inch	OAL	lbs.	pkg.
31805	3/16	3.1"	.13	1
31807	7/32	3.1"	.14	1
31809	1/4	3.1"	.14	1
31811	5/16	3.1"	.16	1
31813	3/8	3.1"	.18	1
31815	7/16	3.1"	.20	1
31817	1/2	3.1"	.22	1

*Sockets must be used with insulated ratchets & extensions



1000V

SHOP

31890 7 Piece Insulated 3/8" Drive Socket Set - Inch

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No.	Set includes the following:	lbs.
31890	3/16, 7/32, 1/4, 5/16, 3/8, 7/16, 1/2"	1.7

Wiha Drive-Loc VI Handles



Allows adjustable blade lengths 1.7" to 4.7" in 1/8" increments



28488 Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

Advantages:

Ergonomic cushion grip, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28488	6.0	115	4.5	36.0	1.41	.26



Allows adjustable blade lengths 1.7" to 4.7" in 1/8" increments



28486 ESD Safe Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

Advantages:

Ergonomic cushion grip, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange. Static Dissipative.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28486	6.0	115	4.5	36.0	1.41	.21



Allows adjustable blade lengths 1.7" to 4.7" in 1/8" increments



28487 Drive-Loc VI MicroFinish Non-Slip Grip Handle

Wiha-MicroFinish handle, won't peel, crack or deteriorate when exposed to petroleum solvents. Ideal for Hex, TORX® & Nut Drivers.

Advantages:

Ergonomic handle shape for maximum comfort, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28487	6.0	115	4.5	36.0	1.41	.20



Wiha Drive-Loc VI Blades



281 Ball End Hex & Hex Metric Drive-Loc VI Interchangeable Blade

Blade High alloy CVM steel, through hardened, hard chrome finish. Ball end enables the user to work at angles up to 25°. Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	mm + mm	lbs.	pkg.	
28116	2.5 2.5	.10	1	
28117	3 3	.10	1	
28118	4 4	.10	1	
28119	5 5	.10	1	
28120	6 6	.10	1	



281 Hex Metric Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	mm + mm	lbs.	pkg.	
28149	2.0 2.5	.09	1	
28150	3.0 4.0	.10	1	
28151	5.0 6.0	.10	1	



281 Hex Inch Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	Inch + Inch	lbs.	pkg.	
28122	3/32 7/64	.10	1	
28123	1/8 9/64	.10	1	
28124	5/32 3/16	.10	1	



28189 15 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 14 interchangeable blades.
Item No. 28189 lbs. 1.28
Slotted: 3.5+4.5, 5.5+6.5 **Phillips:** 1+2 **Security TORX®:** T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s **Hex Inch:** 3/32+7/64, 1/8+9/64, 5/32+3/16 **Hex Metric:** 2.0+2.5, 3.0+4.0, 5.0+6.0mm
 Wiha SoftFinish® Cushion Grip Blade Lock Handle

TorqueControl Tools



+/-6% accuracy
tolerance
Certificate of
calibration



+/-6% accuracy tolerance
Certificate of calibration



285 TorqueFix, With Wiha-SoftFinish® Handle

Fixed Torque value pre-set. Tested in accordance with EN ISO 6798, BS EN 26789, ASME B107.14M, tolerance +/- 6%. Audible and perceptible click when pre-set torque has been attained.

Automatically resets for next torque cycle; 50% greater reverse torque.

Item No.	Pre-Sets						
	oz.	lbs.	Nm	mm	Inch	lbs.	pkg.
28503	80	5	0.56	112	4.4	.16	1
28505	120	7.5	0.84	112	4.4	.15	1
28507	160	10	1.12	119	4.7	.28	1
28509	200	12.5	1.41	119	4.7	.27	1
28511	240	15	1.69	119	4.7	.27	1
28513	320	20	2.25	119	4.7	.28	1
28515	400	25	2.82	126	4.9	.37	1
28517	480	30	3.39	126	4.9	.37	1
28518	560	35	3.95	126	4.9	.37	1
28519	640	40	4.52	126	4.9	.37	1
28521	800	50	5.65	132	5.2	.52	1
28523	960	60	6.78	132	5.2	.52	1
28525	1120	70	7.91	132	5.2	.52	1

Direct Reading Scale



+/-6% accuracy
tolerance
Certificate of
calibration



285 Adjustable TorqueVario With Direct Reading Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Range				
	Inch	lbs.	Increments	mm	lbs.
28501*	15 - 80(in/oz)		2.5 Inch oz	122 - 127	.22
28502	5 - 10		.5 Inch lbs	122 - 127	.41
28504	7.5 - 20		.5 Inch lbs	126 - 131	.50
28506	10 - 50		2 Inch lbs	133 - 138	.59
28508	20 - 70		2 Inch lbs	137 - 142	.74

Above includes Micro Bit Holder 28583

See 4mm Micro Bits on Page 30

* +/- 10% (This unit only)

* (1 Nm = 8.8507)

285 Adjustable TorqueVario-S Handle - In Newton Meter Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Newton Meter Scale	Increments			
			mm	lbs.	pkg.
28550*	0.1 - 0.6Nm	.02 Nm	122 - 127	.35	1
28551	0.4 - 1.0Nm	.05 Nm	122 - 127	.35	1
28552	0.8 - 2.0Nm	.05 Nm	126 - 131	.45	1
28553	1.0 - 5.0Nm	.20 Nm	133 - 138	.55	1
28554	2.0 - 8.0Nm	.25 Nm	137 - 142	.70	1

* +/- 10% (This unit only)

* (1 Nm 8.8507)



285 Hex Metric Interchangeable Blades For TorqueFix & TorqueVario

Hex tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.				Max. Torque	
	mm	mm	lbs.	Nm	pkg.
28545	1.5	175	.07	0.9	1
28546	2.0	175	.07	1.8	1
28547	2.5	175	.07	3.8	1
28548	3.0	175	.07	8.0	1
28549	4.0	175	.07	8.0	1



285 Hex Inch Interchangeable Blades For TorqueFix & TorqueVario

Hex tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.				Max. Torque	
	Inch	mm	lbs.	Nm	pkg.
28555	.050	175	.07	.4	1
28556	1/16	175	.07	.9	1
28557	5/64	175	.07	1.8	1
28558	3/32	175	.07	1.8	1
28559	7/64	175	.07	3.8	1
28560	1/8	175	.07	3.8	1
28587	9/64	175	.07	8.0	1
28588	5/32	175	.07	8.0	1

T-handle TorqueControl Tools



Includes Calibration
Certificate



289 TorqueFix T-handle

EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 6% Accuracy
Ergonomic multi-component handle, light and compact.
With Certificate of calibration.

Item No.	Torque In-lbs.	Torque Nm	 mm x mm	 lbs.	 pkg.
28931	53.1	6	56 x 120	.81	1
28933	70.8	8	56 x 120	.82	1
28935	88.5	10	56 x 120	.79	1
28937	106.2	12	56 x 120	.79	1
28938	110.6	12.5	56 x 120	.80	1
28939	123.9	14	56 x 120	.80	1

Each TorqueFix T-handle has unique serial
number and certificate of calibration



Includes Calibration
Certificate



28940 Adjustable TorqueVario STplus T-handle

EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 6% Accuracy
Ergonomic multi-component handle, light and compact.

Item No.	Torque In-lbs.	Torque Nm	 mm x mm	 lbs.	 pkg.
28940	44.3-123.9	5-14	56 x 120	.81	1

* (1 Nm 8.8507)



289 Hex Metric Interchangeable Blades For TorqueFix T-handle

Hex tip blades on 6mm Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.	 mm	 mm	 Inch	 lbs.	 pkg.
28916	3.0	130	5.1	.11	1
28917	4.0	130	5.1	.11	1
28918	5.0	130	5.1	.11	1
28919	6.0	130	5.1	.11	1



289 Hex Inch Interchangeable Blades For TorqueFix T-handle

Hex tip blades on 6mm Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.	 Inch	 mm	 Inch	 lbs.	 pkg.
28920	1/8	130	5.1	.11	1
28921	9/64	130	5.1	.11	1
28922	5/32	130	5.1	.11	1
28923	3/16	130	5.1	.11	1
28924	7/32	130	5.1	.11	1



Adjustable from
Nm 5-14 or
In-lbs. 44.3-123.9

Wiha Precision ESD Safe Hex Drivers

Wiha Precision ESD Static Dissipative Screwdrivers meet the requirements for tools used in static sensitive areas.



ESD Standard IEC 61340-5-1

Surface resistance of handles is $10^6 - 10^9$ Ohms

Rotating cap for precise turning & control with fingertip

Molded Precision handle of impact resistant dissipative material

Tapered handle allows rapid rotation

Blade, CVM steel, hardened, hard chrome finish

Tip, precision ground for exact fit, Wiha Chromtop finish



275 Inch Hex Driver, With Precision ESD Safe Dissipative

Handle Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1

Item	Hex	mm	Inch	mm	Inch	lbs.	pkg.
No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
27505	0.028	40	1.6	120	4.7	.02	10
27510	0.035	40	1.6	120	4.7	.02	10
27513	0.05	40	1.6	120	4.7	.02	10
27537	1/16	50	2.0	145	5.7	.03	10
27539	5/64	50	2.0	145	5.7	.03	10
27541	3/32	60	2.4	170	6.7	.04	10
27543	7/64	60	2.4	170	6.7	.04	10
27545	1/8	60	2.4	170	6.7	.04	10
27547	9/64	60	2.4	170	6.7	.05	10
27549	5/32	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



275 Metric Hex Metric Driver, With Precision ESD Safe

Dissipative Handle Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1

Item	Hex	mm	Inch	mm	Inch	lbs.	pkg.
No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
27507	0.7	40	1.6	120	4.7	.02	10
27509	0.9	40	1.6	120	4.7	.02	10
27513	1.3	40	1.6	120	4.7	.03	10
27515	1.5	50	2.0	145	5.7	.03	10
27520	2.0	50	2.0	145	5.7	.04	10
27525	2.5	60	2.4	170	6.7	.05	10
27530	3.0	60	2.4	170	6.7	.05	10
27535	4.0	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



ESD standard IEC 61340-5-1

27590 Set 8 Pcs. Hex Metric Precision ESD Safe Dissipative

Handle Blade CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material. In storage pouch

resistant, dissipate heat in storage pouch								
Item				<th></th> <th></th> <th></th> <th></th>				
No.		mm	mm		mm	mm	lbs.	
27590	27507	.71	40	27520	2.0	50	.53	
	27509	.89	40	27525	2.5	60		
	27513	1.3	40	27530	3.0	60		
	27515	1.5	50	27535	4.0	60		



ESD standard IEC 61340-5-1

27591 8 Piece Hex Inch Precision Set, ESD Safe Dissipative

Handle Blade CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material. In storage pouch

Item	Hex	Inch	Inch	Hex	Inch	Inch	lbs.
No.	Inch	Inch	Inch	Inch	Inch	Inch	lbs.
27591	27513	0.05	1.6	27543	7/64	2.4	.57
	27537	1/16	2.0	27545	1/8	2.4	
	27539	5/64	2.0	27547	9/64	2.4	
	27541	3/32	2.4	27549	5/32	2.4	



91118 Rugged Polyester Canvas Storage Pouch

Holds 8 Precision Tools up to 170mm in length. Folding pouch. Has security flaps and velcro closer.

Item	Size	lbs.	pkg.
No.	Size	lbs.	pkg.
91118	14 1/2" W x 7 3/4" L	.13	1

Pico Soft Grip Ball End Inch & Metric



SHOP

264 Ball End Hex Inch Screwdriver, With Precision Soft

PicoFinish Handle Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item						
No.	Inch	Inch	mm	Inch	mm	pkg.
26455	1/16	2.0	50	5.9	150	10
26457	5/64	2.0	50	5.9	150	10
26459	3/32	2.0	50	5.9	150	10
26461	7/64	2.4	60	6.3	160	10
26463	1/8	2.4	60	6.3	160	10
26465	9/64	2.4	60	6.3	160	10
26467	5/32	2.4	60	6.3	160	10

*Metric dimensions actual - Inch dimensions approximate



SHOP

26493 7 Piece Inch Ball End Hex Precision Driver Set, With

Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item	No.	Inch	Inch	Inch	Inch	lbs.
26493	26455	1/16	2.0	26463	1/8	2.4
	26457	5/64	2.0	26465	9/64	2.4
	26459	3/32	2.0	26467	5/32	2.4
	26461	7/64	2.4			



SHOP

264 Ball End Hex Metric Screwdriver, With Precision Soft

PicoFinish Handle. Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item							
No.	mm	mm	Inch	mm	Inch	pkg.	
26441	1.3	40	1.6	134	5.3	10	
26443	1.5	50	2.0	150	5.9	10	
26445	2.0	50	2.0	150	5.9	10	
26447	2.5	60	2.4	160	6.3	10	
26449	3.0	60	2.4	160	6.3	10	

*Metric dimensions actual - Inch dimensions approximate

Pico Soft Grip Hex Inch & Metric



SHOP

263 Hex Inch Screwdriver, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item						
No.	Inch	mm	Inch	mm	Inch	pkg.
26341	0.028(0.7)	40	1.6	134	5.3	10
26343	0.035(0.9)	40	1.6	134	5.3	10
26345	0.05(1.3)	40	1.6	134	5.3	10
26349	5/64(2.0)	50	2.0	150	5.9	10
26363	1/16	50	2.0	144	5.7	10
26367	3/32	60	2.4	160	6.3	10
26369	7/64	60	2.4	160	6.3	10
26371	1/8	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



In storage pouch

SHOP

26392 8 Piece Hex Inch Precision Driver Set

Item	No.	Inch	Inch	Inch	Inch	lbs.
26392	26341	0.028	1.6	26363	1/16	2.0
	26343	0.035	1.6	26367	3/32	2.4
	26345	0.05	1.6	26369	7/64	2.4
	26349	5/64	2.0	26371	1/8	2.4



SHOP

263 Hex Metric Driver, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item						
No.	mm	mm	Inch	mm	Inch	pkg.
26341	0.7(0.028)	40	1.6	134	5.3	10
26343	0.9(0.035)	40	1.6	134	5.3	10
26345	1.3(0.05)	40	1.6	134	5.3	10
26347	1.5	50	2.0	144	5.7	10
26349	2.0(5/64)	50	2.0	150	5.9	10
26351	2.5	60	2.4	160	6.3	10
26353	3.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



In storage pouch

SHOP

26393 7 Pc. Hex Metric Precision Driver Set

Item	No.	mm	mm	mm	mm	lbs.
26393	26341	0.7	40	26349	2.0	50
	26343	0.9	40	26351	2.5	60
	26345	1.3	40	26353	3.0	60
	26347	1.5	50			

Wiha Hex Precision Series



263 Metric Metric Hex Driver, With Precision Handle

Metric sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26307	0.7	0.028	40	1.6	120	4.7	.02	10	
26309	0.9	0.035	40	1.6	120	4.7	.02	10	
26313	1.3	0.05	40	1.6	120	4.7	.02	10	
26315	1.5	-	50	2.0	145	5.7	.03	10	
26320	2.0	5/64	50	2.0	145	5.7	.03	10	
26325	2.5	-	60	2.4	170	6.7	.04	10	
26330	3.0	-	60	2.4	170	6.7	.04	10	
26340	4.0	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



26390 7 Pc. Precision Hex Driver Set - Metric

Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	Inch	Inch	lbs.
26390	26307	0.7	1.6	.28
	26309	0.9	1.6	
	26313	1.3	1.6	
	26315	1.5	2.0	
	26320	2.0	2.0	
	26325	2.5	2.4	
	26330	3.0	2.4	



26399 8 Piece Precision Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item	No.	Inch	Inch	Inch	Inch	lbs.
26399	26307	0.028	1.6	26320	5/64	.55
	26309	0.035	1.6	26323	3/32	2.4
	26313	0.05	1.6	26327	7/64	2.4
	26316	1/16	2.0	26331	1/8	2.4



263 Inch Inch Hex Driver, With Precision Handle

Inch sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	Inch	mm	mm	Inch	mm	Inch	lbs.	pkg.
26307	.028	0.7	40	1.6	120	4.7	.02	10	
26309	.035	0.9	40	1.6	120	4.7	.02	10	
26313	0.05	1.3	40	1.6	120	4.7	.02	10	
26316	1/16	-	50	2.0	145	5.7	.03	10	
26320	5/64	2.0	50	2.0	145	5.7	.03	10	
26323	3/32	-	60	2.4	170	6.7	.04	10	
26327	7/64	-	60	2.4	170	6.7	.04	10	
26331	1/8	-	60	2.4	170	6.7	.04	10	
26333	9/64	-	60	2.4	170	6.7	.05	10	
26336	5/32	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



26391 8 Pc. Precision Hex Driver Set - Inch

Blade high alloy CVM steel.

Item	No.	Inch	Inch	lbs.
26391	26307	0.028	1.6	.32
	26309	0.035	1.6	
	26313	0.05	1.6	
	26316	1/16	2.0	
	26320	5/64	2.0	
	26323	3/32	2.4	
	26327	7/64	2.4	
	26331	1/8	2.4	



Wiha Ball End Precision Series



264 Metric Ball End Hex Metric Screwdriver With Precision Handle

Angle entry up to 30°. Blade high alloy CVM steel.

Item	No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26413	1.3	0.05	40	1.6	120	4.7	.02	10	
26415	1.5	-	50	2.0	145	5.7	.03	10	
26420	2.0	-	50	2.0	145	5.7	.03	10	
26425	2.5	-	60	2.4	170	6.7	.04	10	
26430	3.0	-	60	2.4	170	6.7	.05	10	
26440	4.0	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate




26491 5 Piece Ball End Hex Driver Set - Metric

Angle entry up to 30°.

Blade high alloy CVM steel.

Item	No.	mm	mm	lbs.
26491	26413	1.3	40	.31
	26415	1.5	50	
	26420	2.0	50	
	26425	2.5	60	
	26430	3.0	60	

Wiha Ball End Precision Series



264 Inch Ball End Hex Inch Screwdriver With Precision Handle

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finish.

Item No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26413	0.05	40	1.6	120	4.7	.02	10
26416	1/16	50	2.0	145	5.7	.03	10
26419	5/64	50	2.0	145	5.7	.03	10
26423	3/32	50	2.0	145	5.7	.03	10
26427	7/64	60	2.4	170	6.7	.03	10
26431	1/8	60	2.4	170	6.7	.05	10
26436	9/64	60	2.4	170	6.7	.05	10
26439	5/32	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



26490 8 Piece Ball End Hex Driver Set - Inch

Angle entry up to 30°.

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Inch	Inch	lbs.
26413	0.05	1.6	.40
26416	1/16	2.0	
26419	5/64	2.0	
26423	3/32	2.0	
26427	7/64	2.4	
26431	1/8	2.4	
26436	9/64	2.4	
26439	5/32	2.4	

Wiha Ball End Precision Series



62995 22 Piece Slotted/Phillips/TORX®/Ball End Hex Inch & Metric Tech Pack

Wiha Proturm precision ball retainer handle & 21 Wiha interchangeable blades. Set in canvas storage pouch

62995 Set includes the following blades:

Slotted: 1.5, 2.0, 3.0, 4.0 Phillips: #000, #00, #0, #1

TORX®: T6, T7, T8, T9, T10, T15, T20

Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0mm

lbs. .87

62994 14 Piece Inch/Metric Ball End Hex Work Tech Pack

Proturm precision ball retainer handle & 13 Wiha interchangeable blades.

62994 Set includes the following blades:

Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0mm

lbs. .66 Set in canvas storage pouch

SYS 4 Drive-Loc Precision Locking Tools



26961 ESD Safe Dissipative Precision Drive-Loc Handle

Surface resistant 10⁶-10⁹ Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Ball retainer hold. 105mm/4.13" OAL

Item No.	mm	Inch	mm	Inch	lbs.
26961	4.0	.1574	23	.91	.08



280 SYSTEM 4 Metric Hex Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item No.	mm	mm	lbs.
28003	1.3	1.3	.02
28004	1.5	1.5	.02
28005	2.0	2.0	.02
28006	2.5	2.5	.02
28007	3.0	3.0	.02
28008	4.0	4.0	.02



Rotating Cap
for precise
turning and
control

**Precision
Handle**
high quality
plastic,
cadmium
free. ESD
Safe or
Standard
styles

Tapered Handle
allows rapid
rotation,
requires less
clearance

Tips
exact fit,
precision
machined

Blades
CVM steel, hardened, hard chromed

15mm

Collet Lock Handle
adjustable blade
length from
15 to 95mm/
.6" to 3.75"

95mm



26900 SYS 4 Standard Precision Handle,
with rotating control cap. Accepts all
SYSTEM 4 interchangeable blades. Wiha
Precision handle, tapered, impact resistant.
Ball retainer hold. 110mm/4.3" OAL

Item						
No.	mm	Inch	mm	Inch	lbs.	
26900	4.0	.1574	14.0	.55	.04	



26901 SYSTEM 4 Standard Precision

Adjustable handle with rotating control cap.

- Allows adjustable blade from 15 to 95mm.
- Collet lock allows for quick & easy adjustment.
- Holds blade securely in place. Accepts all SYSTEM 4 blades. 110mm/4.3" OAL

Item						
No.	mm	Inch	mm	Inch	lbs.	
26901	4.0	.1574	14.0	.55	.06	



269 SYSTEM 4 Metric Ball End & Standard Hex, Reversible Blade

Wiha vapor Chrome-Top finish on tips.

One side hex, other side ball end hex.

Item						
No.	mm	mm	mm	Inch	lbs.	
26932	1.27 + 1.27	120	4.7	.05		
26933	1.5 + 1.5	120	4.7	.05		
26934	2.0 + 2.0	120	4.7	.06		
26935	2.5 + 2.5	120	4.7	.06		
26936	3.0 + 3.0	120	4.7	.06		
26937	4.0 + 4.0	120	4.7	.06		



28000 ESD Safe Dissipative Precision

Handle with rotating control cap. Surface
resistant 10^6 - 10^9 Ohms. 4 mm hex retainer
for all SYSTEM 4 interchangeable blades.
Tapered handle, high quality plastic, impact
resistant. Ball retainer hold. 110mm/4.3" OAL

Item						
No.	mm	Inch	mm	Inch	lbs.	
28000	4.0	.1574	14.0	.55	.04	



28001 ESD Safe Dissipative Precision

Adjustable Handle with rotating control cap.

Advantages:

- Use in ESD sensitive applications. Surface resistant 10^6 - 10^9 Ohms.
- Collet lock allows for quick & easy adjustment.
- Holds blade securely in place. Accepts all SYSTEM 4 blades. 110mm/4.3" OAL

Item						
No.	mm	Inch	mm	Inch	lbs.	
28001	4.0	.1574	14.0	.55	.04	



280 SYSTEM 4 Metric Ball End Hex

Interchangeable Blade Ball end works at 30°
angle entry for easy access to fasteners.

Item						
No.	mm	mm	Inch	lbs.	pkg.	
28033	1.5	120	4.7	.06	1	
28034	2.0	120	4.7	.06	1	
28035	2.5	120	4.7	.06	1	
28036	3.0	120	4.7	.06	1	
28037	4.0	120	4.7	.06	1	



280 SYSTEM 4 Inch Ball End Hex

Interchangeable Blade Ball end works at 30°
angle entry for easy access to fasteners.

Item						
No.	Inch	mm	Inch	lbs.		
28021	.050	120	4.7	.06		
28023	1/16	120	4.7	.06		
28024	5/64	120	4.7	.06		
28025	3/32	120	4.7	.06		
28026	7/64	120	4.7	.06		
28027	1/8	120	4.7	.06		
28028	9/64	120	4.7	.06		
28029	5/32	120	4.7	.06		



269 SYSTEM 4 Metric Hex,

Interchangeable Blade High alloy CVM steel,
hardened, corrosion protected.

Item						
No.	mm	mm	Inch	lbs.		
26913	0.7	120	4.7	.06		
26914	0.9	120	4.7	.06		
26915	1.3	120	4.7	.06		
26916	1.5	120	4.7	.06		
26917	2.0	120	4.7	.06		
26918	2.5	120	4.7	.06		
26919	3.0	120	4.7	.06		
26920	4.0	120	4.7	.06		



269 SYSTEM 4 Inch Hex,

Interchangeable Blade High alloy CVM steel,
hardened, corrosion protected.

Item						
No.	Inch	mm	Inch	lbs.		
26921	0.05	120	4.7	.06		
26923	1/16	120	4.7	.06		
26924	5/64	120	4.7	.06		
26925	3/32	120	4.7	.06		
26926	7/64	120	4.7	.06		
26927	1/8	120	4.7	.06		
26928	9/64	120	4.7	.06		
26929	5/32	120	4.7	.06		



Wiha ESD Safe
Precision Collet
Lock handle
and 8 Wiha
interchangeable
blades



26999 9 Pc. Hex Metric Precision Blade Set

Set includes the following blades:

	Hex Metric: 0.7, 0.9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
	lbs. .66



Wiha ESD Safe
Precision Collet
Lock handle
and 8 Wiha
interchangeable
blades



26989 9 Pc. Hex Inch Precision Blade Set

Set includes the following blades:

	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	lbs. .64

SYSTEM 4 Handles & Micro Bits

Tips
exact fit,
precision
machined

Rotating Cap
for precise
turning and
control

Tapered Handle
allows rapid rotation,
requires less clearance

Bits CVM steel,
hardened

Use bits directly in handle or with 4" bit extension



110mm/4.3" OAL

75800 SYSTEM 4 Standard Precision Bit

Handle with rotating control cap. Tapered, high quality plastic, impact resistant, ball retainer. Accepts all SYSTEM 4 Series bits.

Item No.	mm	Inch	mm	Inch	lbs.
75800	4.0	.1574	14.0	.55	.06



110mm/4.3" OAL

75801 SYSTEM 4 ESD Safe Dissipative

Precision Bit Handle with rotating control cap. Tapered, high quality plastic, impact resistant. **Advantages:**

- For working in ESD sensitive applications Surface resistant 10^6 - 10^9 Ohms
- Ball retainer holds bits securely in place
- Accepts all SYSTEM 4 Series bits

Item No.	mm	Inch	mm	Inch	lbs.
75801	4.0	.1574	14.0	.55	.06



75901 Magnetic Bit Extension Blade For SYSTEM 4 Micro Bits Shaft CVM steel, hardened. Magnetic bit holder.

Item No.	Size	mm	mm	lbs.
75901	4.0	100	4.0	.04



75900 Extension Blade For SYSTEM 4 Micro Bits Shaft CVM steel, hardened, corrosion protected. Ball retainer bit extension for 4 mm bits.

Item No.	Size	mm	mm	lbs.
75900	4.0	100	4.0	.07



753 SYSTEM 4 Hex Metric Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item No.	mm	mm	Inch	lbs.
75307	.71	28	1.1	.01
75309	.89	28	1.1	.01
75313	1.3	28	1.1	.01
75315	1.5	28	1.1	.01
75320	2.0	28	1.1	.01
75325	2.5	28	1.1	.01
75330	3.0	28	1.1	.01
75340	4.0	28	1.1	.01



753 SYSTEM 4 Hex Inch Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item No.	Inch	mm	Inch	lbs.
75307	.028	28	1.1	.01
75309	.035	28	1.1	.01
75313	.050	28	1.1	.01
75350	1/16	28	1.1	.01
75352	5/64	28	1.1	.01
75354	3/32	28	1.1	.01
75356	7/64	28	1.1	.01
75358	1/8	28	1.1	.01
75360	9/64	28	1.1	.01
75340	5/32	28	1.1	.01



753 SYSTEM 4 Metric Security Hex Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item No.	mm	mm	Inch	lbs.
75322	2.0	28	1.1	.01
75327	2.5	28	1.1	.01
75332	3.0	28	1.1	.01
75342	4.0	28	1.1	.01



753 SYSTEM 4 Security Hex Inch Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item No.	Inch	mm	Inch	lbs.
75362	5/64	28	1.1	.01
75364	3/32	28	1.1	.01
75366	7/64	28	1.1	.01
75368	1/8	28	1.1	.01
75370	9/64	28	1.1	.01
75372	5/32	28	1.1	.01

Wiha SYSTEM 4 Micro Bits & Compact Bit Sets



75395 18 Piece SYSTEM 4 Hex Inch & Metric Precision Interchangeable Bit Set, In Compact Fold Out Box

Wiha precision handle, bit extension & 16 Wiha interchangeable bits.

Item No. Combination Bit Set

75395 Set with Standard Precision Handle

Set includes the following bits:

- **Hex Metric:** .71, .89, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

• **100mm Bit Extension**

• **lbs.** .58



75096 16 Piece Precision Micro Bit Hex Inch & Metric Sets

ESD Safe precision handle, Bit Extension and 14 CVM steel Micro Bits.

Set includes the following Micro Bits:

- **Inch:** 0.89/0.35", 1.3/.050", 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- **Metric:** 1.5, 2.0, 2.5, 3.0, 4.0mm

• **lbs.** .14



75983 Micro Bit Handle Storage Hex Inch Bit Set, 7 Pcs. Wiha precision storage handle & 6 interchangeable bits.

Item No. Precision Storage Handle Set

75983 Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8"

• **lbs.** .08

Wiha Cushion Grip Stubby Bit Holder

Stubby 6 in 1 Multi-Bit Driver Sets



[SHOP](#)

38056 Ball End Hex SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

● Ball End Hex Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	lbs. .21
--	----------



[SHOP](#)

38057 Hex Metric SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

● Hex Metric: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm	lbs. .18
--	----------



[SHOP](#)

38058 Hex Inch SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

● Hex Inch: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"	lbs. .18
--	----------

Wiha Torque Ratchet Bit Sets

Smooth, high torque, silent ratchet handle

Pistol Grip Handle ergonomic design with free running mechanism. Instant clutch engagement allows constant turning pressure on the fastener.

Hex Retainer for bit holder blades



No release of handle is needed, change of direction can be made with index finger and thumb. **Allows** for quick adjustment to right, left or fixed turning.

Opens a new generation of easier torque transmission



[SHOP](#)

28298 12 Piece Hex Inch Topra Ratchet Bit Set

Set includes Topra Handle, Magnetic bit holder and the following bits:

● Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	lbs. .65
---	----------



[SHOP](#)

28299 10 Piece Hex Metric Topra Ratchet Bit Set

Set includes Topra Handle, Magnetic bit holder and the following bits:

● Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	lbs. .65
--	----------

Wiha Bit Selectors

Compact size and easy bit selection make the Bit Selector an ideal maintenance tool



Plastic storage box is compact, durable and light weight

Slide out drawer allows quick bit access and secure storage



Molded hex cavity in box end Magnetic adapter fits into opening so tool case can be used as a handle on quick fastening jobs

1/4" Magnetic Adapter fits all standard 1/4" bits

792 Sets Bit-Selector Sets

These handy sets include 10 hardened bits of chrome-vanadium-molybdenum steel. 1/4" magnetic bit holder can be used in power tools. Plastic storage box is compact, durable and light weight. Molded hex cavity turns box into handle for quick fastening jobs. Quick bit access with slide out drawer. Packaged in clear blister pack.



79276 Bit-Selector With Ball End Hex Inch Bits. Set Includes Magnetic 1/4" Bit Holder & The Following 8 Bits:

● Ball End Hex Inch: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	⚖️ lbs.
	.30



79246 Bit-Selector With Hex Metric Bits. Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:

● Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	⚖️ lbs.
	.32

79256 Bit-Selector With Hex Metric Bits. Set Includes Magnetic 1/4" Bit Holder & The Following 8 Bits:

● Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	⚖️ lbs.
	.30



79266 Bit-Selector With Security Hex Inch Bits. Set Includes Magnetic 1/4" Bit Holder & The Following 9 Bits:

● Hex Inch: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	⚖️ lbs.
	.31

Screw Holding



MagicRing



71399 Bit-Selector With Metric & Inch MagicRing Insert 1/4" Bits

Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:

● No Ball End	⚖️ lbs.
	.46
Hex Metric: 3.0, 4.0, 5.0, 6.0mm	
Hex Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	

Wiha MagicRing Insert Bits

Screw Holding Hex Bits



713 MagicRing Metric Insert Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.
71304	3.0	25	1	.01
71307	4.0	25	1	.01
71310	5.0	25	1	.01
71311	6.0	25	1	.01

713 MagicRing Inch Insert Bits, 1/4"

Item No.	Inch	mm	pkg.	lbs.
71343	1/8	25	1	.01
71346	9/64	25	1	.01
71349	5/32	25	1	.01
71352	3/16	25	1	.01
71354	7/32	25	1	.01
71358	1/4	25	1	.01



Wiha MagicRing Power Bits

Screw Holding Hex Bits



743 MagicRing Metric Power Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.
74301	3.0	50	1	.02
74305	4.0	50	1	.02
74307	5.0	50	1	.03
74319	6.0	50	1	.03

743 MagicRing Inch Power Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.
74369	1/8	50	1	.02
74371	9/64	50	1	.02
74373	5/32	50	1	.02
74375	3/16	50	1	.03
74377	7/32	50	1	.03
74379	1/4	50	1	.03



Wiha XSelector Bit Sets

Compact size and easy bit selection make the Wiha XSelector an ideal maintenance tool

Easy bit access
with hinged
cover



XSelector Pocket Sized
3-1/8" x 2-1/8" x 1/2"

Sets include Clicfix quick
release holder

794 Sets XSelector Bit Sets

These handy sets include 10 hardened bits of chrome-vanadium-molybdenum steel. 1/4" Quick Release holder can be used in power tools. Quick bit access through integrated bit-clamp.


[SHOP](#)

79446 XSelector Bit Set With Hex Inch Bits

Set Includes Quick Release Holder
and the following 10 bits:

lbs.
.27

Hex Inch: 1/16, 5/64, 3/32, 7/64,
1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Wiha Security Hex Inch & Metric PokitPaks


[SHOP](#)

71998 PokitPak - Security Hex Inch Insert Bits In Molded Case - Set includes 6 - 1/4" Insert Bits

Hex Inch Security Hex:
3/32, 7/64, 1/8, 9/64, 5/32, 3/16"

lbs.
.12


[SHOP](#)

71995 PokitPak - Security Hex Insert Bits In Molded Case - Set includes 6 - 1/4" Insert Bits

Metric Security Hex:
2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm

lbs.
.31

Wiha Power Bit Belt Packs


[SHOP](#)


74986 Power Bit Belt Pack With Inch & Metric Hex Bits

Set includes the following 10 bits:

Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

lbs.
.34

Metric: 3.0, 4.0, 5.0, 6.0mm



Screw Holding
Hex Bits


[SHOP](#)


74989 Power Bit Belt Pack With Screw Holding Hex MagicRing Bits

Set includes the following 10 bits:


Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

lbs.
.34

Metric: 3.0, 4.0, 5.0, 6.0mm



Screw Holding
Hex Bits

[SHOP](#)


74999 Power Bit Belt Pack With Screw Holding Inch & Metric Ball End Hex MagicRing Bits

Set includes the following 10 bits:

Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

lbs.
.37

Metric: 3.0, 4.0, 5.0, 6.0mm

Wiha Security Hex Inch Multi Bit Set


[SHOP](#)

38014 Security Hex Inch Multi-Bit Screwdriver, 6 Pc. Set

With Wiha Powerhandle & CVM steel, hardened shaft.

Set includes the following 1/4" bits:

Security Hex: 3/32, 1/8, 5/32, 3/16, 7/32"

lbs.
.39

Hex Bits

The ideal multi-purpose bits for all around quality & performance

Made in Germany - Production Quality

Highly resistant to wear and tear for a long tool life



Impact resistant modified CVM, tool steel, hardened

Suitable for all applications for both manual & machine Hardness HRC 59-61



713 Hex Inch Insert Bits, 1/4"

Item	No.	Inch	mm	pkg.	lbs.
71329	.050	25	10	.12	
71326	1/16	25	10	.12	
71328	5/64	25	10	.12	
71330	3/32	25	10	.12	
71333	7/64	25	10	.12	
71336	1/8	25	10	.12	
71339	9/64	25	10	.12	
71342	5/32	25	10	.12	
71345	3/16	25	10	.13	
71348	7/32	25	10	.13	
71351	1/4	25	10	.13	
71353	5/16	25	10	.20	
71356	3/8	25	10	.25	



713 Hex Metric Insert Bits, 1/4"

Item	No.	mm	mm	pkg.	lbs.
71303	1.5	25	10	.12	
71306	2.0	25	10	.12	
71308	2.5	25	10	.12	
71309	3.0	25	10	.12	
71312	4.0	25	10	.12	
71315	5.0	25	10	.14	
71318	6.0	25	10	.14	
71321	8.0	25	10	.20	
71324	10.0	25	10	.27	

725 Hex Metric Insert Contractor Grade, 1/4"

Item	No.	Size	mm	pkg.	lbs.
72582	2.0	25	30 pc	.85	
72583	2.5	25	30 pc	.85	
72584	3.0	25	30 pc	.85	
72585	4.0	25	30 pc	.85	
72586	5.0	25	30 pc	.85	
72587	6.0	25	30 pc	.85	

Wiha Hex Inch & Metric Insert Bit Packs, 1"



713 Hex Inch Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	No.	Inch	mm	lbs.
71359	.050	25	.03	
71360	1/16	25	.03	
71361	5/64	25	.03	
71362	3/32	25	.03	
71363	7/64	25	.03	
71364	1/8	25	.03	
71365	9/64	25	.03	
71366	5/32	25	.04	
71367	3/16	25	.04	
71368	7/32	25	.04	
71369	1/4	25	.04	
71373	5/16	25	.05	
71387	3/8	25	.06	

733 Hex Metric Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	No.	mm	mm	lbs.
73301	1.5	25	.03	
73302	2.0	25	.03	
73303	2.5	25	.03	
73304	3.0	25	.03	
73305	4.0	25	.03	
73306	5.0	25	.03	
73307	6.0	25	.04	
73308	8.0	25	.05	
73309	10.0	25	.06	



71396 Hex Inch Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71396 Set includes the following bits:

Hex Inch:	1/16, 3/32, 1/8, 5/32
wt. .13	3/16, 1/4" x 1" (25mm)

71397 Hex Metric Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71397 Set includes the following bits:

Hex Metric:	2.0, 2.5, 3.0, 4.0, 5.0, 6.0
wt. .21	

Wiha Security Hex Insert Bits



719 Security Hex In Insert Bits, 1/4"

Item	No.	Inch	mm	pkg.	lbs.
71930	5/64	25	10	.12	
71932	3/32	25	10	.12	
71934	7/64	25	10	.12	
71936	1/8	25	10	.12	
71938	9/64	25	10	.12	
71940	5/32	25	10	.12	
71955	3/16	25	10	.13	
71956	7/32	25	10	.14	
71960	1/4	25	10	.15	



719 Security Hex Metric Insert Bits, 1/4"

Item	No.	mm	mm	pkg.	lbs.
71939	2.0	25	10	.12	
71941	2.5	25	10	.12	
71942	3.0	25	10	.12	
71943	4.0	25	10	.12	
71944	5.0	25	10	.15	
71945	6.0	25	10	.15	
71946	8.0	25	10	.20	



719 Security Hex Inch Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	No.	Inch	mm	lbs.
71970	5/64	25	.03	
71971	3/32	25	.03	
71972	7/64	25	.03	
71973	1/8	25	.03	
71974	9/64	25	.03	
71975	5/32	25	.03	
71976	3/16	25	.04	
71977	7/32	25	.04	
71978	1/4	25	.04	

719 Security Hex Metric Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	No.	mm	mm	lbs.
71979	2.0	25	.03	
71980	2.5	25	.03	
71981	3.0	25	.03	
71982	4.0	25	.03	
71983	5.0	25	.04	
71984	6.0	25	.04	
71985	8.0	25	.05	

Wiha Hex Inch & Metric Power Bits



743 Hex Inch Power Bits

1/4" Hex Drive, Length 2.0"/50mm

Item				
No.	Inch	mm	pkg.	lbs.
74311	3/32	50	10	.30
74312	7/64	50	10	.30
74313	1/8	50	10	.30
74314	9/64	50	10	.30
74315	5/32	50	10	.30
74316	3/16	50	10	.30
74317	7/32	50	10	.30
74318	1/4	50	10	.30



743 Hex Metric Power Bits

1/4" Hex Drive, Length 2.0"/50mm

Item				
No.	mm	mm	pkg.	lbs.
74325	2.5	50	10	.25
74330	3.0	50	10	.25
74340	4.0	50	10	.25
74350	5.0	50	10	.25
74360	6.0	50	10	.25
74380	8.0	50	10	.38



743 Hex Inch Power Bit Packs, 2"

Item			
No.	Inch	mm	lbs.
74381	3/32	50	.07
74382	7/64	50	.07
74383	1/8	50	.07
74384	9/64	50	.07
74385	5/32	50	.07
74386	3/16	50	.07
74387	7/32	50	.07
74388	1/4	50	.07

743 Hex Metric Power Bit Packs, 2"

Item				
No.	mm	mm	lbs.	
74361	2.5	50	.07	
74362	3.0	50	.07	
74363	4.0	50	.07	
74364	5.0	50	.07	
74365	6.0	50	.07	
74366	8.0	50	.09	



743 Hex Inch Power Bits

1/4" Hex Drive, Length 2.75"/70mm

Item				
No.	Inch	mm	pkg.	lbs.
74341	5/64	70	1	.36
74342	3/32	70	1	.36
74343	7/64	70	1	.36
74344	1/8	70	1	.36
74345	9/64	70	1	.36
74346	5/32	70	1	.36
74347	3/16	70	1	.36
74348	7/32	70	1	.36
74349	1/4	70	1	.36



743 Hex Metric Power Bits

1/4" Hex Drive, Length 2.75"/70mm

Item				
No.	mm	mm	pkg.	lbs.
74351	2.0	70	1	.36
74352	2.5	70	1	.36
74353	3.0	70	1	.36
74354	4.0	70	1	.36
74355	5.0	70	1	.36
74356	6.0	70	1	.36
74357	8.0	70	1	.36

Hex Metric Long Insert Bit On 5/16"



72388 Hex Metric Bit On 5/16" Stock

Item					
No.	mm	mm	pkg.	lbs.	
72388	12.0	75	10	.14	

Stainless Steel Hex Metric Bits



701 Stainless Steel Hex Metric Insert Bits

Item			
No.	mm	mm	pkg.
70170	1.5	25	10
70171	2.0	25	10
70172	2.5	25	10
70173	3.0	25	10
70174	4.0	25	10
70175	5.0	25	10
70176	6.0	25	10

Wiha Ball End Hex Inch Insert Bits



717 Ball End Hex Inch Insert Bits, 1/4"

Item					
No.	Inch	mm	pkg.	lbs.	
71701	3/32	25	10	.12	
71702	7/64	25	10	.12	
71703	1/8	25	10	.12	
71704	9/64	25	10	.12	
71705	5/32	25	10	.12	
71706	3/16	25	10	.13	
71707	7/32	25	10	.13	
71708	1/4	25	10	.13	



717 Ball End Hex Inch Insert Bit Packs, 1"

Item			
No.	Inch	mm	lbs.
71711	3/32	25	.03
71712	7/64	25	.03
71713	1/8	25	.03
71714	9/64	25	.03
71715	5/32	25	.04
71716	3/16	25	.04
71717	7/32	25	.04
71718	1/4	25	.04

Ball End Hex Metric Power Bits



2 pc. bit pack!

717 Ball End Hex Metric Power Bits

1/4" Hex Drive, Length 1.5"/38mm

Item			
No.	mm	mm	pkg.
71719	1.5	38	1
71720	2.0	38	1
71721	2.5	38	1
71722	3.0	38	1
71723	4.0	38	1
71724	5.0	38	1
71725	6.0	38	1

Wiha Terminator Hex Inch & Metric Impact Bits - Insert & Power

**Up To 30X
Performance Over
Standard
Screwdriver Bits**



Dual material
impact absorbing
torsion zone

Impact rated bits for long life in impact applications

Provide up to 30 times impact performance over standard bits

Standard 1/4" drive - No special adaptor required

Wiha enhanced bi-material torsion zone

Precision machined exact fit tips

Wiha exclusive CVM tool steel

Guaranteed to out perform impact imposters



765 Hex Inch Terminator Impact Bits, 1/4" Insert - 10 bit pack

Item No.	Inch	mm	pkg.	SHOP
76530	1/8	29	10	
76531	9/64	29	10	
76532	5/32	29	10	
76533	3/16	29	10	
76534	7/32	29	10	
76535	1/4	29	10	

768 Hex Inch Terminator Impact Bits, 1/4" Insert - 2 bit pack

Item No.	Inch	mm	pkg.	SHOP
76830	1/8	29	2	
76831	9/64	29	2	
76832	5/32	29	2	
76833	3/16	29	2	
76834	7/32	29	2	
76835	1/4	29	2	



765 Hex Metric Terminator Impact Bits, 1/4" Insert - 10 bit pack

Item No.	Inch	mm	pkg.	SHOP
76523	3.0	29	10	
76524	4.0	29	10	
76525	5.0	29	10	
76526	6.0	29	10	

768 Hex Metric Terminator Impact Bits, 1/4" Insert - 2 bit pack

Item No.	Inch	mm	pkg.	SHOP
76823	3.0	29	2	
76824	4.0	29	2	
76825	5.0	29	2	
76826	6.0	29	2	



765 Hex Inch Terminator Impact Bits, 1/4" Power - 10 bit pack

Item No.	Inch	mm	pkg.	SHOP
76570	1/8	49	10	
76571	9/64	49	10	
76572	5/32	49	10	
76573	3/16	49	10	
76574	7/32	49	10	
76575	1/4	49	10	



768 Hex Inch Terminator Impact Bits, 1/4" Power - 2 bit pack

Item No.	Inch	mm	pkg.	SHOP
76870	1/8	49	2	
76871	9/64	49	2	
76872	5/32	49	2	
76873	3/16	49	2	
76874	7/32	49	2	
76875	1/4	49	2	



765 Hex Metric Terminator Impact Bits, 1/4" Power - 10 bit pack

Item No.	Inch	mm	pkg.	SHOP
76563	3.0	49	10	
76564	4.0	49	10	
76565	5.0	49	10	
76566	6.0	49	10	



768 Hex Metric Terminator Impact Bits, 1/4" Power - 2 bit pack

Item No.	Inch	mm	pkg.	SHOP
76863	3.0	49	2	
76864	4.0	49	2	
76865	5.0	49	2	
76866	6.0	49	2	



76894 7 Pc. Bit Buddy Set With Terminator Impact Power Bits - 49mm


76894 Set includes the following bits:

- Hex Inch: 5/32, 3/16, 7/32, 1/4"
- Hex Metric: 4, 5, 6mm



91313 Empty Bit Buddy Case Holds
Terminator Impact Power Bits
91313 Holds 7 Impact Bits

1/4" Drive Insert & Power Bits



**Up To 30X Performance
Over Standard Screwdriver Bits**



76893 7 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76893 Set includes the following bits:

- Hex Inch: 5/32, 3/16, 7/32, 1/4"
- Hex Metric: 4, 5, 6mm



91247 Empty Bit Buddy Case Holds
Terminator Impact Insert Bits
91247 Holds 7 Impact Bits

Wiha Bit Holders

Quick Release



714 ClicFix Bit Holder, Magnetic, For Insert Bits

Item No.	Size	Size	mm	Inch
71490	1/4"	1/4"	60	2.4
71491	1/4"	1/4"	75	2.9

Quick Release



714 CentroFix Bit Holder For Power Bits

Item No.	Size	Size	mm	Inch
71480	1/4"	1/4"	60	2.3

Wiha Impact Bit Holding Sockets



720 Impact Bit Holding Socket With Retaining Ring

For 1/4" drive bits.

Item No.	Bit	mm	Drive	lbs.
72001	1/4	25	1/4"	.05
72002	1/4	30	3/8"	.10
72003	1/4	35	1/2"	.21

72090 3 Piece Bit Holding Socket Set

for use with 1/4" Insert bits

Drive:	lbs.
1/4", 3/8", 1/2"	.40

Long Blade Sockets & Sets



771 Hex Metric Sockets

1/4" Drive 6" Long Bit Socket

Item No.	Size	Inch	lbs.
77140	2.5	6.0	.13
77142	3.0	6.0	.13
77144	4.0	6.0	.13
77146	5.0	6.0	.13
77148	6.0	6.0	.13

77192 5 Pc. Hex Metric Socket Blade Set

Metric: 2.5, 3.0, 4.0, 5.0, 6.0mm

lbs. .70



Long Blade Sockets & Sets



771 Hex Inch Sockets 1/4" Drive 6" Long Bit Socket

Item No.	Size	Inch	lbs.
77128	3/32	6.0	.12
77130	7/64	6.0	.12
77132	1/8	6.0	.12
77134	9/64	6.0	.12
77136	5/32	6.0	.12
77138	3/16	6.0	.12
77139	7/32	6.0	.12
77141	1/4	6.0	.12

77191 8 Piece Hex Inch Socket Blade Set

Inch: 3/32, 7/64, 1/8, 9/64, 5/32,

3/16, 7/32, 1/4" wt. .97



771 Hex Inch Sockets 3/8" Drive 6" Long Bit Socket

Item No.	Size	Inch	lbs.
77165	3/32	6.0	.18
77167	7/64	6.0	.18
77169	1/8	6.0	.18
77171	9/64	6.0	.18
77173	5/32	6.0	.18
77175	3/16	6.0	.18
77177	7/32	6.0	.18
77179	1/4	6.0	.18



77198 22 Piece Hex & TORX® Long Blade Socket Set, 1/4" Drive

Inch Hex: 3/32, 7/64, 1/8, 9/64, 5/32,

3/16, 7/32, 1/4"

Metric Hex: 2.5, 3.0, 4.0, 5.0, 6.0mm

TORX®: T8, T9, T10, T15, T20, T25, T27, T30, T40

lbs. 2.82

Wiha Sockets



713 Hex Sockets 1/4" Square drive socket.

Replaceable bit. 1/4" bits CVM steel.

Item No.	Inch	mm	lbs.
71371	1/16	38	.05
71370	5/64	38	.05
71372	3/32	38	.05
71374	7/64	38	.05
71376	1/8	38	.05
71378	9/64	38	.05
71380	5/32	38	.05
71382	3/16	38	.05
71384	7/32	38	.05
71386	1/4	38	.05

Wiha Sockets


[SHOP](#)

713 Hex Sockets 3/8" Square drive socket.

Replaceable bit. 1/4" bits CVM tool steel.

Item				
No.	Inch	mm	lbs.	
71375	1/8	42	.09	
71377	9/64	42	.09	
71379	5/32	42	.09	
71381	3/16	42	.09	
71383	7/32	42	.09	
71385	1/4	42	.09	
71388	5/16	42	.10	
71390	3/8	42	.10	


[SHOP](#)

713 Hex Metric Sockets 1/4" Square drive

socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	mm	mm	lbs.	
71301	1.5	38	.04	
71302	2.0	38	.04	
71305	2.5	38	.04	
71313	3.0	38	.04	
71314	4.0	38	.04	
71317	5.0	38	.05	
71319	6.0	38	.05	
71327	8.0	38	.05	
71340	10.0	38	.05	


[SHOP](#)

713 Hex Metric Sockets 3/8" Square drive socket.

Replaceable bit. 1/4" bits CVM steel.

Item				
No.	mm	mm	lbs.	
71300	2.0	42	.09	
71316	2.5	42	.09	
71341	3.0	42	.09	
71331	4.0	42	.09	
71323	5.0	42	.09	
71325	6.0	42	.09	
71320	8.0	42	.10	
71322	10.0	42	.11	


[SHOP](#)

713 Hex Metric Sockets 3/8" Square drive socket.

Replaceable bit. 5/16" bits CVM steel.

Item				
No.	mm	mm	lbs.	
71332	12.0	75	.22	



Replaceable bit

[SHOP](#)

761 Security Hex Inch Sockets

3/8" Square drive socket. 1/4" bits CVM steel.

Item				
No.	Inch	mm	lbs.	
76164	5/64	42	.09	
76165	3/32	42	.09	
76166	7/64	42	.09	
76167	1/8	42	.09	
76168	9/64	42	.09	
76169	5/32	42	.09	
76170	3/16	42	.09	
76171	7/32	42	.09	
76172	1/4	42	.09	

761 Security Hex Metric Sockets

3/8" Square drive socket. 1/4" bits CVM steel.

Item				
No.	mm	mm	lbs.	
76132	2.0	42	.09	
76133	2.5	42	.09	
76134	3.0	42	.09	
76135	4.0	42	.09	
76136	5.0	42	.09	
76137	6.0	42	.09	
76138	8.0	42	.09	


[SHOP](#)

717 Ball End Hex Sockets 1/4" Square drive socket. Replaceable bit.

1/4" bits CVM steel.

Item				
No.	Inch	mm	lbs.	
71761	3/32	38	.09	
71762	7/64	38	.09	
71763	1/8	38	.09	
71764	9/64	38	.09	
71765	5/32	38	.09	
71766	3/16	38	.09	
71767	7/32	38	.09	
71768	1/4	38	.09	


[SHOP](#)


717 Ball End Hex Metric Sockets

1/4" Square drive socket. Replaceable bit.

1/4" bits CVM steel.

Item				
No.	mm	mm	lbs.	
71771	1.5	51	.11	
71772	2.0	51	.11	
71773	2.5	51	.11	
71774	3.0	51	.11	
71775	4.0	51	.11	
71776	5.0	51	.12	
71777	6.0	51	.12	

Wiha Socket Sets On Molded Rails



Bits CVM
tool steel




71391 10 Piece Hex Inch Socket Set

1/4" Square drive replaceable bit socket.

Item No. 

71391 lbs. Set includes the following:

.48 1/16, 5/64, 3/32, 7/64, 1/8
9/64, 5/32, 3/16, 7/32, 1/4"



Bits CVM
tool steel




71798 8 Pc. Ball End Hex Inch Socket Set

1/4" Square Drive Replaceable Bit Socket.

Item No. 

71798 lbs. Set includes the following:

.72 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"



Bits CVM
tool steel




71398 7 Pc. Ball End Hex Inch Socket Set

1/4" Square Drive Replaceable Bit Socket.

Item No. 

71398 lbs. Set includes the following:

.48 3/16, 7/32, 1/4"



Bits CVM
tool steel



71797 7 Pc. Ball End Hex Metric Sockets

1/4" Square Drive Replaceable Bit Socket.

Item No. 

71797 lbs. Set includes the following:

.72 3.0, 4.0, 5.0, 6.0mm



Bits CVM
tool steel



71392 8 Piece Hex Inch Socket Set

3/8" Square Drive Replaceable Bit Socket.

Item No. 

71392 lbs. Set includes the following:

.78 1/4, 5/16, 3/8"

Bits CVM
tool steel



71393 5 Piece Hex Inch Socket Set

3/8" Square Drive Replaceable Bit Socket.

Item No. 

71393 lbs. Set includes the following:

.54 1/4, 5/16, 3/8"

Bits CVM
tool steel



71394 5 Piece Hex Metric Socket Set

3/8" Square Drive Replaceable Bit Socket.

Item No. 

71394 lbs. Set includes the following:

.56 8.0, 10.0mm

Bits CVM
tool steel




71996 9 Piece Hex Metric Socket Set

1/4" & 3/8" Sq. Dr. Replaceable Bit Socket

Item No. 

71996 lbs. Set includes the following:

.66 1/4": 1.5, 2.0, 2.5, 3.0, 4.0mm
3/8": 5.0, 6.0, 8.0, 10.0mm



Bits CVM
tool steel



71999 9 Pc. Security Hex Inch Socket Set

3/8" Square Drive Replaceable Bit Socket.

Item No. 

71999 lbs. Set includes the following:

.86 5/64, 3/32, 7/64, 1/8,
9/64, 5/32, 3/16, 7/32, 1/4"



Bits CVM
tool steel



71989 7 Pc. Security Hex Metric Sockets

3/8" Square Drive Replaceable Bit Socket.

Item No. 

71989 lbs. Set includes the following:

.74 2.0, 2.5, 3.0, 4.0, 5.0,
6.0, 8.0mm


Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page
13650 22	26427 29	27545 26	28547 24	33417 13	35104 19
13651 22	26430 28	27547 26	28548 24	33418 12	35108 19
13652 22	26431 29	27549 26	28549 24	33419 13	35112 19
13653 22	26436 29	27590 26	28550 24	33420 12	35116 19
13654 22	26439 29	27591 26	28551 24	33421 13	35120 19
13655 22	26440 28	28000 30	28552 24	33422 12	35124 19
13656 22	26441 27	28001 30	28553 24	33423 13	35128 19
13657 22	26443 27	28003 29	28554 24	33424 12	35132 19
13658 22	26445 27	28004 29	28555 24	33425 13	35136 19
13659 22	26447 27	28005 29	28556 24	33426 12	35140 19
13662 22	26449 27	28006 29	28557 24	33427 13	35143 19
13663 22	26455 27	28007 29	28558 24	33428 12	35144 19
13664 22	26457 27	28008 29	28559 24	33429 13	35145 19
13665 22	26459 27	28021 30	28560 24	33430 12	35146 19
13666 22	26461 27	28023 30	28587 24	33432 12	35147 19
13667 22	26463 27	28024 30	28588 24	33433 12	35150 19
13668 22	26465 27	28025 30	28916 25	33434 13	35152 19
13669 22	26467 27	28026 30	28917 25	33435 13	35153 19
13670 22	26490 29	28027 30	28918 25	33436 13	35155 19
13671 22	26491 28	28028 30	28919 25	33437 13	35156 19
13672 22	26493 27	28029 30	28920 25	33438 13	35159 19
13673 22	26499 29	28033 30	28921 25	33439 12	35162 19
13690 22	26900 30	28034 30	28922 25	33440 12	35165 19
13691 22	26901 30	28035 30	28923 25	33441 21	35168 19
13693 22	26913 30	28036 30	28924 25	33442 12	35171 19
13694 22	26914 30	28037 30	28931 25	33443 21	35174 19
26307 28	26915 30	28116 23	28933 25	33444 12	35175 19
26309 28	26916 30	28117 23	28935 25	33445 21	35176 19
26313 28	26917 30	28118 23	28937 25	33446 12	35177 19
26315 28	26918 30	28119 23	28938 25	33447 21	35178 19
26316 28	26919 30	28120 23	28939 25	33448 12	35179 19
26320 28	26920 30	28122 23	28940 25	33449 21	35180 19
26323 28	26921 30	28123 23	31805 22	33450 12	35191 19
26325 28	26923 30	28124 23	31807 22	33452 12	35192 19
26327 28	26924 30	28149 23	31809 22	33453 13	35193 19
26330 28	26925 30	28150 23	31811 22	33454 12	35194 19
26331 28	26926 30	28151 23	31813 22	33456 13	35195 17
26333 28	26927 30	28189 23	31815 22	33458 12	35196 17
26336 28	26928 30	28298 32	31817 22	33459 13	35197 17
26340 28	26929 30	28299 32	31890 22	33462 13	35198 17
26341 27	26932 30	28486 23	32302 21	33465 13	35200 18
26343 27	26933 30	28487 23	32303 21	33468 13	35201 18
26345 27	26934 30	28488 23	32304 21	33471 13	35202 18
26347 27	26935 30	28501 24	32305 21	33474 13	35203 18
26349 27	26936 30	28502 24	32306 21	33477 13	35204 18
26351 27	26937 30	28503 24	32308 21	33478 21	35205 18
26353 27	26961 29	28504 24	32366 21	33480 13	35206 18
26363 27	26989 30	28505 24	33401 13	33481 21	35208 18
26367 27	26999 30	28506 24	33402 13	33482 21	35210 18
26369 27	27505 26	28507 24	33403 13	33483 21	35211 18
26371 27	27507 26	28508 24	33404 13	33484 13	35212 18
26390 28	27509 26	28509 24	33405 13	33485 21	35213 18
26391 28	27510 26	28511 24	33406 13	33486 21	35214 18
26392 27	27513 26	28513 24	33407 13	33487 21	35215 18
26393 27	27515 26	28515 24	33408 13	33488 13	35216 18
26399 28	27520 26	28517 24	33409 13	33489 12	35217 18
26413 28	27525 26	28518 24	33410 13	33490 21	35218 18
26415 28	27530 26	28519 24	33411 13	33492 13	35219 18
26416 29	27535 26	28521 24	33412 13	33493 13	35220 18
26419 29	27537 26	28523 24	33413 13	33494 12	35221 18
26420 28	27539 26	28525 24	33414 13	33496 12	35222 18
26423 29	27541 26	28545 24	33415 13	33498 12	35223 18
26425 28	27543 26	28546 24	33416 13	33499 12	35224 18

Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page
35225 18	35318 20	36909 9	36990 8	54002 11	66920 4
35226 18	35319 20	36910 9	36991 8	54003 11	66922 6
35227 18	35320 20	36911 7	36992 8	54004 11	66924 4
35228 18	35321 20	36912 8	36993 8	54005 11	66926 6
35230 18	35330 20	36913 7	36995 7	54006 11	66928 4
35231 18	35331 20	36914 7	36996 17	54007 11	66930 6
35232 18	35332 20	36915 7	36997 17	54008 11	66936 4
35233 18	35333 20	36916 8	36998 6	54009 11	66937 6
35234 18	35334 20	36917 7	36999 9	54010 11	66938 6
35235 18	35335 20	36918 7	38014 34	54012 10	66944 4
35236 18	35336 20	36919 7	38056 32	54014 10	66945 4
35237 18	35337 20	36920 8	38057 32	54016 10	66946 4
35238 18	35338 20	36921 7	38058 32	54018 10	66947 4
35239 18	35339 20	36922 7	46701 9	54020 11	66950 4
35240 18	35340 20	36923 9	46702 16	54022 10	66952 4
35241 18	35341 20	36924 8	46703 9	54024 10	66953 4
35242 18	35342 20	36925 9	46704 16	54025 11	66955 4
35243 18	35343 20	36926 9	46705 9	54030 11	66956 4
35244 18	35345 20	36927 9	46706 16	54040 10	66959 4
35245 18	35346 20	36928 8	46707 9	54042 11	66962 4
35246 18	35347 20	36929 9	46708 16	54050 10	66965 4
35247 18	35348 20	36930 9	46709 9	54052 11	66968 4
35248 18	35390 20	36931 9	46710 16	54060 10	66971 4
35249 18	35391 20	36932 9	46711 9	54062 11	66982 7
35250 18	35392 20	36933 9	46712 16	54080 10	66988 7
35251 18	35393 20	36934 9	46713 9	54082 11	66990 4
35252 18	36696 7	36935 9	46714 16	54086 10	66991 4
35253 18	36710 14	36936 8	46715 16	54088 11	66992 4
35254 18	36713 14	36937 9	46716 16	54090 10	66993 6
35255 18	36715 15	36938 9	46717 9	54091 10	66994 6
35256 18	36716 14	36939 9	46718 16	54092 11	66995 6
35257 18	36719 14	36940 6	46719 9	54094 11	66996 7
35258 18	36720 15	36941 6	46720 16	54095 11	66997 17
35259 18	36723 14	36942 6	46721 9	54097 11	66998 6
35260 18	36725 15	36943 6	46722 16	56901 5	70170 36
35261 18	36726 14	36944 8	46723 9	56902 5	70171 36
35270 18	36728 14	36945 8	46724 16	56903 5	70172 36
35280 18	36730 15	36946 8	46725 16	56904 5	70173 36
35282 18	36732 14	36947 8	46726 16	56905 5	70174 36
35284 18	36734 14	36948 6	46727 9	56906 5	70175 36
35285 18	36736 14	36949 6	46728 16	56907 5	70176 36
35286 18	36738 14	36950 8	46730 16	56908 5	71300 39
35288 18	36740 15	36951 6	46731 9	56909 5	71301 39
35290 18	36742 14	36952 8	46732 9	56910 5	71302 39
35291 18	36744 14	36953 8	46733 9	56911 5	71303 35
35295 18	36750 15	36954 6	46734 9	56912 5	71304 33
35297 18	36760 15	36955 8	46735 9	56913 5	71305 39
35301 20	36780 15	36956 8	46736 9	56914 5	71306 35
35302 20	36786 15	36957 6	46737 9	56915 5	71307 33
35303 20	36790 15	36958 6	46738 9	56916 5	71308 35
35304 20	36791 14	36959 8	46739 9	56917 5	71309 35
35305 20	36792 15	36960 6	46740 16	56918 5	71310 33
35306 20	36793 14	36961 6	46741 9	56919 5	71311 33
35307 20	36794 14	36962 8	46750 16	56920 5	71312 35
35308 20	36900 9	36963 6	46760 16	56921 5	71313 39
35309 20	36901 9	36965 8	46780 16	56922 5	71314 39
35310 20	36902 9	36966 9	46786 16	62994 29	71315 35
35311 20	36903 9	36968 8	46793 16	62995 29	71316 39
35312 20	36904 8	36971 8	46794 16	66904 4,6	71317 39
35313 20	36905 9	36986 5	46796 16	66908 4,6	71318 35
35314 20	36906 9	36987 5	46797 16	66912 4,6	71319 39
35316 20	36907 9	36988 7	46799 16	66916 4	71320 39
35317 20	36908 8	36989 9	54001 11	66918 6	71321 35

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
71322	39	71396	35	71970	35	74348	36	75900	31	77132	38
71323	39	71397	35	71971	35	74349	36	75901	31	77134	38
71324	35	71398	40	71972	35	74350	36	75983	31	77136	38
71325	39	71399	33	71973	35	74351	36	76132	39	77138	38
71326	35	71480	38	71974	35	74352	36	76133	39	77139	38
71327	39	71490	38	71975	35	74353	36	76134	39	77140	38
71328	35	71491	38	71976	35	74354	36	76135	39	77141	38
71329	35	71701	36	71977	35	74355	36	76136	39	77142	38
71330	35	71702	36	71978	35	74356	36	76137	39	77144	38
71331	39	71703	36	71979	35	74357	36	76138	39	77146	38
71332	39	71704	36	71980	35	74360	36	76164	39	77148	38
71333	35	71705	36	71981	35	74361	36	76165	39	77165	38
71336	35	71706	36	71982	35	74362	36	76166	39	77167	38
71339	35	71707	36	71983	35	74363	36	76167	39	77169	38
71340	39	71708	36	71984	35	74364	36	76168	39	77171	38
71341	39	71711	36	71985	35	74365	36	76169	39	77173	38
71342	35	71712	36	71989	40	74366	36	76170	39	77175	38
71343	33	71713	36	71995	34	74369	33	76171	39	77177	38
71345	35	71714	36	71996	40	74371	33	76172	39	77179	38
71346	33	71715	36	71998	34	74373	33	76523	37	77191	38
71348	35	71716	36	71999	40	74375	33	76524	37	77192	38
71349	33	71717	36	72001	38	74377	33	76525	37	77198	38
71351	35	71718	36	72002	38	74379	33	76526	37	79246	33
71352	33	71719	36	72003	38	74380	36	76530	37	79256	33
71353	35	71720	36	72090	38	74381	36	76531	37	79266	33
71354	33	71721	36	72388	36	74382	36	76532	37	79276	33
71356	35	71722	36	72582	35	74383	36	76533	37	79446	34
71358	33	71723	36	72583	35	74384	36	76534	37	91118	26
71359	35	71724	36	72584	35	74385	36	76535	37	91247	37
71360	35	71725	36	72585	35	74386	36	76563	37	91313	37
71361	35	71761	39	72586	35	74387	36	76564	37		
71362	35	71762	39	72587	35	74388	36	76565	37		
71363	35	71763	39	73301	35	74986	34	76566	37		
71364	35	71764	39	73302	35	74989	34	76570	37		
71365	35	71765	39	73303	35	74999	34	76571	37		
71366	35	71766	39	73304	35	75096	31	76572	37		
71367	35	71767	39	73305	35	75307	31	76573	37		
71368	35	71768	39	73306	35	75309	31	76574	37		
71369	35	71771	39	73307	35	75313	31	76575	37		
71370	38	71772	39	73308	35	75315	31	76823	37		
71371	38	71773	39	73309	35	75320	31	76824	37		
71372	38	71774	39	74301	33	75322	31	76825	37		
71373	35	71775	39	74305	33	75325	31	76826	37		
71374	38	71776	39	74307	33	75327	31	76830	37		
71375	39	71777	39	74311	36	75330	31	76831	37		
71376	38	71797	40	74312	36	75332	31	76832	37		
71377	39	71798	40	74313	36	75340	31	76833	37		
71378	38	71930	35	74314	36	75342	31	76834	37		
71379	39	71932	35	74315	36	75350	31	76835	37		
71380	38	71934	35	74316	36	75352	31	76863	37		
71381	39	71936	35	74317	36	75354	31	76864	37		
71382	38	71938	35	74318	36	75356	31	76865	37		
71383	39	71939	35	74319	33	75358	31	76866	37		
71384	38	71940	35	74325	36	75360	31	76870	37		
71385	39	71941	35	74330	36	75362	31	76871	37		
71386	38	71942	35	74340	36	75364	31	76872	37		
71387	35	71943	35	74341	36	75366	31	76873	37		
71388	39	71944	35	74342	36	75368	31	76874	37		
71390	39	71945	35	74343	36	75370	31	76875	37		
71391	40	71946	35	74344	36	75372	31	76893	37		
71392	40	71955	35	74345	36	75395	31	76894	37		
71393	40	71956	35	74346	36	75800	31	77128	38		
71394	40	71960	35	74347	36	75801	31	77130	38		

(800) 494-6104
 fax: (800) 494-7456
 email: cservice@wihatools.com
 www.wihatools.com

**SEE OUR GREAT
 WEB SPECIALS!**



Wiha Quality Tools

1348 Dundas Circle
 Monticello, MN 55362
 tel: 763.295.6591
 fax: 763.295.6598

Wiha Tools Canada Ltd.

www.wihatools.ca
 Brampton, ONT L6T 4X4
 tel: 866.494.0096 or 763.295.6591
 fax: 763.295.6598

To:


Catalog Item No. 99934.wo
 version - 5/15/14

Subject to change
 without notice

©2014 Willi Hahn Corporation




91330.wo - Tooling Catalog



99004.wo - Shop Tools Catalog



99914.wo - TORX Catalog



99002.wo - Screwdrivers Catalog



99919.wo - Insulated Catalog



99001.wo - TorqueControl Catalog



99945.wo - ESD Safe Catalog



99951.wo - Bits Catalog



99977.wo - Pliers/Crimpers Catalog



99006.wo - Tech Tools Catalog