


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.		ALL RIGHTS RESERVED.	
DESCRIPTION	MATERIAL	FINISH	
GROMMET	FLUOROSILICONE 40/50 BLEND PER MIL-R-25988	COLOR: BLUE	
SPLICE ASSEMBLY HOUSING	EPOXY	COLOR: BLACK	
CONTACT FEMALE SOCKET	BERYLLIUM COPPER PER QQ-C-533	GOLD PLATE PER MIL-G-45204	
CLIP CONTACT RETAINING	BERYLLIUM COPPER PER QQ-C-533 OR STAINLESS STEEL PER QQ-S-766	NONE	
SHRINK TUBE	PER MIL-1-23053/8	COLOR TRANSPARENT	
CONTACTS 	PER M39029/1-102	GOLD PLATE PER MIL-G-45204	

LOC		DIST		REVISIONS				
P	LYR	DESCRIPTION			DATE	DWN	APVD	
A		REV PER OG3D-0450-00			5-01	CT	DM	



-  MARK WIRE SPLICE WITH *AMP*, AMP PART NO. AND DATE CODE .060 MINIMUM HIGH CHARACTERS AT APPROXIMATE AREA SHOWN.
-  A QUANTITY OF 4 CONTACTS ARE SUPPLIED WITH WIRE SPLICE.
-  MARK WIRE SPLICE BUSSING ARRANGEMENT BOTH ENDS AS SHOWN.

1.522	.13	.275	.400		CLASS C	22	1-592582-5
1.522	.13	.275	.400		CLASS A	20	1-592582-4
1.522	.13	.275	.400		CLASS C	20	1-592582-3
1.922	.13	.300	.500		CLASS B	16	1-592582-2
1.922	.13	.300	.500		CLASS C	16	1-592582-1
1.552	.13	.275	.400		CLASS C	20	1-592582-0
1.552	.13	.275	.400		CLASS C	22	592582-9
1.552	.13	.275	.400		CLASS B	22	592582-8
1.552	.18	.275	.400		CLASS C	22	592582-7
1.992	.18	.300	.500		CLASS B	16	592582-6
1.992	.18	.300	.500		CLASS C	16	592582-5
1.992	.18	.300	.500		CLASS A	16	592582-4
1.552	.13	.275	.400		CLASS B	20	592582-3
1.552	.13	.275	.400		CLASS C	20	592582-2
1.552	.13	.275	.400		CLASS D	20	592582-1
L MAX	C	B MAX	A	REMARKS	MIL-T-81714 CLASS (A, B OR C)	SIZE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. C. THOMAS 11/99	AMP Incorporated Harrisburg Pa. 17105			
DIMENSIONS INCHES		OK D. MILLER 11/99	NAME D. MILLER			
TOLERANCES UNLESS OTHERWISE SPECIFIED		PRODUCT SPEC				
0 PLC ± -		APPLICATION SPEC				
1 PLC ± -		WEIGHT				
2 PLC ± -		CUSTOMER DRAWING				
3 PLC ± .005		SCALE 1:1				
4 PLC ± -		SHEET 1 OF 1				
ANGLES		REV				
FINISH		A1 00779 C-592582				