

T3¼ MINIATURE BAYONET BASE TRIO-LED LAMP

AC/DC OPERATION

WITH HALF WAVE RECTIFIER

PART NO.	COLOR	VOLTAGE V _{OP} [V] AC/DC	CURRENT I _{OP typ.} [mA] AC/DC	LUMI. INTENSITY LED **I _{V typ.} [mcd]	DOMINANT WAVELENGTH λ _D [nm]
WL-18620350	RED	24V	9/17	3 x 2800	630
WL-18620351	GREEN	24V	9/17	3 x 2600	525
WL-18620352	YELLOW	24V	9/17	3 x 700	589
WL-18620357	BLUE	24V	9/17	3 x 800	470
WL-1862035W3	WHITE CLEAR	24V	9/17	3 x 1900	*
WL-1862035W3D	WHITE DIFFUSED	24V	9/17	3 x 900	*
WL-18620450	RED	28V	9/17	3 x 2800	630
WL-18620451	GREEN	28V	9/17	3 x 2600	525
WL-18620452	YELLOW	28V	9/17	3 x 700	589
WL-18620457	BLUE	28V	9/17	3 x 800	470
WL-1862045W3	WHITE CLEAR	28V	9/17	3 x 1900	*
WL-1862045W3D	WHITE DIFFUSED	28V	9/17	3 x 900	*

*Chromaticity coordinates X=0.31 Y=.032

**Luminous intensity data of the used LEDs at: I_{OP} DC


NOTES

1. Storage temperature
T_{STG}: -25°C – +80°C
2. Ambient temperature
T_A: -20°C – +60°C
3. AC/DC operation
4. Voltage tolerance
V_{OP}: ±10%
5. Electro-optical ratings at
T_A=25°C
6. These Wamco LED lamps include a protection diode and can be used on DC and AC voltage. The typical light reduction on AC voltage is approx. 25%
7. Due to production tolerances, slight color variations may be detected within individual consignments
8. Base Type: BA9s

CERTIFICATIONS

RoHS
COMPLIANT

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in mm



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

