

- Locate Distributor

Current refinements (click to remove) Search Tips

Text Search: 'F5LE3-10GM1'

Your search criteria matched only one product, shown below

- Colour-specific keys mechanically and visually distinguish connections to prevent positive and negative unintentional insertion into unlike keyed or non-keyed ports and allows design flexibility and versatility for a more discrete network
- Factory terminated and 100% tested for insertion loss (all) and return loss (10Gig™ and SM). Assures high performance for increased up-time and lower cost of ownership
- Low smoke zero halogen meets IEC -60332 (LSZH) flame rating for standard compliant safety
- Singlemode endfaces UPC polished (55dB min. return loss) ensures a high quality endface for higher return loss to meet application requirements
- Every singlemode endface is 100% factory inspected in compliance with Telcordia GR-326-CORE, Issue 3 requirements to assure high performance
- Keyed LC 10Gig™ Patch Cords and Pigtails are tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10Gb/s for link lengths up to 300 meters for OM3 at 850nm to assure high performance and reliability
- Test data supplied with each patch cord and pigtail establishes a performance reference to

streamline maintenance and troubleshooting

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.

Additional keyed colors include the following: G- Violet, H- Aqua, J- Rose, K- Slate, L- Brown, P- White, Q- Charcoal, R- Lavender, S- Peach, T- Steel Blue, V- Maroon and W- Mint.

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.