

E8Y

Micropressure Sensor with Easy-to-Read Digital Display

- Repeat accuracy of $\pm 1\%$ FS (setting resolution: 0.01 kPa), high-precision pressure control available.
- Compact design (31 × 30 × 30 mm) saves mounting space.
- Easy-to-read red LED indicator.
- Analog current output models available (E8Y-A□Y).
- Pressure port Rc (PT) 1/8 models available (-R).
- EN and UL approved.



Ordering Information

Sensors

Pressure range *	Digital output	Linear output	Model
0 to 200 Pa	NPN open collector	---	E8Y-AR2C
0 to 500 Pa			E8Y-AR5C
0 to 2.00 kPa			E8Y-A2C
0 to 5.00 kPa			E8Y-A5C
0 to 200 Pa		4 to 20 mA	E8Y-AR2Y
0 to 2.00 kPa			E8Y-A2Y
0 to 5.00 kPa			E8Y-A5Y
0 to 5.00 kPa	PNP open collector		E8Y-A5B

Note: Order the optional E89-Y1 Panel-mounting Bracket.
A model number ending in -R indicates the pressure port is die-cast for Rc (PT) 1/8 models.

Accessories (Order Separately)

Panel Attachment Parts Set (For □36 and □45 Models)

Model
E89-Y1 *

* Includes the cover, guide, frame, and holder.

Pressure
Sensors

Sensing
Guide

Pressure
Sensors

Other
Information

E8F2

E8MS
/E8M

E8Y

E8Y-□-□

Ratings

Model		E8Y-AR2C	E8Y-AR5C	E8Y-A2C E8Y-A2C-R	E8Y-A5B E8Y-A5C E8Y-A5C-R	E8Y-AR2Y	E8Y-A2Y E8Y-A2Y-R	E8Y-A5Y E8Y-A5Y-R
Item								
Power supply voltage		12 to 24 VDC ±10% with a ripple (p-p) of 10% max.						
Current consumption		50 mA max.				75 mA max.		
Pressure type		Differential pressure						
Rated pressure range		0 to 200 Pa	0 to 500 Pa	0 to 2.00 kPa	0 to 5.00 kPa	0 to 200 Pa	0 to 2.00 kPa	0 to 5.00 kPa
Withstand pressure		5 kPa		50 kPa		5 kPa	5 kPa	
Applicable fluid		Non-corrosive gas and non-flammable gas						
Linear output	Output current	---	---	---	---	4 to 20 mA		
	Permissible load resistance	---	---	----	---	0 to 250 Ω		
	Precision	---	---	---	---	±2.5%FS	±1.0%FS	
	Linearity	---	---	---	---	±2.5%FS	±1.0%FS	
Digital output	Output form	NPN open collector (NO/NC) *						
	Load current	100 mA						
	Output applied voltage	30 VDC max.						
	Residual voltage	1.0 V max. with a load current of 100 mA or 0.4 V max. with a load current of 16 mA						
	Repeat accuracy	±2.5%FS	±1.0%FS			±2.5%FS	±1.0%FS	
Dis- play	Display	3-digit 7-segment red LED						
	Indicator lamp	Orange LED indicator (OUT1: lit when digital output is ON) Orange LED indicator (OUT2: lit when digital output is ON)						
Response speed		0.5 s max.						
Display accuracy		±1.0%FS						
Setting resolution		1 Pa		0.01 kPa		1 Pa	0.01 kPa	
Protection circuits		Reverse polarity protection, load short-circuit protection						
Ambient temperature		Operating: −10 to 55°C (with no icing)						
Ambient humidity		Operating: 25% to 85% (with no condensation)						
Storage temperature		−25 to 65°C						
Accessories		Mounting Brackets (A and B), Instruction manual						

* The E8Y-A5B provides a PNP open-collector (NO/NC) output.

Specifications

Temperature influence	E8Y-A2C/A5C: $\pm 3\%$ FS max. E8Y-AR5C: $\pm 6\%$ FS max. E8Y-AR2C: $\pm 10\%$ FS max.
Humidity influence	E8Y-A2C/A5C: $\pm 3\%$ FS max. E8Y-AR5C: $\pm 6\%$ FS max. E8Y-AR2C: $\pm 10\%$ FS max.
Degree of protection	IP40 (IEC)
Dielectric strength	1,000 VAC at 50/60 Hz for 1 minute
Insulation resistance	100 M Ω min. (at 500 VDC) between current-carrying parts and case
Vibration resistance	Destruction: 10 to 150 Hz, 0.75-mm single amplitude or 100 m/s ² , 4 times each for 8 min in X, Y and Z directions
Shock resistance	Destruction: 300 m/s ² 3 times each in X, Y and Z directions
Pressure port	4.5-dia resin pipe or Rc (PT) 1/8 taper screw (-R type)
Cable	Vinyl-insulated round cable 4 dia., Standard length: 2 m
Weight	Approx. 80 g

Pressure
Sensors

Sensing
Guide

Pressure
Sensors

Other
Information

E8F2


E8MS
/E8M

E8Y

E8Y-□-□

E8Y

Nomenclature



Display

- (1) Numerical value/menu indication**
Displays the measured pressure and some menu settings.
- (2) Unit**
Shows the measuring unit. Unit currently in use is illuminated.
- (3) OUT 1 indication LED**
In measurement mode, it lights when OUT 1 output is on. In setting mode, it flashes when OUT 1 is being set.
- (4) OUT 2 indication LED**
In measurement mode, it lights when OUT 2 output is on. In setting mode, it flashes when OUT 2 is being set.

Operation Key

- (5) ADJ**
In measurement mode, it adjusts the Zero Point.
In setting mode, it shifts to measurement mode.
- (6) MODE**
In measurement mode, it shifts to setting mode and selects the current setting or menu option.
- (7) UP/DOWN**
In measurement mode, pushing the DOWN key displays the ON and OFF points of OUT 1; pushing the UP key displays the ON and OFF points of OUT 2.
In setting mode, the UP and DOWN keys increase or decrease the numeric value, respectively, or scroll through the menu options.


Dimensions

(Unit: mm)

Sensors


Standard Port Type (Pressure Port: 4.5 dia.)

E8Y-AR5C
E8Y-AR2C
E8Y-A2C
E8Y-A5C
E8Y-A5B
E8Y-AR2Y
E8Y-A2Y
E8Y-A5Y




Die-case Port Type (Pressure port: Rc(PT)1/8)

E8Y-A2C-R
E8Y-A5C-R
E8Y-A2Y-R
E8Y-A5Y-R




Accessories (Provided)

Mounting Bracket A



Mounting Bracket B



Refer to the *E8Y Pressure Sensor Datasheet* (Cat. No. F045) for details.

Terms and Conditions of Sale

1. **Offer; Acceptance.** These terms and conditions (these "Terms") are deemed part of all quotes, agreements, purchase orders, acknowledgments, price lists, catalogs, manuals, brochures and other documents, whether electronic or in writing, relating to the sale of products or services (collectively, the "Products") by Omron Electronics LLC and its subsidiary companies ("Omron"). Omron objects to any terms or conditions proposed in Buyer's purchase order or other documents which are inconsistent with, or in addition to, these Terms.
2. **Prices; Payment Terms.** All prices stated are current, subject to change without notice by Omron. Omron reserves the right to increase or decrease prices on any unshipped portions of outstanding orders. Payments for Products are due net 30 days unless otherwise stated in the invoice.
3. **Discounts.** Cash discounts, if any, will apply only on the net amount of invoices sent to Buyer after deducting transportation charges, taxes and duties, and will be allowed only if (i) the invoice is paid according to Omron's payment terms and (ii) Buyer has no past due amounts.
4. **Interest.** Omron, at its option, may charge Buyer 1-1/2% interest per month or the maximum legal rate, whichever is less, on any balance not paid within the stated terms.
5. **Orders.** Omron will accept no order less than \$200 net billing.
6. **Governmental Approvals.** Buyer shall be responsible for, and shall bear all costs involved in, obtaining any government approvals required for the importation or sale of the Products.
7. **Taxes.** All taxes, duties and other governmental charges (other than general real property and income taxes), including any interest or penalties thereon, imposed directly or indirectly on Omron or required to be collected directly or indirectly by Omron for the manufacture, production, sale, delivery, importation, consumption or use of the Products sold hereunder (including customs duties and sales, excise, use, turnover and license taxes) shall be charged to and remitted by Buyer to Omron.
8. **Financial.** If the financial position of Buyer at any time becomes unsatisfactory to Omron, Omron reserves the right to stop shipments or require satisfactory security or payment in advance. If Buyer fails to make payment or otherwise comply with these Terms or any related agreement, Omron may (without liability and in addition to other remedies) cancel any unshipped portion of Products sold hereunder and stop any Products in transit until Buyer pays all amounts, including amounts payable hereunder, whether or not then due, which are owing to it by Buyer. Buyer shall in any event remain liable for all unpaid accounts.
9. **Cancellation; Etc.** Orders are not subject to rescheduling or cancellation unless Buyer indemnifies Omron against all related costs or expenses.
10. **Force Majeure.** Omron shall not be liable for any delay or failure in delivery resulting from causes beyond its control, including earthquakes, fires, floods, strikes or other labor disputes, shortage of labor or materials, accidents to machinery, acts of sabotage, riots, delay in or lack of transportation or the requirements of any government authority.
11. **Shipping; Delivery.** Unless otherwise expressly agreed in writing by Omron:
 - a. Shipments shall be by a carrier selected by Omron; Omron will not drop ship except in "break down" situations.
 - b. Such carrier shall act as the agent of Buyer and delivery to such carrier shall constitute delivery to Buyer;
 - c. All sales and shipments of Products shall be FOB shipping point (unless otherwise stated in writing by Omron), at which point title and risk of loss shall pass from Omron to Buyer; provided that Omron shall retain a security interest in the Products until the full purchase price is paid;
 - d. Delivery and shipping dates are estimates only; and
 - e. Omron will package Products as it deems proper for protection against normal handling and extra charges apply to special conditions.
12. **Claims.** Any claim by Buyer against Omron for shortage or damage to the Products occurring before delivery to the carrier must be presented in writing to Omron within 30 days of receipt of shipment and include the original transportation bill signed by the carrier noting that the carrier received the Products from Omron in the condition claimed.
13. **Warranties.** (a) **Exclusive Warranty.** Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied. (b) **Limitations.** OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) **Buyer Remedy.** Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty. See <http://www.omron247.com> or contact your Omron representative for published information.
14. **Limitation on Liability; Etc.** OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY. Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.
15. **Indemnities.** Buyer shall indemnify and hold harmless Omron Companies and their employees from and against all liabilities, losses, claims, costs and expenses (including attorney's fees and expenses) related to any claim, investigation, litigation or proceeding (whether or not Omron is a party) which arises or is alleged to arise from Buyer's acts or omissions under these Terms or in any way with respect to the Products. Without limiting the foregoing, Buyer (at its own expense) shall indemnify and hold harmless Omron and defend or settle any action brought against such Companies to the extent based on a claim that any Product made to Buyer specifications infringed intellectual property rights of another party.
16. **Property; Confidentiality.** Any intellectual property in the Products is the exclusive property of Omron Companies and Buyer shall not attempt to duplicate it in any way without the written permission of Omron. Notwithstanding any charges to Buyer for engineering or tooling, all engineering and tooling shall remain the exclusive property of Omron. All information and materials supplied by Omron to Buyer relating to the Products are confidential and proprietary, and Buyer shall limit distribution thereof to its trusted employees and strictly prevent disclosure to any third party.
17. **Export Controls.** Buyer shall comply with all applicable laws, regulations and licenses regarding (i) export of products or information; (ii) sale of products to "forbidden" or other proscribed persons; and (iii) disclosure to non-citizens of regulated technology or information.
18. **Miscellaneous.** (a) **Waiver.** No failure or delay by Omron in exercising any right and no course of dealing between Buyer and Omron shall operate as a waiver of rights by Omron. (b) **Assignment.** Buyer may not assign its rights hereunder without Omron's written consent. (c) **Law.** These Terms are governed by the law of the jurisdiction of the home office of the Omron company from which Buyer is purchasing the Products (without regard to conflict of law principles). (d) **Amendment.** These Terms constitute the entire agreement between Buyer and Omron relating to the Products, and no provision may be changed or waived unless in writing signed by the parties. (e) **Severability.** If any provision hereof is rendered ineffective or invalid, such provision shall not invalidate any other provision. (f) **Setoff.** Buyer shall have no right to set off any amounts against the amount owing in respect of this invoice. (g) **Definitions.** As used herein, "including" means "including without limitation"; and "Omron Companies" (or similar words) mean Omron Corporation and any direct or indirect subsidiary or affiliate thereof.

Certain Precautions on Specifications and Use

1. **Suitability of Use.** Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given:
 - (i) Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document.
 - (ii) Use in consumer products or any use in significant quantities.
 - (iii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.
 - (iv) Systems, machines and equipment that could present a risk to life or property. Please know and observe all prohibitions of use applicable to this Product.
 NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON'S PRODUCT IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.
2. **Programmable Products.** Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.
3. **Performance Data.** Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.
4. **Change in Specifications.** Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.
5. **Errors and Omissions.** Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Complete "Terms and Conditions of Sale" for product purchase and use are on Omron's website at www.omron.com/oei – under the "About Us" tab, in the Legal Matters section.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.



OMRON ELECTRONICS LLC

1 Commerce Drive
Schaumburg, IL 60173
Tel: 847.843.7900

For U.S. technical support or other inquiries: 800.556.6766

OMRON CANADA, INC.

885 Milner Avenue
Toronto, Ontario M1B 5V8
Tel: 416.286.6465

MEXICO SALES OFFICES

Mexico, D.F. (52) 555 660 31 44
Ciudad Juárez (52) 656 623 70 83
Monterrey, N.L. (52) 818 377 42 81
Mexicali, B.C. (52) 686 838 01 15

BRAZIL SALES OFFICES

Sao Paulo (55) 11 2101 6300

ARGENTINA SALES OFFICES

Cono Sur (54) 11 4787 1129

CHILE SALES OFFICES

Santiago (56) 2206 4592

OTHER LATIN AMERICAN SALES

mela@omron.com

OMRON ON-LINE

Global –
www.omron.com

USA –
www.omron247.com

Canada –
www.omron.ca

Brazil –
www.omron.com.br