




THIS DRAWING IS UNPUBLISHED.







RELEASED FOR PUBLICATION

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			

RECOMMENDED PCB LAYOUT (MOUNTING SIDE)
THICKNESS 1.57mm (TOLERANCE:±0.05)

NOTE:

- MATERIAL:
HOUSING: PA9T WITH 33% GF, UL 94V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
SHELL: PHOSPHOR BRONZE.
MYLAR: POLYAMIDE FILM.
- FINISH:
CONTACTS: GOLD FLASH OVER
0.762 μ m [30 μ] MIN. PALLADIUM-NICKEL PLATED ON CONTACT AREA,
2.54 μ m [100 μ] MIN. MATTE-TIN ON SOLDER TAIL, WITH
ENTIRE CONTACT UNDERPLATED 1.27 μ m [50 μ] MIN. NICKEL.
SHELL: 2.03 μ m [80 μ] MIN. NICKEL PLATED OVERALL.
- NO DATECODE ON PRODUCT SURFACE.
- REFLOW SOLDER CAPABLE TO 260°C PER TE TEST SPEC.
109-201, CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 0.38 1 PLC ± 0.25 2 PLC ± 0.13 3 PLC ± 0.05 4 PLC ± — ANGLES ± 3°
MATERIAL SEE NOTE	FINISH SEE NOTE

DWN	CHK	APVD	PRODUCT SPEC	APPLICATION SPEC	WEIGHT	CUSTOMER DRAWING
NAME MINI USB, R/A, SMT, B TYPE						RESTRICTED TO
SIZE	CAGE CODE	DRAWING NO	A300779C=1734035			SCALE
SHEET 2 of 4						REV E1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-



COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

—

P

LTR


DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.



8.25 Kg	5.55 Kg	150	56	8400 PCS	2-1734035-1
					1-1734035-1
					1734035-1
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAYS /CARTON	QUANTITY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity			
		CHK				
		APVD				
		NAME				
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		MINI USB, R/A, SMT, B TYPE		
		0 PLC ± -		SIZE		
		1 PLC ± -		CAGE CODE		
		2 PLC ± -		DRAWING NO		
		3 PLC ± -		RESTRICTED TO		
4 PLC ± -		4 PLC ANGLES ± -		A300779		
MATERIAL		FINISH		C=1734035		
				CUSTOMER DRAWING		
				SCALE		
				SHEET 3 of 4		
				REV E1		

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
DW	—	P	LTR	DESCRIPTION	DATE	DWN APVD
				SEE SHEET 1.		

D


C

B


A




FOR 1734035-3, 1-1734035-3 AND 2-1734035-3 (LONG CARRIER & COVER TAPE)



FOR 1734035-2, 1734035-4, 1734035-5, 1-1734035-2, 3-1734035-2, 2-1734035-2, 2-1734035-4, 4-1734035-2



4.95 Kg	2.31 Kg	700	5	3500	W/	W/O	4-1734035-2
					W/O	W/O	3-1734035-2
					W/	W/O	2-1734035-4
					W/O	W/	2-1734035-3
					W/O	W/O	2-1734035-2
					W/O	W/	1-1734035-3
					W/O	W/O	1-1734035-2
					W/	W/O	1734035-5
					W/	W/O	1734035-4
GROSS WEIGHT	NET WEIGHT	PCS/REER	REERS / CARTON	QUANTITY	W/O	W/	1734035-3
					W/O	W/O	1734035-2
					MYLAR	LONG CARRIER & COVER TAPE	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity		
DIMENSIONS: MM		CHK		NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		MINI USB, R/A, SMT, B TYPE		
0 PLC ±		PRODUCT SPEC		SIZE		
1 PLC ±		APPLICATION SPEC		CAGE CODE		
2 PLC ±		WEIGHT		DRAWING NO		
3 PLC ±		CUSTOMER DRAWING		A3 00779 C=1734035		
4 PLC ±		SCALE		RESTRICTED TO		
MATERIAL		FINISH		SHEET		
				4 of 4		
				REV E1		