

THIS DRAWING IS UNPUBLISHED.




RELEASED FOR PUBLICATION

,19


© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
AF	50				A1	RELEASE PER FASR	2/23/89	—
				A2	REVISED PER ECR-15-015288	02/11/15	T.D	



SECTION A—A
SCALE 10:1



SECTION B—B
SCALE 10:1

F or O	.155	.235	F	.110	.085	14
					.076	16
					.071	18
TYPE	WIDTH	STRIP LENGTH	TYPE	WIDTH	±.002 HEIGHT	WIRE
INSUL BARREL CRIMP		±.015	WIRE BARREL CRIMP			

OBSOLETE		.100—.140		18—14		63518—1			
		INSULATION DIA		WIRE RANGE		PART NO			
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± — 3 PLC DEC ± .010 ANGLES ± —		DR 10/17/88 P FORTNEY		AMP AMP INCORPORATED Harrisburg, Pa. 17105					
		CHK 10/19/88 JR RUTH							
		APPD 10/19/88 D DECKER		NAME RING					
		APPD 10/19/88 TL SHUTTER							
MATERIAL #2 HARD BRASS		PRODUCT SPEC —		SIZE		FSCM NO		DRAWING NO	
FINISH PRE—TIN		APPLICATION SPEC —		B		00779		63518	
		WEIGHT —		SCALE		5:1		SHEET 1 OF 1	