

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0511110200

Status:

Active

Description:

2.50mm Pitch Wire-to-Wire and Wire-to-Board Receptacle Housing, with Retainer, 2 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-51111-001 (PDF)

Product Specification PS-51111-003 (PDF)

Packaging Specification SPK-51111-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Product Name

UPC

Crimp Housings

51111

Signal, Wire-to-Board, Wire-to-Wire

N/A

800754236744

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Capable

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Stackable

Temperature Range - Operating

2

Natural

94V-0

Receptacle

No

Polyester

473.000/mg

1

Bag

No

2.50mm

No

-40°C to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification


Product Specification

Sales Drawing

SPK-51111-001-001

PS-51111-001, PS-51111-003

SD-51111-**00



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/01/2018 (15

January 2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

51111 Series

Mates With

51112 , 51112 With Retainer, 53561 , 53730

Use With

50397 , 51113

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION