




MATERIALS:

Retractable Sheath Banana Plug:

Plug Body: Tellurium Copper, Gold Plated.

Banana Spring: Beryllium Copper, Gold Plated

Compression Spring: Stainless Steel

Tip: Nylon, Color Matches Color of Wire

Insulation: Nylon Molded to the Plug and Wire. Color Matches Color or Wire.

Wire: 12 AWG, Stranding 7 x 38/36 Bare Copper, PVC Insulated, .144 (3,66mm) O.D.

Marking: POMONA 5291A-XX

RATINGS:

Operating Temperature: +55° C (+131° F) Max.

Operating Voltage: 1000V per IEC1010-2-031

Current: 7 Amperes

ORDERING INFORMATION: Model 5291A-XX-*

XX = Wire Length, Standard Lengths: 12" (30,48cm), 36" (91,44cm) & 60" (152,4cm). Additional lengths can be quoted upon request.

* = Color, -0 Black, -2 Red

Ordering Example: 5291A-12-2 Patch Cord is 12" (30,48cm), Color is red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA