



Beakers



Beakers, low form

PYREX®

- Complies with ISO 3819
- **Manufactured from Pyrex® borosilicate glass**
- Excellent thermal performance
- High resistance to chemical attack
- White graduations and marking spot

Catalogue number	Capacity ml	Height mm	Outside diameter mm
1000/03M	5	30	22
1000/05M	10	35	26
1000/11M	25	50	34
1000/02M	50	60	42
1000/04D	100	70	50
1000/06D	150	80	60
1000/10D	250	95	70
1000/14D	400	110	80
1000/18D	600	125	90
1000/20D	800	135	100
1000/22D	1000	145	105
1000/28D	2000	185	130
1000/30D	3000	210	150
1000/34D	5000	270	170
1000/38D*	10000	350	217



*Supplementary to ISO range and not graduated.
Graduations are approximate.