


D

C

B

A



LEGEND
MADE IN SWEDEN
PATENT PENDING

BLADE ADJUSTMENT
HEX SCREWS (3)
REPLACEABLE BLADE CASSETTE
INSIDE TOOL.

1. 2mm HEX KEY 603988-1, SUPPLIED WITH EACH KIT.
 2. FOUR "V" BLOCKS & ADJUSTMENT GAUGE, SUPPLIED WITH EACH KIT.
 3. TOOL KIT PACKED IN VINYL POUCH OR BOX WITH PART NUMBER AND MADE IN SWEDEN ON LABELS
 4. SHIPPING WEIGHT .19 Lb.
- △ SAME AS 603995-1 EXCEPT, 10 PER PACKAGE

TOOL KIT NO.	CASSETTE
603995-1	603996-1
603995-2	603996-2
603995-3	603996-3
603995-5	603996-4
603995-6	603996-5

2 STEP STYLE FOR SINGLE CRIMP BNC△	603995-9
3 STEP STYLE FOR DUAL CRIMP COMMERCIAL BNC	603995-6
3 STEP STYLE FOR DUAL CRIMP BNC	603995-5
2 STEP STYLE FOR ECONOMY UHF	603995-3
2 STEP STYLE FOR COMMERCIAL BNC	603995-2
2 STEP STYLE FOR SINGLE CRIMP BNC	603995-1
DESCRIPTION	PART NO

"V" BLOCK		CABLE	
PART NO.	COLOR	DIA. RANGE	RG #
603997-1	RED	3.05-5.08 [.120-.200]	195
603997-2	BLUE	5.08-6.35 [.200-.250]	58, 59, 62
603997-3	YELLOW	6.35-7.62 [.250-.300]	BELDEN 8281
603997-4	WHITE	2.54-3.05 [.100-.120]	174, 188

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.L.GROFT 6-21-95	TE Connectivity		
		CHK R.J.KOBLER 6-21-95			
DIMENSIONS: MM [INCHES]		APVD R.J.KOBLER 6-21-95	NAME COAXIAL CABLE STRIPPER		
		PRODUCT SPEC			
		APPLICATION SPEC	SIZE A3		
MATERIAL -		WEIGHT -	CAGE CODE 00779	DRAWING NO C-603995	RESTRICTED TO -
FINISH -		CUSTOMER DRAWING		SCALE 1:1	SHEET 1 of 1
				REV P	