





- ① HOUSING MATERIAL: LIQUID CRYSTAL POLYMER
COLOR: NATURAL.
- ② CONTACT MATERIAL: PHOSPHOR BRONZE
- ③ CONTACT FINISH:(B)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.0006 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- ④ PART MARKING LOCATED APPROXIMATELY AS SHOWN.
- ⑤ DIMENSION APPLIES WHEN SEATED ON PRINTED CIRCUIT BOARD.
- ⑥ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINIS



DETAIL Z
SCALE 20:1

 OBSOLETE	130	65	131.88	330	1-5223002-4
	118	59	119.88	300	1-5223002-0
	106	53	107.88	270	5223002-9
	94	47	95.88	240	5223002-8
	82	41	83.88	210	5223002-7
	70	35	71.88	180	5223002-6
	58	29	59.88	150	5223002-5
	46	23	47.88	120	5223002-4
	34	17	35.88	90	5223002-3
	22	11	23.88	60	5223002-2
	10	5	11.88	30	5223002-1
C	B	A	NO OF SIGNAL POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN <u>B. MCMMASTER</u> 19NOV04		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
		OR <u>R. WERTZ</u> 19NOV04			
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: APVD <u>R. WERTZ</u> 19NOV04 PRODUCT SPEC — APPLICATION SPEC —		NAME ASSEMBLY, PIN, SIGNAL, VERTICAL, Z-PACK 2mm FB, 5 ROW, PRESS FIT LEADS	
MATERIAL   		WEIGHT —		SIZE A1	
				CAGE CODE 00779	
				DRAWING NO C-5223002	
				RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 of 1 REV A	