

[Home](#)[About Us](#)[Products](#)[Audio](#)[Video](#)[Lighting](#)[Data Connectors](#)[Industrial](#)[Support](#)[News](#)[Sitemap](#)[Search](#)☐ PRODUCTS ONLY[Search](#)

© Neutrik® AG
All rights reserved
[Legal Notices](#)

**Audio**

AA Series

[back](#)

NC3FAAV-0

Product

Connector Type	XLR
Gender	female

Electrical

Capacitance between contacts	≤ 4 pF
Contact resistance	≤ 6 m Ω
Dielectric strength	1,5 kVdc
Insulation resistance	> 2 G Ω (initial)
Insulation resistance	> 1 G Ω (after damp heat test)
Rated current per contact	6 A
Rated voltage	50 V
Grounding options	no grounding

Mechanical

Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Locking force	> 20 separating force N
Wiring	Vertical PCB mount
Locking device	Retention spring
Mounting direction	rear
Chassis shape	A
Mounting	A-Screw

Material

Contact plating	0.2 μ m AuCo over 2 μ m NiP15 (Tribor®)
Contacts	Bronze (CuSn6)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Steel Ck67
Flange	Black Plastic

Environmental

Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C