



Sample photo

Order symbol: PC 21/18-3
Product nbr: 7525154

EAN: 6418074056733

Description: Enclosure, PC
Remarks: Smoked transparent cover

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Smoked transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:		L	W	H	Rating:
mm:		213	185	118	Ingress Protection (EN 60529): IP 65 Impact Resistance (EN 50102): IK 08/07 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes UV resistance: UL 508 Flammability Rating (UL 746 C 5): UL 94 5V Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 3, 3R, 4X, 12, 13
inch:		8.4	7.3	4.6	
Materials:					
Material:		PC			
Base colour:		RAL 7035			
Cover colour:		Smoked grey			
Gasket material:		EPDM and Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C			Underwriters Laboratories Fimko Europe EN 50298 1998 UL Canada Gost R
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MP 21/18		Mounting plate			
FP 21/18		Front plate			
CM 21/18-3T		Cover			
SET 17/16-21/18-3		Set of hinges and latches			

