


NOTES: UNLESS OTHERWISE SPECIFIED

1. CONSTRUCTION:
INSULATOR: P.V.C. AVAILABLE IN BLACK OR RED.
CONTACT: ANACONDA 7021 OR BOILCAT C97.
GOLD PLATED.
SOCKET: BRASS. TIN PLATED.

2. PERFORMANCE:
MAXIMUM CURRENT: 4 AMPS
MAXIMUM VOLTAGE: 300 V
MAXIMUM TEMPERATURE: 122°F (50°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		CONTRACT NO.		DESCRIPTION	
		TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		APPROVALS		E-Z-HOOK	
		± .XX ± .XXX ± ±		DATE		DIVISION OF TEKTEST INC.	
		MATERIAL		DRAWN		ARCADIA, CA 91006 U.S.A.	
		SEE NOTE.		R.L.		1/11	
		FINISH		APPROVED BY		SIZE	
		SEE NOTE.				CODE IDENT NO.	
						DRAWING NO.	
						SCALE	
						2:1	
						SHEET 1 OF 1	

REVISIONS		DATE	APPROVED
LTR	DESCRIPTION		