

**SPECIFICATION:**

Contact resistance: 20m ohm max. (initial)

Insulation resistance: 100M ohm min. (at 500V DC)

Dielectric strength: 1,500V AC 50/60 Hz for 1 minute

Service life: Mechanically: 100,000 operations min.

Electrically: 30,000 operations min.

Rating: 12A 125V AC / 250V AC






1/2 HP 125VAC / 1HP 250VAC / 5A 125VAC "L"

Function: (ON) - NONE - ON DPDT

KEYWAY  
POSITION

Waterproof rating: IP68

Actuator: Brass / Dull Nickel Plated



( ) = Momentary Function

RoHS Compliant

**CW** INDUSTRIES  
Southampton, Pa. 18966  
Tel 215.355.7080/www.cwind.com

Date Drawn: 3-23-12	Rev. 0	Unit: mm	Checked By: <i>G. Guld</i>
Title: TOGGLE SWITCH	CW P/N: GTB4B18		