




04/04/07

REV.	ECN.NO.	MODIFY CONTENT	DATE
A		ALU發行	03/20/07
B		板面圖紙更新	04/04/07
C		取銷 LOGO 標示	04/14/07



NOTES:

1. SPECIFICATIONS
INSULATION RESISTANCE: 500M min. AT DC 500V DC
WITHSTANDING VOLTAGE: 250V AC rms FOR 1 MINUTE
CONTACT RESISTANCE: 100MΩ max. AT 10MA/20mV max
CURRENT RATING: 0.5A
VOLTAGE RATING: 5.0 vrms
OPERATING TEMP. RANGE: -55°C~+85°C
MATING CYCLES: 5000 INSERTIONS
2. MATERIAL:
INSULATOR: H-TEMPERATURE PLASTIC, UL 94V-0,
COLOR: BLACK
TERMINAL: COPPER ALLOY, T=0.15mm
SWITCH: COPPER ALLOY, T=0.10mm
SHELL: STAINLESS STEEL, T=0.15mm
3. FINISH:
TERMINAL: 50μ" min NICKEL UNDERPLATED ON ALLOY, GOLD PLATING
ON CONTACT AREA, 80μ" min TIN ON SOLDER TAIL
SHELL: 50μ" NICKEL UNDERPLATED ON ALLOY, GOLD FLASH ON SOLDER
LATCH



RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE		FILE.NO.	101-00269		PART.NO.	101-00269-xx	DRAWN	COCO	MATERIAL		SCALE	N/A
X.±0.50	x.°± 5°	REV.	°C		TITLE	SIM CARD READER 6PIN (PUSH/PUSH)W/O SWITCH	CHECKED	楊秀芳	DATE		UNIT	MM
.X±0.38	.x°± 2°	SIZE			SHEET	1/1	APPROVED	陳俊欽	SM Shouh Min Industry (ShenZhen)CO.,LTD			
.XX±0.25	.xx± 1°	A4										