


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
AD	00		G	EC 0G3C 0216 05		28DEC05	BSV JLG


D



C




B



TYPICAL SECTION THRU CAVITY

- 1
- .000015 MIN GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD IN AREA K ALL OVER .000050 MIN NICKEL.
- 2
- "AMP" TRADEMARK SHALL BE ON PART.
- 3
- TOLERANCE NON-CUMMULATIVE.
- 4
- DIMENSION APPLIES AT BASE OF HOUSING.
- 5
- .000015 MIN GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN IN AREA K ALL OVER .000050 MIN NICKEL.

A



RECOMMENDED HOLE LAYOUT

5	1.900	19	2.400	2.430	2.720	40	5-102871-2
5	2.500	25	3.000	3.030	3.320	52	5-102871-1
1	1.900	19	2.400	2.430	2.720	40	102871-2
1	2.500	25	3.000	3.030	3.320	52	102871-1
FINISH	F	E	D	C	B	NO OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	15 DEC 81	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: INCHES		CHK	-				
		APVD	-	NAME			
		PRODUCT SPEC		HEADER ASSEMBLY, MOD II, .025 SQ POST, .100 X .100 C/L, DBL ROW			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 0° 30'		FINISH		A2	00779	C=102871	-
MATERIAL HOUSING: FLAME RETARTANT GLASS FILLED NYLON COLOR-BLACK POSTS: PHOS BRONZE		SEE TABLE		WEIGHT	-	SCALE 1:1	SHEET 1 OF 1
		CUSTOMER DRAWING				REV	G