

Search within category

GO

BUY NOW

DESIGN / INSTALL



CJE5E88TGBU

Category 5e, RJ45, 8-position, 8-wire, universal, corrosive resistant UTP jack module, Blue.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Performance Level	Category 5e			
Termination Style	TG Style			
Module Type	Mini-Com			
Wiring Scheme	T568A/T568B			
Maximum Operating Temperature (°C)	65			
Maximum Operating Temperature (°F)	149			
Minimum Operating Temperature (°C)	-10			
Minimum Operating Temperature (°F)	14			
Maximum Storage Temperature (°C)	70			
Maximum Storage Temperature (°F)	158			
Minimum Storage Temperature (°C)	-40			
Minimum Storage Temperature (°F)	-40			
Color	Blue			
Application	Unshielded			
Material	PBT/Plastic			
Overall Depth (In.)	1.50			
Overall Depth (mm)	38.2			
Overall Height (In.)	0.71			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			