



2013

**wiha**   
Premium Tools





# Complete **TORX®** Program




## Torx® Index

|    | DESCRIPTION                          | Page        |
|------------------------------------------------------------------------------------|--------------------------------------|-------------|
|    | SoftFinish®<br>Cushion Grip          | 5           |
|    | ESD Safe SoftFinish®<br>Cushion Grip | 6           |
|    | Insulated<br>Cushion Grip            | 7           |
|    | Powerhandle                          | 7           |
|    | Stainless Steel<br>Cushion Grip      | 7           |
|    | MicroFinish<br>Non-Slip Grip         | 8           |
|    | Protturn                             | 9           |
|    | 3K Series                            | 10          |
|   | Drive-Loc VI Blades                  | 11          |
|  | T-handle & ComfortGrip               | 12-13       |
|  | L-Keys<br>Offset Screwdrivers        | 13-14<br>14 |
|  | PocketStar Fold Outs                 | 15          |
|  | Wing Handle                          | 16          |
|  | Flag Handle                          | 16          |
|  | TorqueControl Blades                 | 24          |
|  | Precision Tools                      |             |
|  | ESD Safe                             | 26          |
|  | Standard                             | 27          |
|  | PicoFinish                           | 27          |
|  | SYSTEM 4 Micro Bits                  | 28          |
|  | SYSTEM 4 Blades                      | 29          |
|  | Bit Sets                             | 31          |
|  | Insert & Power Bits                  | 34-36       |
|  | Bit Sockets & Sets                   | 39-41       |


## TorxPlus® Index

|    | DESCRIPTION                 | Page  |
|-------------------------------------------------------------------------------------|-----------------------------|-------|
|    | Wing Handle                 | 18    |
|    | Flag Handle                 | 18    |
|    | PocketStar Fold Outs        | 18    |
|    | SoftFinish®<br>Cushion Grip | 19    |
|    | T-handles                   | 19    |
|    | L-Keys Short/Long Arm       | 20    |
|    | TorqueControl Blade         | 24    |
|    | ESD Safe Precision          | 26    |
|   | Bit-Selectors               | 31    |
|  | Insert Bits                 | 38    |
|  | Power Bits                  | 38    |
|  | Bit Sockets & Sets          | 39,41 |


## Ball End Torx® Index

|   | DESCRIPTION                        | Page |
|--------------------------------------------------------------------------------------|------------------------------------|------|
|  | SoftFinish Drivers<br>Cushion Grip | 17   |
|  | L-Keys                             | 17   |
|  | Power Bits                         | 17   |

## Security Torx® Index

|                        | DESCRIPTION                 | Page  |
|--------------------------------------------------------------------------------------------------------|-----------------------------|-------|
|                        | SoftFinish®<br>Cushion Grip | 6     |
|                        | Drive-Loc VI Blades         | 11    |
|                        | L-Keys                      | 14    |
|                        | PocketStar Fold Outs        | 15    |
|                        | SYSTEM 4 Micro Bits         | 28    |
|                        | Bit Sets                    | 32    |
|  | Insert Bits - 1/4" & 5/16"  | 37    |
|                        | Power Bits                  | 37    |
|                        | Bit Sockets                 | 39,41 |

## MagicSpring Screw Holding

|  | DESCRIPTION                               | Page |
|-------------------------------------------------------------------------------------|-------------------------------------------|------|
|   | SoftFinish® Screw Holding<br>Cushion Grip | 21   |
|   | PicoFinish Soft Grip<br>Screw Holding     | 21   |
|   | L-keys Screw Holding                      | 22   |
|   | Wing Handle Screw Holding                 | 22   |
|   | TorqueControl Blades<br>Screw Holding     | 24   |
|   | Power Bits                                | 38   |

## Wing/Flag & L-keys Index

| DESCRIPTION                                                                        | Page                                                   |
|------------------------------------------------------------------------------------|--------------------------------------------------------|
|  | L-Keys 13-14                                           |
|  | Offset Screwdrivers 14                                 |
|  | Wing Handle 16,18,22<br>Torx®, TorxPlus® & MagicSpring |
|  | Flag Handle 16,18<br>Torx® & TorxPlus®                 |

## Screwdrivers Index

|     | DESCRIPTION                                                                        | Page     |
|--------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|----------|
|    | SoftFinish® CushionGrip 5-6,19,21<br>Torx®, Security Torx®, TorxPlus®, MagicSpring |          |
|    | ESD Safe SoftFinish®<br>Cushion Grip - Torx®                                       | 6        |
|    | Insulated<br>Cushion Grip - Torx®                                                  | 7        |
|    | Powerhandle- Torx®                                                                 | 7        |
|    | Stainless Steel<br>Cushion Grip - Torx®                                            | 7        |
|    | MicroFinish<br>Non-Slip Grip - Torx®                                               | 8        |
|    | Protturn - Torx®                                                                   | 9        |
|    | 3K Series - Torx®                                                                  | 10       |
|   | Offset Screwdrivers                                                                | 14       |
|  | T-handle/ComfortGrip<br>Torx® & TorxPlus®                                          | 12-15,19 |
|  | Precision Tools                                                                    |          |
|  | ESD Safe                                                                           | 26       |
|  | Standard                                                                           | 27       |
|  | PicoFinish                                                                         | 27       |


## Drive-Loc VI Interchangeable

| DESCRIPTION                                                                          | Page                                                |
|--------------------------------------------------------------------------------------|-----------------------------------------------------|
|  | Drive-Loc VI Handle<br>SoftFinish® Cushion Grip 11  |
|  | Drive-Loc VI Handle<br>ESD Safe Cushion Grip 11     |
|  | Drive-Loc VI Handle<br>MicroFinish Non-Slip Grip 11 |
|  | Drive-Loc VI Blades<br>Torx® / Security Torx® 11    |

## Fold Outs Index

| DESCRIPTION                                                                          | Page                                               |
|--------------------------------------------------------------------------------------|----------------------------------------------------|
|  | PocketStars<br>Torx, Security Torx, TorxPlus 15,18 |

## TorqueControl Index

| DESCRIPTION                                                                                                                     | Page |
|---------------------------------------------------------------------------------------------------------------------------------|------|
|  TorqueVario Handle                            | 23   |
|  Torx® / TorxPlus® Blades                      | 23   |
|  Insulated Torque Tools                        | 24   |
|  Easy Torque Tools                             | 24   |
|  ESD Safe TorqueControl                        | 24   |
|  ESD Safe Torx® Blades                         | 24   |
|  T-handle Torque Tools                         | 25   |
|  Interchangeable Blades<br>For Torque T-handle | 25   |
|  TorqueControl Sets                            | 25   |


## High Performance Bits Index

| DESCRIPTION                                                                                                                           | Page |
|---------------------------------------------------------------------------------------------------------------------------------------|------|
|  Torx® Dura Insert Bits<br>Tungsten Carbide Coated | 34   |
|  Torx® Diamond Bits                                | 34   |
|  Torx® TiN Coated- Titanium                        | 34   |



## Standard Bits Index

| DESCRIPTION                                                                                                 | Page  |
|-------------------------------------------------------------------------------------------------------------|-------|
|  Torx® Insert/Power Bits | 35-36 |

## Specialty Bits Index

| DESCRIPTION                                                                                                                                                                                                   | Page  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|
|   Ball End Torx®                        | 17,38 |
|   Torx® Align Bits<br>Insert/Power Bits | 36    |
|   Security Torx®<br>Insert/Power Bits   | 37    |
|   TorxPlus® Bits<br>Insert/Power Bits   | 38    |

## Bit Sets Index

| DESCRIPTION                                                                                                                             | Page  |
|-----------------------------------------------------------------------------------------------------------------------------------------|-------|
|  BitFlip Sets                                         | 30    |
|  Topra Bit Sets                                       | 30,32 |
|  Six-in-One Bit Sets                                  | 30,32 |
|  Bit Selector Sets                                    | 31-32 |
|  Power Bit Belt Packs                                 | 31-32 |
|  SYSTEM 4 Sets<br>Micro Bits & Interchangeable Blades | 28-29 |
|  XSelectors                                           | 31-32 |




See Bit Holders on Page 33

## ESD Blade Set Index

| DESCRIPTION                                                                                                    | Page |
|----------------------------------------------------------------------------------------------------------------|------|
|  Interchangeable Blade Set | 6    |

## Sockets Index

| DESCRIPTION                                                                                                                     | Page |
|---------------------------------------------------------------------------------------------------------------------------------|------|
|  Torx® 1/4" Drive                           | 39   |
|  Torx® 3/8" Drive                           | 39   |
|  Torx® 3/8" - 5/16" Bits                    | 39   |
|  Security Torx®<br>3/8", 1/2"               | 39   |
|  External Torx® Sockets<br>1/4", 3/8", 1/2" | 40   |
|  6" Bit Sockets 1/4" & 3/8" Drive           | 40   |
|  Bit Socket Sets                            | 41   |



**Wiha TORX® SoftFinish® Screwdrivers - Ergonomic Cushion Grip Handle**

**362 TORX® Screwdriver, With Wiha-SoftFinish® Handle**

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item  |      |     |      |     |      |     |      |      |      |
|-------|------|-----|------|-----|------|-----|------|------|------|
| No.   | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
| 36264 | T5   | 60  | 2.4  | 2.5 | .098 | 164 | 6.5  | .05  | 10   |
| 36266 | T6   | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36268 | T7   | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36270 | T8   | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36272 | T9   | 60  | 2.4  | 4.0 | .157 | 171 | 6.7  | .10  | 10   |
| 36274 | T10  | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .11  | 10   |
| 36276 | T15  | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .11  | 10   |
| 36278 | T20  | 100 | 3.9  | 4.0 | .157 | 211 | 8.3  | .11  | 10   |
| 36280 | T25  | 100 | 3.9  | 4.5 | .177 | 211 | 8.3  | .12  | 10   |
| 36282 | T27  | 115 | 4.5  | 5.5 | .216 | 233 | 9.2  | .19  | 10   |
| 36284 | T30  | 115 | 4.5  | 6.0 | .236 | 233 | 9.2  | .20  | 10   |
| 36286 | T40  | 130 | 5.1  | 7.0 | .275 | 254 | 10.0 | .27  | 10   |
| 36288 | T45  | 130 | 5.1  | 8.0 | .315 | 254 | 10.0 | .31  | 10   |


**36294 Set 8 Pcs. TORX® Round blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.**

| Item  |           |    |           |     |      |
|-------|-----------|----|-----------|-----|------|
| No.   | Size      | mm | Size      | mm  | lbs. |
| 36294 | 36266 T6  | 60 | 36278 T20 | 100 | 1.24 |
|       | 36270 T8  | 60 | 36280 T25 | 100 |      |
|       | 36274 T10 | 80 | 36282 T27 | 115 |      |
|       | 36276 T15 | 80 | 36284 T30 | 115 |      |


**36291 Set 6 Pcs. TORX®**

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item  |          |    |           |    |      |
|-------|----------|----|-----------|----|------|
| No.   | Size     | mm | Size      | mm | lbs. |
| 36291 | 36266 T6 | 60 | 36272 T9  | 60 | .77  |
|       | 36268 T7 | 60 | 36274 T10 | 80 |      |
|       | 36270 T8 | 60 | 36276 T15 | 80 |      |

**36201 Set 6 Pcs. TORX®**

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item  |           |    |           |     |      |
|-------|-----------|----|-----------|-----|------|
| No.   | Size      | mm | Size      | mm  | lbs. |
| 36201 | 36266 T6  | 60 | 36276 T15 | 80  | .83  |
|       | 36270 T8  | 60 | 36278 T20 | 100 |      |
|       | 36274 T10 | 80 | 36280 T25 | 100 |      |


**36267 Set 12 Pcs. TORX® Round blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.**

| Item  |           |    |           |     |      |
|-------|-----------|----|-----------|-----|------|
| No.   | Size      | mm | Size      | mm  | lbs. |
| 36267 | 36264 T5  | 60 | 36276 T15 | 80  | 2.03 |
|       | 36266 T6  | 60 | 36278 T20 | 100 |      |
|       | 36268 T7  | 60 | 36280 T25 | 100 |      |
|       | 36270 T8  | 60 | 36282 T27 | 115 |      |
|       | 36272 T9  | 60 | 36284 T30 | 115 |      |
|       | 36274 T10 | 80 | 36286 T40 | 130 |      |

## Wiha Security **TORX**® Drivers



### 362 Security **TORX**® Screwdriver With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 36269    | T7s  | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36271    | T8s  | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36273    | T9s  | 60  | 2.4  | 4.0 | .157 | 171 | 6.7  | .10  | 10   |
| 36275    | T10s | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .11  | 10   |
| 36277    | T15s | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .11  | 10   |
| 36279    | T20s | 100 | 3.9  | 4.0 | .157 | 211 | 8.3  | .11  | 10   |
| 36281    | T25s | 100 | 3.9  | 4.5 | .177 | 211 | 8.3  | .11  | 10   |
| 36283    | T27s | 115 | 4.5  | 5.5 | .216 | 233 | 9.2  | .19  | 10   |
| 36285    | T30s | 115 | 4.5  | 6.0 | .236 | 233 | 9.2  | .20  | 10   |
| 36287    | T40s | 130 | 5.1  | 7.0 | .275 | 254 | 10.0 | .28  | 10   |



### 36298 Set 7 Pcs. Security **TORX**®

| Item No. | Size       | mm | Size       | mm  | lbs. |
|----------|------------|----|------------|-----|------|
| 36298    | 36269 T7s  | 60 | 36277 T15s | 80  | .95  |
|          | 36271 T8s  | 60 | 36279 T20s | 100 |      |
|          | 36273 T9s  | 60 | 36281 T25s | 100 |      |
|          | 36275 T10s | 80 |            |     |      |



### 36259 Set 10 Pcs. Security **TORX**®

| Item No. | Size       | mm | Size       | mm  | lbs. |
|----------|------------|----|------------|-----|------|
| 36259    | 36269 T7s  | 60 | 36279 T20s | 100 | 1.5  |
|          | 36271 T8s  | 60 | 36281 T25s | 100 |      |
|          | 36273 T9s  | 60 | 36283 T27s | 115 |      |
|          | 36275 T10s | 80 | 36285 T30s | 115 |      |
|          | 36277 T15s | 80 | 36287 T40s | 130 |      |

## Wiha SoftFinish® ESD Safe Handle



ESD Safe (10<sup>6</sup>-10<sup>9</sup> Ohm)

### 362 ESD Safe **TORX**® Driver, With Wiha-SoftFinish® Handle

**DIN EN 61340-5-1/ 61340-5-2** Round blade, CVM steel, hardened, hard chromed. Offers protection against electrostatic discharge. Dissipative SoftFinish® cushion grip handle, multi-component.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 36260    | T3   | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36204    | T4   | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36200    | T5   | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36206    | T6   | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36208    | T8   | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36209    | T9   | 60  | 2.4  | 4.0 | .157 | 171 | 6.7  | .10  | 10   |
| 36218    | T10  | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .11  | 10   |
| 36219    | T15  | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .11  | 10   |
| 36224    | T20  | 100 | 3.9  | 4.0 | .157 | 211 | 8.3  | .11  | 10   |



### 36289 Set 6 Pcs. ESD Safe **TORX**® Screwdrivers

| Item No. | TORX: T6, T8, T9, T10, T15, T20 | lbs. |
|----------|---------------------------------|------|
| 36289    |                                 | .81  |

## Wiha Stainless Steel **TORX**® Screwdrivers



### 376 **TORX**® Screwdriver, With Wiha-SoftFinish® Handle

High quality stainless steel. SoftFinish® cushion grip handle.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 37608    | T8   | 60  | 2.4  | 4.0 | .139 | 164 | 5.3  | .09  | 10   |
| 37609    | T9   | 60  | 2.4  | 4.0 | .157 | 171 | 5.5  | .11  | 10   |
| 37610    | T10  | 80  | 3.1  | 4.0 | .157 | 191 | 6.7  | .11  | 10   |
| 37615    | T15  | 80  | 3.1  | 4.0 | .157 | 191 | 6.7  | .11  | 10   |
| 37620    | T20  | 100 | 3.9  | 4.0 | .157 | 218 | 7.9  | .16  | 10   |
| 37625    | T25  | 100 | 3.9  | 4.5 | .177 | 218 | 7.9  | .17  | 10   |
| 37627    | T27  | 115 | 4.5  | 5.5 | .216 | 233 | 8.5  | .20  | 10   |
| 37630    | T30  | 115 | 4.5  | 6.0 | .236 | 233 | 8.9  | .21  | 10   |
| 37640    | T40  | 130 | 5.1  | 7.0 | .276 | 254 | 10.0 | .24  | 10   |



### 37690 Set 5 Pcs. Stainless Steel **TORX**® Screwdrivers

| Item No. | TORX: T6, T8, T9, T10, T15, T20 | lbs. |
|----------|---------------------------------|------|
| 37690    |                                 | .81  |

## Wiha Insulated **TORX®** Screwdrivers


 **1000Volt**

### 325 **TORX®** Screwdriver, With Wiha-SoftFinish® Handle

Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E,  up to 1000 Volt. Individually Tested. Blade high alloy cvm steel, hardened, black finish. Insulation molded directly onto blade.

| Item No. | Size | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|------|------|
| 32505    | T5   | 60  | 2.4  | 164 | 6.5  | .06  | 10   |
| 32511    | T6   | 60  | 2.4  | 164 | 6.5  | .06  | 10   |
| 32516    | T7   | 60  | 2.4  | 164 | 6.5  | .06  | 10   |
| 32521    | T8   | 60  | 2.4  | 164 | 6.5  | .06  | 10   |
| 32526    | T9   | 60  | 2.4  | 164 | 6.5  | .06  | 10   |
| 32531    | T10  | 60  | 2.4  | 164 | 6.5  | .06  | 10   |
| 32536    | T15  | 80  | 3.1  | 191 | 7.5  | .12  | 10   |
| 32541    | T20  | 80  | 3.1  | 191 | 7.5  | .12  | 10   |
| 32546    | T25  | 80  | 3.1  | 198 | 7.8  | .17  | 10   |
| 32551    | T27  | 100 | 3.9  | 218 | 8.6  | .20  | 10   |
| 32556    | T30  | 100 | 3.9  | 218 | 8.6  | .20  | 10   |
| 32561    | T40  | 150 | 5.9  | 274 | 10.8 | .30  | 10   |


 **1000Volt**

### 32590 Set 6 Pcs. **TORX®**

| Item No. | Size      | mm | Size      | mm | lbs. |
|----------|-----------|----|-----------|----|------|
| 32590    | 32521 T8  | 60 | 32536 T15 | 80 | .83  |
|          | 32526 T9  | 60 | 32541 T20 | 80 |      |
|          | 32531 T10 | 60 | 32546 T25 | 80 |      |


 **1000Volt**

### 32592 Set 10 Pcs. **TORX®**

| Item No. | Size      | mm | Size      | mm  | lbs. |
|----------|-----------|----|-----------|-----|------|
| 32592    | 32511 T6  | 60 | 32536 T15 | 80  | 1.2  |
|          | 32516 T7  | 60 | 32541 T20 | 80  |      |
|          | 32521 T8  | 60 | 32546 T25 | 80  |      |
|          | 32526 T9  | 60 | 32551 T27 | 100 |      |
|          | 32531 T10 | 60 | 32556 T30 | 100 |      |

## Wiha Powerhandle **TORX®**

Made in Germany



### 362 **TORX®** Screwdriver, With Wiha-Powerhandle CVM steel blade, hardened, hard chromed. Wiha-powerhandle cellulose-acetate.

| Item No. | Size | mm  | Inch | mm  | Inch | lbs. | pkg.       |
|----------|------|-----|------|-----|------|------|------------|
| 36205    | T5   | 50  | 2.0  | 2.5 | .098 | 110  | 4.3 .03 10 |
| 36210    | T6   | 50  | 2.0  | 3.5 | .139 | 125  | 4.9 .06 10 |
| 36212    | T7   | 50  | 2.0  | 3.5 | .139 | 125  | 4.9 .06 10 |
| 36215    | T8   | 60  | 2.4  | 3.5 | .139 | 135  | 5.3 .06 10 |
| 36220    | T9   | 60  | 2.4  | 4.0 | .157 | 140  | 5.5 .09 10 |
| 36225    | T10  | 80  | 3.1  | 4.0 | .157 | 170  | 6.7 .13 10 |
| 36230    | T15  | 80  | 3.1  | 4.0 | .157 | 170  | 6.7 .13 10 |
| 36235    | T20  | 100 | 3.9  | 4.0 | .157 | 200  | 7.9 .17 10 |
| 36240    | T25  | 100 | 3.9  | 4.5 | .177 | 200  | 7.9 .18 10 |
| 36245    | T27  | 115 | 4.5  | 5.5 | .216 | 215  | 8.5 .20 10 |
| 36250    | T30  | 115 | 4.5  | 6.0 | .236 | 225  | 8.9 .28 10 |



### 36292 8 Pc. Set **TORX®** With Wiha-Powerhandle

| Item No. | Includes:                            | lbs. |
|----------|--------------------------------------|------|
| 36292    | T6, T8, T10, T15, T20, T25, T27, T30 | 1.45 |



### 36293 6 Pc. Set **TORX®** With Wiha-Powerhandle

| Item No. | Includes:                | lbs. |
|----------|--------------------------|------|
| 36293    | T6, T7, T8, T9, T10, T15 | .78  |

## Wiha ESD Safe Interchangeable Blade Set



In Durable Pouch

### 10893 ESD Safe **TORX®** Interchangeable Blade Set

5 Pc. Set Includes ESD Safe handle &amp; 4 interchangeable blades.

| Item No. | lbs. |
|----------|------|
| 10893    | .75  |

**TORX®:** T6, T7, T8, T9, T10, T15, T20, T25

Wiha ESD Safe Handle



## Wiha TORX® MicroFinish Handle Non-Slip Grip

**Wiha MicroFinish handle** has a patented non-slip surface - it won't peel, crack or deteriorate when exposed to petroleum solvents. Oil and moisture flow away from the handle surface for a powerful, non-slip grip. You get maximum force and comfort with dry, oily or wet hands.

**Safe**, high density material, eliminates risk of sharp objects becoming embedded in the handle

**Blades** are hardened & hard chromed

**Exact** fit precision ground tips

**MicroFinish Handle** with patented non-slip surface. Ergo handle shape for maximum comfort & exceptional torque transfer

**Blade** CVM, hardened & tempered tool steel, gives exceptional tool life, wear resistance & high torque performance



### 527 TORX® Screwdriver, With Wiha-MicroFinish Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 52711    | T9   | 60  | 2.4  | 4.0 | .157 | 171 | 6.7  | .15  | 10   |
| 52713    | T10  | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .15  | 10   |
| 52716    | T15  | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .15  | 10   |
| 52719    | T20  | 100 | 3.9  | 4.0 | .157 | 211 | 8.3  | .15  | 10   |
| 52722    | T25  | 100 | 3.9  | 4.5 | .177 | 211 | 8.3  | .16  | 10   |
| 52726    | T27  | 115 | 4.5  | 5.5 | .216 | 233 | 9.2  | .25  | 10   |
| 52729    | T30  | 115 | 4.5  | 6.0 | .236 | 233 | 9.2  | .27  | 10   |
| 52732    | T40  | 130 | 5.1  | 7.0 | .275 | 254 | 10.0 | .40  | 10   |



### 52790 Set 5 Pcs. TORX®

Blade chrome-vanadium-molybdenum steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

| Item No. | Size      | mm  | Size      | mm  | lbs. |
|----------|-----------|-----|-----------|-----|------|
| 52790    | 52713 T10 | 80  | 52722 T25 | 100 | 1.0  |
|          | 52716 T15 | 80  | 52729 T30 | 115 |      |
|          | 52719 T20 | 100 |           |     |      |




### 52791 Set 8 Pcs. TORX®

Blade chrome-vanadium-molybdenum steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

| Item No. | Size      | mm  | Size      | mm  | lbs. |
|----------|-----------|-----|-----------|-----|------|
| 52791    | 52711 T9  | 60  | 52722 T25 | 100 | 1.89 |
|          | 52713 T10 | 80  | 52726 T27 | 115 |      |
|          | 52716 T15 | 80  | 52729 T30 | 115 |      |
|          | 52719 T20 | 100 | 52732 T40 | 130 |      |




**Wiha TORX® Protturn Screwdrivers**

**45591 Set 6 Pcs. TORX®**

| Item No. | Size     | mm | Size      | mm  | lbs. |
|----------|----------|----|-----------|-----|------|
| 45591    | 45506 T7 | 50 | 45521 T10 | 80  | .72  |
|          | 45511 T8 | 60 | 45526 T15 | 80  |      |
|          | 45516 T9 | 60 | 45531 T20 | 100 |      |

**45592 Set 8 Pcs. TORX®**

| Item No. | Size      | mm | Size      | mm  | lbs. |
|----------|-----------|----|-----------|-----|------|
| 45592    | 45511 T8  | 60 | 45531 T20 | 100 | 1.07 |
|          | 45516 T9  | 60 | 45536 T25 | 100 |      |
|          | 45521 T10 | 80 | 45541 T27 | 115 |      |
|          | 45526 T15 | 80 | 45546 T30 | 115 |      |


**45589 Set 14 Pcs. TORX®**

| Item No. | Size      | mm  | Size      | mm  | lbs. |
|----------|-----------|-----|-----------|-----|------|
| 45589    | 45505 T6  | 50  | 45531 T20 | 100 | 2.2  |
|          | 45506 T7  | 50  | 45536 T25 | 100 |      |
|          | 45511 T8  | 60  | 45541 T27 | 115 |      |
|          | 45516 T9  | 60  | 45546 T30 | 115 |      |
|          | 45521 T10 | 80  | 45551 T40 | 130 |      |
|          | 45522 T10 | 275 | 45556 T45 | 130 |      |
|          | 45526 T15 | 80  | 45561 T50 | 130 |      |


**48400 1/4" Bit Holding Screwdriver, With Wiha-Protturn Handle**

Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM steel, nickel-plated. Handle, molded on, impact resistant.

| Item No. | Size | mm  | Inch | mm  | Inch | lbs. | pcs. |
|----------|------|-----|------|-----|------|------|------|
| 48400    | 1/4  | 125 | 5.0  | 243 | 9.6  | .24  | 10   |


**455 TORX® Screwdriver, With Wiha-Protturn Handle**

Blade high alloy CVM steel, hardened, black finish. Molded on ergonomic Wiha-Protturn handle, impact resistant.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 45505    | T6   | 50  | 2.0  | 3.5 | .139 | 129 | 5.1  | .05  | 10   |
| 45506    | T7   | 50  | 2.0  | 3.5 | .139 | 129 | 5.1  | .05  | 10   |
| 45511    | T8   | 60  | 2.4  | 3.5 | .139 | 139 | 5.5  | .06  | 10   |
| 45516    | T9   | 60  | 2.4  | 4.0 | .157 | 149 | 5.8  | .08  | 10   |
| 45521    | T10  | 80  | 3.1  | 4.0 | .157 | 170 | 6.7  | .10  | 10   |
| 45522    | T10  | 275 | 10.8 | 4.0 | .157 | 363 | 14.2 | .13  | 10   |
| 45526    | T15  | 80  | 3.1  | 4.0 | .157 | 170 | 6.7  | .10  | 10   |
| 45531    | T20  | 100 | 3.9  | 4.0 | .157 | 190 | 7.5  | .11  | 10   |
| 45536    | T25  | 100 | 3.9  | 4.5 | .177 | 190 | 7.5  | .11  | 10   |
| 45541    | T27  | 115 | 4.5  | 5.5 | .216 | 215 | 8.4  | .11  | 10   |
| 45546    | T30  | 115 | 4.5  | 6.0 | .236 | 215 | 8.4  | .20  | 10   |
| 45551    | T40  | 130 | 5.1  | 7.0 | .275 | 240 | 9.4  | .28  | 10   |
| 45556    | T45  | 130 | 5.1  | 8.0 | .315 | 240 | 9.4  | .27  | 10   |
| 45561    | T50  | 130 | 5.1  | 9.0 | .354 | 240 | 9.4  | .31  | 10   |

## Wiha TORX® 3K Series Drivers and Sets

### 3K Series

Molded on soft grip ergonomic handle, impact resistant

Hole for hanging

Precision black tip

Blade high alloy CVM steel, hardened



**45598 Set 6 Pcs. TORX®** Blade CVM steel, hardened, precision black tip. Wiha-3k Ergo handle, cushion grip.

| Item No. | Size     | mm | Size      | mm | lbs. |
|----------|----------|----|-----------|----|------|
| 45598    | 45504 T6 | 60 | 45509 T9  | 60 | .88  |
|          | 45507 T7 | 60 | 45510 T10 | 80 |      |
|          | 45508 T8 | 60 | 45515 T15 | 80 |      |



#### 455 TORX® Screwdriver, With Wiha-3K Series Handle

Blade high alloy CVM steel, hardened, precision black tip.

Molded on ergonomic Wiha-3K Series handle, impact resistant.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 45504    | T6   | 60  | 2.4  | 3.2 | 9/64 | 145 | 5.7  | .06  | 10   |
| 45507    | T7   | 60  | 2.4  | 3.5 | 9/64 | 129 | 5.1  | .05  | 10   |
| 45508    | T8   | 60  | 2.4  | 3.5 | 9/64 | 139 | 5.5  | .06  | 10   |
| 45509    | T9   | 60  | 2.4  | 4.0 | 5/32 | 149 | 5.8  | .08  | 10   |
| 45510    | T10  | 80  | 3.1  | 4.0 | 5/32 | 170 | 6.7  | .10  | 10   |
| 45515    | T15  | 80  | 3.1  | 4.0 | 5/32 | 190 | 7.5  | .11  | 10   |
| 45520    | T20  | 100 | 3.9  | 5.5 | 7/32 | 215 | 8.4  | .11  | 10   |
| 45525    | T25  | 100 | 3.9  | 6.0 | 1/4  | 215 | 8.4  | .20  | 10   |
| 45527    | T27  | 115 | 4.5  | 7.0 | 9/32 | 240 | 9.4  | .28  | 10   |
| 45530    | T30  | 115 | 4.5  | 6.0 | 1/4  | 233 | 9.1  | .21  | 10   |
| 45540    | T40  | 130 | 5.1  | 7.0 | 9/32 | 248 | 9.7  | .25  | 10   |
| 45545    | T45  | 130 | 5.1  | 8.0 | 5/16 | 249 | 9.8  | .30  | 10   |
| 45550    | T50  | 130 | 5.1  | 9.0 | 3/8  | 249 | 9.8  | .33  | 10   |



**45595 Set 8 Pcs. TORX®** Wiha-3k Ergo handle, cushion grip.

| Item No. | Size      | mm | Size      | mm  | lbs. |
|----------|-----------|----|-----------|-----|------|
| 45595    | 45504 T8  | 60 | 45520 T20 | 100 | 1.36 |
|          | 45509 T9  | 60 | 45525 T25 | 100 |      |
|          | 45510 T10 | 80 | 45527 T27 | 115 |      |
|          | 45515 T15 | 80 | 45530 T30 | 115 |      |



**45593 Set 5 Pcs. TORX®** Blade CVM steel, hardened, precision black tip. Wiha-3k Ergo handle, cushion grip.

| Item No. | Size      | mm | Size      | mm  | lbs. |
|----------|-----------|----|-----------|-----|------|
| 45593    | 45508 T8  | 60 | 45520 T20 | 100 | .86  |
|          | 45510 T10 | 80 | 45525 T25 | 100 |      |
|          | 45515 T15 | 80 |           |     |      |



**45597 Set 11 Pcs. TORX®** 3K Ergo Series Screwdriver Set  
Blade chrome-vanadium-molybdenum steel, hardened, precision black tip. Wiha-3k Ergo handle, cushion grip.

| Item No. | Size      | mm | Size      | mm  | lbs. |
|----------|-----------|----|-----------|-----|------|
| 45597    | 45504 T6  | 60 | 45520 T20 | 100 | 1.72 |
|          | 45507 T7  | 60 | 45525 T25 | 100 |      |
|          | 45508 T8  | 60 | 45527 T27 | 115 |      |
|          | 45509 T9  | 60 | 45530 T30 | 115 |      |
|          | 45510 T10 | 80 | 45540 T40 | 130 |      |
|          | 45515 T15 | 80 |           |     |      |



## Drive-Loc VI

For Adjustable Length Locking Blades



Locking mechanism allows blade length to be adjusted from 40mm-120mm. (1.7 to 4.7" In 1/8" increments)

Blades high quality CVM steel, hard chrome finish.

Ergonomic handles in ESD Safe, cushioned & non-slip grip.



### 28488 Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

#### Advantages:

Ergonomic cushion grip, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange.

| Item  |     |     |      |      |      |      |
|-------|-----|-----|------|------|------|------|
| No.   | mm  | mm  | Inch | mm   | Inch | lbs. |
| 28488 | 6.0 | 115 | 4.5  | 36.0 | 1.41 | .20  |



### 28486 ESD Safe Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

#### Advantages:

Ergonomic cushion grip, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange. Static Dissipative.

| Item  |     |     |      |      |      |      |
|-------|-----|-----|------|------|------|------|
| No.   | mm  | mm  | Inch | mm   | Inch | lbs. |
| 28486 | 6.0 | 115 | 4.5  | 36.0 | 1.41 | .20  |



### 28487 Drive-Loc VI MicroFinish Non-Slip Grip Handle

Wiha-MicroFinish handle, won't peel, crack or deteriorate when exposed to petroleum solvents. Ideal for Hex, TORX® & Nut Drivers.

#### Advantages:

Ergonomic handle shape for maximum comfort, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange.

| Item  |     |     |      |      |      |      |
|-------|-----|-----|------|------|------|------|
| No.   | mm  | mm  | Inch | mm   | Inch | lbs. |
| 28487 | 6.0 | 115 | 4.5  | 36.0 | 1.41 | .20  |



### 281 TORX® Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish.

Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

| Item  |             |      |      |  |
|-------|-------------|------|------|--|
| No.   | Size + Size | lbs. | pkg. |  |
| 28126 | T6 T8       | .09  | 1    |  |
| 28127 | T7 T9       | .09  | 1    |  |
| 28128 | T10 T15     | .10  | 1    |  |
| 28129 | T20 T25     | .10  | 1    |  |
| 28130 | T30 T40     | .10  | 1    |  |



### 281 Security TORX® Drive-Loc VI Interchangeable Blade,

high alloy CVM steel, through hardened, hard chrome finish.

Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

| Item  |             |      |      |  |
|-------|-------------|------|------|--|
| No.   | Size + Size | lbs. | pkg. |  |
| 28132 | T6s T8s     | .09  | 1    |  |
| 28133 | T7s T9s     | .09  | 1    |  |
| 28134 | T10s T15s   | .10  | 1    |  |
| 28135 | T20s T25s   | .10  | 1    |  |
| 28136 | T30s T40s   | .10  | 1    |  |



### 28195 Drive-Loc VI Interchangeable Blade Set, 6 Pcs. In Durable Pouch

Set includes Drive-Loc VI handle & 5 interchangeable blades.

| Item      |  | lbs. |
|-----------|--|------|
| No. 28195 |  | .85  |

TORX®: T6&T8, T7&T9, T10&T15, T20&T25, T30&T40

Wiha SoftFinish® Cushion Grip Blade Lock Handle



### 28197 Drive-Loc VI Interchangeable Blade Set, 6 Pcs. In Durable Pouch

Set includes Drive-Loc VI handle & 5 interchangeable blades.

| Item      |  | lbs. |
|-----------|--|------|
| No. 28197 |  | .83  |

Security TORX®: T6s+T8s, T7s+T9s, T10s+T15s,

T20s+T25s, T30s+T40s & SoftFinish® Cushion Grip Blade Lock Handle



## Wiha Insulated SlimLine Tools

### Insulation Test Standards:

Insulation according to EN/IEC 60900, ASTM F-1505-01, VDE 0682/part 201, DIN 7437, NFPA70E & CSA specification

Ideal for jobs where access is limited


Integrated *Slim* Insulation molded directly onto blade

Insulation does not exceed screw head diameter

High quality chrome vanadium steel, through-hardened

 **1000Volt Rated**  
10,000Volt Tested

**Wiha SlimTECHNOLOGY**  
Achieves blade diameters up to 33% narrower utilizing integrated insulation



 **1000Volt**

**28301** *SlimLine* Blade Holder, With Wiha-SoftFinish® Handle  
Insulation According to VDE, ASTM F-1505-01 and EN/IEC 60900, NFPA70E & CSA,  up to 1000 Volt.

Chrome-vanadium steel, through-hardened. Insulation molded directly onto blade. Quick release holder securely lock blades.

Wiha-SoftFinish® handle, multi-component, cushion grip.

| Item No. | Size | mm | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|----|------|-----|------|------|------|
| 28301    | 1/4" | 50 | 2.0  | 160 | 6.3  | .15  | 1    |



### 283 Insulated TORX® SlimLine Blades

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

| Item No. | Size | mm | Slim Dia. | Working Length | Max Nm | Inch/ lbs. | lbs. | Pkg. |
|----------|------|----|-----------|----------------|--------|------------|------|------|
| 28339    | T8   | 90 | 4.1       | 2.8"           | 1.3    | 11.5       | .02  | 1    |
| 28340    | T10  | 90 | 4.1       | 2.8"           | 3.8    | 33.7       | .02  | 1    |
| 28341    | T15  | 90 | 6.1       | 2.8"           | 5.5    | 48.8       | .02  | 1    |
| 28342    | T20  | 90 | 6.1       | 2.8"           | 5.5    | 48.8       | .02  | 1    |

## WihaTORX® Soft Grip Dual Drive T-handle

### Two Tools In One!



### Maximum Comfort & Maximum Power

Torx - Blades of CVM tool steel, through hardened durability, hard chrome finish

Two component soft grip handle



### 364 Soft Grip TORX® T-handle

Blade CVM steel, through hardened, satin chrome finish. Soft grips are molded on and include through the handle side torque drive.


| Item No. | Size | mm  | lbs. | pkg. |
|----------|------|-----|------|------|
| 36480    | T10  | 100 | .08  | 10   |
| 36481    | T15  | 100 | .08  | 10   |
| 36482    | T20  | 100 | .13  | 10   |
| 36483    | T25  | 150 | .16  | 10   |
| 36484    | T27  | 150 | .19  | 10   |
| 36486    | T30  | 150 | .20  | 10   |
| 36487    | T40  | 150 | .24  | 10   |



### 36497 Set 7 Pcs. TORX® Soft Grip T-handles

| Item No. | Size      | mm  | Size      | mm  | lbs. |
|----------|-----------|-----|-----------|-----|------|
| 36497    | 36480 T10 | 100 | 36484 T27 | 150 | 1.53 |
|          | 36481 T15 | 100 | 36486 T30 | 150 |      |
|          | 36482 T20 | 100 | 36487 T40 | 150 |      |
|          | 36483 T25 | 150 |           |     |      |


## Wiha TORX® T-handle



### 364 TORX® with Wiha T-handles

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chrome finish. Wiha T-handle high quality plastic, impact resistant.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs | pkg. |
|----------|------|-----|------|-----|------|-----|------|-----|------|
| 36409    | T9   | 100 | 3.9  | 4.0 | 5/32 | 80  | 3.1  | .07 | 10   |
| 36410    | T10  | 100 | 3.9  | 4.0 | 5/32 | 80  | 3.1  | .07 | 10   |
| 36415    | T15  | 100 | 3.9  | 4.0 | 5/32 | 80  | 3.1  | .07 | 10   |
| 36417    | T15  | 200 | 7.9  | 5.5 | 7/32 | 80  | 3.1  | .13 | 10   |
| 36420    | T20  | 100 | 3.9  | 4.0 | 5/32 | 100 | 3.9  | .10 | 10   |
| 36422    | T20  | 200 | 7.9  | 5.5 | 7/32 | 100 | 3.9  | .17 | 10   |
| 36425    | T25  | 100 | 3.9  | 4.0 | 5/32 | 100 | 3.9  | .11 | 10   |
| 36427    | T25  | 200 | 7.9  | 5.5 | 7/32 | 100 | 3.9  | .17 | 10   |
| 36430    | T27  | 100 | 3.9  | 5.5 | 7/32 | 100 | 3.9  | .14 | 10   |
| 36432    | T27  | 200 | 7.9  | 5.5 | 7/32 | 100 | 3.9  | .17 | 10   |
| 36435    | T30  | 100 | 3.9  | 7.9 | 6.0  | 100 | 3.9  | .14 | 10   |
| 36437    | T30  | 200 | 7.9  | 6.0 | 1/4  | 100 | 3.9  | .19 | 10   |
| 36440    | T40  | 100 | 3.9  | 7.0 | 9/32 | 100 | 3.9  | .16 | 10   |
| 36442    | T40  | 200 | 7.9  | 7.0 | 9/32 | 100 | 3.9  | .23 | 10   |
| 36445    | T45  | 150 | 5.9  | 8.0 | 5/16 | 120 | 4.7  | .29 | 10   |
| 36450    | T50  | 150 | 5.9  | 9.0 | 3/8  | 120 | 4.7  | .30 | 10   |
| 36452    | T50  | 250 | 9.8  | 9.0 | 3/8  | 120 | 4.7  | .45 | 10   |



#36490

#36492

### 36492 TORX® T-handle Set, 7 Pc.

Equipped with T9, T10, T15, T20, T25, T27, T30

Item No. lbs. pkg.

36492 1.24 1

### 36490 TORX® T-handle Set, 7 Pc. In Metal Stand

Equipped with T10, T15, T20, T25, T30, T40, T50

Item No. lbs. pkg.

36490 2.65 1

- Blade high alloy CVM steel, hardened, hard chrome finish

- Wiha T-handle high quality plastic, impact resistant



### 36494 TORX® T-handle Set, 8 Pc. In Metal Stand

Equipped with T9, T10, T15, T20, T25, T27, T30, T40

Item No. lbs. pkg.

36494 3.10 1



## Wiha TORX® Short Arm L-keys



### 363 TORX® L-key, Short Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

| Item No. | Size | mm  | Inch | mm | Inch | lbs. | pkg. |
|----------|------|-----|------|----|------|------|------|
| 36305    | T5   | 37  | 1.5  | 16 | .6   | .01  | 10   |
| 36306    | T6   | 39  | 1.5  | 16 | .6   | .01  | 10   |
| 36307    | T7   | 42  | 1.7  | 16 | .6   | .01  | 10   |
| 36308    | T8   | 45  | 1.8  | 16 | .6   | .01  | 10   |
| 36309    | T9   | 48  | 1.9  | 16 | .6   | .01  | 10   |
| 36310    | T10  | 51  | 2.0  | 17 | .7   | .01  | 10   |
| 36315    | T15  | 54  | 2.1  | 19 | .7   | .01  | 10   |
| 36320    | T20  | 58  | 2.3  | 19 | .7   | .01  | 10   |
| 36325    | T25  | 63  | 2.5  | 21 | .8   | .02  | 10   |
| 36327    | T27  | 67  | 2.6  | 22 | .9   | .03  | 10   |
| 36330    | T30  | 73  | 2.9  | 24 | .9   | .05  | 10   |
| 36340    | T40  | 79  | 3.1  | 26 | 1.0  | .06  | 10   |
| 36345    | T45  | 82  | 3.2  | 28 | 1.1  | .09  | 10   |
| 36350    | T50  | 95  | 3.7  | 32 | 1.3  | .13  | 10   |
| 36355    | T55  | 108 | 4.3  | 35 | 1.4  | .27  | 10   |
| 36360    | T60  | 120 | 4.7  | 38 | 1.5  | .40  | 10   |



#36392



#36394



#36399

### 36392 TORX® Set, 7 Pc. In Plastic Holder

Equipped with T6, T7, T8, T9, T10, T15, T20

| Item No. | lbs. | pkg. |
|----------|------|------|
| 36392    | .10  | 1    |

### 36394 TORX® Set, 9 Pc. In Plastic Holder

Equipped with T8, T9, T10, T15, T20, T25, T27, T30, T40

| Item No. | lbs. | pkg. |
|----------|------|------|
| 36394    | .30  | 1    |

### 36399 TORX® Set, 16 Pc.

Equipped with T5, T6, T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, T45, T50, T55, T60

| Item No. | lbs. | pkg. |
|----------|------|------|
| 36399    | 1.14 | 1    |



### 36390 TORX® Set, 9 Pc. In Metal Stand

Equipped with T10, T15, T20, T25, T30, T40, T50, T55, T60

| Item No. | lbs. | pkg. |
|----------|------|------|
| 36390    | 1.86 | 1    |



## Wiha TORX® Long Arm L-keys



### 366 TORX® L-key, Long Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

| Item  |      |     |      |    |      |      |      |
|-------|------|-----|------|----|------|------|------|
| No.   | Size | mm  | Inch | mm | Inch | lbs. | pkg. |
| 36645 | T5   | 71  | 2.8  | 12 | .5   | .06  | 10   |
| 36646 | T6   | 78  | 3.1  | 13 | .5   | .07  | 10   |
| 36647 | T7   | 87  | 3.4  | 16 | .6   | .10  | 10   |
| 36648 | T8   | 99  | 3.9  | 18 | .7   | .13  | 10   |
| 36649 | T9   | 106 | 4.2  | 18 | .7   | .17  | 10   |
| 36650 | T10  | 118 | 4.6  | 21 | .8   | .23  | 10   |
| 36651 | T15  | 131 | 5.2  | 23 | .9   | .33  | 10   |
| 36652 | T20  | 144 | 5.7  | 25 | 1.0  | .44  | 10   |
| 36653 | T25  | 158 | 6.2  | 28 | 1.1  | .65  | 10   |
| 36654 | T27  | 169 | 6.7  | 30 | 1.2  | .98  | 10   |
| 36655 | T30  | 184 | 7.2  | 32 | 1.3  | 1.27 | 10   |
| 36659 | T40  | 201 | 7.9  | 35 | 1.4  | 2.09 | 10   |
| 36660 | T45  | 222 | 8.7  | 40 | 1.6  | 2.70 | 10   |
| 36661 | T50  | 213 | 8.4  | 40 | 1.6  | 3.14 | 10   |



### 36699 Long Arm TORX® Set, 13 Pc. in Molded Holder Equipped with T5, T6, T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, T50

| Item  |      |      |
|-------|------|------|
| No.   | lbs. | pkg. |
| 36699 | 1.13 | 1    |



### 36698 Long Arm TORX® Set, 10 Pc. in Molded Holder

Equipped with T6, T7, T8, T9, T10, T15, T20, T25, T27, T30

| Item  |      |      |
|-------|------|------|
| No.   | lbs. | pkg. |
| 36698 | 4.4  | 1    |



### 36694 26 Piece Combo Pack Long Arm TORX® And Hex Inch L-key Sets, In Pouch

Set includes: 36699-13pc set T5-T50 and 36991-13pc set .050 - 3/8"

| Item  |      |      |
|-------|------|------|
| No.   | lbs. | pkg. |
| 36694 | 2.13 | 1    |

## Wiha ErgoStar Ball End TORX® Long L-keys



### 36689 ErgoStar TORX® Long Arm Set, 13 Pc. In Molded Holder

Equipped with T5, T6, T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, T45

| Item  |      |      |
|-------|------|------|
| No.   | lbs. | pkg. |
| 36689 | 1.08 | 1    |



### 363 Security TORX® L-key, Short Arm

High alloy CVM steel, hardened, black finish.

| Item  |      |     |      |    |      |      |      |
|-------|------|-----|------|----|------|------|------|
| No.   | Size | mm  | Inch | mm | Inch | lbs. | pkg. |
| 36321 | T7s  | 42  | 1.7  | 16 | .6   | .01  | 10   |
| 36323 | T8s  | 45  | 1.8  | 16 | .6   | .01  | 10   |
| 36326 | T9s  | 48  | 1.9  | 16 | .6   | .01  | 10   |
| 36328 | T10s | 51  | 2.0  | 17 | .7   | .01  | 10   |
| 36329 | T15s | 54  | 2.1  | 19 | .7   | .01  | 10   |
| 36332 | T20s | 58  | 2.3  | 19 | .7   | .02  | 10   |
| 36335 | T25s | 63  | 2.5  | 21 | .8   | .02  | 10   |
| 36337 | T27s | 67  | 2.6  | 22 | .9   | .03  | 10   |
| 36339 | T30s | 73  | 2.9  | 24 | .9   | .04  | 10   |
| 36342 | T40s | 79  | 3.1  | 26 | 1.0  | .06  | 10   |
| 36346 | T45s | 82  | 3.2  | 28 | 1.1  | .09  | 10   |
| 36352 | T50s | 95  | 3.7  | 35 | 1.3  | .13  | 10   |
| 36357 | T55s | 108 | 4.3  | 38 | 1.4  | .27  | 10   |



### Security Torx® L-Key Set

### 36393 Security TORX® Set, 9 Pcs. In Plastic Holder

Equipped with T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

| Item  |      |      |
|-------|------|------|
| No.   | lbs. | pkg. |
| 36393 | .30  | 1    |



## Wiha Offset Screwdrivers



### 207 TORX® Offset Screwdriver With Molded Handle

For working in confined spaces. Blade CVM special steel, hardened, black finish.

| Item No. | Size      | lbs. | pkg. |
|----------|-----------|------|------|
| 20756    | T6 + T8   | .02  | 1    |
| 20757    | T7 + T9   | .02  | 1    |
| 20758    | T10 + T15 | .02  | 1    |
| 20759    | T20 + T25 | .07  | 1    |
| 20760    | T27 + T30 | .10  | 1    |




### 20799 TORX® Offset Screwdriver Set, 5 Pcs.

With Molded Handle Blade CVM special steel, hardened, black finish.

| Item No. | Set Includes: T6+T8, T7+T9, T10+T15, T20+T25, T27+T30 | lbs. | pkg. |
|----------|-------------------------------------------------------|------|------|
| 20799    |                                                       | .24  | 1    |

## Wiha PocketStar Fold Outs



Push button  
key release



Blade length range  
1.68 - 1.94"

### 36396 TORX® PocketStar Fold Outs, 7 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle. OAL 3.8"

| Item No. | PocketStar | lbs. |
|----------|------------|------|
| 36396    |            | .22  |

**TORX®:** T7, T8, T9, T10, T15, T20, T25



Push button  
key release



Blade length range  
1.68 - 1.94"

### 36395 Security TORX® PocketStar Fold Outs, 7 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle. OAL 3.8"

| Item No. | PocketStar | lbs. |
|----------|------------|------|
| 36395    |            | .22  |

**TR TORX®:** T7s, T8s, T9s, T10s, T15s, T20s, T25s



Push button  
key release



Blade length range  
1.95 - 2.39"

### 36398 TORX® PocketStar Fold Outs, 8 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle. OAL 4.74"

| Item No. | PocketStar | lbs. |
|----------|------------|------|
| 36398    |            | .24  |

**TORX®:** T9, T10, T15, T20, T25, T27, T30, T40



Push button  
key release



Blade length range  
1.95 - 2.39"

### 36397 Security TORX® PocketStar Fold Outs, 8 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle. OAL 4.74"

| Item No. | PocketStar | lbs. |
|----------|------------|------|
| 36397    |            | .24  |

**TR TORX®:** T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

## Wiha TORX® Tools



Ideal for use with indexable carbide tooling and also for working in confined spaces



Ideal for use with indexable carbide tooling and also for working in confined spaces



### 365 TORX® Screwdriver, With Wing Handle

Blade high alloy CVM steel, hardened, black finish.

Wing handle high quality plastic, impact resistant.

| Item  | No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|-------|-----|------|-----|------|-----|------|-----|------|------|------|
| 36510 | T6  | 35   | 1.4 | 70   | 2.7 | 40   | 1.6 | .02  | 10   |      |
| 36512 | T7  | 35   | 1.4 | 70   | 2.7 | 40   | 1.6 | .02  | 10   |      |
| 36515 | T8  | 40   | 1.6 | 75   | 2.9 | 40   | 1.6 | .02  | 10   |      |
| 36520 | T9  | 40   | 1.6 | 75   | 2.9 | 40   | 1.6 | .02  | 10   |      |
| 36525 | T10 | 40   | 1.6 | 75   | 2.9 | 40   | 1.6 | .02  | 10   |      |
| 36530 | T15 | 45   | 1.8 | 80   | 3.1 | 40   | 1.6 | .02  | 10   |      |
| 36535 | T20 | 45   | 1.8 | 80   | 3.1 | 40   | 1.6 | .02  | 10   |      |



### 370 TORX® Screwdriver, With Flag Handle

Blade high alloy CVM steel, hardened, black finish.

Flag handle high quality plastic, impact resistant.

| Item  | No. | Size | mm  | Inch | mm  | Inch | mm   | Inch | lbs. | pkg. |
|-------|-----|------|-----|------|-----|------|------|------|------|------|
| 37013 | T5  | 35   | 1.4 | 63   | 2.6 | 15.0 | .75  | .01  | 10   |      |
| 37016 | T6  | 35   | 1.4 | 63   | 2.6 | 15.0 | .75  | .01  | 10   |      |
| 37019 | T7  | 35   | 1.4 | 67   | 2.6 | 19.0 | .75  | .01  | 10   |      |
| 37022 | T8  | 40   | 1.6 | 72   | 2.8 | 19.0 | .75  | .01  | 10   |      |
| 37026 | T9  | 40   | 1.6 | 74   | 2.9 | 23.5 | .93  | .01  | 10   |      |
| 37029 | T10 | 40   | 1.6 | 74   | 2.9 | 23.5 | .93  | .01  | 10   |      |
| 37032 | T15 | 45   | 1.8 | 80   | 3.1 | 28.0 | 1.10 | .02  | 10   |      |
| 37036 | T20 | 45   | 1.8 | 80   | 3.1 | 28.0 | 1.10 | .02  | 10   |      |



### 36591 Wing Handle TORX® Set, 7 Pc.

Set includes: T6, T7, T8, T9, T10, T15, T20 wt. .16



### 37091 Flag Handle TORX® Set, 7 Pc.

Set includes: T6, T7, T8, T9, T10, T15, T20 wt. .14



### 36590 Wing Handle TORX® Set, 7 Pc. In Metal Stand

Set includes: T6, T7, T8, T9, T10, T15, T20 wt. .32



### 37090 Flag Handle TORX® Set, 7 Pc. in Metal Stand

Set includes: T6, T7, T8, T9, T10, T15, T20 wt. .31

## Wiha Ball End TORX® Screwdrivers

- Ball End For 25° Angle Driving
- Precision Machined Exact Fit Tips
- Through Hardened For Maximum Durability
- WIHA High Performance CRM-72 Tool Steel
- Guaranteed Quality Made By Wiha



### 362 Ball End TORX® Screwdriver, With Wiha-SoftFinish® Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item  | No. | Size | mm  | Inch | mm   | Inch | mm  | Inch | lbs. | pkg. |
|-------|-----|------|-----|------|------|------|-----|------|------|------|
| 36216 | T9  | 60   | 2.4 | 4.0  | .157 | 164  | 6.5 | .10  | 10   |      |
| 36217 | T10 | 60   | 2.4 | 4.0  | .157 | 184  | 7.2 | .11  | 10   |      |
| 36221 | T15 | 80   | 3.1 | 4.0  | .157 | 191  | 7.5 | .11  | 10   |      |
| 36222 | T20 | 80   | 3.1 | 4.0  | .157 | 211  | 8.3 | .11  | 10   |      |
| 36226 | T25 | 100  | 3.9 | 4.5  | .177 | 218  | 8.6 | .12  | 10   |      |
| 36227 | T27 | 115  | 4.5 | 5.5  | .216 | 233  | 9.2 | .19  | 10   |      |
| 36236 | T30 | 115  | 4.5 | 6.0  | .236 | 233  | 9.2 | .20  | 10   |      |



**36237 Set 7 Pcs. TORX®** Blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item  |  |  |  |  |  |
|-------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| No.   | Size                                                                                | mm                                                                                  | Size                                                                                | mm                                                                                  | lbs.                                                                                |
| 36237 | 36216 T9                                                                            | 60                                                                                  | 36226 T25                                                                           | 100                                                                                 | 1.24                                                                                |
|       | 36217 T10                                                                           | 60                                                                                  | 36227 T27                                                                           | 115                                                                                 |                                                                                     |
|       | 36221 T15                                                                           | 80                                                                                  | 36236 T30                                                                           | 115                                                                                 |                                                                                     |
|       | 36222 T20                                                                           | 80                                                                                  |                                                                                     |                                                                                     |                                                                                     |

## Wiha Ball End TORX® L-keys



### 366 Ball End TORX® L-key, Long Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

| Item  | No. | Size | mm  | Inch | mm  | Inch | lbs. | pkg. |
|-------|-----|------|-----|------|-----|------|------|------|
| 36631 | T9  | 111  | 4.4 | 21   | .83 | .17  | 10   |      |
| 36632 | T10 | 121  | 4.8 | 23   | .91 | .23  | 10   |      |
| 36633 | T15 | 136  | 5.4 | 27   | 1.1 | .33  | 10   |      |
| 36634 | T20 | 148  | 5.8 | 29   | 1.1 | .44  | 10   |      |
| 36635 | T25 | 163  | 6.4 | 33   | 1.3 | .65  | 10   |      |
| 36636 | T27 | 176  | 6.9 | 36   | 1.4 | .98  | 10   |      |
| 36637 | T30 | 191  | 7.5 | 38   | 1.5 | 1.27 | 10   |      |
| 36638 | T40 | 210  | 8.3 | 43   | 1.7 | 2.09 | 10   |      |



### 36692 Ball End TORX® L-key Set, 8 Pc. in Plastic Holder

Equipped with T9, T10, T15, T20, T25, T27, T30, T40

| Item  | No. | lbs. | pkg. |
|-------|-----|------|------|
| 36692 |     | 6.16 | 1    |

## Wiha Ball End TORX® Power Bits



### 745 Ball End TORX® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

| Item  | No. | Size | mm | pkg. | lbs. |
|-------|-----|------|----|------|------|
| 74524 | T9  | 50   | 10 | .18  |      |
| 74526 | T10 | 50   | 10 | .18  |      |
| 74528 | T15 | 50   | 10 | .18  |      |
| 74532 | T20 | 50   | 10 | .18  |      |
| 74534 | T25 | 50   | 10 | .18  |      |
| 74537 | T27 | 50   | 10 | .18  |      |
| 74539 | T30 | 50   | 10 | .18  |      |
| 74541 | T40 | 50   | 10 | .18  |      |


### 745 Ball End TORX® Power Bit Packs, 1"

| Item  | No. | Size | mm  | lbs. |
|-------|-----|------|-----|------|
| 74505 | T9  | 50   | .05 |      |
| 74520 | T10 | 50   | .05 |      |
| 74522 | T15 | 50   | .05 |      |
| 74543 | T20 | 50   | .05 |      |
| 74545 | T25 | 50   | .06 |      |
| 74547 | T27 | 50   | .06 |      |
| 74549 | T30 | 50   | .08 |      |
| 74550 | T40 | 50   | .08 |      |



## The TORXPlus® Advantage

The TorxPlus® Drive System offers 100% improvement in driver bit fatigue & 25% average improvement in driver bit torsional strength. In addition its unique design provides optimum torque transfer & eliminates the need for excessive end load pressure while driving the fastener. The TorxPlus® configuration also virtually eliminates tool "camout" & slippage that can damage the head of the fastener and cause reduced tool life.



- Broad Surface For Driving
- Features 0° Drive Angle Between The Fastener & Driver
- Greater Engagement Depth



## Wiha PocketStar Fold Out



Push button  
key release

### 36697 TORXPlus® PocketStar Fold Outs, 8 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle.

| Item No.                                              |            |          |
|-------------------------------------------------------|------------|----------|
| 36697                                                 | PocketStar | lbs. .31 |
| TORXPlus®: IP6, IP7, IP8, IP9, IP10, IP15, IP20, IP25 |            |          |

## Wiha TORXPlus® Tools

### TORXPlus®

Not for use in standard  
Torx fasteners

#37092

### 370 TORXPlus® Screwdriver, With Flag Handle

Ideal for use with indexable carbide tooling and also for working in confined spaces. Blade high alloy CVM steel, hardened, black finish. Flag handle high quality plastic, impact resistant.

| Item  |      |    |      |    |      |      |      |      |      |
|-------|------|----|------|----|------|------|------|------|------|
| No.   | Size | mm | Inch | mm | Inch | mm   | Inch | lbs. | pkg. |
| 37040 | IP5  | 35 | 1.4  | 63 | 2.6  | 15.0 | .75  | .01  | 10   |
| 37042 | IP6  | 35 | 1.4  | 63 | 2.6  | 15.0 | .75  | .01  | 10   |
| 37044 | IP7  | 35 | 1.4  | 67 | 2.6  | 19.0 | .75  | .01  | 10   |
| 37046 | IP8  | 40 | 1.6  | 72 | 2.8  | 19.0 | .75  | .01  | 10   |
| 37048 | IP9  | 40 | 1.6  | 74 | 2.9  | 23.5 | .93  | .01  | 10   |
| 37050 | IP10 | 40 | 1.6  | 74 | 2.9  | 23.5 | .93  | .01  | 10   |
| 37052 | IP15 | 45 | 1.8  | 80 | 3.1  | 28.0 | 1.10 | .02  | 10   |
| 37054 | IP20 | 45 | 1.8  | 80 | 3.1  | 28.0 | 1.10 | .02  | 10   |

### 37092 Flag Handle TORXPlus® Set, 7 Pc. in Metal Stand

Set includes:  wt. .31  
IP6, IP7, IP8, IP9, IP10, IP15, IP20

### TORXPlus®

Not for use in standard Torx fasteners

### 365 TORXPlus® Screwdriver, With Wing Handle

Blade high alloy CVM steel, hardened, black finish.  
Wing handle high quality plastic, impact resistant.

| Item  |      |    |      |    |      |    |      |      |      |
|-------|------|----|------|----|------|----|------|------|------|
| No.   | Size | mm | Inch | mm | Inch | mm | Inch | lbs. | pkg. |
| 36540 | IP5  | 35 | 1.4  | 70 | 2.7  | 40 | 1.6  | .02  | 10   |
| 36542 | IP6  | 35 | 1.4  | 70 | 2.7  | 40 | 1.6  | .02  | 10   |
| 36544 | IP7  | 35 | 1.4  | 70 | 2.7  | 40 | 1.6  | .02  | 10   |
| 36546 | IP8  | 40 | 1.6  | 75 | 3.0  | 40 | 1.6  | .02  | 10   |
| 36548 | IP9  | 40 | 1.6  | 75 | 3.0  | 40 | 1.6  | .02  | 10   |
| 36550 | IP10 | 40 | 1.6  | 75 | 3.0  | 40 | 1.6  | .02  | 10   |
| 36552 | IP15 | 45 | 1.8  | 80 | 3.1  | 40 | 1.6  | .02  | 10   |
| 36554 | IP20 | 45 | 1.8  | 80 | 3.1  | 40 | 1.6  | .02  | 10   |

### 36592 TORXPlus® 7 Pc. Wing Handle

Set In Metal Stand

Equipped with IP6, IP7, IP8, IP9,  
IP10, IP15, IP20

| Item  |      |      |
|-------|------|------|
| No.   | lbs. | pkg. |
| 36592 | .38  | 1    |





## Wiha TORXPlus® Cushion Grip Drivers



Not for use in standard Torx fasteners

### 362 TORXPlus® Screwdriver With Wiha SoftFinish Handle

Round blade high alloy Chrome-vanadium-molybdenum tool steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 36211    | IP6  | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36223    | IP7  | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .06  | 10   |
| 36228    | IP8  | 60  | 2.4  | 4.0 | .157 | 171 | 6.7  | .10  | 10   |
| 36229    | IP9  | 60  | 2.4  | 4.0 | .157 | 171 | 6.7  | .11  | 10   |
| 36233    | IP10 | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .11  | 10   |
| 36238    | IP15 | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .11  | 10   |
| 36239    | IP20 | 100 | 3.9  | 4.5 | .177 | 211 | 8.3  | .11  | 10   |
| 36243    | IP25 | 100 | 3.9  | 5.5 | .216 | 211 | 8.3  | .19  | 10   |
| 36248    | IP27 | 115 | 4.5  | 6.0 | .236 | 233 | 9.2  | .20  | 10   |
| 36253    | IP30 | 115 | 4.5  | 7.0 | .275 | 233 | 9.2  | .28  | 10   |
| 36255    | IP40 | 130 | 5.1  | 7.0 | .275 | 254 | 10.0 | .28  | 10   |



### 36299 Set 7 Pcs. TORXPlus® Blade high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish handle, multi-component.

| Item No. | Size       | mm  | Size       | mm  | lbs. |
|----------|------------|-----|------------|-----|------|
| 36299    | 36228 IP8  | 60  | 36243 IP25 | 100 | 1.23 |
|          | 36233 IP10 | 80  | 36253 IP30 | 115 |      |
|          | 36238 IP15 | 80  | 36255 IP40 | 130 |      |
|          | 36239 IP20 | 100 |            |     |      |



### 36296 Set 6 Pcs. TORXPlus®

Blade high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish handle, multi-component.

| Item No. | Size      | mm | Size       | mm | lbs. |
|----------|-----------|----|------------|----|------|
| 36296    | 36211 IP6 | 60 | 36229 IP9  | 60 | .72  |
|          | 36213 IP7 | 60 | 36233 IP10 | 80 |      |
|          | 36228 IP8 | 60 | 36238 IP15 | 80 |      |

## Wiha T-handle TORXPlus®



Not for use in standard Torx fasteners

### 364 TORXPlus® Screwdriver, With Wiha T-handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha T-handle high quality plastic, impact resistant.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 36461    | IP9  | 100 | 3.9  | 4.0 | .157 | 80  | 3.1  | .07  | 10   |
| 36463    | IP10 | 100 | 3.9  | 4.0 | .157 | 80  | 3.1  | .07  | 10   |
| 36466    | IP15 | 100 | 3.9  | 4.0 | .157 | 80  | 3.1  | .07  | 10   |
| 36469    | IP20 | 100 | 3.9  | 4.0 | .157 | 80  | 3.1  | .10  | 10   |
| 36472    | IP25 | 150 | 5.9  | 8.0 | .315 | 120 | 4.7  | .13  | 10   |
| 36474    | IP27 | 150 | 5.9  | 8.0 | .315 | 120 | 4.7  | .14  | 10   |
| 36476    | IP30 | 150 | 5.9  | 8.0 | .315 | 120 | 4.7  | .16  | 10   |
| 36478    | IP40 | 150 | 5.9  | 8.0 | .315 | 120 | 4.7  | .20  | 10   |




### 36496 Set 6 Pc. TORXPlus® T-handles

Blade CVM steel, hardened, hard chromed. Chromtop blade tips. Wiha T-handle high quality plastic, impact resistant.

| Item No. | Size       | mm  | Size       | mm  | lbs. |
|----------|------------|-----|------------|-----|------|
| 36496    | 36463 IP10 | 100 | 36472 IP25 | 150 | 1.01 |
|          | 36466 IP15 | 100 | 36474 IP27 | 150 |      |
|          | 36469 IP20 | 100 | 36476 IP30 | 150 |      |

## TORXPlus®

For Improved Torque and Longer Tool Life



Not for use in standard  
Torx fasteners

### 361 TORXPlus® L-key, Short Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

| Item No. | Size | mm | Inch | mm | Inch | lbs. | pkg. |
|----------|------|----|------|----|------|------|------|
| 36106    | IP6  | 39 | 1.5  | 16 | .6   | .01  | 10   |
| 36107    | IP7  | 42 | 1.7  | 16 | .6   | .01  | 10   |
| 36108    | IP8  | 45 | 1.8  | 16 | .6   | .01  | 10   |
| 36109    | IP9  | 48 | 1.9  | 16 | .6   | .01  | 10   |
| 36110    | IP10 | 51 | 2.0  | 17 | .7   | .01  | 10   |
| 36115    | IP15 | 55 | 2.2  | 19 | .7   | .01  | 10   |
| 36120    | IP20 | 58 | 2.3  | 19 | .7   | .01  | 10   |
| 36125    | IP25 | 63 | 2.5  | 21 | .8   | .01  | 10   |
| 36127    | IP27 | 68 | 2.7  | 22 | .9   | .02  | 10   |
| 36130    | IP30 | 73 | 2.9  | 24 | .9   | .03  | 10   |
| 36140    | IP40 | 81 | 3.2  | 26 | 1.0  | .05  | 10   |



Not for use in standard  
Torx fasteners

### 366 TORXPlus® L-key, Long Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

| Item No. | Size | mm  | Inch | mm | Inch | lbs. | pkg. |
|----------|------|-----|------|----|------|------|------|
| 36606    | IP6  | 64  | 2.5  | 14 | .6   | .01  | 10   |
| 36607    | IP7  | 68  | 2.7  | 14 | .6   | .01  | 10   |
| 36608    | IP8  | 74  | 2.9  | 15 | .6   | .01  | 10   |
| 36609    | IP9  | 78  | 3.1  | 16 | .6   | .01  | 10   |
| 36610    | IP10 | 83  | 3.3  | 18 | .7   | .01  | 10   |
| 36615    | IP15 | 88  | 3.5  | 18 | .7   | .02  | 10   |
| 36620    | IP20 | 94  | 3.7  | 18 | .7   | .02  | 10   |
| 36625    | IP25 | 98  | 3.9  | 19 | .7   | .03  | 10   |
| 36627    | IP27 | 107 | 4.2  | 23 | .9   | .05  | 10   |
| 36630    | IP30 | 114 | 4.5  | 24 | .9   | .06  | 10   |
| 36640    | IP40 | 118 | 4.6  | 27 | 1.0  | .09  | 10   |



### 36197 TORXPlus® L-key, Short Arm, 7 Pc. Set In Holder

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.


| Item No. | lbs. | pkg. | Set includes the following L-keys:   |
|----------|------|------|--------------------------------------|
| 36197    | .10  | 1    | IP6, IP7, IP8, IP9, IP10, IP15, IP20 |



### 36690 TORXPlus® L-key, Long Arm, 7 Pc. Set In Holder

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

| Item No. | lbs. | pkg. | Set includes the following L-keys:   |
|----------|------|------|--------------------------------------|
| 36690    | .22  | 1    | IP6, IP7, IP8, IP9, IP10, IP15, IP20 |



### 36199 TORXPlus® L-key, Short Arm, 9 Pc. Set In Holder

Set includes the following L-keys:

| Item No. | lbs. | pkg. | Set includes the following L-keys:                 |
|----------|------|------|----------------------------------------------------|
| 36199    | .30  | 1    | IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30, IP40 |



### 36691 TORXPlus® L-key, Long Arm, 9 Pc. Set In Holder

Set includes the following L-keys:

| Item No. | lbs. | pkg. | Set includes the following L-keys:                 |
|----------|------|------|----------------------------------------------------|
| 36691    | .35  | 1    | IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30, IP40 |

## Wiha MagicSpring TORX® Tools

- Laser welded assembly
- Holds screws securely
- Won't damage screws
- Doesn't weaken tool
- Exact fit tips
- Hardened tool steel blades
- Holds standard Torx screws\*

### Screw Holding TORX®



Stainless Rotary Spring

### Laser Welded MagicSpring Assembly



**362 MagicSpring Screw Holding TORX® Driver, With Wiha-SoftFinish® Handle** Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item No. | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|-----|------|------|------|
| 36202    | T6   | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .07  | 10   |
| 36203    | T7   | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .07  | 10   |
| 36207    | T8   | 60  | 2.4  | 3.5 | .139 | 164 | 6.5  | .07  | 10   |
| 36234    | T9   | 60  | 2.4  | 4.0 | .157 | 171 | 6.7  | .11  | 10   |
| 36244    | T10  | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .11  | 10   |
| 36249    | T15  | 80  | 3.1  | 4.0 | .157 | 191 | 7.5  | .11  | 10   |
| 36254    | T20  | 100 | 3.9  | 4.0 | .157 | 211 | 8.3  | .16  | 10   |
| 36256    | T25  | 100 | 3.9  | 4.5 | .177 | 211 | 8.3  | .17  | 10   |
| 36257    | T27  | 115 | 4.5  | 5.5 | .216 | 233 | 9.2  | .20  | 10   |
| 36258    | T30  | 115 | 4.5  | 6.0 | .236 | 233 | 9.2  | .21  | 10   |

**267 MagicSpring Screw Holding TORX® Driver, With Wiha-Precision PicoFinish Handle** Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-Pico Finish precision handle, molded on, soft grips.

| Item No. | Size | mm | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|----|------|-----|------|------|------|
| 26721    | T6   | 40 | 1.6  | 140 | 5.5  | .03  | 10   |
| 26723    | T7   | 40 | 1.6  | 140 | 5.5  | .03  | 10   |
| 26725    | T8   | 40 | 1.6  | 140 | 5.5  | .03  | 10   |
| 26727    | T9   | 50 | 2.0  | 150 | 5.9  | .04  | 10   |
| 26729    | T10  | 50 | 2.0  | 150 | 5.9  | .04  | 10   |
| 26731    | T15  | 60 | 2.4  | 160 | 6.3  | .04  | 10   |



**36290 Set 6 Pcs. MagicSpring Screw Holding TORX® SoftFinish Screwdrivers** Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips. Molded on.

| Item No. | Size      | mm | Size      | mm  | lbs. |
|----------|-----------|----|-----------|-----|------|
| 36290    | 36207 T8  | 60 | 36254 T20 | 100 | .98  |
|          | 36244 T10 | 80 | 36256 T25 | 100 |      |
|          | 36249 T15 | 80 | 36258 T30 | 115 |      |

**26798 Set 6 Pcs. MagicSpring Screw Holding TORX® Screwdriver, With Wiha-Precision PicoFinish Handle** Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-Pico Finish precision handle, molded on, soft grips.

| Item No. | Size     | mm | Size      | mm | lbs. |
|----------|----------|----|-----------|----|------|
| 26798    | 26721 T6 | 40 | 26727 T9  | 50 | .45  |
|          | 26723 T7 | 40 | 26729 T10 | 50 |      |
|          | 26725 T8 | 40 | 26731 T15 | 60 |      |

\*MagicSpring tools will hold Torx® screws made to CamCar Textron Torx® specifications

## Wiha MagicSpring TORX® Tools



### 371 MagicSpring Screw Holding TORX® L-key, Long Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

| Item No. | Size | mm | Inch | lbs. | pkg. |
|----------|------|----|------|------|------|
| 37106    | T6   | 14 | .55  | .001 | 10   |
| 37107    | T7   | 16 | .63  | .002 | 10   |
| 37108    | T8   | 18 | .71  | .003 | 10   |
| 37109    | T9   | 19 | .75  | .005 | 10   |
| 37110    | T10  | 21 | .83  | .007 | 10   |
| 37115    | T15  | 22 | .87  | .009 | 10   |
| 37120    | T20  | 25 | .98  | .01  | 10   |
| 37125    | T25  | 28 | 1.1  | .02  | 10   |
| 37127    | T27  | 30 | 1.2  | .03  | 10   |
| 37130    | T30  | 34 | 1.3  | .04  | 10   |
| 37140    | T40  | 36 | 1.4  | .07  | 10   |



### 37190 MagicSpring Long Arm Screw Holding TORX® Set, 7 Pc. in Plastic Holder

Equipped with T6, T7, T8, T9, T10, T15, T20

| Item No. | lbs. | pkg. |
|----------|------|------|
| 37190    | .20  | 1    |



### 37192 MagicSpring Long Arm Screw Holding TORX® Set, 10 Pc. in Plastic Holder

Equipped with T6, T7, T8, T9, T10, T15, T20, T25, T27, T30

| Item No. | lbs. | pkg. |
|----------|------|------|
| 37192    | .35  | 1    |

## Wiha MagicSpring TORX® Tools



### 365 MagicSpring Screw Holding TORX® driver, With Wing Handle

Ideal for use with indexable carbide tooling and also for working in confined spaces. Blade high alloy CVM steel, hardened, black finish. Wing handle high quality plastic, impact resistant. Molded on.

| Item No. | Size | mm | Inch | mm | Inch | mm | Inch | lbs. | pkg. |
|----------|------|----|------|----|------|----|------|------|------|
| 36556    | T6   | 35 | 1.4  | 70 | 2.7  | 40 | 1.6  | .01  | 10   |
| 36557    | T7   | 35 | 1.4  | 70 | 2.7  | 40 | 1.6  | .02  | 10   |
| 36558    | T8   | 40 | 1.6  | 75 | 3.0  | 40 | 1.6  | .02  | 10   |
| 36559    | T9   | 40 | 1.6  | 75 | 3.0  | 40 | 1.6  | .02  | 10   |
| 36560    | T10  | 40 | 1.6  | 75 | 3.0  | 40 | 1.6  | .02  | 10   |
| 36561    | T15  | 45 | 1.8  | 80 | 3.1  | 40 | 1.6  | .02  | 10   |
| 36562    | T20  | 45 | 1.8  | 80 | 3.1  | 40 | 1.6  | .02  | 10   |



### 36598 MagicSpring Screw Holding TORX® Wing Handle Set, 7 Pc. in Metal Stand

Equipped with T6, T7, T8, T9, T10, T15, T20 .36 lbs.



Screw Holding TORX® Tools



## Wiha TorqueControl Screwdrivers


Molded cushion grip two component handles allow for maximum achievable torque to be reached with comfort

### Precise repeatability!

All TorqueVario tools are tested and comply with:

- EN ISO 6798
- BS EN 26789
- ASME B107.14M

Each tool has unique serial number and certificate of calibration



TorqueVario models include torque setting adjustment tool

and Micro Bit holder

See 4mm Micro Bits on Page 28

Direct Reading Scale



+/-6% accuracy tolerance  
Certificate of calibration

### 285 Adjustable TorqueVario With Direct Reading Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

| Item No. | Range           |             |           |      |      |
|----------|-----------------|-------------|-----------|------|------|
|          | Inch lbs.       | Increments  | mm        | lbs. | pkg. |
| 28501    | 15 - 80 (in/oz) | 2.5 Inch oz | 122 - 127 | .22  | 1    |
| 28502    | 5 - 10          | .2 Inch lbs | 122 - 127 | .41  | 1    |
| 28504    | 7.5 - 20        | .5 Inch lbs | 126 - 131 | .50  | 1    |
| 28506    | 10 - 50         | 2 Inch lbs  | 133 - 138 | .59  | 1    |
| 28508    | 20 - 70         | 2 Inch lbs  | 137 - 142 | .74  | 1    |

Above includes Micro Bit Holder 28583

See 4mm Micro Bits on Page 28

\* +/- 10% (This unit only)



+/-6% accuracy tolerance  
Certificate of calibration

### 285 Adjustable TorqueVario-S Handle - In Newton Meter Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

| Item No. | Newton Meter Scale | Increments | mm        | lbs. | pkg. |
|----------|--------------------|------------|-----------|------|------|
| 28550    | 0.1 - 0.6 Nm       | .02 Nm     | 122 - 127 | .35  | 1    |
| 28551    | 0.4 - 1.0 Nm       | .05 Nm     | 122 - 127 | .35  | 1    |
| 28552    | 0.8 - 2.0 Nm       | .05 Nm     | 126 - 131 | .45  | 1    |
| 28553    | 1.0 - 5.0 Nm       | .20 Nm     | 133 - 138 | .55  | 1    |
| 28554    | 2.0 - 8.0 Nm       | .25 Nm     | 137 - 142 | .70  | 1    |

\* +/- 10% (This unit only)



### 285 TORX® Interchangeable Blades For TorqueFix & TorqueVario

TORX® tip blades on narrow 5/32 Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

| Item No. | Size | mm  | mm  | lbs. | Nm  | pkg. |
|----------|------|-----|-----|------|-----|------|
| 28561    | T5   | 175 | 4.0 | .07  | 0.4 | 1    |
| 28562    | T6   | 175 | 4.0 | .07  | 0.6 | 1    |
| 28563    | T7   | 175 | 4.0 | .07  | 0.9 | 1    |
| 28564    | T8   | 175 | 4.0 | .07  | 1.3 | 1    |
| 28565    | T9   | 175 | 4.0 | .07  | 2.5 | 1    |
| 28566    | T10  | 175 | 4.0 | .07  | 3.5 | 1    |
| 28567    | T15  | 175 | 4.0 | .07  | 5.5 | 1    |
| 28568    | T20  | 175 | 4.0 | .07  | 8.0 | 1    |
| 28569    | T25  | 175 | 4.0 | .07  | 8.0 | 1    |



### 285 TORXPlus® Blades For TorqueFix & TorqueVario

TORXPlus® tip blades on narrow 5/32 Hex shafts.

| Item No. | Size | mm  | mm  | lbs. | Nm  | pkg. |
|----------|------|-----|-----|------|-----|------|
| 28571    | IP5  | 175 | 4.0 | .07  | 0.5 | 1    |
| 28572    | IP6  | 175 | 4.0 | .07  | 0.8 | 1    |
| 28573    | IP7  | 175 | 4.0 | .07  | 1.3 | 1    |
| 28574    | IP8  | 175 | 4.0 | .07  | 2.0 | 1    |
| 28575    | IP9  | 175 | 4.0 | .07  | 3.0 | 1    |
| 28576    | IP10 | 175 | 4.0 | .07  | 4.5 | 1    |
| 28577    | IP15 | 175 | 4.0 | .07  | 6.6 | 1    |
| 28578    | IP20 | 175 | 4.0 | .07  | 8.0 | 1    |
| 28579    | IP25 | 175 | 4.0 | .07  | 8.0 | 1    |



### 285 MagicSpring TORX® Interchangeable Blades For TorqueFix & TorqueVario blades on narrow 5/32 Hex shafts.

| Item No. | Size | mm  | mm  | lbs. | Nm  | pkg. |
|----------|------|-----|-----|------|-----|------|
| 28512    | T6   | 175 | 4.0 | .07  | 0.6 | 1    |
| 28527    | T7   | 175 | 4.0 | .07  | 0.9 | 1    |
| 28528    | T8   | 175 | 4.0 | .07  | 1.3 | 1    |
| 28529    | T9   | 175 | 4.0 | .07  | 2.5 | 1    |
| 28530    | T10  | 175 | 4.0 | .07  | 3.8 | 1    |
| 28531    | T15  | 175 | 4.0 | .07  | 5.5 | 1    |
| 28532    | T20  | 175 | 4.0 | .07  | 8.0 | 1    |
| 28533    | T25  | 175 | 4.0 | .07  | 8.0 | 1    |



Screw Holding



### 286 MagicSpring TORXPlus® Interchangeable Blades For TorqueFix & TorqueVario blades on narrow 5/32 Hex shafts.

| Item No. | Size | mm  | mm  | lbs. | Nm  | pkg. |
|----------|------|-----|-----|------|-----|------|
| 28611    | IP6  | 175 | 4.0 | .07  | 0.8 | 1    |
| 28612    | IP7  | 175 | 4.0 | .07  | 1.3 | 1    |
| 28613    | IP8  | 175 | 4.0 | .07  | 2.0 | 1    |
| 28614    | IP9  | 175 | 4.0 | .07  | 3.0 | 1    |
| 28616    | IP10 | 175 | 4.0 | .07  | 4.5 | 1    |
| 28617    | IP15 | 175 | 4.0 | .07  | 6.6 | 1    |
| 28618    | IP20 | 175 | 4.0 | .07  | 8.0 | 1    |
| 28619    | IP25 | 175 | 4.0 | .07  | 8.0 | 1    |



Screw Holding

## Wiha Easy Torque Handles



- Audible Click At Torque
- Replaceable Blades
- +/- 10% Repeatability
- Improve Productivity
- Reduces Waste
- Controls Costs
- Save Time!

### 292 Easy Torque Screwdriver Handle

Easy Torque value pre-set. Release accuracy +/- 10%.  
SoftFinish cushion grip handle for good power transfer.

| Item No. | Pre-Sets  |     |     |      |      |      |
|----------|-----------|-----|-----|------|------|------|
|          | Inch/lbs. | Nm  | mm  | Inch | lbs. | pkg. |
| 29205    | 4.4       | 0.5 | 137 | 5.4  | .20  | 1    |
| 29206    | 5.3       | 0.6 | 137 | 5.4  | .20  | 1    |
| 29209    | 8.0       | 0.9 | 137 | 5.4  | .20  | 1    |
| 29211    | 9.7       | 1.1 | 137 | 5.4  | .20  | 1    |
| 29212    | 10.6      | 1.2 | 137 | 5.4  | .20  | 1    |
| 29214    | 12.4      | 1.4 | 137 | 5.4  | .20  | 1    |
| 29220    | 17.7      | 2.0 | 137 | 5.4  | .20  | 1    |
| 29225    | 22.1      | 2.5 | 137 | 5.4  | .20  | 1    |
| 29230    | 26.6      | 3.0 | 137 | 5.4  | .20  | 1    |
| 29238    | 33.6      | 3.8 | 137 | 5.4  | .20  | 1    |
| 29241    | 35.4      | 4.0 | 137 | 5.4  | .20  | 1    |
| 29245    | 39.8      | 4.5 | 137 | 5.4  | .20  | 1    |
| 29251    | 44.2      | 5.0 | 137 | 5.4  | .20  | 1    |

\* No Calibration Certificates

## ESD Safe Adjustable TorqueControl Tools

Handle sizes proportioned  
to optimize torque range



Includes Certificate

### 285 ESD Safe TorqueVario-S, With Window Scale

EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 6% Accuracy  
Ergonomic multi-component handle, light and compact.  
Audible and perceptible click when torque setting has been attained.

| Item No. | Range          |             |           |      |      |
|----------|----------------|-------------|-----------|------|------|
|          | Inch lbs.      | Increments  | mm        | lbs. | pkg. |
| 28522*   | 15 - 80(in/oz) | 2.5 Inch oz | 122 - 127 | .33  | 1    |
| 28524    | 5 - 10         | .2 Inch lbs | 122 - 127 | .34  | 1    |
| 28526    | 7.5 - 20       | .5 Inch lbs | 126 - 131 | .42  | 1    |

\* +/- 10% (This unit only)



### 288 ESD Safe TORX® Interchangeable Blades For

TorqueVario-S TORX® tip blades on narrow 5/32" Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, hard chromed.

| Item No. | Size | mm  | mm  | lbs. | Nm  | pkg. |
|----------|------|-----|-----|------|-----|------|
| 28825    | T5   | 175 | 4.0 | .07  | 0.4 | 1    |
| 28826    | T6   | 175 | 4.0 | .07  | 0.6 | 1    |
| 28827    | T7   | 175 | 4.0 | .07  | 0.9 | 1    |
| 28828    | T8   | 175 | 4.0 | .07  | 1.3 | 1    |
| 28829    | T9   | 175 | 4.0 | .07  | 2.5 | 1    |
| 28830    | T10  | 175 | 4.0 | .07  | 3.8 | 1    |

## Wiha Insulated TorqueControl Tools



**1000V**

Includes Certificate

### 287 Insulated TorqueVario-S, With Window Scale Insulation

up to 1000 Volt. EN ISO 6798, BS EN 26789, ASME B107.14M, VDE, ASTM F-1505-01 & NFPA70E, +/- 6% Accuracy. Handle sizes proportioned to optimize torque range. Audible and perceptible click when torque setting has been attained. Includes *SlimLine* blade holder.

| Item No. | Range     |             |           |      |      |
|----------|-----------|-------------|-----------|------|------|
|          | Inch lbs. | Increments  | mm        | lbs. | pkg. |
| 28724    | 7.5 - 20  | .5 Inch lbs | 126 - 131 | .43  | 1    |
| 28726    | 10 - 50   | 2 Inch lbs  | 133 - 138 | .40  | 1    |
| 28727    | 20 - 70   | 2 Inch lbs  | 137 - 142 | .69  | 1    |

**Each TorqueVario handle has unique serial number and certificate of calibration**

### 287 Insulated TorqueVario-S Handle - In Newton Meter Scale

Includes *SlimLine* blade holder.

| Item No. | Range     |     |      |      |  |
|----------|-----------|-----|------|------|--|
|          | Nm        | mm  | lbs. | pkg. |  |
| 28734    | 0.6 - 2.0 | 131 | .45  | 1    |  |
| 28736    | 1.0 - 5.0 | 138 | .45  | 1    |  |
| 28737    | 2.0 - 8.0 | 142 | .72  | 1    |  |

**Each TorqueVario handle has unique serial number and certificate of calibration**



### 283 Insulated TORX® SlimLine Blades

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter than standard insulated tools.

| Item No. | Size | mm | Dia. | Length | Max Nm | Inch/ lbs. | lbs. | Pkg. |
|----------|------|----|------|--------|--------|------------|------|------|
| 28339    | T8   | 90 | 4.1  | 2.8"   | 1.3    | 11.5       | .02  | 1    |
| 28340    | T10  | 90 | 4.1  | 2.8"   | 3.8    | 33.7       | .02  | 1    |
| 28341    | T15  | 90 | 6.1  | 2.8"   | 5.5    | 48.8       | .02  | 1    |
| 28342    | T20  | 90 | 6.1  | 2.8"   | 5.5    | 48.8       | .02  | 1    |

## TorqueControl Tools



With Certificate  
of Calibration

### 28597 Set 8 Pc. TorqueControl Set With **TORX**® Blades

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M

**TORX**®: T7, T8, T9, T10, T15, T20



lbs.

1.01

28597 28506 Handle Range 10 - 50 Inch lbs.



With Certificate  
of Calibration

### 28598 Set 8 Pc. TorqueControl Set With **TORXPlus**® Blades

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M

**TORXPlus**®: IP7, IP8, IP9, IP10, IP15, IP20



lbs.

1.00

28506 Handle Range 10 - 50 Inch lbs.



With Certificate  
of Calibration

### 28599 14 Pc. TorqueControl Set With **TORX**® & **TORXPlus**® Blades

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes Ergonomic multi-component adjustable TorqueVario-S handle, 12 blades & Torque adjustment tool. Packed in a durable canvas pouch.

Item No.

28599 **TORX**®: T7, T8, T9, T10, T15, T20

**TORXPlus**®: IP7, IP8, IP9, IP10, IP15, IP20

28506 - Handle Range 10 - 50 Inch lbs.



lbs.

1.25

With Certificate of Calibration



With Certificate  
of Calibration

Certified to  
EN ISO 6798,  
BS EN 26789,  
ASME B107.14M

### 28690 Set 8 Pc. TorqueControl Set With MagicSpring **TORX**® Screw Holding Blades

28690 MagicSpring **TORX**®:

T7, T8, T9, T10, T15, T20

28506 Handle Range 10 - 50 Inch lbs.



lbs.

1.00

## T-handle TorqueControl Tools



Includes  
Calibration  
Certificate

Ergonomic multi-component  
handle, light and compact.



### 289 TorqueFix T-handle

EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 6% Accuracy.

| Item No. | Torque In-lbs. | Torque Nm | mm x mm  | lbs. | pkg. |
|----------|----------------|-----------|----------|------|------|
| 28931    | 53.1           | 6         | 56 x 120 | .81  | 1    |
| 28933    | 70.8           | 8         | 56 x 120 | .82  | 1    |
| 28935    | 88.5           | 10        | 56 x 120 | .79  | 1    |
| 28937    | 106.2          | 12        | 56 x 120 | .79  | 1    |
| 28938    | 110.6          | 12.5      | 56 x 120 | .80  | 1    |
| 28939    | 123.9          | 14        | 56 x 120 | .80  | 1    |

### 28940 Adjustable TorqueVario STplus T-handle

| Item No. | Torque In-lbs. | Torque Nm | mm x mm  | lbs. | pkg. |
|----------|----------------|-----------|----------|------|------|
| 28940    | 44.3-123.9     | 5-14      | 56 x 120 | .81  | 1    |

\* (1 Nm 8.8507)



### 289 **TORX**® Interchangeable Blades For TorqueFix T-Handle

**TORX**® tip blades on 6mm Hex shafts.

| Item No. | Size | mm  | Inch | mm  | lbs. | pkg. |
|----------|------|-----|------|-----|------|------|
| 28903    | T15  | 130 | 5.1  | 6.0 | .07  | 1    |
| 28904    | T20  | 130 | 5.1  | 6.0 | .07  | 1    |
| 28905    | T25  | 130 | 5.1  | 6.0 | .07  | 1    |
| 28906    | T27  | 130 | 5.1  | 6.0 | .07  | 1    |
| 28907    | T30  | 130 | 5.1  | 6.0 | .07  | 1    |
| 28908    | T40  | 130 | 5.1  | 6.0 | .07  | 1    |



### 289 **TORXPlus**® Interchangeable Blades For TorqueFix

**TORXPlus**® T-Handle tip blades on 6mm Hex shafts.

| Item No. | Size | mm  | Inch | mm  | lbs. | pkg. |
|----------|------|-----|------|-----|------|------|
| 28910    | IP15 | 130 | 5.1  | 6.0 | .07  | 1    |
| 28911    | IP20 | 130 | 5.1  | 6.0 | .07  | 1    |
| 28912    | IP25 | 130 | 5.1  | 6.0 | .07  | 1    |
| 28913    | IP27 | 130 | 5.1  | 6.0 | .07  | 1    |
| 28914    | IP30 | 130 | 5.1  | 6.0 | .07  | 1    |
| 28915    | IP40 | 130 | 5.1  | 6.0 | .07  | 1    |

## Precision ESD Safe TORX® Drivers



### 278 TORX® Screwdriver, With Precision ESD Safe Dissipative

**Handle** Blade high alloy CVM steel. Hard chrome finished. Handle impact resistant, dissipative material. ESD standard IEC 61340-5-1

| Item  |      |    |      |     |      |      |      |
|-------|------|----|------|-----|------|------|------|
| No.   | Size | mm | Inch | mm  | Inch | lbs. | pkg. |
| 27801 | T1   | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27802 | T2   | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27803 | T3   | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27804 | T4   | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27805 | T5   | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27811 | T6   | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27817 | T7   | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27823 | T8   | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27829 | T9   | 50 | 2.0  | 145 | 5.7  | .04  | 10   |
| 27835 | T10  | 50 | 2.0  | 145 | 5.7  | .04  | 10   |
| 27841 | T15  | 60 | 2.4  | 170 | 6.7  | .07  | 10   |
| 27847 | T20  | 60 | 2.4  | 170 | 6.7  | .07  | 10   |

\*Metric dimensions actual - Inch dimensions approximate



### 27890 Set 7 Pcs. TORX® Precision ESD Safe Dissipative Handle

**Blade** high alloy CVM steel, hardened, hard chromed. **Handle** manufactured from impact resistant, dissipative material.

| Item  |          |    |           |    |      |  |
|-------|----------|----|-----------|----|------|--|
| No.   | Size     | mm | Size      | mm | lbs. |  |
| 27890 | 27804 T4 | 40 | 27823 T8  | 40 | .31  |  |
|       | 27805 T5 | 40 | 27829 T9  | 50 |      |  |
|       | 27811 T6 | 40 | 27835 T10 | 50 |      |  |
|       | 27817 T7 | 40 |           |    |      |  |



### 27899 Set 8 Pcs. TORX® Precision ESD Safe Dissipative

**Handle** Set In Pouch Blade high alloy CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material.

| Item  |          |    |                   |    |      |
|-------|----------|----|-------------------|----|------|
| No.   | Size     | mm | Size              | mm | lbs. |
| 27899 | 27801 T1 | 40 | 27805 T5          | 40 | .30  |
|       | 27802 T2 | 40 | 27806 T6          | 40 |      |
|       | 27803 T3 | 40 | 27807 T7          | 40 |      |
|       | 27804 T4 | 40 | 27920 Chip Lifter |    |      |

## Precision ESD Safe TORXPlus® Drivers



### 278 TORXPlus® Driver, With Precision ESD Safe Dissipative

**Handle** Blade high alloy CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material. ESD standard IEC 61340-5-1

| Item  |      |    |      |     |      |      |      |
|-------|------|----|------|-----|------|------|------|
| No.   | Size | mm | Inch | mm  | Inch | lbs. | pkg. |
| 27850 | IP4  | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27851 | IP5  | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27852 | IP6  | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27853 | IP7  | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27854 | IP8  | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 27855 | IP9  | 50 | 2.0  | 145 | 5.7  | .04  | 10   |
| 27856 | IP10 | 50 | 2.0  | 145 | 5.7  | .04  | 10   |
| 27857 | IP15 | 60 | 2.4  | 170 | 6.7  | .07  | 10   |

\*Metric dimensions actual - Inch dimensions approximate



### 27894 Set 7 Pcs. TORXPlus® Precision ESD Safe Dissipative

**Handle** Blade high alloy CVM steel, hardened, hard chromed.

| Item  |           |    |            |    |      |  |
|-------|-----------|----|------------|----|------|--|
| No.   | Size      | mm | Size       | mm | lbs. |  |
| 27894 | 27851 IP5 | 40 | 27855 IP9  | 50 | .32  |  |
|       | 27852 IP6 | 40 | 27856 IP10 | 50 |      |  |
|       | 27853 IP7 | 40 | 27857 IP15 | 60 |      |  |
|       | 27854 IP8 | 40 |            |    |      |  |

## Wiha TORX® Precision Series



### 26799 Set 8 Pcs. TORX® Drivers In Canvas Pouch

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In storage pouch

| Item  |          |    |           |    |      |  |
|-------|----------|----|-----------|----|------|--|
| No.   | Size     | mm | Size      | mm | lbs. |  |
| 26799 | 26703 T3 | 40 | 26707 T7  | 40 | .50  |  |
|       | 26704 T4 | 40 | 26708 T8  | 40 |      |  |
|       | 26705 T5 | 40 | 26709 T9  | 50 |      |  |
|       | 26706 T6 | 40 | 26710 T10 | 50 |      |  |



## Wiha TORX® Precision Series



### 267 TORX® Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

| Item No. | Size | mm | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|----|------|-----|------|------|------|
| 26701    | T1   | 40 | 1.6  | 120 | 4.7  | .01  | 10   |
| 26702    | T2   | 40 | 1.6  | 120 | 4.7  | .02  | 10   |
| 26703    | T3   | 40 | 1.6  | 120 | 4.7  | .02  | 10   |
| 26704    | T4   | 40 | 1.6  | 120 | 4.7  | .02  | 10   |
| 26705    | T5   | 40 | 1.6  | 120 | 4.7  | .02  | 10   |
| 26706    | T6   | 40 | 1.6  | 120 | 4.7  | .02  | 10   |
| 26707    | T7   | 40 | 1.6  | 120 | 4.7  | .02  | 10   |
| 26708    | T8   | 40 | 1.6  | 120 | 4.7  | .03  | 10   |
| 26709    | T9   | 50 | 2.0  | 145 | 5.7  | .03  | 10   |
| 26710    | T10  | 50 | 2.0  | 145 | 5.7  | .03  | 10   |
| 26715    | T15  | 60 | 2.4  | 170 | 6.7  | .05  | 10   |
| 26720    | T20  | 60 | 2.4  | 170 | 6.7  | .05  | 10   |

\*Metric dimensions actual - Inch dimensions approximate



### 26790 Set 6 Pcs. TORX® Driver

Blade high alloy CVM steel.

| Item No. | Size      | mm | lbs. |
|----------|-----------|----|------|
| 26790    | 26706 T6  | 40 | .25  |
|          | 26707 T7  | 40 |      |
|          | 26708 T8  | 40 |      |
|          | 26709 T9  | 50 |      |
|          | 26710 T10 | 50 |      |
|          | 26715 T15 | 60 |      |



### 26791 Set 8 Pcs. TORX® Screwdriver Set

Item No. 26791 T1, T2, T3, T4, T5, T6, T7, T8



### 26792 Set 7 Pcs. TORX® Driver

Blade high alloy CVM steel.

| Item No. | Size      | mm | lbs. |
|----------|-----------|----|------|
| 26792    | 26705 T5  | 40 | .27  |
|          | 26706 T6  | 40 |      |
|          | 26707 T7  | 40 |      |
|          | 26708 T8  | 40 |      |
|          | 26709 T9  | 50 |      |
|          | 26710 T10 | 50 |      |
|          | 26715 T15 | 60 |      |

## Wiha Pico Soft Grip TORX®



### 267 TORX® Screwdriver, With Precision Soft PicoFinish

Handle Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

| Item No. | Size | mm | Inch | mm  | Inch | pkg. |
|----------|------|----|------|-----|------|------|
| 26732    | T1   | 40 | 1.6  | 134 | 5.3  | 10   |
| 26733    | T2   | 40 | 1.6  | 134 | 5.3  | 10   |
| 26735    | T3   | 40 | 1.6  | 134 | 5.3  | 10   |
| 26736    | T4   | 40 | 1.6  | 134 | 5.3  | 10   |
| 26737    | T5   | 40 | 1.6  | 134 | 5.3  | 10   |
| 26739    | T6   | 40 | 1.6  | 140 | 5.5  | 10   |
| 26741    | T7   | 40 | 1.6  | 140 | 5.5  | 10   |
| 26743    | T8   | 40 | 1.6  | 140 | 5.5  | 10   |
| 26745    | T9   | 50 | 2.0  | 150 | 5.9  | 10   |
| 26747    | T10  | 50 | 2.0  | 150 | 5.9  | 10   |
| 26749    | T15  | 60 | 2.4  | 160 | 6.3  | 10   |
| 26751    | T20  | 60 | 2.4  | 160 | 6.3  | 10   |

\*Metric dimensions actual - Inch dimensions approximate



### 26793 Set 8 Pcs. TORX® Precision Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

| Item No. | Size     | mm | lbs. |
|----------|----------|----|------|
| 26793    | 26732 T1 | 40 | .50  |
|          | 26733 T2 | 40 |      |
|          | 26735 T3 | 40 |      |
|          | 26736 T4 | 40 |      |
|          | 26737 T5 | 40 |      |
|          | 26739 T6 | 40 |      |
|          | 26741 T7 | 40 |      |
|          | 26743 T8 | 40 |      |



### 26796 Set 8 Pcs. TORX® Precision Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

| Item No. | Size      | mm | lbs. |
|----------|-----------|----|------|
| 26796    | 26737 T5  | 40 | .57  |
|          | 26739 T6  | 40 |      |
|          | 26741 T7  | 40 |      |
|          | 26743 T8  | 40 |      |
|          | 26745 T9  | 50 |      |
|          | 26747 T10 | 50 |      |
|          | 26749 T15 | 60 |      |
|          | 26751 T20 | 60 |      |

## Wiha SYSTEM 4 Handle, Bits & Sets

### SYSTEM 4 Handles & Micro Bits

#### Tips

Exact fit,  
precision  
machined

#### Rotating Cap

for precise  
turning & control

#### Tapered Handle

allows rapid rotation,  
requires less clearance.  
Static Dissipative  
10<sup>6</sup> - 10<sup>9</sup> ohms

Bits CVM steel,  
hardened

Use bits directly in handle or with 4" bit extension



High alloy CVM steel,  
hardened, on 4 mm stock

#### 757 SYSTEM 4 TORX® Micro Bits

| Item No. | Size | mm | Inch | lbs. |
|----------|------|----|------|------|
| 75703    | T3   | 28 | 1.1  | .01  |
| 75704    | T4   | 28 | 1.1  | .01  |
| 75705    | T5   | 28 | 1.1  | .01  |
| 75706    | T6   | 28 | 1.1  | .01  |
| 75707    | T7   | 28 | 1.1  | .01  |
| 75708    | T8   | 28 | 1.1  | .01  |
| 75709    | T9   | 28 | 1.1  | .01  |
| 75710    | T10  | 28 | 1.1  | .01  |
| 75715    | T15  | 28 | 1.1  | .01  |
| 75720    | T20  | 28 | 1.1  | .01  |



High alloy CVM steel,  
hardened, on 4 mm stock

#### 757 SYSTEM 4 Security TORX® Micro Bits

| Item No. | Size | mm | Inch | lbs. |
|----------|------|----|------|------|
| 75727    | T7s  | 28 | 1.1  | .01  |
| 75728    | T8s  | 28 | 1.1  | .01  |
| 75729    | T9s  | 28 | 1.1  | .01  |
| 75735    | T10s | 28 | 1.1  | .01  |
| 75739    | T15s | 28 | 1.1  | .01  |
| 75742    | T20s | 28 | 1.1  | .01  |



#### 75801 SYSTEM 4 ESD Safe Dissipative Precision Bit Handle with rotating control cap. For Wiha Micro Bits.

##### Advantages:

- For working in ESD sensitive applications
- Surface resistant 10<sup>6</sup>-10<sup>9</sup> Ohms
- Ball retainer holds bits securely in place
- Accepts all SYSTEM 4 Series bits
- 110mm/4.3" OAL



| Item No. | mm  | Inch  | mm   | Inch | lbs. |
|----------|-----|-------|------|------|------|
| 75801    | 4.0 | .1574 | 14.0 | .55  | .06  |

#### 75792 SYSTEM 4 TORX® Precision Interchangeable Bit Set, 11 Pcs. In Compact Fold Out Box

Set includes your choice of Wiha precision handle, bit extension and 9 Wiha interchangeable bits.

##### Item SYSTEM 4

##### No. TORX® Bit Sets

75792 Set with ESD Safe Precision Handle   
Set includes the following bits:

##### TORX® Sizes:

T3, T4, T5, T6, T7, T8, T9, T10, T15

100mm Bit Extension

 lbs. .64



11 Pc. Set



#### 75093 SYSTEM 4 Slotted, Phillips, TORX® Compact ESD Precision Interchangeable Bit Set, 16 Pcs.

##### Item No. Combination Bit Set

75093 Set with Standard Precision Handle 

   Slotted: 1.5, 2.0, 2.5, 3.0mm

 Phillips: 00, 0, 1

 TORX®: T6, T7, T8, T9, T10, T15, T20

 100mm Bit Extension

 lbs. .17



#### 75985 Micro Bit Handle Storage TORX® Bit Set, 7 Pcs.

Wiha precision storage handle & 6 interchangeable bits.

##### Item No. Set with Precision Storage Handle

75985  TORX®: T3, T4, T5, T6, T7, T8

 lbs. .08

## ESD Safe Precision Handles & Blades



**28000 ESD Safe Dissipative Precision Handle** with rotating control cap. Surface resistant  $10^6$ - $10^9$  Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Tapered handle, high quality plastic, impact resistant. Ball retainer hold. 110mm/4.3" OAL

| Item No. | mm  | Inch  | mm   | Inch | lbs. |
|----------|-----|-------|------|------|------|
| 28000    | 4.0 | .1574 | 14.0 | .55  | .04  |



**28001 ESD Safe Dissipative Precision Adjustable Handle** with rotating control cap.

- Use in ESD sensitive applications. Surface resistant  $10^6$ - $10^9$  Ohms.
  - Collet lock allows for quick & easy adjustment.
  - Holds blade securely in place. Accepts all SYSTEM 4 blades.
- 110mm/4.3" OAL

| Item No. | mm  | Inch  | mm   | Inch | lbs. |
|----------|-----|-------|------|------|------|
| 28001    | 4.0 | .1574 | 14.0 | .55  | .04  |



### 269 SYSTEM 4 TORX® Reversible Blade

High alloy CVM steel, hardened, vapor chrome protected, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL.

| Item No. | Size      | Size | lbs. |
|----------|-----------|------|------|
| 26951    | T6 + T8   |      | .03  |
| 26952    | T7 + T9   |      | .03  |
| 26953    | T10 + T15 |      | .03  |
| 26954    | T15 + T20 |      | .03  |



### 269 SYSTEM 4 TORX® Interchangeable Blade

High alloy CVM steel, hardened, Wiha chrome-Top finish on tips. 120mm/4.7" OAL

| Item No. | Size | lbs. |
|----------|------|------|
| 26955    | T3   | .03  |
| 26956    | T4   | .03  |
| 26957    | T5   | .03  |



**28087 TORX® Precision Interchangeable Blade Set, 8 Pcs.** Wiha ESD Safe precision collet lock handle & 7 Wiha blades.

28087 Set includes the following blades:

**TORX®** Sizes on standard blades: T3, T4, T5

**TORX®** Sizes on reversible blades:

T6, T7, T8, T9, T10, T15, T20

lbs. .31



## TORX® ESD Safe SYSTEM 4 Blade Sets



**26995 TORX® Precision Interchangeable Blade Set, 5 Pcs.** Wiha ESD Safe precision collet lock handle & 4 interchangeable blades.

26995 Set includes the following blades:

**TORX®** Sizes:

T6, T7, T8, T9, T10, T15, T20

lbs. .54



**26987 TORX® Precision Interchangeable Blade Set, 8 Pcs.** Wiha ESD Safe precision collet lock handle and 7 interchangeable blades.

26987 Set includes the following blades:

**TORX®** Sizes-standard blades: T3, T4, T5

**TORX®** Sizes-reversible blades:

T6, T7, T8, T9, T10, T15, T20

lbs. .53



## ESD Safe SYS 4 Drive-Loc Handle & Blades



### 26961 ESD Safe Dissipative Precision Drive-Loc Handle

Surface resistant  $10^6$ - $10^9$  Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Ball retainer hold. 110mm/4.3" OAL

| Item No. | mm  | Inch  | mm | Inch | lbs. |
|----------|-----|-------|----|------|------|
| 26961    | 4.0 | .1574 | 23 | .91  | .08  |



### 269 SYSTEM 4 TORX® Drive-Loc Reversible Blades

| Item No. | Size      | Size | lbs. |
|----------|-----------|------|------|
| 26977    | T1 + T2   |      | .03  |
| 26978    | T3 + T4   |      | .03  |
| 26979    | T5 + T6   |      | .03  |
| 26980    | T6 + T8   |      | .03  |
| 26981    | T7 + T9   |      | .03  |
| 26982    | T10 + T15 |      | .03  |

## Wiha CushionGrip Stubby Bit Holders



**38045 TORX® SoftFinish® CushionGrip Stubby Bit Holder**  
with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

★ **TORX®** Sizes: T8, T10, T15, T20, T25, T30 lbs. .20



**38047 Security TORX® SoftFinish® CushionGrip Stubby Bit Holder**  
with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

★ Security **TORX®** Sizes: lbs.  
T8s, T10s, T15s, T20s, T25s, T30s .20



(bits not included)

**28103 1/4" Magnetic Bit Holder With Wiha SoftFinish® Stubby Handle**  
Works in confined spaces. Stainless steel with strong magnet.

| Item No. | Inch | mm | Inch | lbs. | pkg. |
|----------|------|----|------|------|------|
| 28103    | 1/4" | 57 | 2.2  | .11  | 1    |


## Wiha Topra Ratchet Handle Sets



**28295 TORX® Topra Ratchet Bit Set, 12 Pcs.**

Set Includes Topra Handle, Magnetic Bit Holder & The Following Bits: lbs.

★ **TORX®** Sizes: T7, T8, T9, T10, T15, T20, T25, T27, T30, T40 .65



**28297 Security TORX® Topra Ratchet Bit Set, 12 Pcs.**

Set Includes Topra Handle, Magnetic Bit Holder & The Following Bits: lbs.

★ Security **TORX®** Sizes: .65  
T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

## Wiha BitFlip Bit Set

BitFlip Standard



**38028 TORX® BitFlip Standard**

with Wiha cushion grip handle and insulated shaft.

Set includes the following 1/4" bits:

★ **TORX®** Sizes: T8, T10, T15, T20, T25, T27, T30, T40 lbs. .44

## Wiha Multi-Bit Screwdriver Sets



**38003 TORX® Multi-Bit Screwdriver with Wiha Powerhandle**

Set includes the following 1/4" bits:

★ **TORX®** Sizes: lbs.  
T5, T6, T7, T8, T9, T10 .36

**38004 TORX® Multi-Bit Screwdriver with Wiha Powerhandle**

Set includes the following 1/4" bits:

★ **TORX®** Sizes: lbs.  
T8, T9, T10, T15, T20, T25 .36

**38008 TORX® Multi-Bit Screwdriver with Wiha Powerhandle**

Set includes the following 1/4" bits:

★ **TORX®** Sizes: lbs.  
T10, T15, T20, T25, T30, T40 .36



**38009 Security TORX® Screwdriver With Wiha Powerhandle**

Set includes the following 1/4" bits:

★ Security **TORX®** Sizes: lbs.  
T7s, T8s, T9s, T10s, T15s, T20s .36

**38010 Security TORX® Screwdriver With Wiha Powerhandle**

Set includes the following 1/4" bits:

★ Security **TORX®** Sizes: lbs.  
T10s, T15s, T20s, T25s, T30s, T40s .36

(bits not included)



**38015 1/4" Magnetic Bit Holder, Cavity holds up to 6 bits.**

| Item No. | Size | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|------|------|
| 38015    | 1/4" | 120 | 4.7  | 230 | 9.0  | .25  | 1    |



## Wiha Insert Bit Selectors



### 79242 Bit-Selector With **TORX**® Bits

Set includes magnetic 1/4" bit holder lbs.

✱ **TORX**® Sizes: T5, T6, T7, T8, T9, T10, T15, T20, T25, T30 .32

### 79245 Bit-Selector With **TORX**® Bits

Set includes magnetic 1/4" bit holder lbs.

✱ **TORX**® Sizes: T7, T8, T9, T10, T15, T20, T25, T27, T30, T40 .32



### 79247 Bit-Selector With Security **TORX**® Bits

Set includes magnetic 1/4" bit holder lbs.

✱ Security **TORX**® Sizes: T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s .32

### 70190 Bit-Selector With Security **TORX**® Bits

Set includes the following 7 bits: lbs.

✱ Security **TORX**® Sizes: T7s, T8s, T9s, T10s, T15s, T20s, T25s .21



### 71690 Bit-Selector With **TORXPlus**® Bits

Set includes magnetic 1/4" bit holder lbs.

✱ **TORXPlus**® Sizes: IP7, IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30, IP40 .31

### 71692 Bit-Selector With **TORXPlus**® Bits

Set includes magnetic 1/4" bit holder lbs.

✱ **TORXPlus**® Sizes: IP3, IP4, IP5, IP6, IP7, IP8, IP9, IP10, IP15, IP20 .31

## Wiha Power Bit Belt Packs



### 74985 Power Bit Belt Pack With **TORX**® Bits

Set includes the following 10 bits: lbs.

✱ **TORX**® Sizes: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30 .28



### 74981 Power Bit Belt Pack With **TORX**® Align Bits

Set includes the following 10 bits: lbs.

✱ **TORX**® Sizes: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30 .28



### 74987 Power Bit Belt Pack With Security **TORX**® Bits

Set includes the following 10 bits: lbs.

✱ Security **TORX**® Sizes: T7s, T8s, T9s, T10s, T15s, T20s, T27s, T25s, T30s, T40s .29



### 74982 Power Bit Belt Pack With **TORXPlus**® Bits

Set includes the following 10 bits: lbs.

✱ **TORXPlus**® Sizes: IP6, IP7, IP8, IP9, IP10, IP15, IP20, IP25, IP30 .28

## Wiha XSelector Bit Sets



Easy bit  
access with  
hinged cover



Includes Clicfix quick release holder

|              |                                                                   |  |      |
|--------------|-------------------------------------------------------------------|--|------|
| <b>79445</b> | <b>XSelector Bit Set With TORX® Bits</b>                          |  | lbs. |
|              | Set Includes Quick Release Holder                                 |  | .29  |
|              | and the following 10 bits:                                        |  |      |
|              | <b>TORX®</b> Sizes: T7, T8, T9, T10, T15, T20, T25, T27, T30, T40 |  |      |



XSelector Pocket Sized  
3 1/8" x 2 1/8" x 1/2"

|              |                                                                                      |  |      |
|--------------|--------------------------------------------------------------------------------------|--|------|
| <b>79447</b> | <b>XSelector Bit Set With Security TORX® Bits</b>                                    |  | lbs. |
|              | Set Includes Quick Release Holder                                                    |  | .27  |
|              | and the following 10 bits:                                                           |  |      |
|              | <b>Security TORX®</b> Sizes: T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s |  |      |

## Wiha Insert PokitPaks



|              |                                                                                                                  |  |      |
|--------------|------------------------------------------------------------------------------------------------------------------|--|------|
| <b>71195</b> | <b>PokitPak - TORX® Insert Bits In Molded Case - Set includes 6 - 1/4" Insert Bits &amp; Magnetic Bit Holder</b> |  |      |
|              | <b>TORX®:</b>                                                                                                    |  | lbs. |
|              | T8, T10, T15, T20, T25, T30                                                                                      |  | .15  |



|              |                                                                                                   |      |     |
|--------------|---------------------------------------------------------------------------------------------------|------|-----|
| <b>79283</b> | <b>PokitPak TORX® Align Coated Insert Bits In Molded Case - Set Includes 6 - 1/4" Insert Bits</b> |      |     |
|              | <b>TORX® Align:</b>                                                                               |      |     |
|              | T10, T15, T20, T25, T30, T40                                                                      |      |     |
|              |                                                                                                   | lbs. | .12 |

## Wiha 1/4" Bit Holders



Magnetic

|            |                                                                                                                         |  |  |
|------------|-------------------------------------------------------------------------------------------------------------------------|--|--|
| <b>384</b> | <b>1/4" Magnetic Bit Holding Screwdrivers, With Wiha-SoftFinish® Handle</b>                                             |  |  |
|            | Ergonomic cushion grip, magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM steel, nickel-plated. |  |  |

| Item         |      |     |      |     |       |      |      |
|--------------|------|-----|------|-----|-------|------|------|
| No.          | Size | mm  | Inch | mm  | Inch  | lbs. | pkg. |
| <b>38450</b> | 1/4" | 125 | 5.0  | 240 | 9.46  | .23  | 1    |
| <b>38460</b> | 1/4" | 300 | 11.8 | 400 | 15.69 | .37  | 1    |



Adjustable Blade Length  
Magnetic Bit Holder

|              |                                                                                                                     |  |  |
|--------------|---------------------------------------------------------------------------------------------------------------------|--|--|
| <b>28489</b> | <b>Drive-Loc VI Bit Holder</b>                                                                                      |  |  |
|              | High alloy CVM steel, through hardened, hard chrome finish. Wiha-SoftFinish® handle multi-component, cushion grips. |  |  |

| Item  |  |  |  |  |
|-------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| No.   | Inch                                                                              | Extends                                                                             | lbs.                                                                                | pkg.                                                                                |
| 28489 | 1/4"                                                                              | 1-3/4" to 4-7/8"                                                                    | .36                                                                                 | 1                                                                                   |



|            |                                                      |  |  |
|------------|------------------------------------------------------|--|--|
| <b>714</b> | <b>ClicFix Bit Holder, Magnetic For Insert Bits.</b> |  |  |
|            | Quick release                                        |  |  |

| Item         |      |      |    |      |
|--------------|------|------|----|------|
| No.          | Size | Size | mm | Inch |
| <b>71490</b> | 1/4" | 1/4" | 60 | 2.4  |
| <b>71491</b> | 1/4" | 1/4" | 75 | 2.9  |



|              |                                            |  |  |
|--------------|--------------------------------------------|--|--|
| <b>71480</b> | <b>CentroFix Bit Holder For Power Bits</b> |  |  |
|              | Quick release                              |  |  |

| Item         |      |      |    |      |
|--------------|------|------|----|------|
| No.          | Size | Size | mm | Inch |
| <b>71480</b> | 1/4" | 1/4" | 60 | 2.3  |




|              |                                                                                                    |  |  |
|--------------|----------------------------------------------------------------------------------------------------|--|--|
| <b>71470</b> | <b>Auto Lock Magnetic Bit Holder, Spring Loaded Bit Ejection, 1/4" For Insert &amp; Power Bits</b> |  |  |
|--------------|----------------------------------------------------------------------------------------------------|--|--|

| Item  |  |  |  |  |  |
|-------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| No.   | Size                                                                                | Size                                                                                  | mm                                                                                    | Inch                                                                                  | lbs.                                                                                  |
| 71470 | 1/4"                                                                                | 1/4"                                                                                  | 60                                                                                    | 2.4                                                                                   | .08                                                                                   |

**Wiha Terminator TORX® Impact Bits - Insert & Power**

**Up To 30X  
Performance Over  
Standard  
Screwdriver Bits**



Impact rated bits for long life in impact applications

Provide up to 30 times impact performance over standard bits



Standard 1/4" drive - No special adaptor required

Wiha enhanced bi-material torsion zone


Precision machined exact fit tips

Wiha exclusive CVM tool steel

Guaranteed to out perform impact imposters

**1/4" Drive Insert & Power Bits**

**768 TORX® Terminator Impact Bits, 1/4" Insert - 2 bit pack**

| Item No. | Size | mm | pkg. |
|----------|------|----|------|
| 76810    | T10  | 29 | 2    |
| 76811    | T15  | 29 | 2    |
| 76812    | T20  | 29 | 2    |
| 76813    | T25  | 29 | 2    |
| 76816    | T30  | 29 | 2    |
| 76817    | T40  | 29 | 2    |


**768 TORX® Terminator Impact Bits, 1/4" Power - 2 bit pack**

| Item No. | Size | mm | pkg. |
|----------|------|----|------|
| 76853    | T10  | 49 | 2    |
| 76854    | T15  | 49 | 2    |
| 76855    | T20  | 49 | 2    |
| 76856    | T25  | 49 | 2    |
| 76858    | T30  | 49 | 2    |
| 76859    | T40  | 49 | 2    |


**765 TORX® Terminator Impact Bits, 1/4" Insert - 10 Pack**

| Item No. | Size | mm | pkg. |
|----------|------|----|------|
| 76510    | T10  | 29 | 10   |
| 76511    | T15  | 29 | 10   |
| 76512    | T20  | 29 | 10   |
| 76513    | T25  | 29 | 10   |
| 76516    | T30  | 29 | 10   |
| 76517    | T40  | 29 | 10   |


**765 TORX® Terminator Impact Bits, 1/4" Power - 10 Pack**

| Item No. | Size | mm | pkg. |
|----------|------|----|------|
| 76553    | T10  | 49 | 10   |
| 76554    | T15  | 49 | 10   |
| 76555    | T20  | 49 | 10   |
| 76556    | T25  | 49 | 10   |
| 76558    | T30  | 49 | 10   |
| 76559    | T40  | 49 | 10   |


**76895 7 Pc. Bit Buddy Set**

With Terminator Impact Insert Bits - 29mm

Set includes the following bits:

Torx®: T10, T15, T20, T25 (2), T30, T40


**76896 7 Pc. Bit Buddy Set**

With Terminator Impact Power Bits - 49mm

Set includes the following bits:

Torx®: T10, T15, T20, T25 (2), T30, T40

## Stainless Steel 1/4" Insert & Power Bits and 1/4" Bit Holder



**704** Stainless Steel **TORX**® Power Bits  
1/4" Hex Drive, Length 2.0"/50mm

| Item  |      |    |      |
|-------|------|----|------|
| No.   | Size | mm | pkg. |
| 70411 | T15  | 50 | 10   |
| 70413 | T20  | 50 | 10   |
| 70414 | T25  | 50 | 10   |
| 70416 | T30  | 50 | 10   |
| 70417 | T40  | 50 | 10   |



**71494** Stainless Steel Bit Holder, 1/4"

**For Insert Bits** Internal C-ring for bit holding & magnet.

| Item  |      |      |    |           |
|-------|------|------|----|-----------|
| No.   | Size | Size | mm | Inch lbs. |
| 71494 | 1/4" | 1/4" | 54 | 2.1" .05  |



**715** Stainless Steel **TORX**® Bits, 1/4"

| Item  |      |    |      |
|-------|------|----|------|
| No.   | Size | mm | pkg. |
| 71500 | T8   | 25 | 10   |
| 71501 | T9   | 25 | 10   |
| 71502 | T10  | 25 | 10   |
| 71503 | T15  | 25 | 10   |
| 71504 | T20  | 25 | 10   |
| 71511 | T25  | 25 | 10   |
| 71512 | T30  | 25 | 10   |
| 71513 | T40  | 25 | 10   |

### Stainless Steel

High-quality, non-rusting stainless steel, completely vacuum-hardened.

## Dura Torsion Insert Bits



**71596** PokitPak **-TORX**® Dura Insert Bits  
In Molded Case -

Set Includes 6 - 1/4" Insert Bits

|  |                              |
|--|------------------------------|
|  | T10, T15, T20, T25, T30, T40 |
|  | Lbs. .36                     |


## Dura Torsion Insert Bits

With the Dura bit Wiha has again proved it's power of innovation.

The extra hard, elastic Quattro Torsion bit is equipped with an extremely wear resistant tungsten carbide coating that grips the screw head.

Positive location in the screw head with decrease of:

- necessary pressure forces
- working time
- costs
- wear & tear of bits & screw heads
- anti-cam-out effect



Torsion Zone



**715** **TORX**® Dura Bits, 1/4"

| Item  |      |    |      |
|-------|------|----|------|
| No.   | Size | mm | lbs. |
| 71574 | T10  | 25 | .02  |
| 71576 | T15  | 25 | .02  |
| 71578 | T20  | 25 | .02  |
| 71580 | T25  | 25 | .02  |
| 71582 | T30  | 25 | .02  |
| 71584 | T40  | 25 | .03  |

## Diamond Torsion Insert Bits

Diamond bits supplement Wiha's range of high-quality special bits. When used with machines, the increased tool life of the Wiha Diamond bit reduces cost.

- High wear resistance
- Micro particle coating with sapphire and diamond contents
- Optimized torsion zone

### Reduction of:

- pressure forces to be applied
- wear and tear of bit and screw head
- working time & costs
- Cam-out effect

The ideal bit even for the most difficult of applications



Torsion Zone




**715** **TORX**® Diamond Bits, 1/4"

| Item  |      |    |      |
|-------|------|----|------|
| No.   | Size | mm | lbs. |
| 71516 | T10  | 25 | .02  |
| 71517 | T15  | 25 | .02  |
| 71518 | T20  | 25 | .02  |
| 71519 | T25  | 25 | .02  |
| 71521 | T30  | 25 | .02  |
| 71522 | T40  | 25 | .03  |

## TiN Coated Insert Bits

The abbreviation TiN stands for Titanium-Nitride, which has a hardness up to 85 HRC. This coating guarantees a high wear and tear resistance.



Torsion Zone

- Tough, hard torsion quality with very hard TiN coating
- Optimized torsion zone
- High wear resistance



**715** **TORX**® TiN Coated Insert Bits, 1/4"

| Item  |      |    |      |
|-------|------|----|------|
| No.   | Size | mm | lbs. |
| 71585 | T5   | 25 | .02  |
| 71586 | T6   | 25 | .02  |
| 71587 | T7   | 25 | .02  |
| 71588 | T8   | 25 | .02  |
| 71562 | T9   | 25 | .02  |
| 71563 | T10  | 25 | .02  |
| 71564 | T15  | 25 | .02  |
| 71565 | T20  | 25 | .02  |
| 71566 | T25  | 25 | .02  |
| 71569 | T27  | 25 | .02  |
| 71567 | T30  | 25 | .02  |
| 71568 | T40  | 25 | .02  |

TiN - Titanium Nitride



# TORX® Bits

The ideal multi-purpose bits for all around quality & performance

*Made in Germany - Production Quality*

Highly resistant to wear and tear for a long tool life



Impact resistant modified CVM, tool steel, hardened

Suitable for all applications for both manual and machine  
Hardness HRC 59-61



## 725 TORX® Bits, 5/16"

| Item  | No. | Size | mm | pkg. | lbs. |
|-------|-----|------|----|------|------|
| 72525 | T25 | 35   | 10 | .27  |      |
| 72527 | T27 | 35   | 10 | .27  |      |
| 72530 | T30 | 35   | 10 | .27  |      |
| 72540 | T40 | 35   | 10 | .28  |      |
| 72545 | T45 | 35   | 10 | .31  |      |
| 72550 | T50 | 35   | 10 | .32  |      |
| 72555 | T55 | 35   | 10 | .52  |      |



2 bit pack



## 725 TORX® Insert Bit Packs, 5/16"

| Item  | No. | Size | mm  | lbs. |
|-------|-----|------|-----|------|
| 72531 | T30 | 35   | .28 |      |
| 72541 | T40 | 35   | .28 |      |
| 72546 | T45 | 35   | .31 |      |
| 72551 | T50 | 35   | .32 |      |
| 72556 | T55 | 35   | .52 |      |



## 745 TORX® Power Bits

1/4" Hex Drive, Length 2.0"/50mm

| Item  | No. | Size | mm | pkg. | lbs. |
|-------|-----|------|----|------|------|
| 74511 | T6  | 50   | 10 | .18  |      |
| 74512 | T7  | 50   | 10 | .18  |      |
| 74513 | T8  | 50   | 10 | .18  |      |
| 74517 | T9  | 50   | 10 | .18  |      |
| 74519 | T10 | 50   | 10 | .18  |      |
| 74521 | T15 | 50   | 10 | .18  |      |
| 74523 | T20 | 50   | 10 | .18  |      |
| 74529 | T25 | 50   | 10 | .18  |      |
| 74531 | T27 | 50   | 10 | .18  |      |
| 74533 | T30 | 50   | 10 | .18  |      |
| 74535 | T40 | 50   | 10 | .18  |      |



## 745 TORX® Power Bits

1/4" Hex Drive, Length 2.75"/70mm

| Item  | No. | Size | mm | pkg. | lbs. |
|-------|-----|------|----|------|------|
| 74536 | T6  | 70   | 1  | .02  |      |
| 74538 | T7  | 70   | 1  | .02  |      |
| 74542 | T8  | 70   | 1  | .02  |      |
| 74544 | T9  | 70   | 1  | .02  |      |
| 74546 | T10 | 70   | 1  | .02  |      |
| 74548 | T15 | 70   | 1  | .02  |      |
| 74551 | T20 | 70   | 1  | .03  |      |
| 74553 | T25 | 70   | 1  | .03  |      |
| 74556 | T27 | 70   | 1  | .04  |      |
| 74558 | T30 | 70   | 1  | .04  |      |
| 74561 | T40 | 70   | 1  | .04  |      |



## 745 TORX® Power Bits

1/4" Hex Drive, Length 3.5"/90mm

| Item  | No. | Size | mm | pkg. | lbs. |
|-------|-----|------|----|------|------|
| 74563 | T6  | 90   | 10 | .03  |      |
| 74565 | T7  | 90   | 10 | .03  |      |
| 74567 | T8  | 90   | 10 | .03  |      |
| 74569 | T9  | 90   | 10 | .03  |      |
| 74571 | T10 | 90   | 10 | .03  |      |
| 74573 | T15 | 90   | 10 | .03  |      |
| 74575 | T20 | 90   | 10 | .04  |      |
| 74577 | T25 | 90   | 10 | .04  |      |
| 74579 | T27 | 90   | 10 | .04  |      |
| 74581 | T30 | 90   | 10 | .04  |      |
| 74583 | T40 | 90   | 10 | .04  |      |



## 745 TORX® Power Bits

1/4" Hex Drive, Length 6.0"/150mm

| Item  | No. | Size | mm | pkg. | lbs. |
|-------|-----|------|----|------|------|
| 74586 | T10 | 150  | 10 | .04  |      |
| 74587 | T15 | 150  | 10 | .04  |      |
| 74588 | T20 | 150  | 10 | .04  |      |
| 74589 | T25 | 150  | 10 | .04  |      |
| 74590 | T27 | 150  | 10 | .04  |      |
| 74591 | T30 | 150  | 10 | .04  |      |

## Wiha TORX® Bit Packs



2 bit pack

## 715 TORX® Insert Bit Packs

1" CVM S2 modified tool steel.

| Item  | No. | Size | mm  | lbs. |
|-------|-----|------|-----|------|
| 71548 | T3  | 25   | .03 |      |
| 71549 | T4  | 25   | .03 |      |
| 71550 | T5  | 25   | .03 |      |
| 71551 | T6  | 25   | .03 |      |
| 71552 | T7  | 25   | .03 |      |
| 71553 | T8  | 25   | .03 |      |
| 71554 | T9  | 25   | .03 |      |
| 71555 | T10 | 25   | .03 |      |
| 71556 | T15 | 25   | .03 |      |
| 71557 | T20 | 25   | .03 |      |
| 71558 | T25 | 25   | .03 |      |
| 71559 | T27 | 25   | .04 |      |
| 71560 | T30 | 25   | .04 |      |
| 71561 | T40 | 25   | .04 |      |



## 715 TORX® Bits, 1/4"

| Item  | No. | Size | mm | pkg. | lbs. |
|-------|-----|------|----|------|------|
| 71523 | T3  | 25   | 10 | .12  |      |
| 71524 | T4  | 25   | 10 | .12  |      |
| 71505 | T5  | 25   | 10 | .12  |      |
| 71506 | T6  | 25   | 10 | .12  |      |
| 71507 | T7  | 25   | 10 | .12  |      |
| 71508 | T8  | 25   | 10 | .12  |      |
| 71509 | T9  | 25   | 10 | .12  |      |
| 71510 | T10 | 25   | 10 | .12  |      |
| 71515 | T15 | 25   | 10 | .12  |      |
| 71520 | T20 | 25   | 10 | .12  |      |
| 71525 | T25 | 25   | 10 | .12  |      |
| 71527 | T27 | 25   | 10 | .13  |      |
| 71530 | T30 | 25   | 10 | .14  |      |
| 71540 | T40 | 25   | 10 | .15  |      |

## 725 TORX® Bits, 1/4" Bulk Packs

| Item  | No. | Size | mm | pkg. | lbs. |
|-------|-----|------|----|------|------|
| 72573 | T8  | 25   | 30 | .36  |      |
| 72575 | T10 | 25   | 30 | .36  |      |
| 72576 | T15 | 25   | 30 | .36  |      |
| 72577 | T20 | 25   | 30 | .36  |      |
| 72578 | T25 | 25   | 30 | .36  |      |
| 72579 | T27 | 25   | 30 | .36  |      |
| 72580 | T30 | 25   | 30 | .36  |      |
| 72581 | T40 | 25   | 30 | .36  |      |

## Wiha TORX® Bit Packs



### 71571 TORX® Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

#### 71571 Set includes the following bits:

##### TORX® Sizes:

T15, T20, T25, T27,  
wt. .08 T30, T40 x 1" (25mm)

### 71570 TORX® Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc bit pack.

#### 71570 Set includes the following bits:

##### TORX® Sizes:

T5, T6, T7, T8, T9,  
wt. .07 T10 x 1" (25mm)



2 bit  
pack

### 745 TORX® Power Bit Packs, 2"

CVM S2 modified tool steel

| Item  | No. | Size | mm  | lbs. |
|-------|-----|------|-----|------|
| 74501 | T6  | 50   | .05 |      |
| 74502 | T7  | 50   | .05 |      |
| 74503 | T8  | 50   | .05 |      |
| 74504 | T9  | 50   | .05 |      |
| 74506 | T10 | 50   | .05 |      |
| 74508 | T15 | 50   | .05 |      |
| 74510 | T20 | 50   | .05 |      |
| 74514 | T25 | 50   | .06 |      |
| 74515 | T27 | 50   | .06 |      |
| 74516 | T30 | 50   | .06 |      |
| 74518 | T40 | 50   | .06 |      |

## Wiha TORX® Align Insert Bits and Power Bits

### Torx® Align Tapered For Snug Fit In Screw

Highly resistant  
to wear and  
tear for a  
long tool life



Impact resistant modified  
chrome-vanadium-  
molybdenum, tool steel,  
hardened

**Made in Germany -  
Production Quality**

Suitable for all applications  
for both manual and machine  
Hardness HRC 59-61



### 715 TORX® Align Bits, 1/4"

| Item  | No. | Size | mm | pkg. | lbs. |
|-------|-----|------|----|------|------|
| 71536 | T6  | 25   | 10 | .12  |      |
| 71537 | T7  | 25   | 10 | .12  |      |
| 71538 | T8  | 25   | 10 | .12  |      |
| 71539 | T9  | 25   | 10 | .12  |      |
| 71541 | T10 | 25   | 10 | .12  |      |
| 71542 | T15 | 25   | 10 | .12  |      |
| 71543 | T20 | 25   | 10 | .12  |      |
| 71544 | T25 | 25   | 10 | .13  |      |
| 71545 | T27 | 25   | 10 | .13  |      |
| 71546 | T30 | 25   | 10 | .14  |      |
| 71547 | T40 | 25   | 10 | .15  |      |

\*Also Known As Torx Wedge Fit



### 747 TORX® Align Bits, 1/4" Hex Drive, Length 2.0"/50mm

| Item  | No. | Size | mm | pkg. | lbs. |
|-------|-----|------|----|------|------|
| 74711 | T6  | 50   | 10 | .18  |      |
| 74714 | T7  | 50   | 10 | .18  |      |
| 74717 | T8  | 50   | 10 | .18  |      |
| 74721 | T9  | 50   | 10 | .18  |      |
| 74724 | T10 | 50   | 10 | .18  |      |
| 74728 | T15 | 50   | 10 | .20  |      |
| 74732 | T20 | 50   | 10 | .22  |      |
| 74736 | T25 | 50   | 10 | .22  |      |
| 74739 | T27 | 50   | 10 | .22  |      |
| 74742 | T30 | 50   | 10 | .22  |      |

\*Also Known As Torx Wedge Fit



2 bit  
pack



2 bit  
pack

### 733 TORX® Align Insert Bit Packs, 1"

CVM S2 modified tool steel

| Item  | No. | Size | mm  | lbs. |
|-------|-----|------|-----|------|
| 73310 | T6  | 25   | .03 |      |
| 73311 | T7  | 25   | .03 |      |
| 73312 | T8  | 25   | .03 |      |
| 73313 | T9  | 25   | .03 |      |
| 73314 | T10 | 25   | .03 |      |
| 73315 | T15 | 25   | .03 |      |
| 73316 | T20 | 25   | .03 |      |
| 73317 | T25 | 25   | .03 |      |
| 73318 | T27 | 25   | .03 |      |
| 73319 | T30 | 25   | .03 |      |
| 73320 | T40 | 25   | .04 |      |

### 747 TORX® Align Power Bit Packs, 2"

| Item  | No. | Size | mm  | lbs. |
|-------|-----|------|-----|------|
| 74760 | T6  | 50   | .05 |      |
| 74761 | T7  | 50   | .05 |      |
| 74762 | T8  | 50   | .05 |      |
| 74763 | T9  | 50   | .05 |      |
| 74764 | T10 | 50   | .05 |      |
| 74765 | T15 | 50   | .05 |      |
| 74766 | T20 | 50   | .06 |      |
| 74767 | T25 | 50   | .06 |      |
| 74768 | T27 | 50   | .06 |      |
| 74769 | T30 | 50   | .06 |      |

## Torx® Profiles



Torx®



Security  
Torx®



TorxPlus®



Security  
TorxPlus®



Ball End  
Torx®

**Wiha Security TORX® Insert Bits and Power Bits**

# Security Torx®

*Made in Germany -  
Production Quality*



Impact resistant modified  
CVM tool steel, hardened

Highly resistant  
to wear and  
tear for a  
long tool life

Suitable for all applications  
for both manual and machine  
Hardness HRC 59-61



2 bit  
pack


**705 Security TORX® Power Bit Packs, 2"**

| Item No. | Size | mm | lbs. |
|----------|------|----|------|
| 70556    | T7s  | 50 | .07  |
| 70557    | T8s  | 50 | .07  |
| 70558    | T9s  | 50 | .07  |
| 70559    | T10s | 50 | .07  |
| 70560    | T15s | 50 | .07  |
| 70561    | T20s | 50 | .07  |
| 70562    | T25s | 50 | .07  |
| 70563    | T27s | 50 | .07  |
| 70564    | T30s | 50 | .07  |
| 70565    | T40s | 50 | .07  |
| 70566    | T45s | 50 | .07  |
| 70567    | T50s | 50 | .07  |
| 70568    | T55s | 50 | .07  |


**701 Security TORX® Bits, 1/4"**

| Item No. | Size | mm | pkg. | lbs. |
|----------|------|----|------|------|
| 70127    | T7s  | 25 | 10   | .12  |
| 70128    | T8s  | 25 | 10   | .12  |
| 70129    | T9s  | 25 | 10   | .12  |
| 70135    | T10s | 25 | 10   | .12  |
| 70139    | T15s | 25 | 10   | .12  |
| 70142    | T20s | 25 | 10   | .12  |
| 70148    | T25s | 25 | 10   | .12  |
| 70160    | T27s | 25 | 10   | .13  |
| 70163    | T30s | 25 | 10   | .13  |
| 70168    | T40s | 25 | 10   | .14  |



2 bit  
pack


**701 Security TORX® Insert Bit Packs, 1" CVM S2 modified tool steel.**

| Item No. | Size | mm | lbs. |
|----------|------|----|------|
| 70150    | T7s  | 25 | .03  |
| 70151    | T8s  | 25 | .03  |
| 70152    | T9s  | 25 | .03  |
| 70153    | T10s | 25 | .03  |
| 70154    | T15s | 25 | .03  |
| 70155    | T20s | 25 | .03  |
| 70156    | T25s | 25 | .03  |
| 70157    | T27s | 25 | .03  |
| 70158    | T30s | 25 | .03  |
| 70159    | T40s | 25 | .03  |



5/16"

**725 Security TORX® Bits, 5/16"**

| Item No. | Size | mm | pkg. | lbs. |
|----------|------|----|------|------|
| 72542    | T40s | 35 | 10   | .28  |
| 72547    | T45s | 35 | 10   | .32  |
| 72552    | T50s | 35 | 10   | .34  |
| 72557    | T55s | 35 | 10   | .52  |



2 bit  
pack


**725 Security TORX® Bits, 5/16" 2 Bit Pack**

| Item No. | Size | mm | lbs. |
|----------|------|----|------|
| 72562    | T40s | 35 | .28  |
| 72563    | T45s | 35 | .29  |
| 72564    | T50s | 35 | .30  |
| 72567    | T55s | 35 | .32  |


**Wiha Security TORXPlus® Insert Bit**
**716 Security TORXPlus® Insert Bits, 1/4" Hex, 1" OAL**

| Item No. | Size  | mm | pkg. | lbs. |
|----------|-------|----|------|------|
| 71648    | IPR8  | 25 | 1    | .11  |
| 71650    | IPR10 | 25 | 1    | .11  |
| 71652    | IPR15 | 25 | 1    | .11  |
| 71654    | IPR20 | 25 | 1    | .12  |
| 71656    | IPR25 | 25 | 1    | .13  |
| 71657    | IPR27 | 25 | 1    | .13  |
| 71658    | IPR30 | 25 | 1    | .14  |
| 71660    | IPR40 | 35 | 1    | .14  |



XSelector  
Pocket Sized  
3 1/8" x 2 1/8" x 1/2"

**79450 XSelector Bit Set With Security TORXPlus® Bits**

Set Includes Quick Release Holder  
and the following 7 bits:

.18 Security TORXPlus® Sizes:  
IPR8, IPR10, IPR15, IPR20,  
IPR25, IPR27, IPR30

## Wiha TORXPlus® Insert Bits and Power Bits

### TORXPlus®

Made in Germany -  
Production Quality

Highly resistant  
to wear and  
tear for a  
long tool  
life

Impact resistant modified  
chrome-vanadium-molybdenum,  
tool steel, hardened

Suitable for all applications  
for both manual and machine  
Hardness HRC 59-61



#### 716 TORXPlus® Insert Bits, 1/4" Hex, 1"

| Item No. | Size | mm | pkg. | lbs. |
|----------|------|----|------|------|
| 71603    | IP3  | 25 | 10   | .12  |
| 71604    | IP4  | 25 | 10   | .12  |
| 71605    | IP5  | 25 | 10   | .12  |
| 71606    | IP6  | 25 | 10   | .12  |
| 71607    | IP7  | 25 | 10   | .12  |
| 71608    | IP8  | 25 | 10   | .12  |
| 71609    | IP9  | 25 | 10   | .12  |
| 71610    | IP10 | 25 | 10   | .12  |
| 71615    | IP15 | 25 | 10   | .12  |
| 71620    | IP20 | 25 | 10   | .12  |
| 71625    | IP25 | 25 | 10   | .12  |
| 71627    | IP27 | 25 | 10   | .13  |
| 71630    | IP30 | 25 | 10   | .13  |
| 71640    | IP40 | 25 | 10   | .15  |



#### 746 TORXPlus® Power Bits, 1/4" Hex, 2"

| Item No. | Size | mm | pkg. | lbs. |
|----------|------|----|------|------|
| 74601    | IP5  | 50 | 10   | .18  |
| 74602    | IP6  | 50 | 10   | .18  |
| 74603    | IP7  | 50 | 10   | .18  |
| 74604    | IP8  | 50 | 10   | .18  |
| 74608    | IP9  | 50 | 10   | .18  |
| 74612    | IP10 | 50 | 10   | .20  |
| 74616    | IP15 | 50 | 10   | .20  |
| 74620    | IP20 | 50 | 10   | .20  |
| 74624    | IP25 | 50 | 10   | .20  |
| 74628    | IP27 | 50 | 10   | .25  |
| 74632    | IP30 | 50 | 10   | .25  |
| 74636    | IP40 | 50 | 10   | .25  |



2 bit  
pack

#### 716 TORXPlus® Insert Bit Packs, 1"

CVM S2 modified tool steel

| Item No. | Size | mm | lbs. |
|----------|------|----|------|
| 71631    | IP3  | 25 | .03  |
| 71632    | IP4  | 25 | .03  |
| 71633    | IP5  | 25 | .03  |
| 71634    | IP6  | 25 | .03  |
| 71635    | IP7  | 25 | .03  |
| 71636    | IP8  | 25 | .03  |
| 71637    | IP9  | 25 | .03  |
| 71638    | IP10 | 25 | .03  |
| 71639    | IP15 | 25 | .03  |
| 71641    | IP20 | 25 | .03  |
| 71642    | IP25 | 25 | .03  |
| 71643    | IP27 | 25 | .03  |
| 71644    | IP30 | 25 | .03  |
| 71645    | IP40 | 25 | .04  |



2 bit  
pack

#### 746 TORXPlus® Power Bit Packs, 2"

| Item No. | Size | mm | lbs. |
|----------|------|----|------|
| 74659    | IP5  | 50 | .05  |
| 74660    | IP6  | 50 | .05  |
| 74661    | IP7  | 50 | .05  |
| 74662    | IP8  | 50 | .05  |
| 74663    | IP9  | 50 | .05  |
| 74664    | IP10 | 50 | .05  |
| 74665    | IP15 | 50 | .05  |
| 74666    | IP20 | 50 | .05  |
| 74667    | IP25 | 50 | .05  |
| 74668    | IP27 | 50 | .05  |
| 74669    | IP30 | 50 | .05  |
| 74670    | IP40 | 50 | .05  |

## Wiha Ball End TORX® Bits



See additional Ball End TORX  
Tools on Page 17

## Wiha TORX® MagicSpring Screw Holding Power Bits

Screw Holding  
TORX Bits



Stainless  
rotary spring 2 bit pack

#### 745 TORX® MagicSpring Screw Holding Power Bits, 1/4" Hex Drive, 2.0"/50mm OAL

| Item No. | Size | mm | pkg. | lbs. |
|----------|------|----|------|------|
| 74552    | T10  | 50 | 2    | .05  |
| 74554    | T15  | 50 | 2    | .05  |
| 74555    | T20  | 50 | 2    | .05  |
| 74557    | T25  | 50 | 2    | .05  |
| 74562    | T30  | 50 | 2    | .05  |
| 74564    | T40  | 50 | 2    | .05  |

## Wiha Double End TORX® Bits



#### 744 TORX® Double End Bits

1/4" Hex Drive, Length 2.56"/65mm

| Item No. | Size | Size | mm | pkg. | lbs. |
|----------|------|------|----|------|------|
| 74411    | T6   | T6   | 65 | 10   | .32  |
| 74413    | T7   | T7   | 65 | 10   | .32  |
| 74415    | T8   | T8   | 65 | 10   | .32  |
| 74417    | T9   | T9   | 65 | 10   | .32  |
| 74419    | T10  | T10  | 65 | 10   | .32  |
| 74421    | T15  | T15  | 65 | 10   | .32  |
| 74423    | T20  | T20  | 65 | 10   | .32  |
| 74429    | T25  | T25  | 65 | 10   | .33  |
| 74431    | T27  | T27  | 65 | 10   | .34  |
| 74433    | T30  | T30  | 65 | 10   | .35  |
| 74435    | T40  | T40  | 65 | 10   | .38  |

2 bit  
pack



#### 744 TORX® Double End Bits

1/4" Hex Drive, Length 2.56"/65mm

| Item No. | Size | Size | mm | lbs. |
|----------|------|------|----|------|
| 74460    | T6   | T6   | 65 | .05  |
| 74461    | T7   | T7   | 65 | .05  |
| 74462    | T8   | T8   | 65 | .05  |
| 74463    | T9   | T9   | 65 | .05  |
| 74464    | T10  | T10  | 65 | .05  |
| 74465    | T15  | T15  | 65 | .05  |
| 74466    | T20  | T20  | 65 | .05  |
| 74467    | T25  | T25  | 65 | .05  |
| 74468    | T27  | T27  | 65 | .05  |
| 74469    | T30  | T30  | 65 | .05  |
| 74470    | T40  | T40  | 65 | .05  |



## Wiha Sockets



Set Screw  
Replaceable  
Bit

| 761 TORX® Sockets 1/4" Square Drive |      |    |      |  |
|-------------------------------------|------|----|------|--|
| Item                                |      |    |      |  |
| No.                                 | Size | mm | lbs. |  |
| 76106                               | T6   | 38 | .04  |  |
| 76107                               | T7   | 38 | .04  |  |
| 76109                               | T8   | 38 | .04  |  |
| 76111                               | T9   | 38 | .04  |  |
| 76113                               | T10  | 38 | .04  |  |
| 76117                               | T15  | 38 | .04  |  |
| 76119                               | T20  | 38 | .04  |  |
| 76121                               | T25  | 38 | .04  |  |
| 76123                               | T27  | 38 | .04  |  |
| 76129                               | T30  | 38 | .05  |  |
| 76131                               | T40  | 38 | .05  |  |



| 763 TORX® Sockets 3/8" Square Drive, Set Screw Replaceable Bit. 1/4" bits |      |    |      |  |
|---------------------------------------------------------------------------|------|----|------|--|
| Item                                                                      |      |    |      |  |
| No.                                                                       | Size | mm | lbs. |  |
| 76312                                                                     | T9   | 42 | .09  |  |
| 76314                                                                     | T10  | 42 | .09  |  |
| 76316                                                                     | T15  | 42 | .09  |  |
| 76318                                                                     | T20  | 42 | .09  |  |
| 76322                                                                     | T25  | 42 | .09  |  |
| 76324                                                                     | T27  | 42 | .09  |  |
| 76326                                                                     | T30  | 42 | .09  |  |
| 76328                                                                     | T40  | 42 | .09  |  |



| 763 TORX® Sockets 3/8" Square Drive, Set Screw Replaceable Bit. 5/16" Bit. 2" OAL |      |    |      |  |
|-----------------------------------------------------------------------------------|------|----|------|--|
| Item                                                                              |      |    |      |  |
| No.                                                                               | Size | mm | lbs. |  |
| 76346                                                                             | T40  | 51 | .11  |  |
| 76348                                                                             | T45  | 51 | .11  |  |
| 76352                                                                             | T50  | 51 | .11  |  |
| 76354                                                                             | T55  | 51 | .13  |  |



716 TORXPlus® Sockets 1/4" Square Drive, Set Screw Replaceable Bit. 1/4" bits

| Item  |      |    |      |  |
|-------|------|----|------|--|
| No.   | Size | mm | lbs. |  |
| 71661 | IP6  | 38 | .04  |  |
| 71662 | IP7  | 38 | .04  |  |
| 71663 | IP8  | 38 | .04  |  |
| 71664 | IP9  | 38 | .04  |  |
| 71665 | IP10 | 38 | .04  |  |
| 71666 | IP15 | 38 | .04  |  |
| 71667 | IP20 | 38 | .04  |  |
| 71668 | IP25 | 38 | .04  |  |
| 71669 | IP27 | 38 | .04  |  |
| 71670 | IP30 | 38 | .04  |  |
| 71671 | IP40 | 38 | .04  |  |



716 TORXPlus® Sockets 3/8" Square Drive, Set Screw Replaceable Bit. 1/4" bits

| Item  |      |    |      |  |
|-------|------|----|------|--|
| No.   | Size | mm | lbs. |  |
| 71673 | IP9  | 42 | .09  |  |
| 71674 | IP10 | 42 | .09  |  |
| 71675 | IP15 | 42 | .09  |  |
| 71676 | IP20 | 42 | .09  |  |
| 71677 | IP25 | 42 | .09  |  |
| 71678 | IP27 | 42 | .09  |  |
| 71680 | IP30 | 42 | .09  |  |
| 71681 | IP40 | 42 | .09  |  |



Set Screw  
Replaceable  
Bit

763 Security TORX® Sockets 1/4" Square drive, 1/4" bits

| Item  |      |    |  |  |
|-------|------|----|--|--|
| No.   | Size | mm |  |  |
| 76329 | T7s  | 38 |  |  |
| 76330 | T8s  | 38 |  |  |
| 76331 | T9s  | 38 |  |  |
| 76332 | T10s | 38 |  |  |
| 76333 | T15s | 38 |  |  |
| 76334 | T20s | 38 |  |  |
| 76335 | T25s | 38 |  |  |
| 76335 | T27s | 38 |  |  |
| 76337 | T30s | 38 |  |  |
| 76338 | T40s | 38 |  |  |



Set Screw  
Replaceable  
Bit

701 Security TORX® Sockets 3/8" Square drive, 1/4" bits. 2" OAL

| Item  |      |    |      |  |
|-------|------|----|------|--|
| No.   | Size | mm | lbs. |  |
| 70107 | T7s  | 42 | .09  |  |
| 70108 | T8s  | 42 | .09  |  |
| 70109 | T9s  | 42 | .09  |  |
| 70110 | T10s | 42 | .09  |  |
| 70113 | T15s | 42 | .09  |  |
| 70115 | T20s | 42 | .09  |  |
| 70117 | T25s | 42 | .09  |  |
| 70119 | T27s | 42 | .09  |  |
| 70121 | T30s | 42 | .09  |  |
| 70123 | T40s | 42 | .09  |  |



Set Screw  
Replaceable  
Bit

763 Security TORX® Sockets 3/8" Square drive, 5/16" bits

| Item  |      |    |  |  |
|-------|------|----|--|--|
| No.   | Size | mm |  |  |
| 76339 | T40s | 51 |  |  |
| 76340 | T45s | 51 |  |  |
| 76341 | T50s | 51 |  |  |
| 76342 | T55s | 51 |  |  |

## 1/2" Square Drive Sockets



Set Screw  
Replaceable  
Bit

764 TORX® Sockets 1/2" Square Drive

| Item  |      |    |      |      |  |
|-------|------|----|------|------|--|
| No.   | Size | mm | lbs. | pkg. |  |
| 76403 | T30  | 59 | .10  | 1    |  |
| 76404 | T40  | 59 | .10  | 1    |  |
| 76405 | T45  | 59 | .10  | 1    |  |
| 76406 | T50  | 59 | .10  | 1    |  |
| 76407 | T55  | 59 | .11  | 1    |  |



Set Screw  
Replaceable  
Bit

764 Security TORX® Sockets 1/2" Square Drive

| Item  |      |    |      |      |  |
|-------|------|----|------|------|--|
| No.   | Size | mm | lbs. | pkg. |  |
| 76411 | T40s | 59 | .11  | 1    |  |
| 76412 | T45s | 59 | .11  | 1    |  |
| 76413 | T50s | 59 | .11  | 1    |  |
| 76414 | T55s | 59 | .12  | 1    |  |

## Wiha Long Blade Sockets



### 771 TORX® Sockets

1/4" Drive 6" Long Bit Socket.

| Item No. | Size | Inch | lbs. |
|----------|------|------|------|
| 77151    | T8   | 6    | .12  |
| 77153    | T9   | 6    | .12  |
| 77152    | T10  | 6    | .12  |
| 77154    | T15  | 6    | .12  |
| 77156    | T20  | 6    | .12  |
| 77158    | T25  | 6    | .12  |
| 77160    | T27  | 6    | .12  |
| 77162    | T30  | 6    | .12  |
| 77164    | T40  | 6    | .12  |

### 77193 7 Pc. TORX® Socket Blade Set

TORX®: T10, T15, T20, T25, T27, T30, T40    wt. .69



### 771 TORX® Sockets

3/8" Drive 6" Long Bit Socket.

| Item No. | Size | Inch | lbs. |
|----------|------|------|------|
| 77101    | T8   | 6    | .12  |
| 77103    | T9   | 6    | .12  |
| 77105    | T10  | 6    | .12  |
| 77107    | T15  | 6    | .12  |
| 77109    | T20  | 6    | .12  |
| 77111    | T25  | 6    | .12  |
| 77113    | T27  | 6    | .12  |
| 77115    | T30  | 6    | .12  |
| 77117    | T40  | 6    | .12  |

### 77195 9 Pc. TORX® Socket Blade Set

TORX®: T8, T9, T10, T15, T20, T25, T27, T30, T40    wt. .93

## Wiha External Sockets



### 773 TORX® External Sockets 1/4" Square drive socket.

| Item No. | Size | mm | lbs. |
|----------|------|----|------|
| 77304    | E4   | 25 | .03  |
| 77305    | E5   | 25 | .03  |
| 77306    | E6   | 25 | .03  |
| 77307    | E7   | 25 | .04  |
| 77308    | E8   | 25 | .04  |
| 77310    | E10  | 25 | .04  |

### 773 TORX® External Sockets 3/8" Square drive socket.

| Item No. | Size | mm | lbs. |
|----------|------|----|------|
| 77331    | E8   | 28 | .07  |
| 77333    | E10  | 28 | .07  |
| 77335    | E12  | 28 | .07  |
| 77337    | E14  | 28 | .08  |



### 773 TORX® External Sockets 1/2" Square drive socket.

| Item No. | Size | mm | lbs. |
|----------|------|----|------|
| 77341    | E12  | 37 | .12  |
| 77343    | E14  | 37 | .12  |
| 77345    | E16  | 37 | .14  |
| 77347    | E18  | 37 | .14  |
| 77349    | E20  | 37 | .15  |
| 77353    | E24  | 40 | .26  |



### 77390 22 pc. TORX® Set 1/4" Drive Socket

Ratchet 5.5", extension 2" & 4", swivel and hand driver in steel box. Hard chromed and polished.

#### Item No.    wt.

77390    lbs.    Set includes the following:  
2.14    E4, E5, E6, E7, E8, E10,  
T6, T7, T8, T9, T10, T15,  
T20, T25, T27, T30, T40

## Wiha E-TORX® Socket Set On Molded Rails



### 77391 8 pc. E-TORX® Socket Set

#### Item No.    wt.

77391    lbs.    Set includes the following:  
.62    1/4" drive: E6, E7, E8, E10  
3/8" drive: E12, E14  
1/2" drive: E16, E18

## Wiha Socket Sets On Molded Rails



### 76191 10 pc. **TORX**® Socket Set

1/4" Square Drive Replaceable Bit Socket. Bits CVM tool steel.  
OAL 1.5"

Item No.

**76191** lbs. Set includes the following:  
.48 T7, T8, T9, T10, T15,  
T20, T25, T27, T30, T40



### 76194 6 pc. **TORX**® Socket Set

1/4" Square Drive Replaceable Bit Socket. Bits CVM tool steel.

Item No.

**76194** lbs. Set includes the following:  
.20 T10, T15, T20, T25, T27, T30



### 76395 8 pc. **TORX**® Socket Set 3/8" Square Drive Replaceable Bit Socket. Bits CVM tool steel. OAL 1.5"

Item No.

**76395** lbs. Set includes the following:  
.75 T9, T10, T15, T20, T25,  
T27, T30, T40



### 76396 8 pc. **TORX**® Socket Set 3/8" Square Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel. OAL 1.65"

Item No.

**76396** lbs. Set includes the following:  
.84 1/4": T20, T25, T27, T30, T40  
5/16": T45, T50, T55

## Security Torx®




### 70195 10 pc. Security **TORX**® Socket Set

1/4" Square drive replaceable bit socket. 1/4" Bits CVM tool steel.

Item No.

**70195** lbs. Set includes the following:  
.48 T7s, T8s, T9s, T10s, T15s,  
T20s, T25s, T27s, T30s, T40s




### 76397 9 pc. Security **TORX**® Socket Set

3/8" Sq. Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel.

Item No.

**76397** lbs. Set includes the following:  
.85 1/4": T10s, T15s, T20s, T27s, T30s  
3/8": T40s (1/4" bit)  
3/8": T45s, T50s (5/16" bit)



### 76399 12 pc. Security **TORX**® Socket Set 1/4" & 3/8" Square Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel.

Item No.

**76399** lbs. Set includes the following:  
.77 1/4": T7s, T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s  
5/16": T45s, T50s, T55s



### 71698 8 pc. **TORXPlus**® Socket Set On Rail

In Vinyl Pouch 1/4" & 3/8" Square Drive Replaceable Bit Socket. Bits Chrome-vanadium-molybdenum tool steel.

Item No.

**71698** lbs. Set includes the following:  
.60 1/4": IP9, IP10, IP15, IP20  
3/8": IP25, IP27, IP30, IP40

| Item No. | Page | Item No. | Page  | Item No. | Page | Item No. | Page | Item No. | Page | Item No. | Page | Item No. | Page |
|----------|------|----------|-------|----------|------|----------|------|----------|------|----------|------|----------|------|
| 10893    | 7    | 27856    | 26    | 28616    | 23   | 36202    | 21   | 36294    | 5    | 36497    | 12   | 37044    | 18   |
| 20756    | 15   | 27857    | 26    | 28617    | 23   | 36203    | 21   | 36296    | 19   | 36510    | 16   | 37046    | 18   |
| 20757    | 15   | 27890    | 26    | 28618    | 23   | 36204    | 6    | 36298    | 6    | 36512    | 16   | 37048    | 18   |
| 20758    | 15   | 27894    | 26    | 28619    | 23   | 36205    | 7    | 36299    | 19   | 36515    | 16   | 37050    | 18   |
| 20759    | 15   | 27899    | 26    | 28690    | 25   | 36206    | 6    | 36305    | 13   | 36520    | 16   | 37052    | 18   |
| 20760    | 15   | 28000    | 29    | 28724    | 24   | 36207    | 21   | 36306    | 13   | 36525    | 16   | 37054    | 18   |
| 20799    | 15   | 28001    | 29    | 28726    | 24   | 36208    | 6    | 36307    | 13   | 36530    | 16   | 37090    | 16   |
| 26701    | 27   | 28087    | 29    | 28727    | 24   | 36209    | 6    | 36308    | 13   | 36535    | 16   | 37091    | 16   |
| 26702    | 27   | 28103    | 33    | 28734    | 24   | 36210    | 7    | 36309    | 13   | 36540    | 18   | 37092    | 18   |
| 26703    | 27   | 28126    | 11    | 28736    | 24   | 36211    | 19   | 36310    | 13   | 36542    | 18   | 37106    | 22   |
| 26704    | 27   | 28127    | 11    | 28737    | 24   | 36212    | 7    | 36315    | 13   | 36544    | 18   | 37107    | 22   |
| 26705    | 27   | 28128    | 11    | 28825    | 24   | 36215    | 7    | 36320    | 13   | 36546    | 18   | 37108    | 22   |
| 26706    | 27   | 28129    | 11    | 28826    | 24   | 36216    | 17   | 36321    | 14   | 36548    | 18   | 37109    | 22   |
| 26707    | 27   | 28130    | 11    | 28827    | 24   | 36217    | 17   | 36323    | 14   | 36550    | 18   | 37110    | 22   |
| 26708    | 27   | 28132    | 11    | 28828    | 24   | 36218    | 6    | 36325    | 13   | 36552    | 18   | 37115    | 22   |
| 26709    | 27   | 28133    | 11    | 28829    | 24   | 36219    | 6    | 36326    | 14   | 36554    | 18   | 37120    | 22   |
| 26710    | 27   | 28134    | 11    | 28830    | 24   | 36220    | 7    | 36327    | 13   | 36556    | 22   | 37125    | 22   |
| 26715    | 27   | 28135    | 11    | 28903    | 25   | 36221    | 17   | 36328    | 14   | 36557    | 22   | 37127    | 22   |
| 26720    | 27   | 28136    | 11    | 28904    | 25   | 36222    | 17   | 36329    | 14   | 36558    | 22   | 37130    | 22   |
| 26721    | 21   | 28195    | 11    | 28905    | 25   | 36223    | 19   | 36330    | 13   | 36559    | 22   | 37140    | 22   |
| 26723    | 21   | 28197    | 11    | 28906    | 25   | 36224    | 6    | 36332    | 14   | 36560    | 22   | 37190    | 22   |
| 26725    | 21   | 28295    | 30    | 28907    | 25   | 36225    | 7    | 36335    | 14   | 36561    | 22   | 37192    | 22   |
| 26727    | 21   | 28297    | 32    | 28908    | 25   | 36226    | 17   | 36337    | 14   | 36562    | 22   | 37608    | 6    |
| 26729    | 21   | 28301    | 12    | 28910    | 25   | 36227    | 17   | 36339    | 14   | 36590    | 16   | 37609    | 6    |
| 26731    | 21   | 28339    | 12,24 | 28911    | 25   | 36228    | 19   | 36340    | 13   | 36591    | 16   | 37610    | 6    |
| 26732    | 27   | 28340    | 12,24 | 28912    | 25   | 36229    | 19   | 36342    | 14   | 36592    | 18   | 37615    | 6    |
| 26733    | 27   | 28341    | 12,24 | 28913    | 25   | 36230    | 7    | 36345    | 13   | 36598    | 22   | 37620    | 6    |
| 26735    | 27   | 28342    | 12,24 | 28914    | 25   | 36233    | 19   | 36346    | 14   | 36606    | 20   | 37625    | 6    |
| 26736    | 27   | 28486    | 11    | 28915    | 25   | 36234    | 21   | 36350    | 13   | 36607    | 20   | 37627    | 6    |
| 26737    | 27   | 28487    | 11    | 28931    | 25   | 36235    | 7    | 36352    | 14   | 36608    | 20   | 37630    | 6    |
| 26739    | 27   | 28488    | 11    | 28933    | 25   | 36236    | 17   | 36355    | 13   | 36609    | 20   | 37640    | 6    |
| 26741    | 27   | 28489    | 33    | 28935    | 25   | 36237    | 17   | 36357    | 14   | 36610    | 20   | 37690    | 6    |
| 26743    | 27   | 28501    | 23    | 28937    | 25   | 36238    | 19   | 36360    | 13   | 36615    | 20   | 38003    | 30   |
| 26745    | 27   | 28502    | 23    | 28938    | 25   | 36239    | 19   | 36390    | 13   | 36620    | 20   | 38004    | 30   |
| 26747    | 27   | 28504    | 23    | 28939    | 25   | 36240    | 7    | 36392    | 13   | 36625    | 20   | 38008    | 30   |
| 26749    | 27   | 28506    | 23    | 28940    | 25   | 36243    | 19   | 36393    | 14   | 36627    | 20   | 38009    | 32   |
| 26751    | 27   | 28508    | 23    | 29205    | 24   | 36244    | 21   | 36394    | 13   | 36630    | 20   | 38010    | 32   |
| 26790    | 27   | 28512    | 23    | 29206    | 24   | 36245    | 7    | 36395    | 15   | 36631    | 17   | 38015    | 33   |
| 26791    | 27   | 28522    | 24    | 29209    | 24   | 36248    | 19   | 36396    | 15   | 36632    | 17   | 38028    | 30   |
| 26792    | 27   | 28524    | 24    | 29211    | 24   | 36249    | 21   | 36397    | 15   | 36633    | 17   | 38045    | 30   |
| 26793    | 27   | 28526    | 24    | 29212    | 24   | 36250    | 7    | 36398    | 15   | 36634    | 17   | 38047    | 32   |
| 26796    | 27   | 28527    | 23    | 29214    | 24   | 36253    | 19   | 36399    | 13   | 36635    | 17   | 38450    | 33   |
| 26798    | 21   | 28528    | 23    | 29220    | 24   | 36254    | 21   | 36409    | 13   | 36636    | 17   | 38460    | 33   |
| 26799    | 26   | 28529    | 23    | 29225    | 24   | 36255    | 19   | 36410    | 13   | 36637    | 17   | 45504    | 10   |
| 26951    | 29   | 28530    | 23    | 29230    | 24   | 36256    | 21   | 36415    | 13   | 36638    | 17   | 45505    | 9    |
| 26952    | 29   | 28531    | 23    | 29238    | 24   | 36257    | 21   | 36417    | 13   | 36640    | 20   | 45506    | 9    |
| 26953    | 29   | 28532    | 23    | 29241    | 24   | 36258    | 21   | 36420    | 13   | 36645    | 14   | 45507    | 10   |
| 26954    | 29   | 28533    | 23    | 29245    | 24   | 36259    | 6    | 36422    | 13   | 36646    | 14   | 45508    | 10   |
| 26955    | 29   | 28550    | 23    | 29251    | 24   | 36260    | 6    | 36425    | 13   | 36647    | 14   | 45509    | 10   |
| 26956    | 29   | 28551    | 23    | 32505    | 7    | 36264    | 5    | 36427    | 13   | 36648    | 14   | 45510    | 10   |
| 26957    | 29   | 28552    | 23    | 32511    | 7    | 36266    | 5    | 36430    | 13   | 36649    | 14   | 45511    | 9    |
| 26961    | 29   | 28553    | 23    | 32516    | 7    | 36267    | 5    | 36432    | 13   | 36650    | 14   | 45515    | 10   |
| 26977    | 29   | 28554    | 23    | 32521    | 7    | 36268    | 5    | 36435    | 13   | 36651    | 14   | 45516    | 9    |
| 26978    | 29   | 28561    | 23    | 32526    | 7    | 36269    | 6    | 36437    | 13   | 36652    | 14   | 45520    | 10   |
| 26979    | 29   | 28562    | 23    | 32531    | 7    | 36270    | 5    | 36440    | 13   | 36653    | 14   | 45521    | 9    |
| 26980    | 29   | 28563    | 23    | 32536    | 7    | 36271    | 6    | 36442    | 13   | 36654    | 14   | 45522    | 9    |
| 26981    | 29   | 28564    | 23    | 32541    | 7    | 36272    | 5    | 36445    | 13   | 36655    | 14   | 45525    | 10   |
| 26982    | 29   | 28565    | 23    | 32546    | 7    | 36273    | 6    | 36450    | 13   | 36659    | 14   | 45526    | 9    |
| 26987    | 29   | 28566    | 23    | 32551    | 7    | 36274    | 5    | 36452    | 13   | 36660    | 14   | 45527    | 10   |
| 26995    | 29   | 28567    | 23    | 32556    | 7    | 36275    | 6    | 36461    | 19   | 36661    | 14   | 45530    | 10   |
| 27801    | 26   | 28568    | 23    | 32561    | 7    | 36276    | 5    | 36463    | 19   | 36689    | 14   | 45531    | 9    |
| 27802    | 26   | 28569    | 23    | 32590    | 7    | 36277    | 6    | 36466    | 19   | 36690    | 20   | 45536    | 9    |
| 27803    | 26   | 28571    | 23    | 32592    | 7    | 36278    | 5    | 36469    | 19   | 36691    | 20   | 45540    | 10   |
| 27804    | 26   | 28572    | 23    | 36106    | 20   | 36279    | 6    | 36472    | 19   | 36692    | 17   | 45541    | 9    |
| 27805    | 26   | 28573    | 23    | 36107    | 20   | 36280    | 5    | 36474    | 19   | 36694    | 14   | 45545    | 10   |
| 27811    | 26   | 28574    | 23    | 36108    | 20   | 36281    | 6    | 36476    | 19   | 36697    | 18   | 45546    | 9    |
| 27817    | 26   | 28575    | 23    | 36109    | 20   | 36282    | 5    | 36478    | 19   | 36698    | 14   | 45550    | 10   |
| 27823    | 26   | 28576    | 23    | 36110    | 20   | 36283    | 6    | 36480    | 12   | 36699    | 14   | 45551    | 9    |
| 27829    | 26   | 28577    | 23    | 36115    | 20   | 36284    | 5    | 36481    | 12   | 37013    | 16   | 45556    | 9    |
| 27835    | 26   | 28578    | 23    | 36120    | 20   | 36285    | 6    | 36482    | 12   | 37016    | 16   | 45561    | 9    |
| 27841    | 26   | 28579    | 23    | 36125    | 20   | 36286    | 5    | 36483    | 12   | 37019    | 16   | 45589    | 9    |
| 27847    | 26   | 28597    | 25    | 36127    | 20   | 36287    | 6    | 36484    | 12   | 37022    | 16   | 45591    | 9    |
| 27850    | 26   | 28598    | 25    | 36130    | 20   | 36288    | 5    | 36486    | 12   | 37026    | 16   | 45592    | 9    |
| 27851    | 26   | 28599    | 25    | 36140    | 20   | 36289    | 6    | 36487    | 12   | 37029    | 16   | 45593    | 10   |
| 27852    | 26   | 28611    | 23    | 36197    | 20   | 36290    | 21   | 36490    | 13   | 37032    | 16   | 45595    | 10   |
| 27853    | 26   | 28612    | 23    | 36199    | 20   | 36291    | 5    | 36492    | 13   | 37036    | 16   | 45597    | 10   |
| 27854    | 26   | 28613    | 23    | 36200    | 6    | 36292    | 7    | 36494    | 13   | 37040    | 18   | 45598    | 10   |
| 27855    | 26   | 28614    | 23    | 36201    | 5    | 36293    | 7    | 36496    | 19   | 37042    | 18   | 48400    | 9    |



| Item No. | Page | Item No. | Page | Item No. | Page | Item No. | Page | Item No. | Page | Item No. | Page | Item No. | Page |
|----------|------|----------|------|----------|------|----------|------|----------|------|----------|------|----------|------|
| 52711    | 8    | 71475    | 33   | 71582    | 34   | 72555    | 35   | 74536    | 35   | 74762    | 36   | 76405    | 39   |
| 52713    | 8    | 71476    | 33   | 71584    | 34   | 72556    | 35   | 74537    | 17   | 74763    | 36   | 76406    | 39   |
| 52716    | 8    | 71477    | 33   | 71585    | 34   | 72557    | 37   | 74538    | 35   | 74764    | 36   | 76407    | 39   |
| 52719    | 8    | 71478    | 33   | 71586    | 34   | 72562    | 37   | 74539    | 17   | 74765    | 36   | 76411    | 39   |
| 52722    | 8    | 71479    | 33   | 71587    | 34   | 72563    | 37   | 74541    | 17   | 74766    | 36   | 76412    | 39   |
| 52726    | 8    | 71480    | 33   | 71588    | 34   | 72564    | 37   | 74542    | 35   | 74767    | 36   | 76413    | 39   |
| 52729    | 8    | 71490    | 33   | 71596    | 34   | 72567    | 37   | 74543    | 17   | 74768    | 36   | 76414    | 39   |
| 52732    | 8    | 71491    | 33   | 71603    | 38   | 72573    | 35   | 74544    | 35   | 74769    | 36   | 76510    | 33   |
| 52790    | 8    | 71492    | 33   | 71604    | 38   | 72575    | 35   | 74545    | 17   | 74950    | 37   | 76511    | 33   |
| 52791    | 8    | 71493    | 33   | 71605    | 38   | 72576    | 35   | 74546    | 35   | 74981    | 31   | 76512    | 33   |
| 70107    | 39   | 71494    | 34   | 71606    | 38   | 72577    | 35   | 74547    | 17   | 74982    | 31   | 76513    | 33   |
| 70108    | 39   | 71500    | 34   | 71607    | 38   | 72578    | 35   | 74548    | 35   | 74985    | 31   | 76516    | 33   |
| 70109    | 39   | 71501    | 34   | 71608    | 38   | 72579    | 35   | 74549    | 17   | 74987    | 32   | 76517    | 33   |
| 70110    | 39   | 71502    | 34   | 71609    | 38   | 72580    | 35   | 74550    | 17   | 75093    | 28   | 76553    | 33   |
| 70113    | 39   | 71503    | 34   | 71610    | 38   | 72581    | 35   | 74551    | 35   | 75703    | 28   | 76554    | 33   |
| 70115    | 39   | 71504    | 34   | 71615    | 38   | 73310    | 36   | 74552    | 38   | 75704    | 28   | 76555    | 33   |
| 70117    | 39   | 71505    | 35   | 71620    | 38   | 73311    | 36   | 74553    | 35   | 75705    | 28   | 76556    | 33   |
| 70119    | 39   | 71506    | 35   | 71625    | 38   | 73312    | 36   | 74554    | 38   | 75706    | 28   | 76558    | 33   |
| 70121    | 39   | 71507    | 35   | 71627    | 38   | 73313    | 36   | 74555    | 38   | 75707    | 28   | 76559    | 33   |
| 70123    | 39   | 71508    | 35   | 71630    | 38   | 73314    | 36   | 74556    | 35   | 75708    | 28   | 76810    | 33   |
| 70127    | 37   | 71509    | 35   | 71631    | 38   | 73315    | 36   | 74557    | 38   | 75709    | 28   | 76811    | 33   |
| 70128    | 37   | 71510    | 35   | 71632    | 38   | 73316    | 36   | 74558    | 35   | 75710    | 28   | 76812    | 33   |
| 70129    | 37   | 71511    | 34   | 71633    | 38   | 73317    | 36   | 74561    | 35   | 75715    | 28   | 76813    | 33   |
| 70135    | 37   | 71512    | 34   | 71634    | 38   | 73318    | 36   | 74562    | 38   | 75720    | 28   | 76816    | 33   |
| 70139    | 37   | 71513    | 34   | 71635    | 38   | 73319    | 36   | 74564    | 38   | 75727    | 28   | 76817    | 33   |
| 70142    | 37   | 71515    | 35   | 71636    | 38   | 73320    | 36   | 74563    | 35   | 75728    | 28   | 76853    | 33   |
| 70148    | 37   | 71516    | 34   | 71637    | 38   | 74411    | 38   | 74565    | 35   | 75729    | 28   | 76854    | 33   |
| 70150    | 37   | 71517    | 34   | 71638    | 38   | 74413    | 38   | 74567    | 35   | 75735    | 28   | 76855    | 33   |
| 70151    | 37   | 71518    | 34   | 71639    | 38   | 74415    | 38   | 74569    | 35   | 75739    | 28   | 76856    | 33   |
| 70152    | 37   | 71519    | 34   | 71640    | 38   | 74417    | 38   | 74571    | 35   | 75742    | 28   | 76858    | 33   |
| 70153    | 37   | 71520    | 35   | 71641    | 38   | 74419    | 38   | 74573    | 35   | 75792    | 28   | 76859    | 33   |
| 70154    | 37   | 71521    | 34   | 71642    | 38   | 74421    | 38   | 74575    | 35   | 75801    | 28   | 76895    | 33   |
| 70155    | 37   | 71522    | 34   | 71643    | 38   | 74423    | 38   | 74577    | 35   | 75985    | 28   | 76896    | 33   |
| 70156    | 37   | 71523    | 35   | 71644    | 38   | 74429    | 38   | 74579    | 35   | 76106    | 39   | 77101    | 40   |
| 70157    | 37   | 71524    | 35   | 71645    | 38   | 74431    | 38   | 74581    | 35   | 76107    | 39   | 77103    | 40   |
| 70158    | 37   | 71525    | 35   | 71648    | 37   | 74433    | 38   | 74583    | 35   | 76109    | 39   | 77105    | 40   |
| 70159    | 37   | 71527    | 35   | 71650    | 37   | 74435    | 38   | 74586    | 35   | 76111    | 39   | 77107    | 40   |
| 70160    | 37   | 71530    | 35   | 71652    | 37   | 74460    | 38   | 74587    | 35   | 76113    | 39   | 77109    | 40   |
| 70163    | 37   | 71536    | 36   | 71654    | 37   | 74461    | 38   | 74588    | 35   | 76117    | 39   | 77111    | 40   |
| 70168    | 37   | 71537    | 36   | 71656    | 37   | 74462    | 38   | 74589    | 35   | 76119    | 39   | 77113    | 40   |
| 70190    | 32   | 71538    | 36   | 71657    | 37   | 74463    | 38   | 74590    | 35   | 76121    | 39   | 77115    | 40   |
| 70195    | 41   | 71539    | 36   | 71658    | 37   | 74464    | 38   | 74591    | 35   | 76123    | 39   | 77117    | 40   |
| 70411    | 34   | 71540    | 35   | 71660    | 37   | 74465    | 38   | 74601    | 38   | 76129    | 39   | 77151    | 40   |
| 70413    | 34   | 71541    | 36   | 71661    | 39   | 74466    | 38   | 74602    | 38   | 76131    | 39   | 77152    | 40   |
| 70414    | 34   | 71542    | 36   | 71662    | 39   | 74467    | 38   | 74603    | 38   | 76191    | 41   | 77153    | 40   |
| 70416    | 34   | 71543    | 36   | 71663    | 39   | 74468    | 38   | 74604    | 38   | 76194    | 41   | 77154    | 40   |
| 70417    | 34   | 71544    | 36   | 71664    | 39   | 74469    | 38   | 74608    | 38   | 76312    | 39   | 77156    | 40   |
| 70507    | 37   | 71545    | 36   | 71665    | 39   | 74470    | 38   | 74612    | 38   | 76314    | 39   | 77158    | 40   |
| 70508    | 37   | 71546    | 36   | 71666    | 39   | 74501    | 36   | 74616    | 38   | 76316    | 39   | 77160    | 40   |
| 70509    | 37   | 71547    | 36   | 71667    | 39   | 74502    | 36   | 74620    | 38   | 76318    | 39   | 77162    | 40   |
| 70510    | 37   | 71548    | 35   | 71668    | 39   | 74503    | 36   | 74624    | 38   | 76322    | 39   | 77164    | 40   |
| 70515    | 37   | 71549    | 35   | 71669    | 39   | 74504    | 36   | 74628    | 38   | 76324    | 39   | 77193    | 40   |
| 70520    | 37   | 71550    | 35   | 71670    | 39   | 74505    | 17   | 74632    | 38   | 76326    | 39   | 77195    | 40   |
| 70525    | 37   | 71551    | 35   | 71671    | 39   | 74506    | 36   | 74636    | 38   | 76328    | 39   | 77304    | 40   |
| 70527    | 37   | 71552    | 35   | 71673    | 39   | 74508    | 36   | 74659    | 38   | 76329    | 39   | 77305    | 40   |
| 70530    | 37   | 71553    | 35   | 71674    | 39   | 74510    | 36   | 74660    | 38   | 76330    | 39   | 77306    | 40   |
| 70540    | 37   | 71554    | 35   | 71675    | 39   | 74511    | 35   | 74661    | 38   | 76331    | 39   | 77307    | 40   |
| 70545    | 37   | 71555    | 35   | 71676    | 39   | 74512    | 35   | 74662    | 38   | 76332    | 39   | 77308    | 40   |
| 70550    | 37   | 71556    | 35   | 71677    | 39   | 74513    | 35   | 74663    | 38   | 76333    | 39   | 77310    | 40   |
| 70555    | 37   | 71557    | 35   | 71678    | 39   | 74514    | 36   | 74664    | 38   | 76334    | 39   | 77331    | 40   |
| 70556    | 37   | 71558    | 35   | 71680    | 39   | 74515    | 36   | 74665    | 38   | 76335    | 39   | 77333    | 40   |
| 70557    | 37   | 71559    | 35   | 71681    | 39   | 74516    | 36   | 74666    | 38   | 76336    | 39   | 77335    | 40   |
| 70558    | 37   | 71560    | 35   | 71690    | 31   | 74517    | 35   | 74667    | 38   | 76337    | 39   | 77337    | 40   |
| 70559    | 37   | 71561    | 35   | 71692    | 31   | 74518    | 36   | 74668    | 38   | 76338    | 39   | 77341    | 40   |
| 70560    | 37   | 71562    | 34   | 71698    | 41   | 74519    | 35   | 74669    | 38   | 76339    | 39   | 77343    | 40   |
| 70561    | 37   | 71563    | 34   | 72525    | 35   | 74520    | 17   | 74670    | 38   | 76340    | 39   | 77345    | 40   |
| 70562    | 37   | 71564    | 34   | 72527    | 35   | 74521    | 35   | 74711    | 36   | 76341    | 39   | 77347    | 40   |
| 70563    | 37   | 71565    | 34   | 72530    | 35   | 74522    | 17   | 74714    | 36   | 76342    | 39   | 77349    | 40   |
| 70564    | 37   | 71566    | 34   | 72531    | 35   | 74523    | 35   | 74717    | 36   | 76346    | 39   | 77353    | 40   |
| 70565    | 37   | 71567    | 34   | 72540    | 35   | 74524    | 17   | 74721    | 36   | 76348    | 39   | 77390    | 40   |
| 70566    | 37   | 71568    | 34   | 72541    | 35   | 74526    | 17   | 74724    | 36   | 76352    | 39   | 77391    | 40   |
| 70567    | 37   | 71569    | 34   | 72542    | 37   | 74528    | 17   | 74728    | 36   | 76354    | 39   | 79242    | 31   |
| 70568    | 37   | 71570    | 36   | 72545    | 35   | 74529    | 35   | 74732    | 36   | 76395    | 41   | 79245    | 31   |
| 71130    | 33   | 71571    | 36   | 72546    | 35   | 74531    | 35   | 74736    | 36   | 76396    | 41   | 79247    | 32   |
| 71131    | 33   | 71574    | 34   | 72547    | 37   | 74532    | 17   | 74739    | 36   | 76397    | 41   | 79283    | 31   |
| 71195    | 30   | 71576    | 34   | 72550    | 35   | 74533    | 35   | 74742    | 36   | 76399    | 41   | 79445    | 31   |
| 71470    | 33   | 71578    | 34   | 72551    | 35   | 74534    | 17   | 74760    | 36   | 76403    | 39   | 79447    | 32   |
| 71474    | 33   | 71580    | 34   | 72552    | 37   | 74535    | 35   | 74761    | 36   | 76404    | 39   | 79450    | 37   |

(800) 494-6104  
 fax: (800) 494-7456  
 email: [cservice@wihatools.com](mailto:cservice@wihatools.com)  
[www.wihatools.com](http://www.wihatools.com)



### Wiha Quality Tools

1348 Dundas Circle  
 Monticello, MN 55362  
 tel: 763.295.6591  
 fax: 763.295.6598

### Wiha Tools Canada Ltd.

[www.wihatools.ca](http://www.wihatools.ca)  
 Brampton, ONT L6T 4X4  
 tel: 866.494.0096 or 763.295.6591  
 fax: 763.295.6598

To:

Catalog Item No. 99914 .wo  
 version - 6/1/13

Subject to change  
 without notice

©2013 Willi Hahn Corporation


®Torx is a registered trademark of  
 Acument Intellectual Properties LLC.




99060.wo - Product Guide



99004.wo - Shop Tools Catalog



99919.wo - Insulated Catalog



99002.wo - Screwdrivers Catalog



99951.wo - Bits Catalog



99001.wo - TorqueControl Catalog



99934.wo - Hex Tools Catalog



99006.wo - Tech Tools Catalog



99945.wo - ESD Catalog



99977.wo - Pliers/Crimpers Catalog

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Wiha:

|                              |                              |                              |                              |                              |                              |                              |                              |                              |                              |                              |                              |                              |                              |                              |
|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|
| <a href="#"><u>74602</u></a> | <a href="#"><u>52732</u></a> | <a href="#"><u>70151</u></a> | <a href="#"><u>71563</u></a> | <a href="#"><u>75742</u></a> | <a href="#"><u>76131</u></a> | <a href="#"><u>76853</u></a> | <a href="#"><u>76895</u></a> | <a href="#"><u>76896</u></a> | <a href="#"><u>76856</u></a> | <a href="#"><u>76512</u></a> | <a href="#"><u>71524</u></a> | <a href="#"><u>76553</u></a> | <a href="#"><u>76855</u></a> | <a href="#"><u>76817</u></a> |
| <a href="#"><u>77156</u></a> | <a href="#"><u>71512</u></a> | <a href="#"><u>76516</u></a> | <a href="#"><u>76556</u></a> | <a href="#"><u>71548</u></a> | <a href="#"><u>76812</u></a> | <a href="#"><u>74669</u></a> | <a href="#"><u>76113</u></a> | <a href="#"><u>76129</u></a> | <a href="#"><u>76194</u></a> | <a href="#"><u>76346</u></a> | <a href="#"><u>76348</u></a> | <a href="#"><u>77390</u></a> | <a href="#"><u>28103</u></a> | <a href="#"><u>70564</u></a> |
| <a href="#"><u>74462</u></a> | <a href="#"><u>74508</u></a> | <a href="#"><u>74510</u></a> | <a href="#"><u>74548</u></a> | <a href="#"><u>75705</u></a> | <a href="#"><u>38047</u></a> | <a href="#"><u>71475</u></a> | <a href="#"><u>26982</u></a> | <a href="#"><u>28195</u></a> | <a href="#"><u>74433</u></a> | <a href="#"><u>74529</u></a> | <a href="#"><u>74569</u></a> | <a href="#"><u>74579</u></a> | <a href="#"><u>74589</u></a> | <a href="#"><u>74624</u></a> |
| <a href="#"><u>74987</u></a> | <a href="#"><u>76340</u></a> | <a href="#"><u>77113</u></a> | <a href="#"><u>76336</u></a> | <a href="#"><u>76339</u></a> | <a href="#"><u>76411</u></a> | <a href="#"><u>72552</u></a> | <a href="#"><u>72564</u></a> | <a href="#"><u>72576</u></a> | <a href="#"><u>74539</u></a> | <a href="#"><u>74541</u></a> | <a href="#"><u>74982</u></a> | <a href="#"><u>76324</u></a> | <a href="#"><u>76333</u></a> | <a href="#"><u>76342</u></a> |
| <a href="#"><u>76399</u></a> | <a href="#"><u>77101</u></a> | <a href="#"><u>72547</u></a> | <a href="#"><u>73314</u></a> | <a href="#"><u>73316</u></a> | <a href="#"><u>74435</u></a> | <a href="#"><u>74533</u></a> | <a href="#"><u>74536</u></a> | <a href="#"><u>76312</u></a> | <a href="#"><u>71478</u></a> | <a href="#"><u>72577</u></a> | <a href="#"><u>74537</u></a> | <a href="#"><u>71690</u></a> | <a href="#"><u>72556</u></a> | <a href="#"><u>73311</u></a> |
| <a href="#"><u>74522</u></a> | <a href="#"><u>74528</u></a> | <a href="#"><u>74549</u></a> | <a href="#"><u>76330</u></a> | <a href="#"><u>76332</u></a> | <a href="#"><u>76414</u></a> | <a href="#"><u>71680</u></a> | <a href="#"><u>75706</u></a> | <a href="#"><u>75715</u></a> | <a href="#"><u>75728</u></a> | <a href="#"><u>76111</u></a> | <a href="#"><u>52791</u></a> | <a href="#"><u>71571</u></a> | <a href="#"><u>71607</u></a> | <a href="#"><u>71671</u></a> |
| <a href="#"><u>71674</u></a> | <a href="#"><u>71675</u></a> | <a href="#"><u>71677</u></a> | <a href="#"><u>74557</u></a> | <a href="#"><u>71503</u></a> | <a href="#"><u>37625</u></a> | <a href="#"><u>71567</u></a> | <a href="#"><u>71637</u></a> | <a href="#"><u>71552</u></a> | <a href="#"><u>74768</u></a> |                              |                              |                              |                              |                              |