


Item no.: 750-1405
Product description: 16-CHANNEL DIGITAL INPUT MODULE DC 24 V POSITIVE SWITCHING



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

No. of inputs	16
CURRENT CONSUMPTION (INTERNAL)	25 mA
Voltage supply	DC 24 V (-25% / + 30%)
Signal voltage (0)	DC -3 V ... +5 V
Signal voltage (1)	DC 15 V ... 30 V
Input filter (ms)	3 ms
Input current typ.	+0.6 mA (at DC -3 V ... +5 V); +2.1 mA ... +2.4 mA (at DC 15 V ... +32V)
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [AWG]	22 - 16 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm ²]	0.08 - 1.5 mm ²
Cross section [AWG]	28 - 16 AWG
Wiring method	solid
Weight	50 g
Color	light gray
Height	64 mm
Height	2.52 in
Width	12 mm

Width	0.472 in
Depth	100 mm
Depth	3.937 in
Strip length from	8 mm



Strip length to	9 mm
Strip length	0.33 in
Customs Tariff No.	84733080
Country of Origin	Deutschland

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected