


Non-NEMA Twist-Lock® Devices

20 Ampere, 250, 125/250 Volts and 3Ø Y 120/208 Volts AC

Insulgrip® Plugs, Flanged Inlets, Connector Bodies and Receptacles

For Replacement Use Only

IP20
SUITABILITY

Connector Bodies

Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.360"-.930" (9-24)	HBL7314GCB	HBL7314C
Corrosion resistant, yellow nylon.	.360"-.930" (9-24)	-	HBL73CM14C

Accessories on page B-51.

Single Flush Receptacles

Description	Catalog Numbers
Black urea face, back wired.	HBL7310BG HBL7310B


Accessories on page B-50.

Flanged Receptacles

Description	Catalog Numbers
Nylon casing, back wired.	- HBL3326C

Accessories on page B-50.

For Replacement Use Only

IP20
SUITABILITY

Connector Bodies

Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.35"-1.15" (9-29)	HBL7413GCB	HBL7413C

Accessories on page B-53.

Single Flush Receptacles

Description	Catalog Numbers
Black urea face, back wired.	HBL7410BG HBL7410B
Mounted on a 4" (101.6) round metal cover.	- HBL7417B

Accessories on page B-52.





Flanged Receptacles

Description	Catalog Numbers
Nylon casing, back wired.	- HBL7409C

Accessories on page B-52.

Note: The devices shown on this page are not listed by Underwriters Laboratories Inc. and are for replacement use only in existing installations.

CAUTION: To avoid electrical shock, review premises carefully and do not use if slot or blade configuration (design) is already in a circuit having a rating differing from the rating of this device.

**HBL7314C****HBL7310B****HBL3326C****HBL7413GCB****HBL7410BG****HBL7409C**