



NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 225/245 TOOL, USE ATTACHMENT P/N 119400-1 AND STROKE LIMITER 118362
- 3 FOR USE WITH 2500 TOOL, USE ATTACHMENT P/N 119400-1 AND STROKE LIMITER KIT 119888
- 4 FOR OTHER TOOLS AND/OR OTHER TOOL AND STROKE COMBINATIONS, CONSULT ENGINEERING DEPARTMENT
- 5 SHIP WITH STOP 126747
- 6 SHIP WITH DEFLECTOR 126748-2
- 7 SHIP WITH (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE
- 8 PRIMARILY USED WITH 206-375 TOOLS

REV	DESCRIPTION	DET	DATE
B	128600C ASSY WAS 126694C COLLET & 126707 DRAWBAR, ADDED NOTE 7		03/04/08
C	128490C WAS 128600C ADDED 128487	JJC	07/31/12
D	ADDED 508511, 130322CS WAS 127582-1, 130326 WAS 126745	NDG	06/04/13

(D)	508511	2	#6-32 B.H.C.S.	10
	128487	1	DRAWBAR	9
	126748-2	1	UNITIZED DEFLECTOR	8
(D)	128490C	1	COLLET	7
	130326	1	GUARD	6
	120095	1	DEFLECTOR	5
	122727	1	BARBED RETAINER	4
	122725	1	UNITIZED CHUCK JAW	3
(D)	130322CS	1	TOP GUARD	2
	126696C	1	ANVIL	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH			
ITAR:	HUCK INTERNATIONAL, INC., I.S.D. 1 CORPORATE DR, P.O. BOX 2270 KINGSTON, NEW YORK 12401		
ECCN: EAR99	CLEARANCE NOSE ASSEMBLY -08 LGP STRADDLE		
SCH B#: 8467.99.0190	DET: MVM	CK:	DATE: 10/14/04 SCALE: 2:1
HTS: 8467.99.0190	B	99-3735C	