


Date	Rev.	Description



NOTE:

1. MAXIMUM ELECTRIC CURRENT :

A.W.G.	22	20	18	16
AMP.	3	4	7	10
2. MAXIMUM ELECTRICAL RATING : 75°C 300 VOLTS MAX.
3. INSULATION MATERIAL : VINYL
4. INSULATION COLOR : RED
5. TERMINAL MATERIAL : BRASS
6. WIRE RANGE : 22-16 A.W.G.(0.5-1.5 mm²)
7. TERMINALS SURFACE TREATMENT : TIN PLATED
8. THICKNESS : 0.35 mm
9. NEMA TAB : 0.020*0.187 (0.5 * 4.75)

Tolerance Unless Otherwise Specified	
0 > 6 mm ± 0.20	ANGLE
6 > 18 mm ± 0.30	0° > ° REF ±
18 > 30 mm ± 0.40	° > ° ±
30 > 75 mm ± 0.50	° > ° ±

DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
		JAMECO NO.	GOLDSUN NO.		
		106922	FDV1-187 (8)		
DRAWN: Kiki Chen		Description			Rev.
VERIFY PEOPLE: Ada Zheng , Ivy Lan		DISCONNECT SOLDERLESS			1
		UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No: