



LED Decorative Bulkhead



Description

This fitting is ideal for outdoor applications, and also areas such as corridors where anti-vandal lighting is required. These bulkheads are an energy efficient replacement for fluorescent and incandescent fittings, and are available with a 3 hour emergency duration.

Features

- Energy efficient replacement for CFL and incandescent fittings
- High quality black die-cast body
- Daylight (6000K) colour temperature
- Polycarbonate opal diffuser
- Integral driver
- Equivalent light output to a 28W 2D fitting
- Rated life of 60,000 hours
- 3hr emergency version available
- 12 month guarantee

Technical Specification

Voltage	230V ~ 50Hz
Driver	Integral
Lamp colour temp.	6000K
Wattage	18W
Lumen output	1400lm
Emergency lumen output	200lm
IP Rating	IP65

Range

LED 18W Decorative Bulkhead	7959384
LED 18W Decorative Bulkhead – 3hr emergency	7959388

Dimensions (mm)

	Height	Diameter
7959384/7959388	130mm	350mmØ

Standards

- BS EN 60598-1: 2008+A11: 2009
- BS EN 60598-2-1: 1989
- BS EN 55015: 2006+A1: 2007+A2: 2009
- BS EN 61000-3-2: 2006+A1: 2009+A2: 2009
- BS EN 61000-3-3: 2008
- BS EN 61000-4-2: 2009
- BS EN 61000-4-3: 2006+A2: 2010
- BS EN 61000-4-4: 2004+A1: 2010
- BS EN 61000-4-5: 2006
- BS EN 61000-4-6: 2009
- BS EN 61000-4-8: 2010
- BS EN 61000-4-11: 2004
- BS EN 61547: 2009