

**DO-214AA (SMB)****Bidirectional Surface Mount THYZORB®
Thyristor Overvoltage Protectors****DO-214AC (SMA)****Symbol****Stand-off Voltage** 58 to 320V
Breakover Voltage 70 to 395V
Holding Current 150mA minimum**Mechanical Data****Case:** JEDEC DO-214AA molded plastic body over passivated junction**Terminals:** Solder plated, solderable per MIL-STD-750, Method 2026High temperature soldering guaranteed:
250°C/10 seconds at terminals**Mounting Position:** Any**Weight:** 0.003 ounces, 0.093 gram**Features**

- Bidirectional crowbar protection
- Complies with Bellcore TR-NWT-001089, and IEC-1000-4-5 standards
- Series is designed to protect telecommunication equipment against lightening and AC induced transients
- Plastic package has UL Flammability Classification 94V-0
- Low profile package with built-in strain relief for surface mounted applications
- 50 Amp (10/1000µs) available in SMA package

Maximum Ratings and Thermal Characteristics T_A= 25°C unless otherwise noted.

Parameter	Symbol	AA	A	C	Unit
Case outline	—	SMA	SMB		—
Peak Pulse Current 10/1000µs 8/20µs	I _{PP}	50 200	50 200	100 300	A
Non-repetitive surge peak on-state current at 60Hz	I _{TSM}	20	20	60	A
Critical rate of rise of off-state voltage (V _{RM})	dV/dt	5			KV/µs
Storage temperature range	T _{stg}	-55 to +150			°C
Junction temperature range	T _j	-40 to 150			°C
Thermal resistance junction to leads	R _{θJL}	30		20	°C/W
Thermal resistance junction to ambient on P.C.B. with recommended pad layout	R _{θJA}	120		90	°C/W

I_{PP} Ratings for the Following Surge Standards

Standard	Waveform	I _{PP} (A, AA)	I _{PP} (C)
GR-1089-CORE	2/10µs	300A ⁺	500A
IEC61000-4-5	8/20µs	200A ⁺	300A
FCC Part 68	10/160µs	120A ⁺	250A ⁺
ITU-TK20/21	10/700µs	100A	200A
FCC Part 68	10/560µs	75A ⁺	160A ⁺
GR-1089-CORE	10/1000µs	50A ⁺	100A

Values with ⁺ have improved I_{PP} specs over equivalent competitor part numbers

Electrical Characteristics (T_A = 25°C unless otherwise noted)

Type	Stand-off Voltage V _{DRM} (V)	Max. Reverse Leakage at V _{DRM} I _{DRM} (μA)	Maximum Breakover Voltage V _{BO} (V) ⁽¹⁾⁽³⁾	Maximum Breakover Current I _{BO} (mA) ⁽¹⁾	Max. On-State Voltage at I _T = 1 A V _T (V)	Minimum Holding Current I _H (mA)	Typical Capacitance C (pF) ⁽²⁾	
							AA, A	C
P0640S_	58	5	70*	800	3.0	150	75	115
P0720S_	65	5	80*	800	3.0	150	70	115
P0900S_	75	5	95*	800	3.0	150	66	115
P1100S_	90	5	115*	800	3.0	150	60	75
P1300S_	120	5	145*	800	3.0	150	50	70
P1500S_	140	5	180	800	3.0	150	45	65
P1800S_	160	5	220	800	3.0	150	45	65
P2300S_	190	5	250*	800	3.0	150	45	65
P2600S_	220	5	290*	800	3.0	150	40	65
P3100S_	275	5	350	800	3.0	150	40	60
P3500S_	320	5	395*	800	3.0	150	35	60

Notes: (1) dv/dt = 100V/μs


(2) V_R = 2V, f = 1MHz

(3) Values with * have improved VBO specs over equivalent competitor part numbers


Device Marking

Type	Suffix		
	AA	A	C
P0640S_	06A	P06A	P06C
P0720S_	07A	P07A	P07C
P0900S_	09A	P09A	P09C
P1100S_	11A	P11A	P11C
P1300S_	13A	P13A	P13C
P1500S_	15A	P15A	P15C
P1800S_	18A	P18A	P18C
P2300S_	23A	P23A	P23B
P2600S_	26A	P26A	P26B
P3100S_	31A	P31A	P31C
P3500S_	35A	P35A	P35C


DO-214AA (SMB)



SMB Mounting Pad Layout



DO-214AC (SMA)



SMA Mounting Pad Layout

