


METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP	E13288 Listed
WIRE RANGE	
22-16 AWG STRANDED	22-16 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± .005 3 PLC DEC ± .002 ANGLES ± .005	DR 2-3-93 TA BRIKMAN CHK 2-3-93 DA PATTERSON APPD 2-3-93 DE MILLER APPD 2-3-93 JL MECKLEY PRODUCT SPEC FINISH TIN PLATE 0.00254 [0.000100] MIN THK PER MIL-T-10727	NAME AMP Incorporated Harrisburg, PA 17105-3608
TERMINAL, RING TONGUE, BUDGET	APPLICATION SPEC	SIZE CAGE CODE 00779 DRAWING NO 31173
5000	ON TAPE	3-31173-3
---	LOOSE PIECE	31173
QUANTITY	PACKAGE TYPE	PART NO