

LR44

Calculator Battery
Swiss Made

Technical Data Sheet


Specifications

Chemical system	Zinc / Manganese Dioxide, high drain
Nominal Voltage	1,50 V
Capacity	105 mAh, Discharge over 8,25 k Ω at 20°C to 0,9 V
Internal Resistance	Below 20 Ω at 20°C
Operating Temperature	0°C – 60°C
Self Discharge	Less than 10% per year at 20°C
Weight	~1,75 g

Dimensions


(according IEC 60086-3)

Diameter	11,60 mm (0,457")
Height	5,40 mm (0,213")



Discharge Curve

Constant Load	8,25 k Ω
Starting Drain	181,8 μ A
Temperature	20°C



Rev. LR44.03 06/02