



T50RDH0UVC2

Double Head Tie, 8.3" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg

Article Number: 117-05011

Part Number: T50RDH0UVC2

Type: T50RDH



Base Data

Part No.	T50RDH0UVC2
Type	T50RDH
Color	Black (BK)
Features	• UV stabilized cable ties contain an inhibitor which prolongs the life of the tie in UV exposures. • The tie contains a dual locking design to secure two bundles at once. • Head design can also provide spacing between parallel bundles. • Bent tail allows for quick insertion into head.
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	HellermannTyton's PA66UV stabilized double head ties provides a second loop that may also serve as a positioning device for a single bundle.
Variant	Inside Serrated

Product Dimensions

Min. Tensile Strength	50.0lbs / 225.0N
Length (L)	8.3" / 210.0mm
Bundle Diameter 2nd Loop max (imperial)	0.75"

Width (W) (imperial)	0.19"
Width (W)	4.7mm
Min. Ø Bundle	0.06" / 1.6mm
Max. Ø Bundle	1.97" / 50.0mm
Bundle Diameter 1st Loop max (imperial)	1.7"
Ø max. center loop	44.4mm
Cable Tie Head Height	6mm
Cable Tie Head Length	13.5mm
Cable Tie Head Width	8mm
Min Tensile Strength 2nd Loop (imperial)	40.0lbs
Min. Tensile Strength 2nd loop (N)	180.0N
Ø max. side loops	19.0mm
Thickness	1.4mm

Material and Specifications

Material	Polyamide 6.6 UV-stabilized (PA66UV)
Flammability	UL94 V2
Material Specification	RoHS
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	 RoHS
Specification	UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No

Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	100
Carton Qty.	5000
EAN code	4031026422299
UPC	089306203896

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512