


PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS - IN.				
		A $\pm$.03	W $\pm$.01	C $\pm$.02	M $\pm$.03	H $\pm$.01
PK6-8R	#8	1.59 (40.39)	.47 (11.94)	.43 (10.92)	1.36 (34.54)	.18 (4.57)
PK6-10R	#10	1.60 (40.64)	.47 (11.94)	.43 (10.92)	1.36 (34.54)	.20 (5.08)
PK6-14R	1/4"	1.63 (41.40)	.47 (11.94)	.48 (12.19)	1.36 (34.54)	.27 (6.86)
PK6-56R	5/16"	1.72 (43.69)	.62 (15.75)	.53 (13.46)	1.42 (36.07)	.33 (8.38)
PK6-38R	3/8"	1.72 (43.69)	.62 (15.75)	.51 (12.95)	1.42 (36.07)	.40 (10.16)
PK6-12R	1/2"	1.82 (46.23)	.82 (20.83)	.51 (12.95)	1.42 (36.07)	.52 (13.21)

NOTES:

- RATED FOR:
A. #6 AWG STRANDED COPPER WIRE
- SEE www.panduit.com FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE.
- MATERIAL:
A. STAMPING - .045" (1.14) THK COPPER,
TIN PLATED
B. HOUSING - KYNAR, BLUE STRIPE
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- INSTALLATION TOOL:
TOOL: CT-2600
DIE: CD-2600-PV6, CD-2600-6
- WIRE STRIP LENGTH: 7/16" +1/32" (11.1 +0.8)
-0 -0.0



BLUE COLOR STRIPE
(3 PLCS @ 120° APART)



CERTIFIED
LR31312



LISTED
587H
E52164

						PANDUIT CORP. TINLEY PARK, ILLINOIS			
03	8/11	SHOR	MODIFIED NOTE #2, ADDED UL & CSA SYMBOLS			#6 BARREL KYNAR INSULATED RING TONGUE .360 (9.14) MAX. WIRE INSUL. DIAMETER			
01	1/09	JHNU	ADDED P/N'S PK6-8R, PK6-56R, & PK6-12R REVISED INSTALL TOOL & DIE TO CT-2600 & CD26000-PV6						
00	2/05	JHNU	DRAWING RELEASED						
REV	DATE	BY	DESCRIPTION	CUST	PM	DRAWN BY	CHK'D	SCALE	DRAWING NO.
						JHNU		NONE	A41715