

General Information

Extended Product Type:	ZS4-SF1
Product ID:	1SNK508410R0000
EAN:	3472595084104
Catalog Description:	ZS4-SF1 Screw Clamp Terminal Block - for Fuses 5x20 and 5x25 mm - Grey
Long Description:	ZS4-SF1 Screw Clamp Terminal Block - for Fuses 5x20 and 5x25mm - Grey 4mm ² RatedCrossSection 8mmSpacing TH 35-7.5, TH 35-15 Rail

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Screw Clamp Terminal Blocks

Ordering

EAN:	3472595084104
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	8 mm
Product Net Height:	59.7 mm
Product Net Depth:	45.6 mm
Product Net Weight:	13.30 g

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	82 mm
Package Level 1 Height:	48 mm
Package Level 1 Length:	252 mm
Package Level 1 Gross Weight:	0.67 kg
Package Level 1 EAN:	3472595084104
Package Level 2 Units:	450 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	200 mm
Package Level 2 Length:	400 mm
Package Level 2 Gross Weight:	6.53 kg
Product Packing Type:	Box

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 300 V
Connecting Capacity-Main Circuit UL/CSA:	Screw Clamp / Rigid 1x24...10 AWG Screw Clamp / Flexible 1x24...10 AWG Screw Clamp / Without Insulated Ferrule 1x24...12 AWG Screw Clamp / With Insulated Ferrule 1x24...12 AWG Screw Clamp / Rigid 2x24...16 AWG Screw Clamp / Flexible 2x24...16 AWG Screw Clamp / With Twin Ferrule 2x24...16 AWG
Flammability According to UL94:	V0

Additional Information

Ambient Temperature:	-5 ... +40 °C
Color:	Grey, Dark Grey
Connecting Capacity-Main Circuit:	Screw Clamp / Rigid 1x0.2...4 mm ² Screw Clamp / Flexible 1x0.22...4 mm ² Screw Clamp / Without Insulated Ferrule 1x0.22...4 mm ² Screw Clamp / With Insulated Ferrule 1x0.22...4 mm ² Screw Clamp / Rigid 2x0.2...1.5 mm ² Screw Clamp / Flexible 2x0.2...1.5 mm ² Screw Clamp / With Twin Ferrule 2x0.22...1.5 mm ²
Connection Type:	Screw clamp

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Dielectric Test Voltage:	2200 V
Function:	Fuse
Gauge Type:	A3-B3
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Pollution Degree:	3
Product Main Type:	ZS4-SF1
Product Name:	Terminal block
Rated Cross-Section:	4 mm ²
Rated Current (I _n):	Main Circuit 6.3 A
Rated Impulse Withstand Voltage (U _{imp}):	Main Circuit 8000 V
Rated Voltage (U _r):	250 V
Recommended Screw Driver:	3.5 mm
RoHS Date:	18 08 2005
Spacing:	8 mm
Sub-Function:	For 5x20 and 5x25 Fuses
Wire Stripping Length:	Main Circuit 11 mm

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225098C1002
GOST Certificate:	1SND161005A1103

Classifications

E-nummer:	2925967
Object Classification Code:	X

