




REV.	DATE	DESCRIPTION
NC	06/06/99	INITIAL RELEASE
A	07/20/05	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS; DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex							
7						DRAWN	G.R.S.						07/20/05		
6						CHECKED									
5	HEX NUT	BRASS	NICKEL	1					PART DESCRIPTION						
4	LOCK WASHER	BRASS	NICKEL	1					SMB R/A P.C. MOUNT BULKHEAD JACK						
3	CONTACT PIN	BRASS	GOLD	1					PART NO.						
2	INSULATOR	TEFLON	NATURAL	1					142184						
1	BODY	BRASS	GOLD	1					DWG. NO.						
DESCRIPTION		MATERIAL	FINISH	QTY		C:/142/142184.DWG		142184.DWG		REV.	A	SIZE	A	SCALE	NA