






Dimensions: mm (in.)



P.C. Mounting

POS.1	POS.2	POS.3
(ON)	OFF	(ON)
2-3	OPEN	2-1

Switch Function

**Mechanical Specifications:**

- Mechanical Life: 50,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

Electrical Specifications:

- Rating: 0.4VA Max./20V AC or DC Max.
- Contact Resistance: 20mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Dielectric Strength: 1,000 V RMS@sea level

Note:

- RoHS Compliant by Exemption

Soldering Process:

- Wave soldering: Recommended soldering temperature: 260±5°C Duration of solder immersion: 5±1 seconds (PCB is 1.6mm in thickness)

Sealed Sub-Miniature Toggle Switch
108-2BS4T1T48-EVX

Mountain
Switch

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-2BS4T1T48-EVX](#)