



4. RoHS COMPLIANT AND CERTIFIED.



Power	° C/W @ Ambient	° C/W @ 200 LFM	° C/W @ 400 LFM	° C/W @ 600 LFM
5 Watts	12.34	5.26	3.51	2.91
10 Watts	11.12	5.16	3.52	2.81
15 Watts	10.21	5.14	3.52	2.84

SECTION B-B

CUSTOMER DRAWING

SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE

ITEM	DESCRIPTION	QTY	DO NOT SCALE	tyco / Electronics Attleboro Falls Massachusetts 02763				CONFIDENTIAL PROPERTY OF TYCO ELECTRONICS. NOT TO BE DISCLOSED TO OTHERS, REPRODUCED OR USED FOR ANY PURPOSES EXCEPT AS AUTHORIZED IN WRITING BY AN AUTHORIZED OFFICIAL OF TYCO. MUST BE RETURNED TO TYCO ON DEMAND, ON COMPLETION OF ORDERS OR OTHER PURPOSES FOR WHICH LENT.		TITLE:		
				UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:	DRAWN BY:	DATE	MATERIAL:			25mm HEATSINK ASSEMBLY (HTS592-U)		
1	MOUNTING CLIP	1		.XX ± .	ENGINEER:	DATE	SEE NOTE	DIMENSIONS ARE IN:	SCALE:	PART NO:	SHEET	
2	HEAT SINK	1		.XXX ± .	B.PETROCELLI	04/22/04		FINISH:	INCHES	1:5.1	5-1542003-0	1 OF 1
3	INTERFACE	1		.XXXX ± .	FILENAME	PROJECT	SYSTEM	SEE NOTE	TNRD ANGLE PROJECTION	SIZE:	DWG. NO.	REV:
				ANGLES ± °								