



Quality Products. Service Excellence.

Studio Grade - Impedance Matching Audio Transformers *140EX Series*

Features



- Studio grade frequency response: 20 Hz. - 20 KHz. (+/- 1 db, ref. @ 1 KHz.) minimum (see individual PDF data sheets below).
- Excellent frequency response utilizing a 80% nickel core providing high permeability combined with low losses.
- Designed for maximum bandwidth, lowest distortion at +10 dbm power level or less (see individual PDF data sheets below).
- Plated steel cans
- Adjustable height case bracket.
- Net weight 3 oz.

Part No.	Typical Applications	Nominal Impedance (Ohms)		Overall Turns Ratio Pri. to Sec.	Lead Length	Case Height	Case Diameter	Mounting Holes
		Primary	Secondary					
140MEX	Crystal/Ceramic MIC. to Base	100K	1500	8:1	5.00	1.00	1.25	1.88
140NEX	Dynamic MIC to Base	50	1500	1:5:5	5.00	1.00	1.25	1.88
140PEX	Line to Base	150/600	600/2,400	1:2	5.00	1.00	1.25	1.88
140QEX	Line to Line, Isolation	600 C.T.	600 C.T.	1:1	5.00	1.00	1.25	1.88
140REX	Line to Line, Isolation	600 C.T.	150	2:1	5.00	1.00	1.25	1.88
140TEX	Input/Output Isolation	1000	1000	1:1	5.00	1.00	1.25	1.88
140UEX	Input/Output Isolation	10K	10K	1:1	5.00	1.00	1.25	1.88

Data subject to change without notice

© 2020. Hammond Manufacturing Ltd. All rights reserved.