


NOTES:

1. FOR USE WITH COMMSCOPE 77538 & BELDEN 1855A & 1865A CABLES.
2. FOR CABLING INSTRUCTIONS SEE 3-661-1.
3. FOR CRIMPING USE DIE KTH-2025.
4. CENTER CONTACT, 1-6690-7MA9, AND K-GRIP SLEEVE 1-33983-1M06 SUPPLIED UNASSEMBLED.
5. INTERFACE PER MIL-STD-348, FIG. 301-1 (AS APPLICABLE).
6. MATERIAL SPECIFICATIONS:
INSULATOR: TEFLON PER ASTM D4894.
GASKET: SILICONE RUBBER PER ZZ-R765.
SPRING WASHER AND OUTER CONTACT: BERYLLIUM COPPER PER ASTM B196.
ALL OTHER METAL PARTS: BRASS PER ASTM B16.
7. FINISH SPECIFICATIONS:
CENTER CONTACT: GOLD PER MIL-G-45204
SPRING WASHER: SILVER PER QQ-S-365
ALL OTHER METAL PARTS: NICKEL PER QQ-N-290

8. ELECTRICAL SPECIFICATIONS:
IMPEDANCE: 75 OHMS
WORKING VOLTAGE: 500 VOLTS RMS
FREQUENCY RANGE: DC - 12 GHz
RETURN LOSS: -30dB MAX TO 3.0 GHz
-20dB MAX TO 6.0 GHz
9. COMPLIANT TO 3G/6G/12G SDI SMPTE REQUIREMENTS.
10. MARK PACKAGE: KINGS 2065-11-9.

REV	DESCRIPTION	BY DATE	APPD
J	ER057798	04/10/15	YA



CATALOG P/N: 2065-11-9

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [X.X] ± .01 [0.3] .XXX [X.XX] ± .005 [0.13] .XXXX [X.XXX] ± .XXXX ANGLES: ± 2° SCALE: 4:1				 by WINCHESTER Winchester Electronics Corporation 199 Park Road Ext Suite 104 Middlebury, Connecticut 06762			
CUSTOMER SALES DRAWING				75 OHM BNC PLUG FOR BELDEN 1855A OR EQUIVALENT CABLE (RoHS)			
DRAWN J	DATE 04/09/2015	APPROVED MAR	DATE 07/28/2015	A			
APPROVED YA	DATE 04/09/2015	APPROVED XXX	DATE XX/XX/XX				
				SD2065-11-9		SHT 1	OF 1
						REV J	